



FEATURES:

- Test accessories comply with IEC 1010-2-031 requirements
- Extended slide on tip adapter fits directly over probe, allowing testing of hard to reach test points
- Compatible with most Fluke, Amprobe, H.P., Tektronic & Wavetek digital multimeters

MATERIALS:

Model **6365**: Probe Body: Outer Insulation - Santoprene® Rubber, Color: Gray, Inner Insulation – Polypropylene Fire Retardant, Color: One Black, One Red, Tip: Brass, Wire: 18 AWG, 65 x 36 Tinned Copper Stand, Silicone Insulation, Length: 48" (122cm), O.D. .144" (3,66mm)

Banana Plug: Body – Brass, Nickel Plated, Spring – Beryllium Copper, Nickel Plated, Insulation – Polypropylene, Color: One Black, One Red, **RATINGS:** IEC 1010-2-031, Category III, P2 Compliant, Operating Voltage: 1000V, Current: 10 Amperes

Model **6264**: Body–Steel, Nickel Plated, Insulation–Polypropylene fire retardant, Spring: Music Wire, **RATINGS:** IEC 1010-2-031, Category III, P2 Compliant, Operating Voltage: 300V, Current: 3 Amperes.

Model **6262**: Tip: Stainless Steel, Tip Insulation: Kynar, Body: Polypropylene fire retardant, **RATINGS:** IEC 1010-2-031, Category II, P2 Compliant, Operating Voltage: 300V, Current: 3 Amperes.

ORDERING INFORMATION: 6344 (Includes a kit of items from above)

Replacement P/N's: Model **6264**: Probe Adapter Alligator Tip, Model 6262: Probe Adapter Extended Fine Tip, Model **6365**: Probe to Straight DMM Plug.

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6344