


49/U Series

■Features

- Compact and light weight.
- Excellent vibration resistance and shock resistance.
- Stable temperature characteristics.



■Specifications

Type	Number of inner units	Pass Bandwidth		Ripple	Insertion Loss	Stop Bandwidth		Terminating Impedance	Operating Temp. Range	Outline
		dB	kHz			dB	kHz MAX			
MXF10.7-6A	1	3	$\pm(2.5\sim3.5)$	1	1.5	30	55	1.5k//3	-40~+85	Fig.1
MXF10.7-6AL	1	3	$\pm(2.5\sim3.5)$	1	3	30	55	1.5k//3	-40~+85	Fig.2
MXF10.7-7.5A	1	3	± 3.75 MIN	0.5	1.5	20	± 18	1.8k//5	-40~+85	Fig.1
MXF10.7-7.5AL	1	3	± 3.75 MIN	0.5	3	20	± 18	1.8k//5	-40~+85	Fig.2
MXF10.8-6A	1	3	$\pm(2.5\sim3.5)$	1	1.5	30	55	1.5k//3	-40~+85	Fig.1
MXF10.8-6AL	1	3	$\pm(2.5\sim3.5)$	1	3	30	55	1.5k//3	-40~+85	Fig.2

■Outline

Fig. 1

49/U-11




Fig. 2

49/U-9

