

3M™ ROUND CONDUCTOR FLAT CABLE, 3801 SERIES
.050" 26 AWG STRANDED, PVC




TABLE 1			
NUMBER OF CONDUCTORS	3M PART NUMBER	DIMENSION "A"	DIMENSION "B"
04	3801/04	.200±.010 [5.08]	.150±.007 [3.18]
05	3801/05	.250±.010 [6.35]	.200±.007 [5.08]
06	3801/06	.300±.010 [7.62]	.250±.007 [6.35]
07	3801/07	.350±.010 [8.89]	.300±.007 [7.62]
08	3801/08	.400±.010 [10.16]	.350±.007 [8.89]
09	3801/09	.450±.010 [11.43]	.400±.007 [10.16]
10	3801/10	.500±.010 [12.70]	.450±.007 [11.43]
12	3801/12	.600±.010 [15.24]	.550±.007 [13.97]
14	3801/14	.700±.010 [17.78]	.650±.007 [16.51]
15	3801/15	.750±.010 [19.05]	.700±.007 [17.78]
16	3801/16	.800±.015 [20.32]	.750±.011 [19.05]
18	3801/18	.900±.015 [22.86]	.850±.011 [21.59]
20	3801/20	1.000±.015 [25.40]	.950±.011 [24.13]
24	3801/24	1.200±.015 [30.48]	1.150±.011 [29.21]
25	3801/25	1.250±.015 [31.75]	1.200±.011 [30.48]
26	3801/26	1.300±.015 [33.02]	1.250±.011 [31.75]
30	3801/30	1.500±.020 [38.10]	1.450±.015 [36.83]
34	3801/34	1.700±.020 [43.18]	1.650±.015 [41.91]
36	3801/36	1.800±.020 [45.72]	1.750±.015 [44.45]
37	3801/37	1.850±.020 [46.99]	1.800±.015 [45.72]
40	3801/40	2.000±.020 [50.80]	1.950±.015 [49.53]
44	3801/44	2.200±.020 [55.88]	2.150±.015 [54.61]
50	3801/50	2.500±.020 [63.50]	2.450±.015 [62.23]
60	3801/60	3.000±.020 [76.20]	2.950±.015 [74.93]
64	3801/64	3.200±.020 [81.28]	3.150±.015 [80.07]

1. REGULATORY INFORMATION:
VISIT 3M.com/regs OR CONTACT
YOUR 3M REPRESENTATIVE TO FIND
THE RoHS COMPLIANCE STATUS OF
THE 3M PART YOU ARE INTERESTED
IN.

UL FILE: E42769
STYLE: 2651
2. IN THE EVENT OF CONFLICT
BETWEEN THIS DATA AND THAT
CONTAINED IN THE PRODUCT
SPECIFICATION, THE PRODUCT
SPECIFICATION TAKES PRECEDENT.

2 PHYSICAL :

INSULATION: POLYVINYL CHLORIDE (PVC)
MATERIAL: POLYVINYL CHLORIDE (PVC)
COLOR: SEE ORDERING INFORMATION
MARKING:
STANDARD: NONE
CANADIAN: SEE "PRINTING ILLUSTRATION" VIEW

CONDUCTORS: 26 AWG 7 X 34 [7 X .160] TINNED STRANDED COPPER

2 ELECTRICAL :

VOLTAGE RATING: USA 300V CANADIAN 300V EU: <50V
INSULATION RESISTANCE: >1 X 10¹⁰Ω/10ft. [3m]

UNBALANCED
CHARACTERISTIC IMPEDANCE: 89Ω
CAPACITANCE: 16.2 pF/ft [53.1 pF/m]
INDUCTANCE: .13μH/ft [.43μH/m]
PROPAGATION DELAY: 1.44 ns/ft [4.72 ns/m]
VELOCITY OF PROPAGATION: 71%

NOTE: UNBALANCED IS MEASURED BETWEEN GROUND-SIGNAL-GROUND CONDUCTORS.

2 ENVIRONMENTAL :

TEMPERATURE RATING: -20°C TO 105°C
FLAMMABILITY RATING: USA: VW-1 CANADA: FT1

ORDERING INFORMATION

X3801X / XX XX

BLANK= STANDARD
C= CANADIAN CERTIFIED
VERSION

BLANK= STANDARD
SF= SPLICE FREE

No. OF CONDUCTORS:
(SEE TABLE 1)

COLOR OPTIONS:
BLANK= GRAY (STANDARD PRODUCT)
A= BLACK (SPECIAL PRODUCT)

NOTE:
AVAILABLE IN STANDARD 100FT OR 300FT ROLLS.
PLEASE SPECIFY WHEN ORDERING.
CONTACT 3M FOR AVAILABILITY OF ADDITIONAL
CONDUCTOR COUNTS AND/OR CUSTOM ROLL LENGTHS.

CANADIAN OPTION
"PRINTING ILLUSTRATION"



AWM 2651 105C 300V VW1 3M NU




AWM 1A 105C 300V FT1 EU <50V

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3Mconnectors.com>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

INCH [MM]		
TOLERANCE - UNLESS NOTED		
.X	.XX	.XXX
[INCH] ±.1	±.01	±.005
[] = DIM. FOR REFERENCE ONLY		

DESIGN REFERENCE		NEXT ASSEMBLY	
ACCESS CODES			
DIVISION		DIVISION CODE	
DO NOT SCALE DRAWING	SCALE <u>25</u> 1	TOLERANCES EXCEPT AS NOTED	
			
THIRD ANGLE PROJECTION			
INTERPRET PER ASME Y14.5 - 2018			
MAX. SURFACE ROUGHNESS		INCHES	
SURFACES		MILLIMETERS	
MARKED ONLY		ANGLES	

D	0104000	MAY 04,2022	LDS	FJR
		ADDED 12 CONDUCTOR TO TABLE 1		
C	73662	MAY 10,2017	JNC	RDE
		REVISED AND REDRAWN		
REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
CHKD	CHKD	DATE	DATE	DATE
DIVISION		DIVISION CODE		
DO NOT SCALE DRAWING		EMSD		
THIRD ANGLE PROJECTION		TOLERANCES EXCEPT AS NOTED		
MAX SURFACE ROUGHNESS		INCHES		
SURFACES		MILLIMETERS		
MARKED ONLY		ANGLES		

3M		© 3M COPYRIGHT 2022		
3M Center St. Paul, MN 55144		This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.		
TITLE		ROUND CONDUCTOR FLAT CABLE, .050", 26 AWG STRANDED, PVC		
CAGE NUMBER		DRAWING NO.		
D		78-5100-0063-7		
MODEL		REV.		
3801		D		
		DET		
		LISTS		
		YES		
		NO		
		SHT 1 OF 2		

3M™ ROUND CONDUCTOR FLAT CABLE, 3801 SERIES
.050" 26 AWG STRANDED, PVC

Regulatory: For regulatory information about this product, visit 3M.com/regs or contact your 3M representative.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OR TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

3M Electronics Materials Solutions Division
13011 McCallen Pass, Bldg. C
Austin, TX 78753-5380
1-800-225-5373
www.3M.com/interconnect

DESIGN REFERENCE		NEXT ASSEMBLY		REV	ECO	ISSUE DATE AND DESCRIPTION		DRFT	CHKD
XREF CODES				DRP	DATE		MFG	DATE	
				CHKD	MAY 10,2017			MAY 10,2017	
DIVISION		DIVISION CODE		APPR		DATE		DATE	
		EMSD		R. EDWARDS		MAY 10,2017			
DO NOT SCALE DRAWING		SCALE 1 1		TOLERANCES EXCEPT AS NOTED		3M 3M Center St. Paul, MN 55144 © 3M COPYRIGHT 2022 This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.			
THIRD ANGLE PROJECTION		INCHES		MILLIMETERS		TITLE			
INTERPRET PER ASME Y14.5 - 2018		.00 ±		.00 ±		ROUND CONDUCTOR FLAT CABLE, .050", 26 AWG STRANDED, PVC			
MAX SURFACE ROUGHNESS		.000 ±		.00 ±		CAGE NUMBER		SIZE	DRAWING NO.
✓ MARKED SURFACES		.000 ±		.00 ±		D78-5100-0063-7		REV.	
		ANGLES		MODEL		3801		DET	
						LISTS		YES	NO
						SHT		2 OF 2	