

10 9 8 7 6 5 4 3 2 1

NOTES:


- 1.) MATERIAL -  
INSULATOR - LCP, UL 94V-0, COLOR BLACK  
CONTACTS - PHOSPHOR BRONZE
- 2.) SEE SHT. 5 & 6 FOR CHART DIMENSIONS AND EDP NO.'S
- 3.) RECOMMENDED MATING PIN LENGTH:  
LOWER ROW - .200" MIN., .285" MAX.  
UPPER ROW - .200" MIN.
- 4.) REFER TO PRODUCT SPECIFICATION PS-71973-9999 FOR PERFORMANCE DATA
- 5.) MANUFACTURED DATE CODE - YEAR, WEEK.
- 6.) PACKAGING: FOR THIS PRODUCT IN TUBES SEE SHT. 6 & 7  
FOR THIS PRODUCT IN TRAYS SEE SHT. 8 & 9

FINISHES


- 15 GOLD .000015 MINIMUM GOLD PLATE IN SELECT AREA OVER  
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH  
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 30 GOLD .000030 MINIMUM GOLD PLATE IN SELECT AREA OVER  
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH  
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 50 GOLD .000050 MINIMUM GOLD PLATE IN SELECT AREA OVER  
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH  
.000100 MINIMUM TIN PLATE IN SELECT AREA.

.105  
(2.67)


POINT OF  
CONTACT



SECTION C-C



4 DIGIT DATE CODE  
SEE NOTE 5





- ⊕ Ø.015(5) TAIL TO TAIL  
⊕ Ø.020(5) X(5) Y(5) TAIL TO INSULATOR

OPTION "A" ASSEMBLY  
STANDARD HOUSING

NOTE FOR LEAD FREE CONVERSION:


THE PRIMARY SHIPPING CARTON WILL BE  
LABELED "COMPLIANT TO RoHS DIRECTIVE  
2002/95/EC AND ELV ANNEX II OF  
DIRECTIVE 2000/53/EC". CARTONS WITHOUT  
THIS LABEL MAY CONTAIN PRODUCT WITH  
LEAD.



OPTION "B" ASSEMBLY  
STD. HOUSING W/MOUNTING EARS  
SCALE 4:1


REFER TO OPT. A FOR ALL OTHER INFORMATION

OPTION "J" ASSEMBLY  
OPTION "J" IS THE SAME AS OPTION "B" EXCEPT  
DATE CODE IS NOT STAMPED ON HOUSING.




RECOMMENDED P.C.B.  
LAYOUT

|                                                                                                                 |                                                                    |             |                                                            |        |                                                                                                                                  |                    |                                                                                    |                      |                        |
|-----------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------|-------------|------------------------------------------------------------|--------|----------------------------------------------------------------------------------------------------------------------------------|--------------------|------------------------------------------------------------------------------------|----------------------|------------------------|
| ADD OPTION K & L<br>EC NO: S2010-0534<br>DRWN:KANG 2009/12/30<br>CHKD:ATSEE 2010/01/08<br>APPR:MLONG 2010/01/14 | QUALITY SYMBOLS<br><div>FA=0</div> <div>FC=0</div> <div>FP=0</div> | DESCRIPTION | GENERAL TOLERANCES (UNLESS SPECIFIED)                      |        | DIMENSION STYLE<br>IN/MM                                                                                                         |                    | SCALE<br>NTS                                                                       | DESIGN UNITS<br>INCH | THIRD ANGLE PROJECTION |
|                                                                                                                 |                                                                    |             | mm                                                         | INCH   | DRAWN BY<br>DJB                                                                                                                  | DATE<br>1991/10/21 | TITLE<br>EARLY ENTRY R/A RECPT<br>.120"PC TAIL W/O LOWER<br>ROW PINSTOP-.100" GRID |                      |                        |
|                                                                                                                 |                                                                    |             | 4 PLACES ± ---                                             | ± ---  | CHECKED BY<br>DJB                                                                                                                | DATE<br>1991/10/21 |                                                                                    |                      |                        |
|                                                                                                                 |                                                                    |             | 3 PLACES ± ---                                             | ± .010 | APPROVED BY<br>MLONG                                                                                                             |                    | DATE<br>2010/01/14                                                                 | MOLEX INCORPORATED   |                        |
|                                                                                                                 |                                                                    |             | 2 PLACES ± 0.25                                            | ± ---  | MATERIAL NO.                                                                                                                     |                    | DOCUMENT NO.                                                                       |                      |                        |
| K                                                                                                               | REV                                                                |             | ANGULAR ± 1/2°                                             |        | SEE TABLE                                                                                                                        |                    | SDA-71973-****                                                                     |                      | 1 OF 26                |
|                                                                                                                 |                                                                    |             | DRAFT WHERE APPLICABLE<br>MUST REMAIN<br>WITHIN DIMENSIONS |        | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX<br>INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |                    |                                                                                    |                      |                        |



4 DIGIT DATE CODE  
SEE NOTE 5



OPTION "C" ASSEMBLY  
STANDARD HOUSING

NOTE FOR LEAD FREE CONVERSION:  
THE PRIMARY SHIPPING CARTON WILL BE  
LABELED "COMPLIANT TO RoHS DIRECTIVE  
2002/95/EC AND ELV ANNEX II OF  
DIRECTIVE 2000/53/EC". CARTONS WITHOUT  
THIS LABEL MAY CONTAIN PRODUCT WITH  
LEAD.


tb\_frame\_A3\_P\_AM\_T  
Rev. F 2009/06/18

#### NOTES:



- 1.) MATERIAL-  
INSULATOR - LCP, UL 94V-0, COLOR BLACK  
CONTACTS - PHOSPHOR BRONZE
- 2.) SEE SHT. 9 & 10 FOR CHART DIMENSIONS AND EDP NO.'S
- 3.) RECOMMENDED MATING PIN LENGTH:  
LOWER ROW - .200" MIN., .285" MAX.  
UPPER ROW - .200" MIN.
- 4.) REFER TO PRODUCT SPECIFICATION PS-71973-9999 FOR  
PERFORMANCE DATA
- 5.) MANUFACTURED DATE CODE - YEAR, WEEK.
- 6.) PACKAGING: FOR THIS PRODUCT IN TUBES SEE SHT. 10 & 11  
FOR THIS PRODUCT IN TRAYS SEE SHT. 12 & 13

#### FINISHES

- |         |                                                                                                                                                |
|---------|------------------------------------------------------------------------------------------------------------------------------------------------|
| 15 GOLD | .000015 MINIMUM GOLD PLATE IN SELECT AREA OVER<br>.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH<br>.000075 MINIMUM TIN PLATE IN SELECT AREA. |
| 30 GOLD | .000030 MINIMUM GOLD PLATE IN SELECT AREA OVER<br>.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH<br>.000075 MINIMUM TIN PLATE IN SELECT AREA. |
| 50 GOLD | .000050 MINIMUM GOLD PLATE IN SELECT AREA OVER<br>.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH<br>.000100 MINIMUM TIN PLATE IN SELECT AREA. |




SECTION C-C



OPTION "D" ASSEMBLY  
STD. HOUSING W/MOUNTING EARS  
SCALE 4:1

REFER TO OPT. C FOR ALL OTHER INFORMATION



RECOMMENDED P.C.B. LAYOUT

| ADD OPTION K & L  |            | QUALITY SYMBOLS   |  | GENERAL TOLERANCES (UNLESS SPECIFIED) |  | DIMENSION STYLE |  | SCALE        |  | DESIGN UNITS           |  | THIRD ANGLE PROJECTION |  |
|-------------------|------------|-------------------|--|---------------------------------------|--|-----------------|--|--------------|--|------------------------|--|------------------------|--|
| EC NO: S2010-0534 |            | F <sub>A</sub> =0 |  | mm                                    |  | IN/MM           |  | NTS          |  | INCH                   |  |                        |  |
| 2009/12/30        | DRWN:SKANG | F <sub>B</sub> =0 |  | INCH                                  |  | DRAWN BY        |  | DATE         |  | TITLE                  |  |                        |  |
| 2010/01/08        | CHKD:ATSEE | F <sub>P</sub> =0 |  | 4 PLACES ± --- ± ---                  |  | DATE            |  | 1991/10/21   |  | EARLY ENTRY R/A RECPT  |  |                        |  |
| 2010/01/14        | APPR:MLONG |                   |  | 3 PLACES ± --- ± .010                 |  | CHECKED BY      |  | DATE         |  | .120"PC TAIL W/O LOWER |  |                        |  |
|                   |            |                   |  | 2 PLACES ± 0.25 ± ---                 |  | DATE            |  | 1991/10/21   |  | ROW PINSTOP-.100" GRID |  |                        |  |
|                   |            |                   |  | 1 PLACE ± --- ± ---                   |  | APPROVED BY     |  | DATE         |  | MOLEX INCORPORATED     |  |                        |  |
|                   |            |                   |  | ANGULAR ± 1/2°                        |  | MLONG           |  | 2010/01/14   |  | SDA-71973-****         |  |                        |  |
|                   |            |                   |  | DRAFT WHERE APPLICABLE                |  | MATERIAL NO.    |  | DOCUMENT NO. |  | SHEET NO.              |  |                        |  |
|                   |            |                   |  | MUST REMAIN                           |  | SEE TABLE       |  |              |  | 2 OF 26                |  |                        |  |
|                   |            |                   |  | WITHIN DIMENSIONS                     |  | SIZE            |  |              |  |                        |  |                        |  |
|                   |            |                   |  |                                       |  | A3              |  |              |  |                        |  |                        |  |
|                   |            |                   |  |                                       |  |                 |  |              |  |                        |  |                        |  |

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX  
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION



10 9 8 7 6 5 4 3 2 1

NOTES:

- 1.) MATERIAL -  
INSULATOR - LCP, UL 94V-0, COLOR BLACK  
CONTACTS - PHOSPHOR BRONZE
- 2.) SEE SHT. 13 & 14 FOR CHART DIMENSIONS AND EDP NO.'S
- 3.) RECOMMENDED MATING PIN LENGTH:  
LOWER ROW - .200" MIN., .250" MAX.  
UPPER ROW - .200" MIN.
- 4.) REFER TO PRODUCT SPECIFICATION PS-71973-9999 FOR PERFORMANCE DATA
- 5.) MANUFACTURED DATE CODE - YEAR, WEEK.
- 6.) PACKAGING: FOR THIS PRODUCT IN TUBES SEE SHT. 14 & 15  
FOR THIS PRODUCT IN TRAYS SEE SHT. 16 & 17

FINISHES


- 15 GOLD .000015 MINIMUM GOLD PLATE IN SELECT AREA OVER  
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH  
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 30 GOLD .000030 MINIMUM GOLD PLATE IN SELECT AREA OVER  
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH  
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 50 GOLD .000050 MINIMUM GOLD PLATE IN SELECT AREA OVER  
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH  
.000100 MINIMUM TIN PLATE IN SELECT AREA.





OPTION "E" ASSEMBLY  
STANDARD HOUSING

NOTE FOR LEAD FREE CONVERSION:


THE PRIMARY SHIPPING CARTON WILL BE  
LABELED "COMPLIANT TO ROHS DIRECTIVE  
2002/95/EC AND ELV ANNEX II OF  
DIRECTIVE 2000/53/EC". CARTONS WITHOUT  
THIS LABEL MAY CONTAIN PRODUCT WITH  
LEAD.



SECTION C-C




OPTION "F" ASSEMBLY  
STD. HOUSING W/MOUNTING EARS  
AND LOWER ROW PINSTOP  
SCALE 4:1  
REFER TO OPT. E FOR ALL OTHER INFORMATION




RECOMMENDED P.C.B. LAYOUT

| GENERAL TOLERANCES (UNLESS SPECIFIED)                      |  | DIMENSION STYLE |        | SCALE       |            | DESIGN UNITS                                                                                    |  | THIRD ANGLE PROJECTION |  |
|------------------------------------------------------------|--|-----------------|--------|-------------|------------|-------------------------------------------------------------------------------------------------|--|------------------------|--|
|                                                            |  | IN/MM           |        | NTS         |            | INCH                                                                                            |  |                        |  |
|                                                            |  | mm              | INCH   | DRAWN BY    | DATE       | TITLE                                                                                           |  |                        |  |
| 4 PLACES                                                   |  | ± .005          | ± .002 | DJB         | 1991/10/21 | EARLY ENTRY R/A RECPT<br>.120"PC TAIL W/O LOWER<br>ROW PINSTOP-.100" GRID<br>MOLEX INCORPORATED |  | SHEET NO.<br>3 OF 26   |  |
| 3 PLACES                                                   |  | ± .010          | ± .005 | CHECKED BY  | DATE       |                                                                                                 |  |                        |  |
| 2 PLACES                                                   |  | ± .025          | ± .010 | DJB         | 1991/10/21 |                                                                                                 |  |                        |  |
| 1 PLACE                                                    |  | ± .050          | ± .020 | APPROVED BY | DATE       |                                                                                                 |  |                        |  |
| ANGULAR ± 1/2°                                             |  |                 |        | MLONG       | 2010/01/14 | DOCUMENT NO.<br>SDA-71973-****                                                                  |  |                        |  |
| DRAFT WHERE APPLICABLE<br>MUST REMAIN<br>WITHIN DIMENSIONS |  | SEE TABLE       |        |             |            |                                                                                                 |  |                        |  |
|                                                            |  | SIZE<br>A3      |        |             |            |                                                                                                 |  |                        |  |
|                                                            |  |                 |        |             |            |                                                                                                 |  |                        |  |

10 9 8 7 6 5 4 3 2 1



4 DIGIT DATE CODE  
SEE NOTE 5



⊕ Ø.015(5) TAIL TO TAIL  
⊕ Ø.020(5) X(5) Y(5) TAIL TO INSULATOR

### OPTION "G" ASSEMBLY STANDARD HOUSING


NOTE FOR LEAD FREE CONVERSION:

THE PRIMARY SHIPPING CARTON WILL BE LABELED "COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC". CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH LEAD.



- NOTES:**
- 1.) MATERIAL -  
INSULATOR - LCP, UL 94V-0, COLOR BLACK  
CONTACTS - PHOSPHOR BRONZE
  - 2.) SEE SHT. 17 & 18 FOR CHART DIMENSIONS AND EDP NO.'S
  - 3.) RECOMMENDED MATING PIN LENGTH:  
LOWER ROW - .200" MIN., .250" MAX.  
UPPER ROW - .200" MIN.
  - 4.) REFER TO PRODUCT SPECIFICATION PS-71973-9999 FOR PERFORMANCE DATA
  - 5.) MANUFACTURED DATE CODE - YEAR, WEEK.
  - 6.) PACKAGING: FOR THIS PRODUCT IN TUBES SEE SHT. 18 & 19  
FOR THIS PRODUCT IN TRAYS SEE SHT. 20 & 21

### FINISHES

- 15 GOLD .000015 MINIMUM GOLD PLATE IN SELECT AREA OVER  
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH  
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 30 GOLD .000030 MINIMUM GOLD PLATE IN SELECT AREA OVER  
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH  
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 50 GOLD .000050 MINIMUM GOLD PLATE IN SELECT AREA OVER  
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH  
.000100 MINIMUM TIN PLATE IN SELECT AREA.




### SECTION C-C



### OPTION "H" ASSEMBLY STD. HOUSING W/MOUNTING EARS AND LOWER PINSTOP SCALE 4:1



REFER TO OPT. G FOR ALL OTHER INFORMATION



### RECOMMENDED P.C.B. LAYOUT

|                                                                                                                           |                                                                                                     |             |                                       |        |                          |                      |                    |                                                                                                                               |                           |  |         |  |  |
|---------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------|-------------|---------------------------------------|--------|--------------------------|----------------------|--------------------|-------------------------------------------------------------------------------------------------------------------------------|---------------------------|--|---------|--|--|
| ADD OPTION K & L<br>EC NO: S2010-0534<br>2009/12/30<br>DRWN:SKANG<br>CHKD:ATSEE<br>2010/01/08<br>APPR:MLONG<br>2010/01/14 | QUALITY SYMBOLS<br><div>F<sub>A</sub>=0</div> <div>F<sub>E</sub>=0</div> <div>F<sub>P</sub>=0</div> | DESCRIPTION | GENERAL TOLERANCES (UNLESS SPECIFIED) |        | DIMENSION STYLE<br>IN/MM |                      | SCALE<br>NTS       | DESIGN UNITS<br>INCH                                                                                                          | THIRD ANGLE<br>PROJECTION |  |         |  |  |
|                                                                                                                           |                                                                                                     |             |                                       | mm     | INCH                     | DRAWN BY<br>DJB      | DATE<br>1991/10/21 | TITLE<br>EARLY ENTRY R/A RECPT<br>.120"PC TAIL W/O LOWER<br>ROW PINSTOP-.100" GRID                                            |                           |  |         |  |  |
|                                                                                                                           |                                                                                                     |             | 4 PLACES                              | ± ---  | ± ---                    | CHECKED BY<br>DJB    | DATE<br>1991/10/21 |                                                                                                                               |                           |  |         |  |  |
|                                                                                                                           |                                                                                                     |             | 3 PLACES                              | ± ---  | ± .010                   | APPROVED BY<br>MLONG |                    | DATE<br>2010/01/14                                                                                                            | molex MOLEX INCORPORATED  |  |         |  |  |
|                                                                                                                           |                                                                                                     |             | 2 PLACES                              | ± 0.25 | ± ---                    | MATERIAL NO.         |                    | DOCUMENT NO.                                                                                                                  |                           |  |         |  |  |
|                                                                                                                           |                                                                                                     |             | 1 PLACE                               | ± ---  | ± ---                    | SIZE<br>A3           |                    | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |                           |  |         |  |  |
| DRAFT WHERE APPLICABLE<br>MUST REMAIN<br>WITHIN DIMENSIONS                                                                |                                                                                                     |             |                                       |        | SEE TABLE                |                      | SDA-71973-****     |                                                                                                                               |                           |  | 4 OF 26 |  |  |


10 9 8 7 6 5 4 3 2 1



RECOMMENDED P.C.B.  
LAYOUT

SCALE 4:1

SECTION D-D



NOTES:


- 1.) MATERIAL -  
INSULATOR - LCP, UL 94V-0, COLOR BLACK  
CONTACTS - PHOSPHOR BRONZE
- 2.) SEE SHT. 22 FOR CHART DIMENSIONS AND ITEM NO.'S
- 3.) RECOMMENDED MATING PIN LENGTH:  
LOWER ROW - .200" MINIMUM, .285" MAX.  
UPPER ROW - .200" MINIMUM
- 4.) REFER TO PRODUCT SPECIFICATION PS-71973-9999 FOR PERFORMANCE DATA
- 5.) MANUFACTURED DATE CODE - YEAR, WEEK.
- 6.) PACKAGING: FOR THIS PRODUCT IN TUBES SEE SHT. 22

FINISHES PER ES-88-(\*\*\*)

- 15 GOLD .000015 MINIMUM GOLD PLATE IN SELECT AREA OVER  
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH  
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 30 GOLD .000030 MINIMUM GOLD PLATE IN SELECT AREA OVER  
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH  
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 50 GOLD .000050 MINIMUM GOLD PLATE IN SELECT AREA OVER  
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH  
.000100 MINIMUM TIN PLATE IN SELECT AREA.

NOTE FOR LEAD FREE CONVERSION:

THE PRIMARY SHIPPING CARTON WILL BE  
LABELED "COMPLIANT TO ROHS DIRECTIVE  
2002/95/EC AND ELV ANNEX II OF  
DIRECTIVE 2000/53/EC". CARTONS WITHOUT  
THIS LABEL MAY CONTAIN PRODUCT WITH  
LEAD.



.028±.002  
(0.71±0.05)  
Ø .015 TAIL TO TAIL  
Ø .020 X S Y TAIL TO INSULATOR  
(SEE NOTE 7)

OPTION "I" ASSEMBLY

STANDARD HOUSING W/ PEGS AND MOUNTING EARS

|                                                                                                                           |                                                                    |             |                                       |        |                                                            |                    |                                                                                                                                  |                      |                        |
|---------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------|-------------|---------------------------------------|--------|------------------------------------------------------------|--------------------|----------------------------------------------------------------------------------------------------------------------------------|----------------------|------------------------|
| ADD OPTION K & L<br>EC NO: S2010-0534<br>DRWN:SKANG<br>CHKD:ATSEE<br>APPR:MLONG<br>2009/12/30<br>2010/01/08<br>2010/01/14 | QUALITY SYMBOLS<br><div>FA=0</div> <div>FC=0</div> <div>FP=0</div> | DESCRIPTION | GENERAL TOLERANCES (UNLESS SPECIFIED) |        | DIMENSION STYLE<br>IN/MM                                   |                    | SCALE<br>NTS                                                                                                                     | DESIGN UNITS<br>INCH | THIRD ANGLE PROJECTION |
|                                                                                                                           |                                                                    |             | mm                                    | INCH   | DRAWN BY<br>DJB                                            | DATE<br>1991/10/21 | TITLE<br>EARLY ENTRY R/A RECPT<br>.120"PC TAIL W/O LOWER<br>ROW PINSTOP-.100" GRID<br><br>MOLEX INCORPORATED                     |                      |                        |
|                                                                                                                           |                                                                    |             | 4 PLACES ± ---                        | ± ---  | CHECKED BY<br>DJB                                          | DATE<br>1991/10/21 |                                                                                                                                  |                      |                        |
|                                                                                                                           |                                                                    |             | 3 PLACES ± ---                        | ± .010 | APPROVED BY<br>MLONG                                       | DATE<br>2010/01/14 |                                                                                                                                  |                      |                        |
|                                                                                                                           |                                                                    |             | 2 PLACES ± 0.25                       | ± ---  | MATERIAL NO.<br>SEE TABLE                                  |                    |                                                                                                                                  |                      |                        |
| K                                                                                                                         | REV                                                                |             | ANGULAR ±1/2°                         |        | DRAFT WHERE APPLICABLE<br>MUST REMAIN<br>WITHIN DIMENSIONS |                    | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX<br>INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |                      |                        |



9 8 7 6 5 4 3 2 1

# FINISHES



- 15 GOLD .000015 MINIMUM GOLD PLATE IN SELECT AREA OVER  
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH  
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 30 GOLD .000030 MINIMUM GOLD PLATE IN SELECT AREA OVER  
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH  
.000075 MINIMUM TIN PLATE IN SELECT AREA.
- 50 GOLD .000050 MINIMUM GOLD PLATE IN SELECT AREA OVER  
.000050 MINIMUM NICKEL UNDERPLATE OVER-ALL WITH  
.000100 MINIMUM TIN PLATE IN SELECT AREA.

# NOTES:

- 1.) MATERIAL-  
INSULATOR - LCP, UL 94V-0, COLOR BLACK  
CONTACTS - PHOSPHOR BRONZE
- 2.) SEE SHT.25 FOR CHART DIMENSIONS AND ITEM NO.'S
- 3.) RECOMMENDED MATING PIN LENGTH:  
LOWER ROW - .200" MINIMUM, .285" MAX.  
UPPER ROW - .200" MINIMUM
- 4.) REFER TO PRODUCT SPECIFICATION PS-71973-9999 FOR PERFORMANCE DATA
- 5.) MANUFACTURED DATE CODE - YEAR, WEEK.
- 6.) PACKAGING: FOR THIS PRODUCT IN TUBES SEE SHT.25



# SECTION D-D



RECOMMENDED P.C.B.  
LAYOUT

.028±.002  
(0.71±0.05)  
Ø .015 (S) TAIL TO TAIL  
Ø .020 (S) X (S) Y (S) TAIL TO INSULATOR  
(SEE NOTE 8)

OPTION "K" ASSEMBLY  
STANDARD HOUSING W/ PEGS

|                                                                                                                  |                                                                    |                                                                                                                               |                 |                  |                                                                           |              |                                   |  |
|------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|-----------------|------------------|---------------------------------------------------------------------------|--------------|-----------------------------------|--|
| ADD OPTION K & L<br>EC NO: S2010-0534<br>DRWN:SKANG 2009/12/30<br>CHKD:ATSEE 2010/01/08<br>APPR:MLONG 2010/01/14 | QUALITY SYMBOLS<br><div>FA=0</div> <div>FC=0</div> <div>FP=0</div> | GENERAL TOLERANCES (UNLESS SPECIFIED)                                                                                         | DIMENSION STYLE |                  | SCALE                                                                     | DESIGN UNITS | <div>THIRD ANGLE PROJECTION</div> |  |
|                                                                                                                  |                                                                    |                                                                                                                               | IN/MM           |                  | NTS                                                                       | INCH         |                                   |  |
|                                                                                                                  |                                                                    |                                                                                                                               | mm              | INCH             | TITLE                                                                     |              |                                   |  |
|                                                                                                                  |                                                                    |                                                                                                                               | DRAWN BY DATE   |                  | EARLY ENTRY R/A RECPT<br>.120"PC TAIL W/O LOWER<br>ROW PINSTOP-.100" GRID |              |                                   |  |
|                                                                                                                  |                                                                    |                                                                                                                               | CHECKED BY DATE |                  | MOLEX INCORPORATED                                                        |              |                                   |  |
| K                                                                                                                | DESCRIPTION                                                        | 4 PLACES                                                                                                                      | ± --- ± ---     | DJB              | 1991/10/21                                                                |              |                                   |  |
|                                                                                                                  |                                                                    | 3 PLACES                                                                                                                      | ± --- ± .010    |                  |                                                                           |              |                                   |  |
|                                                                                                                  |                                                                    | 2 PLACES                                                                                                                      | ± 0.25 ± ---    | DJB              | 1991/10/21                                                                |              |                                   |  |
|                                                                                                                  |                                                                    | 1 PLACE                                                                                                                       | ± --- ± ---     | APPROVED BY DATE |                                                                           |              |                                   |  |
|                                                                                                                  |                                                                    | ANGULAR ±1/2°                                                                                                                 |                 | MLONG 2010/01/14 |                                                                           |              |                                   |  |
| REV                                                                                                              | DRAFT WHERE APPLICABLE<br>MUST REMAIN<br>WITHIN DIMENSIONS         | MATERIAL NO.                                                                                                                  |                 | DOCUMENT NO.     |                                                                           | SHEET NO.    |                                   |  |
|                                                                                                                  |                                                                    | SEE TABLE                                                                                                                     |                 | SDA-71973-****   |                                                                           | 6 OF 26      |                                   |  |
|                                                                                                                  |                                                                    | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |                 |                  |                                                                           |              |                                   |  |





| <u>FINISHES</u> |      |                                                       |                                                                                                |
|-----------------|------|-------------------------------------------------------|------------------------------------------------------------------------------------------------|
| 15              | GOLD | .000015 MINIMUM<br>.000050 MINIMUM<br>.000075 MINIMUM | GOLD PLATE IN SELECT AREA OVER<br>NICKEL UNDERPLATE OVER-ALL WITH<br>TIN PLATE IN SELECT AREA. |
| 30              | GOLD | .000030 MINIMUM<br>.000050 MINIMUM<br>.000075 MINIMUM | GOLD PLATE IN SELECT AREA OVER<br>NICKEL UNDERPLATE OVER-ALL WITH<br>TIN PLATE IN SELECT AREA. |
| 50              | GOLD | .000050 MINIMUM<br>.000050 MINIMUM<br>.000100 MINIMUM | GOLD PLATE IN SELECT AREA OVER<br>NICKEL UNDERPLATE OVER-ALL WITH<br>TIN PLATE IN SELECT AREA. |

NOTES:

- 1.) MATERIAL -  
INSULATOR - LCP, UL 94V-0, COLOR BLACK  
CONTACTS - PHOSPHOR BRONZE
- 2.) SEE SHT. 22 FOR CHART DIMENSIONS AND ITEM NO.'S
- 3.) RECOMMENDED MATING PIN LENGTH:  
LOWER ROW - .200" MINIMUM, .250" MAX.  
UPPER ROW - .200" MINIMUM
- 4.) REFER TO PRODUCT SPECIFICATION PS-71973-9999 FOR  
PERFORMANCE DATA
- 5.) MANUFACTURED DATE CODE - YEAR, WEEK.
- 6.) PACKAGING: FOR THIS PRODUCT IN TUBES SEE SHT. 26

## SECTION D-D



$\frac{.028 \pm .002}{(0.71 \pm 0.05)}$

|   |       |   |                         |
|---|-------|---|-------------------------|
| ⊕ | Ø.015 | Ⓢ | TAIL TO TAIL            |
| ⊕ | Ø.020 | Ⓢ | XⓈ YⓈ TAIL TO INSULATOR |

(SEE NOTE 8)

OPTION "L" ASSEMBLY  
STANDARD HOUSING W/ PEGS

|                                                                                                                            |                                               |                                                                                                                               |                                                                                                                               |                                            |                     |                                                                           |                      |                           |  |  |
|----------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------|---------------------|---------------------------------------------------------------------------|----------------------|---------------------------|--|--|
| ADD OPTION K & L<br>EC NO: S2010-0534<br>DRWN:SKANG<br>CHK'D:ATSEE<br>APPR:MLONG<br>2009/12/30<br>2010/01/08<br>2010/01/14 | QUALITY SYMBOLS<br><br>DESCRIPTION<br><br>REV | GENERAL TOLERANCES (UNLESS SPECIFIED)                                                                                         |                                                                                                                               | DIMENSION STYLE<br>IN/MM                   |                     | SCALE<br>NTS                                                              | DESIGN UNITS<br>INCH | THIRD ANGLE<br>PROJECTION |  |  |
|                                                                                                                            |                                               | $\sqrt{E}=0$                                                                                                                  | mm<br>INCH                                                                                                                    | DRAWN BY<br>DATE                           | TITLE               | EARLY ENTRY R/A RECPT<br>.120"PC TAIL W/O LOWER<br>ROW PINSTOP-.100" GRID |                      |                           |  |  |
|                                                                                                                            |                                               | $\sqrt{F}=0$                                                                                                                  | 4 PLACES $\pm$ --- $\pm$ ---<br>3 PLACES $\pm$ --- $\pm$ .010<br>2 PLACES $\pm$ 0.25 $\pm$ ---<br>1 PLACE $\pm$ --- $\pm$ --- | D/J/B<br>1991/10/21<br>D/J/B<br>1991/10/21 | CHECKED BY<br>DATE  |                                                                           |                      |                           |  |  |
|                                                                                                                            |                                               | $\sqrt{F}=0$                                                                                                                  | ANGULAR $\pm 1/2^\circ$                                                                                                       | APPROVED BY<br>DATE                        | MLONG<br>2010/01/14 | MOLEX<br>MOLEX INCORPORATED                                               |                      | SHEET NO.<br>7 OF 26      |  |  |
|                                                                                                                            |                                               | DRAFT WHERE APPLICABLE<br>MUST REMAIN<br>WITHIN DIMENSIONS                                                                    |                                                                                                                               | MATERIAL NO.<br>SEE TABLE                  |                     | DOCUMENT NO.<br>SDA-71973-****                                            |                      |                           |  |  |
| K                                                                                                                          |                                               | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |                                                                                                                               |                                            |                     |                                                                           |                      |                           |  |  |

| 10                                                                                                                    |       | 9                                                                                                   |  | 8       |            | 7          |            | 6                |                  | 5                                                    |   | 4                                                                                                                                                                   |  | 3                                                                                                                             |  | 2                                                                                                                                     |            | 1            |            |                  |                  |                   |   |                        |  |           |  |  |  |
|-----------------------------------------------------------------------------------------------------------------------|-------|-----------------------------------------------------------------------------------------------------|--|---------|------------|------------|------------|------------------|------------------|------------------------------------------------------|---|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------------------------------------------------------|------------|--------------|------------|------------------|------------------|-------------------|---|------------------------|--|-----------|--|--|--|
| NO. OF CKTS                                                                                                           |       | OPTION A ASSEMBLY<br>PACKAGED IN TUBES PER PK-70873-0138<br>(SEE SHEET I FOR FINISH SPECIFICATIONS) |  |         |            |            |            | DIMENSION        |                  |                                                      |   | NO. OF CKTS                                                                                                                                                         |  | OPTION A ASSEMBLY<br>PACKAGED IN TUBES PER PK-70873-0138<br>(SEE SHEET I FOR FINISH SPECIFICATIONS)                           |  |                                                                                                                                       |            |              |            | DIMENSION        |                  |                   |   |                        |  |           |  |  |  |
| PER ROW                                                                                                               | TOTAL |                                                                                                     |  | 15 GOLD |            | 30 GOLD    |            | 50 GOLD          |                  | A                                                    | B |                                                                                                                                                                     |  |                                                                                                                               |  | 15 GOLD                                                                                                                               |            | 30 GOLD      |            | 50 GOLD          |                  | A                 | B |                        |  |           |  |  |  |
| 4                                                                                                                     | 8     |                                                                                                     |  |         | 71973-0204 | 71973-0304 | 71973-0404 | .300<br>(7.62)   | .395<br>(10.03)  |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       | 71973-0233 | 71973-0333   | 71973-0433 | 3.200<br>(81.28) | 3.295<br>(83.69) |                   |   |                        |  |           |  |  |  |
| 5                                                                                                                     | 10    |                                                                                                     |  |         | 71973-0205 | 71973-0305 | 71973-0405 | .400<br>(10.16)  | .495<br>(12.57)  |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       | 71973-0234 | 71973-0334   | 71973-0434 | 3.300<br>(83.82) | 3.395<br>(86.23) |                   |   |                        |  |           |  |  |  |
| 6                                                                                                                     | 12    |                                                                                                     |  |         | 71973-0206 | 71973-0306 | 71973-0406 | .500<br>(12.70)  | .595<br>(15.11)  |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       | 71973-0235 | 71973-0335   | 71973-0435 | 3.400<br>(86.36) | 3.495<br>(88.77) |                   |   |                        |  |           |  |  |  |
| 7                                                                                                                     | 14    |                                                                                                     |  |         | 71973-0207 | 71973-0307 | 71973-0407 | .600<br>(15.24)  | .695<br>(17.65)  |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       | 71973-0236 | 71973-0336   | 71973-0436 | 3.500<br>(88.90) | 3.595<br>(91.31) |                   |   |                        |  |           |  |  |  |
| 8                                                                                                                     | 16    |                                                                                                     |  |         | 71973-0208 | 71973-0308 | 71973-0408 | .700<br>(17.78)  | .795<br>(20.19)  |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 9                                                                                                                     | 18    |                                                                                                     |  |         | 71973-0209 | 71973-0309 | 71973-0409 | .800<br>(20.32)  | .895<br>(22.73)  |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 10                                                                                                                    | 20    |                                                                                                     |  |         | 71973-0210 | 71973-0310 | 71973-0410 | .900<br>(22.86)  | .995<br>(25.27)  |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 11                                                                                                                    | 22    |                                                                                                     |  |         | 71973-0211 | 71973-0311 | 71973-0411 | 1.000<br>(25.40) | 1.095<br>(27.81) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 12                                                                                                                    | 24    |                                                                                                     |  |         | 71973-0212 | 71973-0312 | 71973-0412 | 1.100<br>(27.94) | 1.195<br>(30.35) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 13                                                                                                                    | 26    |                                                                                                     |  |         | 71973-0213 | 71973-0313 | 71973-0413 | 1.200<br>(30.48) | 1.295<br>(32.89) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 14                                                                                                                    | 28    |                                                                                                     |  |         | 71973-0214 | 71973-0314 | 71973-0414 | 1.300<br>(33.02) | 1.395<br>(35.43) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 15                                                                                                                    | 30    |                                                                                                     |  |         | 71973-0215 | 71973-0315 | 71973-0415 | 1.400<br>(35.56) | 1.495<br>(37.97) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 16                                                                                                                    | 32    |                                                                                                     |  |         | 71973-0216 | 71973-0316 | 71973-0416 | 1.500<br>(38.10) | 1.595<br>(40.51) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 17                                                                                                                    | 34    |                                                                                                     |  |         | 71973-0217 | 71973-0317 | 71973-0417 | 1.600<br>(40.64) | 1.695<br>(43.05) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 18                                                                                                                    | 36    |                                                                                                     |  |         | 71973-0218 | 71973-0318 | 71973-0418 | 1.700<br>(43.18) | 1.795<br>(45.59) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 19                                                                                                                    | 38    |                                                                                                     |  |         | 71973-0219 | 71973-0319 | 71973-0419 | 1.800<br>(45.72) | 1.895<br>(48.13) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 20                                                                                                                    | 40    |                                                                                                     |  |         | 71973-0220 | 71973-0320 | 71973-0420 | 1.900<br>(48.26) | 1.995<br>(50.67) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 21                                                                                                                    | 42    |                                                                                                     |  |         | 71973-0221 | 71973-0321 | 71973-0421 | 2.000<br>(50.80) | 2.095<br>(53.21) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 22                                                                                                                    | 44    |                                                                                                     |  |         | 71973-0222 | 71973-0322 | 71973-0422 | 2.100<br>(53.34) | 2.195<br>(55.75) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 23                                                                                                                    | 46    |                                                                                                     |  |         | 71973-0223 | 71973-0323 | 71973-0423 | 2.200<br>(55.88) | 2.295<br>(58.29) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 24                                                                                                                    | 48    |                                                                                                     |  |         | 71973-0224 | 71973-0324 | 71973-0424 | 2.300<br>(58.42) | 2.395<br>(60.83) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 25                                                                                                                    | 50    |                                                                                                     |  |         | 71973-0225 | 71973-0325 | 71973-0425 | 2.400<br>(60.96) | 2.495<br>(63.37) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 26                                                                                                                    | 52    |                                                                                                     |  |         | 71973-0226 | 71973-0326 | 71973-0426 | 2.500<br>(63.50) | 2.595<br>(65.91) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 27                                                                                                                    | 54    |                                                                                                     |  |         | 71973-0227 | 71973-0327 | 71973-0427 | 2.600<br>(66.04) | 2.695<br>(68.45) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 28                                                                                                                    | 56    |                                                                                                     |  |         | 71973-0228 | 71973-0328 | 71973-0428 | 2.700<br>(68.58) | 2.795<br>(70.99) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 29                                                                                                                    | 58    |                                                                                                     |  |         | 71973-0229 | 71973-0329 | 71973-0429 | 2.800<br>(71.12) | 2.895<br>(73.53) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 30                                                                                                                    | 60    |                                                                                                     |  |         | 71973-0230 | 71973-0330 | 71973-0430 | 2.900<br>(73.66) | 2.995<br>(76.07) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 31                                                                                                                    | 62    |                                                                                                     |  |         | 71973-0231 | 71973-0331 | 71973-0431 | 3.000<br>(76.20) | 3.095<br>(78.61) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| 32                                                                                                                    | 64    |                                                                                                     |  |         | 71973-0232 | 71973-0332 | 71973-0432 | 3.100<br>(78.74) | 3.195<br>(81.15) |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| ADD OPTION K & L<br>EC NO: S2010-0534<br>DRWN:SKANG 2009/12/30<br>CHKD:ATSEE 2010/01/08<br>APPR:MLONG 2010/01/14<br>K |       |                                                                                                     |  |         |            |            |            |                  |                  | QUALITY SYMBOLS<br>F=0<br>F=0<br>F=0                 |   | GENERAL TOLERANCES (UNLESS SPECIFIED)<br>mm INCH<br>4 PLACES ± --- ± ---<br>3 PLACES ± --- ± .010<br>2 PLACES ± 0.25 ± ---<br>1 PLACE ± --- ± ---<br>ANGULAR ± 1/2° |  |                                                                                                                               |  | DIMENSION STYLE IN/MM<br>DRAWN BY DATE<br>DJB 1991/10/21<br>CHECKED BY DATE<br>DJB 1991/10/21<br>APPROVED BY DATE<br>MLONG 2010/01/14 |            |              |            | SCALE NTS        |                  | DESIGN UNITS INCH |   | THIRD ANGLE PROJECTION |  |           |  |  |  |
|                                                                                                                       |       |                                                                                                     |  |         |            |            |            |                  |                  | DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS |   |                                                                                                                                                                     |  | SEE TABLE                                                                                                                     |  |                                                                                                                                       |            | MATERIAL NO. |            |                  |                  | DOCUMENT NO.      |   |                        |  | SHEET NO. |  |  |  |
|                                                                                                                       |       |                                                                                                     |  |         |            |            |            |                  |                  | A3                                                   |   |                                                                                                                                                                     |  | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
|                                                                                                                       |       |                                                                                                     |  |         |            |            |            |                  |                  |                                                      |   |                                                                                                                                                                     |  |                                                                                                                               |  |                                                                                                                                       |            |              |            |                  |                  |                   |   |                        |  |           |  |  |  |
| tb_frame_A3_P_AM.T<br>Rev. F 2009/06/18                                                                               |       | 9                                                                                                   |  | 8       |            | 7          |            | 6                |                  | 5                                                    |   | 4                                                                                                                                                                   |  | 3                                                                                                                             |  | 2                                                                                                                                     |            | 1            |            |                  |                  |                   |   |                        |  |           |  |  |  |

tb\_frame\_A3\_P\_AM\_T  
Rev. F 2009/06/18

tb\_frame\_A3\_P\_AM\_T  
Rev. F 2009/06/18

tb\_frame\_A3\_P\_AM\_T  
Rev. F 2009/06/18



tb\_frame\_A3\_P\_AM\_T  
Rev. F 2009/06/18

tb\_frame\_A3\_P\_AM\_T  
Rev. F 2009/06/18

tb\_frame\_A3\_P\_AM\_T  
Rev. F 2009/06/18

[illegible]

tb\_frame\_A3\_P\_AM\_T  
Rev. F 2009/06/18

|                                         | 10          |       | 9                                                                                                   |            | 8                                                          |            | 7          |                  | 6                                                                                                                                |   | 5            |   | 4              |            | 3                                                                                                   |            | 2                |                  | 1 |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
|-----------------------------------------|-------------|-------|-----------------------------------------------------------------------------------------------------|------------|------------------------------------------------------------|------------|------------|------------------|----------------------------------------------------------------------------------------------------------------------------------|---|--------------|---|----------------|------------|-----------------------------------------------------------------------------------------------------|------------|------------------|------------------|---|--|-----------|---------------------------------------------------------------------------------------------------------------------------|--|--------------------|--------------------------------------|---------------------------------------|-------|--------------------------|------------|--------------|---------------------------------------------------------------------------|----------------------|--|------------------------|--|---|
| F                                       | NO. OF CKTS |       | OPTION E ASSEMBLY<br>PACKAGED IN TRAYS PER PK-70873-0239<br>(SEE SHEET I FOR FINISH SPECIFICATIONS) |            |                                                            |            |            |                  | DIMENSION                                                                                                                        |   |              |   | NO. OF CKTS    |            | OPTION E ASSEMBLY<br>PACKAGED IN TRAYS PER PK-70873-0239<br>(SEE SHEET I FOR FINISH SPECIFICATIONS) |            |                  |                  |   |  | DIMENSION |                                                                                                                           |  |                    | F                                    |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
|                                         | PER ROW     | TOTAL |                                                                                                     |            | 15 GOLD                                                    | 30 GOLD    | 50 GOLD    | A                | B                                                                                                                                |   |              |   |                | 15 GOLD    | 30 GOLD                                                                                             | 50 GOLD    | A                | B                |   |  | E         |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
|                                         |             |       |                                                                                                     |            |                                                            |            |            |                  |                                                                                                                                  |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 4                                       | 8           |       |                                                                                                     |            | 71973-8204                                                 | 71973-8304 | 71973-8404 | .300<br>(7.62)   | .395<br>(10.03)                                                                                                                  |   |              |   |                | 71973-8234 | 71973-8334                                                                                          | 71973-8434 | 3.300<br>(83.82) | 3.395<br>(86.23) |   |  |           | E                                                                                                                         |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 5                                       | 10          |       |                                                                                                     |            | 71973-8205                                                 | 71973-8305 | 71973-8405 | .400<br>(10.16)  | .495<br>(12.57)                                                                                                                  |   |              |   |                | 71973-8235 | 71973-8335                                                                                          | 71973-8435 | 3.400<br>(86.36) | 3.495<br>(88.77) |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 6                                       | 12          |       |                                                                                                     |            | 71973-8206                                                 | 71973-8306 | 71973-8406 | .500<br>(12.70)  | .595<br>(15.11)                                                                                                                  |   |              |   |                | 71973-8236 | 71973-8336                                                                                          | 71973-8436 | 3.500<br>(88.90) | 3.595<br>(91.31) |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 7                                       | 14          |       |                                                                                                     |            | 71973-8207                                                 | 71973-8307 | 71973-8407 | .600<br>(15.24)  | .695<br>(17.65)                                                                                                                  |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  | D         |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 8                                       | 16          |       |                                                                                                     |            | 71973-8208                                                 | 71973-8308 | 71973-8408 | .700<br>(17.78)  | .795<br>(20.19)                                                                                                                  |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 9                                       | 18          |       |                                                                                                     |            | 71973-8209                                                 | 71973-8309 | 71973-8409 | .800<br>(20.32)  | .895<br>(22.73)                                                                                                                  |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 10                                      | 20          |       |                                                                                                     |            | 71973-8210                                                 | 71973-8310 | 71973-8410 | .900<br>(22.86)  | .995<br>(25.27)                                                                                                                  |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  | C         |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 11                                      | 22          |       |                                                                                                     |            | 71973-8211                                                 | 71973-8311 | 71973-8411 | 1.000<br>(25.40) | 1.095<br>(27.81)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 12                                      | 24          |       |                                                                                                     |            | 71973-8212                                                 | 71973-8312 | 71973-8412 | 1.100<br>(27.94) | 1.195<br>(30.35)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 13                                      | 26          |       |                                                                                                     |            | 71973-8213                                                 | 71973-8313 | 71973-8413 | 1.200<br>(30.48) | 1.295<br>(32.89)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  | B         |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 14                                      | 28          |       |                                                                                                     |            | 71973-8214                                                 | 71973-8314 | 71973-8414 | 1.300<br>(33.02) | 1.395<br>(35.43)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 15                                      | 30          |       |                                                                                                     |            | 71973-8215                                                 | 71973-8315 | 71973-8415 | 1.400<br>(35.56) | 1.495<br>(37.97)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 16                                      | 32          |       |                                                                                                     |            | 71973-8216                                                 | 71973-8316 | 71973-8416 | 1.500<br>(38.10) | 1.595<br>(40.51)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  | A         |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 17                                      | 34          |       |                                                                                                     |            | 71973-8217                                                 | 71973-8317 | 71973-8417 | 1.600<br>(40.64) | 1.695<br>(43.05)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 18                                      | 36          |       |                                                                                                     |            | 71973-8218                                                 | 71973-8318 | 71973-8418 | 1.700<br>(43.18) | 1.795<br>(45.59)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 19                                      | 38          |       |                                                                                                     |            | 71973-8219                                                 | 71973-8319 | 71973-8419 | 1.800<br>(45.72) | 1.895<br>(48.13)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 20                                      | 40          |       |                                                                                                     |            | 71973-8220                                                 | 71973-8320 | 71973-8420 | 1.900<br>(48.26) | 1.995<br>(50.67)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 21                                      | 42          |       |                                                                                                     |            | 71973-8221                                                 | 71973-8321 | 71973-8421 | 2.000<br>(50.80) | 2.095<br>(53.21)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 22                                      | 44          |       |                                                                                                     |            | 71973-8222                                                 | 71973-8322 | 71973-8422 | 2.100<br>(53.34) | 2.195<br>(55.75)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 23                                      | 46          |       |                                                                                                     |            | 71973-8223                                                 | 71973-8323 | 71973-8423 | 2.200<br>(55.88) | 2.295<br>(58.29)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 24                                      | 48          |       |                                                                                                     |            | 71973-8224                                                 | 71973-8324 | 71973-8424 | 2.300<br>(58.42) | 2.395<br>(60.83)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 25                                      | 50          |       |                                                                                                     |            | 71973-8225                                                 | 71973-8325 | 71973-8425 | 2.400<br>(60.96) | 2.495<br>(63.37)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 26                                      | 52          |       |                                                                                                     |            | 71973-8226                                                 | 71973-8326 | 71973-8426 | 2.500<br>(63.50) | 2.595<br>(65.91)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 27                                      | 54          |       |                                                                                                     |            | 71973-8227                                                 | 71973-8327 | 71973-8427 | 2.600<br>(66.04) | 2.695<br>(68.45)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 28                                      | 56          |       |                                                                                                     |            | 71973-8228                                                 | 71973-8328 | 71973-8428 | 2.700<br>(68.58) | 2.795<br>(70.99)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 29                                      | 58          |       |                                                                                                     |            | 71973-8229                                                 | 71973-8329 | 71973-8429 | 2.800<br>(71.12) | 2.895<br>(73.53)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 30                                      | 60          |       |                                                                                                     |            | 71973-8230                                                 | 71973-8330 | 71973-8430 | 2.900<br>(73.66) | 2.995<br>(76.07)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 31                                      | 62          |       |                                                                                                     |            | 71973-8231                                                 | 71973-8331 | 71973-8431 | 3.000<br>(76.20) | 3.095<br>(78.61)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 32                                      | 64          |       |                                                                                                     |            | 71973-8232                                                 | 71973-8332 | 71973-8432 | 3.100<br>(78.74) | 3.195<br>(81.15)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 33                                      | 66          |       |                                                                                                     |            | 71973-8233                                                 | 71973-8333 | 71973-8433 | 3.200<br>(81.28) | 3.295<br>(83.69)                                                                                                                 |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| *X* INDICATES TOOLING IS NOT AVAILABLE. |             |       |                                                                                                     |            |                                                            |            |            |                  |                                                                                                                                  |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           | ADD OPTION K & L<br>EC NO: S2010-0534<br>2009/12/30<br>DRWN:SKANG<br>CHKD:ATSEE<br>2010/01/08<br>APPR:MLONG<br>2010/01/14 |  | DESCRIPTION<br>REV | QUALITY SYMBOLS<br>F=0<br>F=0<br>F=0 | GENERAL TOLERANCES (UNLESS SPECIFIED) |       | DIMENSION STYLE<br>IN/MM |            | SCALE<br>NTS |                                                                           | DESIGN UNITS<br>INCH |  | THIRD ANGLE PROJECTION |  | A |
|                                         |             |       |                                                                                                     |            |                                                            |            |            |                  |                                                                                                                                  |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      | mm                                    | INCH  | DRAWN BY                 | DATE       | TITLE        |                                                                           |                      |  |                        |  |   |
|                                         |             |       |                                                                                                     |            |                                                            |            |            |                  |                                                                                                                                  |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      | 4 PLACES                              | ± --- | ± ---                    | DJB        | 1991/10/21   | EARLY ENTRY R/A RECPT<br>.120"PC TAIL W/O LOWER<br>ROW PINSTOP-.100" GRID |                      |  |                        |  |   |
|                                         |             |       |                                                                                                     |            |                                                            |            |            |                  |                                                                                                                                  |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      | 3 PLACES                              | ± --- | ± .010                   | CHECKED BY | DATE         | MOLEX INCORPORATED                                                        |                      |  |                        |  |   |
| 2 PLACES                                | ± 0.25      | ± --- | DJB                                                                                                 | 1991/10/21 |                                                            |            |            |                  |                                                                                                                                  |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| 1 PLACE                                 | ± ---       | ± --- | APPROVED BY                                                                                         | DATE       |                                                            |            |            |                  |                                                                                                                                  |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
|                                         |             |       |                                                                                                     |            | ANGULAR ±1/2°                                              |            | MLONG      |                  | 2010/01/14                                                                                                                       |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
|                                         |             |       |                                                                                                     |            | DRAFT WHERE APPLICABLE<br>MUST REMAIN<br>WITHIN DIMENSIONS |            | SEE TABLE  |                  | MATERIAL NO.                                                                                                                     |   | DOCUMENT NO. |   | SDA-71973-**** |            | SHEET NO.<br>18 OF 26                                                                               |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
|                                         |             |       |                                                                                                     |            |                                                            |            | SIZE<br>A3 |                  | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX<br>INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |   |              |   |                |            |                                                                                                     |            |                  |                  |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |
| fb_frame_A3_P_AM_T<br>Rev. F 2009/06/18 |             | 9     |                                                                                                     | 8          |                                                            | 7          |            | 6                |                                                                                                                                  | 5 |              | 4 |                | 3          |                                                                                                     | 2          |                  | 1                |   |  |           |                                                                                                                           |  |                    |                                      |                                       |       |                          |            |              |                                                                           |                      |  |                        |  |   |

tb\_frame\_A3\_P\_AM\_T  
Rev. F 2009/06/18

| 10                                      |  |  |  |  |  |  |  |  |  | 9                                                                                                                         |  |  |  |  | 8 |  |  |  |  | 7                                    |  |  |  |  | 6 |  |  |  |  | 5                                                                                                                                                                   |  |  |  |  | 4 |  |  |  |  | 3                                                                                                   |  |  |  |  | 2 |  |  |  |  | 1                                                                                                                                        |  |  |  |  |  |  |  |  |  |                                                                                                    |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|-----------------------------------------|--|--|--|--|--|--|--|--|--|---------------------------------------------------------------------------------------------------------------------------|--|--|--|--|---|--|--|--|--|--------------------------------------|--|--|--|--|---|--|--|--|--|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|---|--|--|--|--|-----------------------------------------------------------------------------------------------------|--|--|--|--|---|--|--|--|--|------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|--|--|--|--|--|----------------------------------------------------------------------------------------------------|--|--|--|--|--|--|--|--|--|---------------------------------------------------|--|--|--|--|--|--|--|--|--|-------------------------------------------------------|--|--|--|--|--|--|--|--|--|--------------|--|--|--|--|--|--|--|--|--|--------------|--|--|--|--|--|--|--|--|--|--------------|--|--|--|--|--|--|--|--|--|------------------|--|--|--|--|--|--|--|--|--|------------------|--|--|--|--|--|--|--|--|--|
| NO. OF CKTS                             |  |  |  |  |  |  |  |  |  | OPTION G ASSEMBLY<br>PACKAGED IN TUBES PER PK-70873-0138<br>(SEE SHEET I FOR FINISH SPECIFICATIONS)                       |  |  |  |  |   |  |  |  |  | DIMENSION                            |  |  |  |  |   |  |  |  |  | NO. OF CKTS                                                                                                                                                         |  |  |  |  |   |  |  |  |  | OPTION G ASSEMBLY<br>PACKAGED IN TUBES PER PK-70873-0138<br>(SEE SHEET I FOR FINISH SPECIFICATIONS) |  |  |  |  |   |  |  |  |  | DIMENSION                                                                                                                                |  |  |  |  |  |  |  |  |  |                                                                                                    |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
| PER ROW                                 |  |  |  |  |  |  |  |  |  | TOTAL                                                                                                                     |  |  |  |  |   |  |  |  |  | A                                    |  |  |  |  |   |  |  |  |  | B                                                                                                                                                                   |  |  |  |  |   |  |  |  |  | PER ROW                                                                                             |  |  |  |  |   |  |  |  |  | TOTAL                                                                                                                                    |  |  |  |  |  |  |  |  |  | A                                                                                                  |  |  |  |  |  |  |  |  |  | B                                                 |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
| 4                                       |  |  |  |  |  |  |  |  |  | 8                                                                                                                         |  |  |  |  |   |  |  |  |  | X 71973-5004                         |  |  |  |  |   |  |  |  |  | X 71973-5104                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5204                                                                                        |  |  |  |  |   |  |  |  |  | .300<br>(7.62)                                                                                                                           |  |  |  |  |  |  |  |  |  | .395<br>(10.03)                                                                                    |  |  |  |  |  |  |  |  |  | 32                                                |  |  |  |  |  |  |  |  |  | 64                                                    |  |  |  |  |  |  |  |  |  | X 71973-5032 |  |  |  |  |  |  |  |  |  | X 71973-5132 |  |  |  |  |  |  |  |  |  | X 71973-5232 |  |  |  |  |  |  |  |  |  | 3.100<br>(78.74) |  |  |  |  |  |  |  |  |  | 3.195<br>(81.15) |  |  |  |  |  |  |  |  |  |
| 5                                       |  |  |  |  |  |  |  |  |  | 10                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5005                         |  |  |  |  |   |  |  |  |  | X 71973-5105                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5205                                                                                        |  |  |  |  |   |  |  |  |  | .400<br>(10.16)                                                                                                                          |  |  |  |  |  |  |  |  |  | .495<br>(12.57)                                                                                    |  |  |  |  |  |  |  |  |  | 33                                                |  |  |  |  |  |  |  |  |  | 66                                                    |  |  |  |  |  |  |  |  |  | X 71973-5033 |  |  |  |  |  |  |  |  |  | X 71973-5133 |  |  |  |  |  |  |  |  |  | X 71973-5233 |  |  |  |  |  |  |  |  |  | 3.200<br>(81.28) |  |  |  |  |  |  |  |  |  | 3.295<br>(83.69) |  |  |  |  |  |  |  |  |  |
| 6                                       |  |  |  |  |  |  |  |  |  | 12                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5006                         |  |  |  |  |   |  |  |  |  | X 71973-5106                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5206                                                                                        |  |  |  |  |   |  |  |  |  | .500<br>(12.70)                                                                                                                          |  |  |  |  |  |  |  |  |  | .595<br>(15.11)                                                                                    |  |  |  |  |  |  |  |  |  | 34                                                |  |  |  |  |  |  |  |  |  | 68                                                    |  |  |  |  |  |  |  |  |  | X 71973-5034 |  |  |  |  |  |  |  |  |  | X 71973-5134 |  |  |  |  |  |  |  |  |  | X 71973-5234 |  |  |  |  |  |  |  |  |  | 3.300<br>(83.82) |  |  |  |  |  |  |  |  |  | 3.395<br>(86.23) |  |  |  |  |  |  |  |  |  |
| 7                                       |  |  |  |  |  |  |  |  |  | 14                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5007                         |  |  |  |  |   |  |  |  |  | X 71973-5107                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5207                                                                                        |  |  |  |  |   |  |  |  |  | .600<br>(15.24)                                                                                                                          |  |  |  |  |  |  |  |  |  | .695<br>(17.65)                                                                                    |  |  |  |  |  |  |  |  |  | 35                                                |  |  |  |  |  |  |  |  |  | 70                                                    |  |  |  |  |  |  |  |  |  | X 71973-5035 |  |  |  |  |  |  |  |  |  | X 71973-5135 |  |  |  |  |  |  |  |  |  | X 71973-5235 |  |  |  |  |  |  |  |  |  | 3.400<br>(86.36) |  |  |  |  |  |  |  |  |  | 3.495<br>(88.77) |  |  |  |  |  |  |  |  |  |
| 8                                       |  |  |  |  |  |  |  |  |  | 16                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5008                         |  |  |  |  |   |  |  |  |  | X 71973-5108                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5208                                                                                        |  |  |  |  |   |  |  |  |  | .700<br>(17.78)                                                                                                                          |  |  |  |  |  |  |  |  |  | .795<br>(20.19)                                                                                    |  |  |  |  |  |  |  |  |  | 36                                                |  |  |  |  |  |  |  |  |  | 72                                                    |  |  |  |  |  |  |  |  |  | X 71973-5036 |  |  |  |  |  |  |  |  |  | X 71973-5136 |  |  |  |  |  |  |  |  |  | X 71973-5236 |  |  |  |  |  |  |  |  |  | 3.500<br>(88.90) |  |  |  |  |  |  |  |  |  | 3.595<br>(91.31) |  |  |  |  |  |  |  |  |  |
| 9                                       |  |  |  |  |  |  |  |  |  | 18                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5009                         |  |  |  |  |   |  |  |  |  | X 71973-5109                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5209                                                                                        |  |  |  |  |   |  |  |  |  | .800<br>(20.32)                                                                                                                          |  |  |  |  |  |  |  |  |  | .895<br>(22.73)                                                                                    |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
| E                                       |  |  |  |  |  |  |  |  |  | 10                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5010                         |  |  |  |  |   |  |  |  |  | X 71973-5110                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5210                                                                                        |  |  |  |  |   |  |  |  |  | .900<br>(22.86)                                                                                                                          |  |  |  |  |  |  |  |  |  | .995<br>(25.27)                                                                                    |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 11                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5011                         |  |  |  |  |   |  |  |  |  | X 71973-5111                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5211                                                                                        |  |  |  |  |   |  |  |  |  | 1.000<br>(25.40)                                                                                                                         |  |  |  |  |  |  |  |  |  | 1.095<br>(27.81)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 12                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5012                         |  |  |  |  |   |  |  |  |  | X 71973-5112                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5212                                                                                        |  |  |  |  |   |  |  |  |  | 1.100<br>(27.94)                                                                                                                         |  |  |  |  |  |  |  |  |  | 1.195<br>(30.35)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 13                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5013                         |  |  |  |  |   |  |  |  |  | X 71973-5113                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5213                                                                                        |  |  |  |  |   |  |  |  |  | 1.200<br>(30.48)                                                                                                                         |  |  |  |  |  |  |  |  |  | 1.295<br>(32.89)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 14                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5014                         |  |  |  |  |   |  |  |  |  | X 71973-5114                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5214                                                                                        |  |  |  |  |   |  |  |  |  | 1.300<br>(33.02)                                                                                                                         |  |  |  |  |  |  |  |  |  | 1.395<br>(35.43)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 15                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5015                         |  |  |  |  |   |  |  |  |  | X 71973-5115                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5215                                                                                        |  |  |  |  |   |  |  |  |  | 1.400<br>(35.56)                                                                                                                         |  |  |  |  |  |  |  |  |  | 1.495<br>(37.97)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
| D                                       |  |  |  |  |  |  |  |  |  | 16                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5016                         |  |  |  |  |   |  |  |  |  | X 71973-5116                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5216                                                                                        |  |  |  |  |   |  |  |  |  | 1.500<br>(38.10)                                                                                                                         |  |  |  |  |  |  |  |  |  | 1.595<br>(40.51)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 17                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5017                         |  |  |  |  |   |  |  |  |  | X 71973-5117                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5217                                                                                        |  |  |  |  |   |  |  |  |  | 1.600<br>(40.64)                                                                                                                         |  |  |  |  |  |  |  |  |  | 1.695<br>(43.05)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 18                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5018                         |  |  |  |  |   |  |  |  |  | X 71973-5118                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5218                                                                                        |  |  |  |  |   |  |  |  |  | 1.700<br>(43.18)                                                                                                                         |  |  |  |  |  |  |  |  |  | 1.795<br>(45.59)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 19                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5019                         |  |  |  |  |   |  |  |  |  | X 71973-5119                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5219                                                                                        |  |  |  |  |   |  |  |  |  | 1.800<br>(45.72)                                                                                                                         |  |  |  |  |  |  |  |  |  | 1.895<br>(48.13)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 20                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5020                         |  |  |  |  |   |  |  |  |  | X 71973-5120                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5220                                                                                        |  |  |  |  |   |  |  |  |  | 1.900<br>(48.26)                                                                                                                         |  |  |  |  |  |  |  |  |  | 1.995<br>(50.67)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 21                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5021                         |  |  |  |  |   |  |  |  |  | X 71973-5121                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5221                                                                                        |  |  |  |  |   |  |  |  |  | 2.000<br>(50.80)                                                                                                                         |  |  |  |  |  |  |  |  |  | 2.095<br>(53.21)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 22                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5022                         |  |  |  |  |   |  |  |  |  | X 71973-5122                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5222                                                                                        |  |  |  |  |   |  |  |  |  | 2.100<br>(53.34)                                                                                                                         |  |  |  |  |  |  |  |  |  | 2.195<br>(55.75)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
| C                                       |  |  |  |  |  |  |  |  |  | 23                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5023                         |  |  |  |  |   |  |  |  |  | X 71973-5123                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5223                                                                                        |  |  |  |  |   |  |  |  |  | 2.200<br>(55.88)                                                                                                                         |  |  |  |  |  |  |  |  |  | 2.295<br>(58.29)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 24                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5024                         |  |  |  |  |   |  |  |  |  | X 71973-5124                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5224                                                                                        |  |  |  |  |   |  |  |  |  | 2.300<br>(58.42)                                                                                                                         |  |  |  |  |  |  |  |  |  | 2.395<br>(60.83)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 25                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5025                         |  |  |  |  |   |  |  |  |  | X 71973-5125                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5225                                                                                        |  |  |  |  |   |  |  |  |  | 2.400<br>(60.96)                                                                                                                         |  |  |  |  |  |  |  |  |  | 2.495<br>(63.37)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 26                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5026                         |  |  |  |  |   |  |  |  |  | X 71973-5126                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5226                                                                                        |  |  |  |  |   |  |  |  |  | 2.500<br>(63.50)                                                                                                                         |  |  |  |  |  |  |  |  |  | 2.595<br>(65.91)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 27                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5027                         |  |  |  |  |   |  |  |  |  | X 71973-5127                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5227                                                                                        |  |  |  |  |   |  |  |  |  | 2.600<br>(66.04)                                                                                                                         |  |  |  |  |  |  |  |  |  | 2.695<br>(68.45)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 28                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5028                         |  |  |  |  |   |  |  |  |  | X 71973-5128                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5228                                                                                        |  |  |  |  |   |  |  |  |  | 2.700<br>(68.58)                                                                                                                         |  |  |  |  |  |  |  |  |  | 2.795<br>(70.99)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
| B                                       |  |  |  |  |  |  |  |  |  | 29                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5029                         |  |  |  |  |   |  |  |  |  | X 71973-5129                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5229                                                                                        |  |  |  |  |   |  |  |  |  | 2.800<br>(71.12)                                                                                                                         |  |  |  |  |  |  |  |  |  | 2.895<br>(73.53)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 30                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5030                         |  |  |  |  |   |  |  |  |  | X 71973-5130                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5230                                                                                        |  |  |  |  |   |  |  |  |  | 2.900<br>(73.66)                                                                                                                         |  |  |  |  |  |  |  |  |  | 2.995<br>(76.07)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  | 31                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5031                         |  |  |  |  |   |  |  |  |  | X 71973-5131                                                                                                                                                        |  |  |  |  |   |  |  |  |  | X 71973-5231                                                                                        |  |  |  |  |   |  |  |  |  | 3.000<br>(76.20)                                                                                                                         |  |  |  |  |  |  |  |  |  | 3.095<br>(78.61)                                                                                   |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
| "X" INDICATES TOOLING IS NOT AVAILABLE. |  |  |  |  |  |  |  |  |  | ADD OPTION K & L<br>EC NO: S2010-0534<br>2009/12/30<br>DRWN:SKANG<br>CHKD:ATSEE<br>2010/01/08<br>APPR:MLONG<br>2010/01/14 |  |  |  |  |   |  |  |  |  | QUALITY SYMBOLS<br>F=0<br>F=0<br>F=0 |  |  |  |  |   |  |  |  |  | GENERAL TOLERANCES (UNLESS SPECIFIED)<br>mm INCH<br>4 PLACES ± --- ± ---<br>3 PLACES ± --- ± .010<br>2 PLACES ± 0.25 ± ---<br>1 PLACE ± --- ± ---<br>ANGULAR ± 1/2° |  |  |  |  |   |  |  |  |  | DRAFT WHERE APPLICABLE<br>MUST REMAIN<br>WITHIN DIMENSIONS                                          |  |  |  |  |   |  |  |  |  | DIMENSION STYLE<br>IN/MM<br>DRAWN BY DATE<br>DJB 1991/10/21<br>CHECKED BY DATE<br>DJB 1991/10/21<br>APPROVED BY DATE<br>MLONG 2010/01/14 |  |  |  |  |  |  |  |  |  | SCALE<br>NTS<br>TITLE<br>EARLY ENTRY R/A RECPT<br>.120"PC TAIL W/O LOWER<br>ROW PINSTOP-.100" GRID |  |  |  |  |  |  |  |  |  | DESIGN UNITS<br>INCH<br>THIRD ANGLE<br>PROJECTION |  |  |  |  |  |  |  |  |  | MATERIAL NO.<br>DOCUMENT NO.<br>SHEET NO.<br>20 OF 26 |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  |                                                                                                                           |  |  |  |  |   |  |  |  |  |                                      |  |  |  |  |   |  |  |  |  |                                                                                                                                                                     |  |  |  |  |   |  |  |  |  | SEE TABLE                                                                                           |  |  |  |  |   |  |  |  |  | MOLEX INCORPORATED                                                                                                                       |  |  |  |  |  |  |  |  |  | SDA-71973-****                                                                                     |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  |                                                                                                                           |  |  |  |  |   |  |  |  |  |                                      |  |  |  |  |   |  |  |  |  |                                                                                                                                                                     |  |  |  |  |   |  |  |  |  | SIZE<br>A3                                                                                          |  |  |  |  |   |  |  |  |  | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX<br>INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION         |  |  |  |  |  |  |  |  |  |                                                                                                    |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
|                                         |  |  |  |  |  |  |  |  |  |                                                                                                                           |  |  |  |  |   |  |  |  |  |                                      |  |  |  |  |   |  |  |  |  |                                                                                                                                                                     |  |  |  |  |   |  |  |  |  |                                                                                                     |  |  |  |  |   |  |  |  |  |                                                                                                                                          |  |  |  |  |  |  |  |  |  |                                                                                                    |  |  |  |  |  |  |  |  |  |                                                   |  |  |  |  |  |  |  |  |  |                                                       |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |
| fb_frame_A3_P_AM_T<br>Rev. F 2009/06/18 |  |  |  |  |  |  |  |  |  | 9                                                                                                                         |  |  |  |  |   |  |  |  |  | 8                                    |  |  |  |  |   |  |  |  |  | 7                                                                                                                                                                   |  |  |  |  |   |  |  |  |  | 6                                                                                                   |  |  |  |  |   |  |  |  |  | 5                                                                                                                                        |  |  |  |  |  |  |  |  |  | 4                                                                                                  |  |  |  |  |  |  |  |  |  | 3                                                 |  |  |  |  |  |  |  |  |  | 2                                                     |  |  |  |  |  |  |  |  |  | 1            |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |              |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |                  |  |  |  |  |  |  |  |  |  |

|   | 10          |       |  | 9                                                                                                   |   |            | 8       |            |   | 7          |  |                  | 6                |             |                  | 5 |                                                                                                     |       | 4 |         |   | 3          |           |            | 2 |            |   | 1                |                  |   |                  |   |  |
|---|-------------|-------|--|-----------------------------------------------------------------------------------------------------|---|------------|---------|------------|---|------------|--|------------------|------------------|-------------|------------------|---|-----------------------------------------------------------------------------------------------------|-------|---|---------|---|------------|-----------|------------|---|------------|---|------------------|------------------|---|------------------|---|--|
| F | NO. OF CKTS |       |  | OPTION H ASSEMBLY<br>PACKAGED IN TUBES PER PK-70873-0139<br>(SEE SHEET I FOR FINISH SPECIFICATIONS) |   |            |         |            |   | DIMENSION  |  |                  |                  | NO. OF CKTS |                  |   | OPTION H ASSEMBLY<br>PACKAGED IN TUBES PER PK-70873-0139<br>(SEE SHEET I FOR FINISH SPECIFICATIONS) |       |   |         |   |            | DIMENSION |            |   |            | F |                  |                  |   |                  |   |  |
|   | PER ROW     | TOTAL |  | 15 GOLD                                                                                             |   |            | 30 GOLD |            |   | 50 GOLD    |  |                  | A                | B           |                  | D | PER ROW                                                                                             | TOTAL |   | 15 GOLD |   |            | 30 GOLD   |            |   | 50 GOLD    |   |                  | A                | B |                  | D |  |
|   |             |       |  |                                                                                                     |   |            |         |            |   |            |  |                  |                  |             |                  |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 4           | 8     |  |                                                                                                     | X | 71973-5804 | X       | 71973-5904 | X | 71973-6004 |  | .300<br>(7.62)   | .395<br>(10.03)  |             | .658<br>(16.71)  |   | 31                                                                                                  | 62    |   |         | X | 71973-5831 | X         | 71973-5931 | X | 71973-6031 |   | 3.000<br>(76.20) | 3.095<br>(78.61) |   | 3.358<br>(85.29) |   |  |
|   | 5           | 10    |  |                                                                                                     | X | 71973-5805 | X       | 71973-5905 | X | 71973-6005 |  | .400<br>(10.16)  | .495<br>(12.57)  |             | .758<br>(19.25)  |   | 32                                                                                                  | 64    |   |         | X | 71973-5832 | X         | 71973-5932 | X | 71973-6032 |   | 3.100<br>(78.74) | 3.195<br>(81.15) |   | 3.458<br>(87.83) |   |  |
|   | 6           | 12    |  |                                                                                                     | X | 71973-5806 | X       | 71973-5906 | X | 71973-6006 |  | .500<br>(12.70)  | .595<br>(15.11)  |             | .858<br>(21.79)  |   | 33                                                                                                  | 66    |   |         | X | 71973-5833 | X         | 71973-5933 | X | 71973-6033 |   | 3.200<br>(81.28) | 3.295<br>(83.69) |   | 3.558<br>(90.37) |   |  |
| E | 7           | 14    |  |                                                                                                     | X | 71973-5807 | X       | 71973-5907 | X | 71973-6007 |  | .600<br>(15.24)  | .695<br>(17.65)  |             | .958<br>(24.33)  |   | 34                                                                                                  | 68    |   |         | X | 71973-5834 | X         | 71973-5934 | X | 71973-6034 |   | 3.300<br>(83.82) | 3.395<br>(86.23) |   | 3.658<br>(92.91) |   |  |
|   | 8           | 16    |  |                                                                                                     | X | 71973-5808 | X       | 71973-5908 | X | 71973-6008 |  | .700<br>(17.78)  | .795<br>(20.19)  |             | 1.058<br>(26.87) |   | 35                                                                                                  | 70    |   |         | X | 71973-5835 | X         | 71973-5935 | X | 71973-6035 |   | 3.400<br>(86.36) | 3.495<br>(88.77) |   | 3.758<br>(95.45) |   |  |
|   | 9           | 18    |  |                                                                                                     | X | 71973-5809 | X       | 71973-5909 | X | 71973-6009 |  | .800<br>(20.32)  | .895<br>(22.73)  |             | 1.158<br>(29.41) |   | 36                                                                                                  | 72    |   |         | X | 71973-5836 | X         | 71973-5936 | X | 71973-6036 |   | 3.500<br>(88.90) | 3.595<br>(91.31) |   | 3.858<br>(97.99) |   |  |
|   | 10          | 20    |  |                                                                                                     | X | 71973-5810 | X       | 71973-5910 | X | 71973-6010 |  | .900<br>(22.86)  | .995<br>(25.27)  |             | 1.258<br>(31.95) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 11          | 22    |  |                                                                                                     | X | 71973-5811 | X       | 71973-5911 | X | 71973-6011 |  | 1.000<br>(25.40) | 1.095<br>(27.81) |             | 1.358<br>(34.49) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
| D | 12          | 24    |  |                                                                                                     | X | 71973-5812 | X       | 71973-5912 | X | 71973-6012 |  | 1.100<br>(27.94) | 1.195<br>(30.35) |             | 1.458<br>(37.03) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 13          | 26    |  |                                                                                                     | X | 71973-5813 | X       | 71973-5913 | X | 71973-6013 |  | 1.200<br>(30.48) | 1.295<br>(32.89) |             | 1.558<br>(39.57) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 14          | 28    |  |                                                                                                     | X | 71973-5814 | X       | 71973-5914 | X | 71973-6014 |  | 1.300<br>(33.02) | 1.395<br>(35.43) |             | 1.658<br>(42.11) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 15          | 30    |  |                                                                                                     | X | 71973-5815 | X       | 71973-5915 | X | 71973-6015 |  | 1.400<br>(35.56) | 1.495<br>(37.97) |             | 1.758<br>(44.65) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 16          | 32    |  |                                                                                                     | X | 71973-5816 | X       | 71973-5916 | X | 71973-6016 |  | 1.500<br>(38.10) | 1.595<br>(40.51) |             | 1.858<br>(47.19) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
| C | 17          | 34    |  |                                                                                                     | X | 71973-5817 | X       | 71973-5917 | X | 71973-6017 |  | 1.600<br>(40.64) | 1.695<br>(43.05) |             | 1.958<br>(49.73) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 18          | 36    |  |                                                                                                     | X | 71973-5818 | X       | 71973-5918 | X | 71973-6018 |  | 1.700<br>(43.18) | 1.795<br>(45.59) |             | 2.058<br>(52.27) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 19          | 38    |  |                                                                                                     | X | 71973-5819 | X       | 71973-5919 | X | 71973-6019 |  | 1.800<br>(45.72) | 1.895<br>(48.13) |             | 2.158<br>(54.81) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 20          | 40    |  |                                                                                                     | X | 71973-5820 | X       | 71973-5920 | X | 71973-6020 |  | 1.900<br>(48.26) | 1.995<br>(50.67) |             | 2.258<br>(57.35) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 21          | 42    |  |                                                                                                     | X | 71973-5821 | X       | 71973-5921 | X | 71973-6021 |  | 2.000<br>(50.80) | 2.095<br>(53.21) |             | 2.358<br>(59.89) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
| B | 22          | 44    |  |                                                                                                     | X | 71973-5822 | X       | 71973-5922 | X | 71973-6022 |  | 2.100<br>(53.34) | 2.195<br>(55.75) |             | 2.458<br>(62.43) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 23          | 46    |  |                                                                                                     | X | 71973-5823 | X       | 71973-5923 | X | 71973-6023 |  | 2.200<br>(55.88) | 2.295<br>(58.29) |             | 2.558<br>(64.97) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 24          | 48    |  |                                                                                                     | X | 71973-5824 | X       | 71973-5924 | X | 71973-6024 |  | 2.300<br>(58.42) | 2.395<br>(60.83) |             | 2.658<br>(67.51) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 25          | 50    |  |                                                                                                     | X | 71973-5825 | X       | 71973-5925 | X | 71973-6025 |  | 2.400<br>(60.96) | 2.495<br>(63.37) |             | 2.758<br>(70.05) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 26          | 52    |  |                                                                                                     | X | 71973-5826 | X       | 71973-5926 | X | 71973-6026 |  | 2.500<br>(63.50) | 2.595<br>(65.91) |             | 2.858<br>(72.59) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 27          | 54    |  |                                                                                                     | X | 71973-5827 | X       | 71973-5927 | X | 71973-6027 |  | 2.600<br>(66.04) | 2.695<br>(68.45) |             | 2.958<br>(75.13) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 28          | 56    |  |                                                                                                     | X | 71973-5828 | X       | 71973-5928 | X | 71973-6028 |  | 2.700<br>(68.58) | 2.795<br>(70.99) |             | 3.058<br>(77.67) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 29          | 58    |  |                                                                                                     | X | 71973-5829 | X       | 71973-5929 | X | 71973-6029 |  | 2.800<br>(71.12) | 2.895<br>(73.53) |             | 3.158<br>(80.21) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |
|   | 30          | 60    |  |                                                                                                     | X | 71973-5830 | X       | 71973-5930 | X | 71973-6030 |  | 2.900<br>(73.66) | 2.995<br>(76.07) |             | 3.258<br>(82.75) |   |                                                                                                     |       |   |         |   |            |           |            |   |            |   |                  |                  |   |                  |   |  |

\*X\* INDICATES TOOLING IS NOT AVAILABLE.

|   |                                         |  |  |  |             |  |  |  |                   |  |                                       |  |  |         |                  |                                                                                                                               |                |  |              |  |                          |  |   |
|---|-----------------------------------------|--|--|--|-------------|--|--|--|-------------------|--|---------------------------------------|--|--|---------|------------------|-------------------------------------------------------------------------------------------------------------------------------|----------------|--|--------------|--|--------------------------|--|---|
| A | "X" INDICATES TOOLING IS NOT AVAILABLE. |  |  |  |             |  |  |  |                   |  |                                       |  |  |         |                  |                                                                                                                               |                |  |              |  |                          |  |   |
|   | ADD OPTION K & L                        |  |  |  | DESCRIPTION |  |  |  | QUALITY SYMBOLS   |  | GENERAL TOLERANCES (UNLESS SPECIFIED) |  |  |         | DIMENSION STYLE  |                                                                                                                               | SCALE          |  | DESIGN UNITS |  | THIRD ANGLE PROJECTION   |  | A |
|   | EC NO: S2010-0534                       |  |  |  | 2009/12/30  |  |  |  | F <sub>A</sub> =0 |  | mm INCH                               |  |  |         | DRAWN BY DATE    |                                                                                                                               | NTS            |  | INCH         |  | TITLE                    |  |   |
|   | DRWN:SKANG                              |  |  |  | 2010/01/08  |  |  |  | F <sub>C</sub> =0 |  | 4 PLACES ± --- ± ---                  |  |  |         | DJB 1991/10/21   |                                                                                                                               |                |  |              |  | EARLY ENTRY R/A RECPT    |  |   |
|   | CHKD:ATSEE                              |  |  |  | 2010/01/14  |  |  |  | F <sub>P</sub> =0 |  | 3 PLACES ± --- ± .010                 |  |  |         | CHECKED BY DATE  |                                                                                                                               |                |  |              |  | .120"PC TAIL W/O LOWER   |  |   |
|   | APPR:MLONG                              |  |  |  |             |  |  |  |                   |  | 2 PLACES ± 0.25 ± ---                 |  |  |         | DJB 1991/10/21   |                                                                                                                               |                |  |              |  | ROW PINSTOP-.100" GRID   |  |   |
|   |                                         |  |  |  |             |  |  |  |                   |  | 1 PLACE ± --- ± ---                   |  |  |         | APPROVED BY DATE |                                                                                                                               |                |  |              |  | MOLEX MOLEX INCORPORATED |  |   |
|   |                                         |  |  |  |             |  |  |  |                   |  | ANGULAR ±1/2°                         |  |  |         | MLONG 2010/01/14 |                                                                                                                               |                |  |              |  |                          |  |   |
|   |                                         |  |  |  |             |  |  |  |                   |  | DRAFT WHERE APPLICABLE                |  |  |         | MATERIAL NO.     |                                                                                                                               | DOCUMENT NO.   |  | SHEET NO.    |  |                          |  |   |
|   |                                         |  |  |  |             |  |  |  |                   |  | MUST REMAIN WITHIN DIMENSIONS         |  |  |         | SEE TABLE        |                                                                                                                               | SDA-71973-**** |  | 21 OF 26     |  |                          |  |   |
|   |                                         |  |  |  |             |  |  |  |                   |  |                                       |  |  | SIZE A3 |                  | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |                |  |              |  |                          |  |   |

[illegible]

[illegible]

| 10                                      |       | 9                                                                                                   |  | 8          |            | 7          |                                                                                                                           | 6                |                  | 5                |                                                  | 4     |                                                                                                                                                                                                         | 3 |                                                                                                                                          | 2          |                                                                                                                          | 1                |                                                |                  |                                                                                                                                                                       |  |                       |  |
|-----------------------------------------|-------|-----------------------------------------------------------------------------------------------------|--|------------|------------|------------|---------------------------------------------------------------------------------------------------------------------------|------------------|------------------|------------------|--------------------------------------------------|-------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---|------------------------------------------------------------------------------------------------------------------------------------------|------------|--------------------------------------------------------------------------------------------------------------------------|------------------|------------------------------------------------|------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-----------------------|--|
| NO. OF CKTS                             |       | OPTION I ASSEMBLY<br>PACKAGED IN TUBES PER PK-70873-0138<br>(SEE SHEET I FOR FINISH SPECIFICATIONS) |  |            |            |            | DIMENSION                                                                                                                 |                  |                  |                  | NO. OF CKTS                                      |       | OPTION I ASSEMBLY<br>PACKAGED IN TUBES PER PK-70873-0138<br>(SEE SHEET I FOR FINISH SPECIFICATIONS)                                                                                                     |   |                                                                                                                                          |            |                                                                                                                          | DIMENSION        |                                                |                  |                                                                                                                                                                       |  |                       |  |
| PER ROW                                 | TOTAL |                                                                                                     |  | 15 GOLD    | 30 GOLD    | 50 GOLD    | A                                                                                                                         | B                | C                | D                | PER ROW                                          | TOTAL |                                                                                                                                                                                                         |   | 15 GOLD                                                                                                                                  | 30 GOLD    | 50 GOLD                                                                                                                  | A                | B                                              | C                | D                                                                                                                                                                     |  |                       |  |
| F                                       | 4     | 8                                                                                                   |  | 71973-9704 | 71973-9804 | 71973-9904 | .300<br>(7.62)                                                                                                            | .395<br>(10.03)  | .200<br>(5.08)   | .658<br>(16.71)  | 34                                               | 68    |                                                                                                                                                                                                         |   | 71973-9734                                                                                                                               | 71973-9834 | 71973-9934                                                                                                               | 3.300<br>(83.82) | 3.395<br>(86.23)                               | 3.200<br>(81.28) | 3.658<br>(92.91)                                                                                                                                                      |  |                       |  |
|                                         | 5     | 10                                                                                                  |  | 71973-9705 | 71973-9805 | 71973-9905 | .400<br>(10.16)                                                                                                           | .495<br>(12.57)  | .300<br>(7.62)   | .758<br>(19.25)  | 35                                               | 70    |                                                                                                                                                                                                         |   | 71973-9735                                                                                                                               | 71973-9835 | 71973-9935                                                                                                               | 3.400<br>(86.36) | 3.495<br>(88.77)                               | 3.300<br>(83.82) | 3.758<br>(95.45)                                                                                                                                                      |  |                       |  |
|                                         | 6     | 12                                                                                                  |  | 71973-9706 | 71973-9806 | 71973-9906 | .500<br>(12.70)                                                                                                           | .595<br>(15.11)  | .400<br>(10.16)  | .858<br>(21.79)  | 36                                               | 72    |                                                                                                                                                                                                         |   | 71973-9736                                                                                                                               | 71973-9836 | 71973-9936                                                                                                               | 3.500<br>(88.90) | 3.595<br>(91.31)                               | 3.400<br>(86.36) | 3.858<br>(97.99)                                                                                                                                                      |  |                       |  |
|                                         | 7     | 14                                                                                                  |  | 71973-9707 | 71973-9807 | 71973-9907 | .600<br>(15.24)                                                                                                           | .695<br>(17.65)  | .500<br>(12.70)  | .958<br>(24.33)  |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 8     | 16                                                                                                  |  | 71973-9708 | 71973-9808 | 71973-9908 | .700<br>(17.78)                                                                                                           | .795<br>(20.19)  | .600<br>(15.24)  | 1.058<br>(26.87) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 9     | 18                                                                                                  |  | 71973-9709 | 71973-9809 | 71973-9909 | .800<br>(20.32)                                                                                                           | .895<br>(22.73)  | .700<br>(17.78)  | 1.158<br>(29.41) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
| E                                       | 10    | 20                                                                                                  |  | 71973-9710 | 71973-9810 | 71973-9910 | .900<br>(22.86)                                                                                                           | .995<br>(25.27)  | .800<br>(20.32)  | 1.258<br>(31.95) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 11    | 22                                                                                                  |  | 71973-9711 | 71973-9811 | 71973-9911 | 1.000<br>(25.40)                                                                                                          | 1.095<br>(27.81) | .900<br>(22.86)  | 1.358<br>(34.49) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 12    | 24                                                                                                  |  | 71973-9712 | 71973-9812 | 71973-9912 | 1.100<br>(27.94)                                                                                                          | 1.195<br>(30.35) | 1.000<br>(25.40) | 1.458<br>(37.03) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 13    | 26                                                                                                  |  | 71973-9713 | 71973-9813 | 71973-9913 | 1.200<br>(30.48)                                                                                                          | 1.295<br>(32.89) | 1.100<br>(27.94) | 1.558<br>(39.57) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 14    | 28                                                                                                  |  | 71973-9714 | 71973-9814 | 71973-9914 | 1.300<br>(33.02)                                                                                                          | 1.395<br>(35.43) | 1.200<br>(30.48) | 1.658<br>(42.11) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 15    | 30                                                                                                  |  | 71973-9715 | 71973-9815 | 71973-9915 | 1.400<br>(35.56)                                                                                                          | 1.495<br>(37.97) | 1.300<br>(33.02) | 1.758<br>(44.65) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 16    | 32                                                                                                  |  | 71973-9716 | 71973-9816 | 71973-9916 | 1.500<br>(38.10)                                                                                                          | 1.595<br>(40.51) | 1.400<br>(35.56) | 1.858<br>(47.19) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
| D                                       | 17    | 34                                                                                                  |  | 71973-9717 | 71973-9817 | 71973-9917 | 1.600<br>(40.64)                                                                                                          | 1.695<br>(43.05) | 1.500<br>(38.10) | 1.958<br>(49.73) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 18    | 36                                                                                                  |  | 71973-9718 | 71973-9818 | 71973-9918 | 1.700<br>(43.18)                                                                                                          | 1.795<br>(45.59) | 1.600<br>(40.64) | 2.058<br>(52.27) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 19    | 38                                                                                                  |  | 71973-9719 | 71973-9819 | 71973-9919 | 1.800<br>(45.72)                                                                                                          | 1.895<br>(48.13) | 1.700<br>(43.18) | 2.158<br>(54.81) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 20    | 40                                                                                                  |  | 71973-9720 | 71973-9820 | 71973-9920 | 1.900<br>(48.26)                                                                                                          | 1.995<br>(50.67) | 1.800<br>(45.72) | 2.258<br>(57.35) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 21    | 42                                                                                                  |  | 71973-9721 | 71973-9821 | 71973-9921 | 2.000<br>(50.80)                                                                                                          | 2.095<br>(53.21) | 1.900<br>(48.26) | 2.358<br>(59.89) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 22    | 44                                                                                                  |  | 71973-9722 | 71973-9822 | 71973-9922 | 2.100<br>(53.34)                                                                                                          | 2.195<br>(55.75) | 2.000<br>(50.80) | 2.458<br>(62.43) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 23    | 46                                                                                                  |  | 71973-9723 | 71973-9823 | 71973-9923 | 2.200<br>(55.88)                                                                                                          | 2.295<br>(58.29) | 2.100<br>(53.34) | 2.558<br>(64.97) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
| C                                       | 24    | 48                                                                                                  |  | 71973-9724 | 71973-9824 | 71973-9924 | 2.300<br>(58.42)                                                                                                          | 2.395<br>(60.83) | 2.200<br>(55.88) | 2.658<br>(67.51) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 25    | 50                                                                                                  |  | 71973-9725 | 71973-9825 | 71973-9925 | 2.400<br>(60.96)                                                                                                          | 2.495<br>(63.37) | 2.300<br>(58.42) | 2.758<br>(70.05) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 26    | 52                                                                                                  |  | 71973-9726 | 71973-9826 | 71973-9926 | 2.500<br>(63.50)                                                                                                          | 2.595<br>(65.91) | 2.400<br>(60.96) | 2.858<br>(72.59) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 27    | 54                                                                                                  |  | 71973-9727 | 71973-9827 | 71973-9927 | 2.600<br>(66.04)                                                                                                          | 2.695<br>(68.45) | 2.500<br>(63.50) | 2.958<br>(75.13) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 28    | 56                                                                                                  |  | 71973-9728 | 71973-9828 | 71973-9928 | 2.700<br>(68.58)                                                                                                          | 2.795<br>(70.99) | 2.600<br>(66.04) | 3.058<br>(77.67) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 29    | 58                                                                                                  |  | 71973-9729 | 71973-9829 | 71973-9929 | 2.800<br>(71.12)                                                                                                          | 2.895<br>(73.53) | 2.700<br>(68.58) | 3.158<br>(80.21) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 30    | 60                                                                                                  |  | 71973-9730 | 71973-9830 | 71973-9930 | 2.900<br>(73.66)                                                                                                          | 2.995<br>(76.07) | 2.800<br>(71.12) | 3.258<br>(82.75) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
| B                                       | 31    | 62                                                                                                  |  | 71973-9731 | 71973-9831 | 71973-9931 | 3.000<br>(76.20)                                                                                                          | 3.095<br>(78.61) | 2.900<br>(73.66) | 3.358<br>(85.29) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 32    | 64                                                                                                  |  | 71973-9732 | 71973-9832 | 71973-9932 | 3.100<br>(78.74)                                                                                                          | 3.195<br>(81.15) | 3.000<br>(76.20) | 3.458<br>(87.83) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         | 33    | 66                                                                                                  |  | 71973-9733 | 71973-9833 | 71973-9933 | 3.200<br>(81.28)                                                                                                          | 3.295<br>(83.69) | 3.100<br>(78.74) | 3.558<br>(90.37) |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
| A                                       |       | *X INDICATES TOOLING IS NOT AVAILABLE                                                               |  |            |            |            | ADD OPTION K & L<br>EC NO: S2010-0534<br>DRWN:SKANG<br>CHYD:ATSEE<br>APPR:MLONG<br>2009/12/30<br>2010/01/08<br>2010/01/14 |                  |                  |                  | QUALITY SYMBOLS<br>$F_A=0$<br>$F_B=0$<br>$F_P=0$ |       | GENERAL TOLERANCES (UNLESS SPECIFIED)<br>mm INCH<br>4 PLACES $\pm$ --- $\pm$ ---<br>3 PLACES $\pm$ --- $\pm$ .010<br>2 PLACES $\pm$ 0.25 $\pm$ ---<br>1 PLACE $\pm$ --- $\pm$ ---<br>ANGULAR $\pm$ 1/2° |   | DIMENSION STYLE<br>IN/MM<br>DRAWN BY DATE<br>DJB 1991/10/21<br>CHECKED BY DATE<br>DJB 1991/10/21<br>APPROVED BY DATE<br>MLONG 2010/01/14 |            | SCALE<br>NTS<br>TITLE<br>EARLY ENTRY R/A RECPT<br>.120"PC TAIL W/O LOWER<br>ROW PINSTOP-.100" GRID<br>MOLEX INCORPORATED |                  | DESIGN UNITS<br>INCH<br>THIRD ANGLE PROJECTION |                  | MATERIAL NO.<br>SEE TABLE<br>SIZE A3<br>THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |  | SHEET NO.<br>24 OF 26 |  |
|                                         |       |                                                                                                     |  |            |            |            |                                                                                                                           |                  |                  |                  |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         |       |                                                                                                     |  |            |            |            |                                                                                                                           |                  |                  |                  |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         |       |                                                                                                     |  |            |            |            |                                                                                                                           |                  |                  |                  |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
|                                         |       |                                                                                                     |  |            |            |            |                                                                                                                           |                  |                  |                  |                                                  |       |                                                                                                                                                                                                         |   |                                                                                                                                          |            |                                                                                                                          |                  |                                                |                  |                                                                                                                                                                       |  |                       |  |
| tb_frame_A3_P_AM_T<br>Rev. F 2009/06/18 |       | 9                                                                                                   |  | 8          |            | 7          |                                                                                                                           | 6                |                  | 5                |                                                  | 4     |                                                                                                                                                                                                         | 3 |                                                                                                                                          | 2          |                                                                                                                          | 1                |                                                |                  |                                                                                                                                                                       |  |                       |  |

| 10                                      |       | 9                                                                                                   |  | 8       |            | 7       |            | 6         |            | 5                                                                                                                         |                  | 4                                       |  | 3                                                                                                                                                                   |       | 2                                                                                                                                        |  | 1                              |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
|-----------------------------------------|-------|-----------------------------------------------------------------------------------------------------|--|---------|------------|---------|------------|-----------|------------|---------------------------------------------------------------------------------------------------------------------------|------------------|-----------------------------------------|--|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|------------------------------------------------------------------------------------------------------------------------------------------|--|--------------------------------|------------|-----------------------|------------|----------------------------------------------------------------------------------------------------------------------------------|------------|----------------------------------------------------------------------------------------------------------|------------------|--|--|
| NO. OF CKTS                             |       | OPTION K ASSEMBLY<br>PACKAGED IN TUBES PER PK-70873-0138<br>(SEE SHEET I FOR FINISH SPECIFICATIONS) |  |         |            |         |            | DIMENSION |            |                                                                                                                           |                  | NO. OF CKTS                             |  | OPTION K ASSEMBLY<br>PACKAGED IN TUBES PER PK-70873-0138<br>(SEE SHEET I FOR FINISH SPECIFICATIONS)                                                                 |       |                                                                                                                                          |  |                                |            | DIMENSION             |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| PER ROW                                 | TOTAL |                                                                                                     |  | 15 GOLD |            | 30 GOLD |            | 50 GOLD   |            | A                                                                                                                         | B                |                                         |  | PER ROW                                                                                                                                                             | TOTAL |                                                                                                                                          |  | 15 GOLD                        |            | 30 GOLD               |            | 50 GOLD                                                                                                                          |            | A                                                                                                        | B                |  |  |
| 4                                       | 8     |                                                                                                     |  |         | 71973-6204 |         | 71973-6304 |           | 71973-6404 | .300<br>(7.62)                                                                                                            | .395<br>(10.03)  |                                         |  | 32                                                                                                                                                                  | 64    |                                                                                                                                          |  |                                | 71973-6232 |                       | 71973-6332 |                                                                                                                                  | 71973-6432 | 3.100<br>(78.74)                                                                                         | 3.195<br>(81.15) |  |  |
| 5                                       | 10    |                                                                                                     |  |         | 71973-6205 |         | 71973-6305 |           | 71973-6405 | .400<br>(10.16)                                                                                                           | .495<br>(12.57)  |                                         |  | 33                                                                                                                                                                  | 66    |                                                                                                                                          |  |                                | 71973-6233 |                       | 71973-6333 |                                                                                                                                  | 71973-6433 | 3.200<br>(81.28)                                                                                         | 3.295<br>(83.69) |  |  |
| 6                                       | 12    |                                                                                                     |  |         | 71973-6206 |         | 71973-6306 |           | 71973-6406 | .500<br>(12.70)                                                                                                           | .595<br>(15.11)  |                                         |  | 34                                                                                                                                                                  | 68    |                                                                                                                                          |  |                                | 71973-6234 |                       | 71973-6334 |                                                                                                                                  | 71973-6434 | 3.300<br>(83.82)                                                                                         | 3.395<br>(86.23) |  |  |
| 7                                       | 14    |                                                                                                     |  |         | 71973-6207 |         | 71973-6307 |           | 71973-6407 | .600<br>(15.24)                                                                                                           | .695<br>(17.65)  |                                         |  | 35                                                                                                                                                                  | 70    |                                                                                                                                          |  |                                | 71973-6235 |                       | 71973-6335 |                                                                                                                                  | 71973-6435 | 3.400<br>(86.36)                                                                                         | 3.495<br>(88.77) |  |  |
| 8                                       | 16    |                                                                                                     |  |         | 71973-6208 |         | 71973-6308 |           | 71973-6408 | .700<br>(17.78)                                                                                                           | .795<br>(20.19)  |                                         |  | 36                                                                                                                                                                  | 72    |                                                                                                                                          |  |                                | 71973-6236 |                       | 71973-6336 |                                                                                                                                  | 71973-6436 | 3.500<br>(88.90)                                                                                         | 3.595<br>(91.31) |  |  |
| 9                                       | 18    |                                                                                                     |  |         | 71973-6209 |         | 71973-6309 |           | 71973-6409 | .800<br>(20.32)                                                                                                           | .895<br>(22.73)  |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 10                                      | 20    |                                                                                                     |  |         | 71973-6210 |         | 71973-6310 |           | 71973-6410 | .900<br>(22.86)                                                                                                           | .995<br>(25.27)  |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 11                                      | 22    |                                                                                                     |  |         | 71973-6211 |         | 71973-6311 |           | 71973-6411 | 1.000<br>(25.40)                                                                                                          | 1.095<br>(27.81) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 12                                      | 24    |                                                                                                     |  |         | 71973-6212 |         | 71973-6312 |           | 71973-6412 | 1.100<br>(27.94)                                                                                                          | 1.195<br>(30.35) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 13                                      | 26    |                                                                                                     |  |         | 71973-6213 |         | 71973-6313 |           | 71973-6413 | 1.200<br>(30.48)                                                                                                          | 1.295<br>(32.89) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 14                                      | 28    |                                                                                                     |  |         | 71973-6214 |         | 71973-6314 |           | 71973-6414 | 1.300<br>(33.02)                                                                                                          | 1.395<br>(35.43) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 15                                      | 30    |                                                                                                     |  |         | 71973-6215 |         | 71973-6315 |           | 71973-6415 | 1.400<br>(35.56)                                                                                                          | 1.495<br>(37.97) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 16                                      | 32    |                                                                                                     |  |         | 71973-6216 |         | 71973-6316 |           | 71973-6416 | 1.500<br>(38.10)                                                                                                          | 1.595<br>(40.51) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 17                                      | 34    |                                                                                                     |  |         | 71973-6217 |         | 71973-6317 |           | 71973-6417 | 1.600<br>(40.64)                                                                                                          | 1.695<br>(43.05) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 18                                      | 36    |                                                                                                     |  |         | 71973-6218 |         | 71973-6318 |           | 71973-6418 | 1.700<br>(43.18)                                                                                                          | 1.795<br>(45.59) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 19                                      | 38    |                                                                                                     |  |         | 71973-6219 |         | 71973-6319 |           | 71973-6419 | 1.800<br>(45.72)                                                                                                          | 1.895<br>(48.13) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 20                                      | 40    |                                                                                                     |  |         | 71973-6220 |         | 71973-6320 |           | 71973-6420 | 1.900<br>(48.26)                                                                                                          | 1.995<br>(50.67) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 21                                      | 42    |                                                                                                     |  |         | 71973-6221 |         | 71973-6321 |           | 71973-6421 | 2.000<br>(50.80)                                                                                                          | 2.095<br>(53.21) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 22                                      | 44    |                                                                                                     |  |         | 71973-6222 |         | 71973-6322 |           | 71973-6422 | 2.100<br>(53.34)                                                                                                          | 2.195<br>(55.75) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 23                                      | 46    |                                                                                                     |  |         | 71973-6223 |         | 71973-6323 |           | 71973-6423 | 2.200<br>(55.88)                                                                                                          | 2.295<br>(58.29) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 24                                      | 48    |                                                                                                     |  |         | 71973-6224 |         | 71973-6324 |           | 71973-6424 | 2.300<br>(58.42)                                                                                                          | 2.395<br>(60.83) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 25                                      | 50    |                                                                                                     |  |         | 71973-6225 |         | 71973-6325 |           | 71973-6425 | 2.400<br>(60.96)                                                                                                          | 2.495<br>(63.37) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 26                                      | 52    |                                                                                                     |  |         | 71973-6226 |         | 71973-6326 |           | 71973-6426 | 2.500<br>(63.50)                                                                                                          | 2.595<br>(65.91) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 27                                      | 54    |                                                                                                     |  |         | 71973-6227 |         | 71973-6327 |           | 71973-6427 | 2.600<br>(66.04)                                                                                                          | 2.695<br>(68.45) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 28                                      | 56    |                                                                                                     |  |         | 71973-6228 |         | 71973-6328 |           | 71973-6428 | 2.700<br>(68.58)                                                                                                          | 2.795<br>(70.99) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 29                                      | 58    |                                                                                                     |  |         | 71973-6229 |         | 71973-6329 |           | 71973-6429 | 2.800<br>(71.12)                                                                                                          | 2.895<br>(73.53) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 30                                      | 60    |                                                                                                     |  |         | 71973-6230 |         | 71973-6330 |           | 71973-6430 | 2.900<br>(73.66)                                                                                                          | 2.995<br>(76.07) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| 31                                      | 62    |                                                                                                     |  |         | 71973-6231 |         | 71973-6331 |           | 71973-6431 | 3.000<br>(76.20)                                                                                                          | 3.095<br>(78.61) |                                         |  |                                                                                                                                                                     |       |                                                                                                                                          |  |                                |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |
| *X* INDICATES TOOLING IS NOT AVAILABLE  |       |                                                                                                     |  |         |            |         |            |           |            | ADD OPTION K & L<br>EC NO: S2010-0534<br>DRWN:SKANG<br>CHKD:ATSEE<br>APPR:MLONG<br>2009/12/30<br>2010/01/08<br>2010/01/14 |                  | QUALITY SYMBOLS<br>▽A=0<br>▽C=0<br>▽P=0 |  | GENERAL TOLERANCES (UNLESS SPECIFIED)<br>mm INCH<br>4 PLACES ± --- ± ---<br>3 PLACES ± --- ± .010<br>2 PLACES ± 0.25 ± ---<br>1 PLACE ± --- ± ---<br>ANGULAR ± 1/2° |       | DIMENSION STYLE<br>IN/MM<br>DRAWN BY DATE<br>DJB 1991/10/21<br>CHECKED BY DATE<br>DJB 1991/10/21<br>APPROVED BY DATE<br>MLONG 2010/01/14 |  | SCALE<br>NTS                   |            | DESIGN UNITS<br>INCH  |            | THIRD ANGLE PROJECTION                                                                                                           |            | TITLE<br>EARLY ENTRY R/A RECPT<br>.120"PC TAIL W/O LOWER<br>ROW PINSTOP-.100" GRID<br>MOLEX INCORPORATED |                  |  |  |
|                                         |       |                                                                                                     |  |         |            |         |            |           |            | K                                                                                                                         |                  | REV                                     |  | DRAFT WHERE APPLICABLE<br>MUST REMAIN<br>WITHIN DIMENSIONS                                                                                                          |       | MATERIAL NO.<br>SEE TABLE                                                                                                                |  | DOCUMENT NO.<br>SDA-71973-**** |            | SHEET NO.<br>25 OF 26 |            | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX<br>INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |            |                                                                                                          |                  |  |  |
| tb_frame_A3_P_AM_T<br>Rev. F 2009/06/18 |       | 9                                                                                                   |  | 8       |            | 7       |            | 6         |            | 5                                                                                                                         |                  | 4                                       |  | 3                                                                                                                                                                   |       | 2                                                                                                                                        |  | 1                              |            |                       |            |                                                                                                                                  |            |                                                                                                          |                  |  |  |

| 10                                     |  |        |  |                |  |  |  |  |  | 9                                                                                                                         |  |  |  |  |  | 8          |  |  |  |  |  | 7          |  |  |  |  |  | 6                                                                              |  |                                       |  |       |  | 5                     |  |               |  |           |  | 4                 |  |                                                                                                 |  |  |  | 3           |  |  |  |  |  | 2          |  |  |  |                                                                                                     |  | 1          |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
|----------------------------------------|--|--------|--|----------------|--|--|--|--|--|---------------------------------------------------------------------------------------------------------------------------|--|--|--|--|--|------------|--|--|--|--|--|------------|--|--|--|--|--|--------------------------------------------------------------------------------|--|---------------------------------------|--|-------|--|-----------------------|--|---------------|--|-----------|--|-------------------|--|-------------------------------------------------------------------------------------------------|--|--|--|-------------|--|--|--|--|--|------------|--|--|--|-----------------------------------------------------------------------------------------------------|--|------------|--|--|--|--|--|------------------|--|------------------|--|--|--|--|--|--|--|-----------|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|----|--|
| NO. OF CKTS                            |  |        |  |                |  |  |  |  |  | OPTION L ASSEMBLY<br>PACKAGED IN TUBES PER PK-70873-0138<br>(SEE SHEET I FOR FINISH SPECIFICATIONS)                       |  |  |  |  |  |            |  |  |  |  |  |            |  |  |  |  |  | DIMENSION                                                                      |  |                                       |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  | NO. OF CKTS |  |  |  |  |  |            |  |  |  | OPTION L ASSEMBLY<br>PACKAGED IN TUBES PER PK-70873-0138<br>(SEE SHEET I FOR FINISH SPECIFICATIONS) |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  | DIMENSION |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| PER ROW TOTAL                          |  |        |  |                |  |  |  |  |  | 15 GOLD                                                                                                                   |  |  |  |  |  | 30 GOLD    |  |  |  |  |  | 50 GOLD    |  |  |  |  |  | A                                                                              |  | B                                     |  |       |  |                       |  | PER ROW TOTAL |  |           |  |                   |  |                                                                                                 |  |  |  | 15 GOLD     |  |  |  |  |  | 30 GOLD    |  |  |  |                                                                                                     |  | 50 GOLD    |  |  |  |  |  | A                |  | B                |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 4 8                                    |  |        |  |                |  |  |  |  |  | 71973-5404                                                                                                                |  |  |  |  |  | 71973-5504 |  |  |  |  |  | 71973-5604 |  |  |  |  |  | .300<br>(7.62)                                                                 |  | .395<br>(10.03)                       |  |       |  |                       |  | 31 62         |  |           |  |                   |  |                                                                                                 |  |  |  | 71973-5431  |  |  |  |  |  | 71973-5531 |  |  |  |                                                                                                     |  | 71973-5631 |  |  |  |  |  | 3.000<br>(76.20) |  | 3.095<br>(78.61) |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 5 10                                   |  |        |  |                |  |  |  |  |  | 71973-5405                                                                                                                |  |  |  |  |  | 71973-5505 |  |  |  |  |  | 71973-5605 |  |  |  |  |  | .400<br>(10.16)                                                                |  | .495<br>(12.57)                       |  |       |  |                       |  | 32 64         |  |           |  |                   |  |                                                                                                 |  |  |  | 71973-5432  |  |  |  |  |  | 71973-5532 |  |  |  |                                                                                                     |  | 71973-5632 |  |  |  |  |  | 3.100<br>(78.74) |  | 3.195<br>(81.15) |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 6 12                                   |  |        |  |                |  |  |  |  |  | 71973-5406                                                                                                                |  |  |  |  |  | 71973-5506 |  |  |  |  |  | 71973-5606 |  |  |  |  |  | .500<br>(12.70)                                                                |  | .595<br>(15.11)                       |  |       |  |                       |  | 33 66         |  |           |  |                   |  |                                                                                                 |  |  |  | 71973-5433  |  |  |  |  |  | 71973-5533 |  |  |  |                                                                                                     |  | 71973-5633 |  |  |  |  |  | 3.200<br>(81.28) |  | 3.295<br>(83.69) |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 7 14                                   |  |        |  |                |  |  |  |  |  | 71973-5407                                                                                                                |  |  |  |  |  | 71973-5507 |  |  |  |  |  | 71973-5607 |  |  |  |  |  | .600<br>(15.24)                                                                |  | .695<br>(17.65)                       |  |       |  |                       |  | 34 68         |  |           |  |                   |  |                                                                                                 |  |  |  | 71973-5434  |  |  |  |  |  | 71973-5534 |  |  |  |                                                                                                     |  | 71973-5634 |  |  |  |  |  | 3.300<br>(83.82) |  | 3.395<br>(86.23) |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 8 16                                   |  |        |  |                |  |  |  |  |  | 71973-5408                                                                                                                |  |  |  |  |  | 71973-5508 |  |  |  |  |  | 71973-5608 |  |  |  |  |  | .700<br>(17.78)                                                                |  | .795<br>(20.19)                       |  |       |  |                       |  | 35 70         |  |           |  |                   |  |                                                                                                 |  |  |  | 71973-5435  |  |  |  |  |  | 71973-5535 |  |  |  |                                                                                                     |  | 71973-5635 |  |  |  |  |  | 3.400<br>(86.36) |  | 3.495<br>(88.77) |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 9 18                                   |  |        |  |                |  |  |  |  |  | 71973-5409                                                                                                                |  |  |  |  |  | 71973-5509 |  |  |  |  |  | 71973-5609 |  |  |  |  |  | .800<br>(20.32)                                                                |  | .895<br>(22.73)                       |  |       |  |                       |  | 36 72         |  |           |  |                   |  |                                                                                                 |  |  |  | 71973-5436  |  |  |  |  |  | 71973-5536 |  |  |  |                                                                                                     |  | 71973-5636 |  |  |  |  |  | 3.500<br>(88.90) |  | 3.595<br>(91.31) |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 10 20                                  |  |        |  |                |  |  |  |  |  | 71973-5410                                                                                                                |  |  |  |  |  | 71973-5510 |  |  |  |  |  | 71973-5610 |  |  |  |  |  | .900<br>(22.86)                                                                |  | .995<br>(25.27)                       |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 11 22                                  |  |        |  |                |  |  |  |  |  | 71973-5411                                                                                                                |  |  |  |  |  | 71973-5511 |  |  |  |  |  | 71973-5611 |  |  |  |  |  | 1.000<br>(25.40)                                                               |  | 1.095<br>(27.81)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 12 24                                  |  |        |  |                |  |  |  |  |  | 71973-5412                                                                                                                |  |  |  |  |  | 71973-5512 |  |  |  |  |  | 71973-5612 |  |  |  |  |  | 1.100<br>(27.94)                                                               |  | 1.195<br>(30.35)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 13 26                                  |  |        |  |                |  |  |  |  |  | 71973-5413                                                                                                                |  |  |  |  |  | 71973-5513 |  |  |  |  |  | 71973-5613 |  |  |  |  |  | 1.200<br>(30.48)                                                               |  | 1.295<br>(32.89)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 14 28                                  |  |        |  |                |  |  |  |  |  | 71973-5414                                                                                                                |  |  |  |  |  | 71973-5514 |  |  |  |  |  | 71973-5614 |  |  |  |  |  | 1.300<br>(33.02)                                                               |  | 1.395<br>(35.43)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 15 30                                  |  |        |  |                |  |  |  |  |  | 71973-5415                                                                                                                |  |  |  |  |  | 71973-5515 |  |  |  |  |  | 71973-5615 |  |  |  |  |  | 1.400<br>(35.56)                                                               |  | 1.495<br>(37.97)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 16 32                                  |  |        |  |                |  |  |  |  |  | 71973-5416                                                                                                                |  |  |  |  |  | 71973-5516 |  |  |  |  |  | 71973-5616 |  |  |  |  |  | 1.500<br>(38.10)                                                               |  | 1.595<br>(40.51)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 17 34                                  |  |        |  |                |  |  |  |  |  | 71973-5417                                                                                                                |  |  |  |  |  | 71973-5517 |  |  |  |  |  | 71973-5617 |  |  |  |  |  | 1.600<br>(40.64)                                                               |  | 1.695<br>(43.05)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 18 36                                  |  |        |  |                |  |  |  |  |  | 71973-5418                                                                                                                |  |  |  |  |  | 71973-5518 |  |  |  |  |  | 71973-5618 |  |  |  |  |  | 1.700<br>(43.18)                                                               |  | 1.795<br>(45.59)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 19 38                                  |  |        |  |                |  |  |  |  |  | 71973-5419                                                                                                                |  |  |  |  |  | 71973-5519 |  |  |  |  |  | 71973-5619 |  |  |  |  |  | 1.800<br>(45.72)                                                               |  | 1.895<br>(48.13)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 20 40                                  |  |        |  |                |  |  |  |  |  | 71973-5420                                                                                                                |  |  |  |  |  | 71973-5520 |  |  |  |  |  | 71973-5620 |  |  |  |  |  | 1.900<br>(48.26)                                                               |  | 1.995<br>(50.67)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 21 42                                  |  |        |  |                |  |  |  |  |  | 71973-5421                                                                                                                |  |  |  |  |  | 71973-5521 |  |  |  |  |  | 71973-5621 |  |  |  |  |  | 2.000<br>(50.80)                                                               |  | 2.095<br>(53.21)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 22 44                                  |  |        |  |                |  |  |  |  |  | 71973-5422                                                                                                                |  |  |  |  |  | 71973-5522 |  |  |  |  |  | 71973-5622 |  |  |  |  |  | 2.100<br>(53.34)                                                               |  | 2.195<br>(55.75)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 23 46                                  |  |        |  |                |  |  |  |  |  | 71973-5423                                                                                                                |  |  |  |  |  | 71973-5523 |  |  |  |  |  | 71973-5623 |  |  |  |  |  | 2.200<br>(55.88)                                                               |  | 2.295<br>(58.29)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 24 48                                  |  |        |  |                |  |  |  |  |  | 71973-5424                                                                                                                |  |  |  |  |  | 71973-5524 |  |  |  |  |  | 71973-5624 |  |  |  |  |  | 2.300<br>(58.42)                                                               |  | 2.395<br>(60.83)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 25 50                                  |  |        |  |                |  |  |  |  |  | 71973-5425                                                                                                                |  |  |  |  |  | 71973-5525 |  |  |  |  |  | 71973-5625 |  |  |  |  |  | 2.400<br>(60.96)                                                               |  | 2.495<br>(63.37)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 26 52                                  |  |        |  |                |  |  |  |  |  | 71973-5426                                                                                                                |  |  |  |  |  | 71973-5526 |  |  |  |  |  | 71973-5626 |  |  |  |  |  | 2.500<br>(63.50)                                                               |  | 2.595<br>(65.91)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 27 54                                  |  |        |  |                |  |  |  |  |  | 71973-5427                                                                                                                |  |  |  |  |  | 71973-5527 |  |  |  |  |  | 71973-5627 |  |  |  |  |  | 2.600<br>(66.04)                                                               |  | 2.695<br>(68.45)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 28 56                                  |  |        |  |                |  |  |  |  |  | 71973-5428                                                                                                                |  |  |  |  |  | 71973-5528 |  |  |  |  |  | 71973-5628 |  |  |  |  |  | 2.700<br>(68.58)                                                               |  | 2.795<br>(70.99)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 29 58                                  |  |        |  |                |  |  |  |  |  | 71973-5429                                                                                                                |  |  |  |  |  | 71973-5529 |  |  |  |  |  | 71973-5629 |  |  |  |  |  | 2.800<br>(71.12)                                                               |  | 2.895<br>(73.53)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 30 60                                  |  |        |  |                |  |  |  |  |  | 71973-5430                                                                                                                |  |  |  |  |  | 71973-5530 |  |  |  |  |  | 71973-5630 |  |  |  |  |  | 2.900<br>(73.66)                                                               |  | 2.995<br>(76.07)                      |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| "X" INDICATES TOOLING IS NOT AVAILABLE |  |        |  |                |  |  |  |  |  | ADD OPTION K & L<br>EC NO: S2010-0534<br>2009/12/30<br>DRWN:SKANG<br>CHKD:ATSEE<br>2010/01/08<br>APPR:MLONG<br>2010/01/14 |  |  |  |  |  |            |  |  |  |  |  |            |  |  |  |  |  | QUALITY SYMBOLS<br>F <sub>A</sub> =0<br>F <sub>B</sub> =0<br>F <sub>P</sub> =0 |  | GENERAL TOLERANCES (UNLESS SPECIFIED) |  |       |  | DIMENSION STYLE IN/MM |  |               |  | SCALE NTS |  | DESIGN UNITS INCH |  | THIRD ANGLE PROJECTION                                                                          |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
|                                        |  |        |  |                |  |  |  |  |  |                                                                                                                           |  |  |  |  |  |            |  |  |  |  |  |            |  |  |  |  |  |                                                                                |  | mm                                    |  | INCH  |  | DRAWN BY DATE         |  | TITLE         |  |           |  |                   |  | EARLY ENTRY R/A RECPT<br>.120"PC TAIL W/O LOWER<br>ROW PINSTOP-.100" GRID<br>MOLEX INCORPORATED |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
|                                        |  |        |  |                |  |  |  |  |  |                                                                                                                           |  |  |  |  |  |            |  |  |  |  |  |            |  |  |  |  |  |                                                                                |  | 4 PLACES ± --- ± ---                  |  | ± --- |  | CHECKED BY DATE       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |    |  |
| 3 PLACES ± --- ± .010                  |  | ± .010 |  | DJB 1991/10/21 |  |  |  |  |  |                                                                                                                           |  |  |  |  |  |            |  |  |  |  |  |            |  |  |  |  |  |                                                                                |  |                                       |  |       |  |                       |  |               |  |           |  |                   |  |                                                                                                 |  |  |  |             |  |  |  |  |  |            |  |  |  |                                                                                                     |  |            |  |  |  |  |  |                  |  |                  |  |  |  |  |  |  |  |           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  | </ |  |





# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

71973-1027