


ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE
	D	ECR # 101126-5 ADD NUT	11/26/10'



NOTE:

- CABLE: UL-2919 28AWG(7/0.127 T.C)*3COAX INS:FO-PE+SPIRAL JACKET:PVC
 OD: ϕ 2.5 $\pm$ 0.15mm COLOR: RED, GRAY, BLUE+28AWG(7/0.127 T.C)*8C
 INS: PVC+AL/MYLAR+D.W+BRAID SHIELD(85%)COVERAGE+OUTER
 JACKET: MATTED PVC, COLOR: BLACK(NK-K01) OD: ϕ 8.5 $\pm$ 0.2mm, (C2919365-1)
- CONNECTOR:
 P1: HDB15P MALE, GOLD FLASH CONTACT, NICKEL PLATED SHELL
 (THE 9TH PIN UNLOAD)
 P2: HDB15P FEMALE, GOLD FLASH CONTACT, NICKEL PLATED SHELL
- SHIELD: COPPER-FOIL 360° SOLDERED TO CONNECTOR SHELL & CABLE BRAID
- HOOD: MOLDED TYPE, PVC 45P, COLOR: BLACK(NK-K01)
- ELECTRICAL TEST: <1>. 100% OPEN SHORT & MIS WIRE TEST
 <2>. CONTACT RESISTANCE 3 Ohms MAX
 <3>. INSULATION RESISTANCE 10M Ohms MIN
- PACKING: EACH PC / BLISTER(K) + BACK CARD (Maxxtro VGA Cable) + LABEL.

PIN OUT			
P1		P2	
1	RED	10	ORANGE
6		11	WHITE
2	GREY	12	YELLOW
7		13	GREEN
3	BLUE	14	RED
8		15	BLUE
4	BROWN	4	SHELL BRAID SHELL
5	BLACK	5	CENTER SHIELDING

Tolerance	Inch	M/M
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05

Maxxtro®

Title
HDB15/M - HDB15/F CABLE


Customer P/N:
App'd *Dmy* Customer T-JPC

Scale NONE Units m/m Third Angle Projection


Dwg No. 120-3270 REV: D Sheet 1/2

120-3270-2	100641	4000 $\pm$ 50	7612320116700	LABEL 2
120-3270-1	100636	3000 $\pm$ 30	7612320116694	LABEL 1
DWG	P/N	L±T(mm)	BAR CODE	LABEL


BACK CARD



LABEL 1



LABEL 2



Tolerance	Inch	M/M
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05

Draw
FANNIE 11/26/10'
Chck
Engr

Maxxtro®			
Title HDB15/M - HDB15/F CABLE			
Customer P/N:			
App'd	Customer	T-JPC	
Scale	NONE	Units	m/m
Dwg No.	120-3270	REV	D
Sheet	2/2		