# **D** Series

# High Voltage relays 10kV & 15kV



Very high isolation voltages, up to 15kV, are achieved through the use of high vacuum reed switches with either Rhodium or Tungsten contacts and make these relays suitable for high reliability applications, such as cardiac defibrillators, test equipment and high voltage power supplies.

The Rhodium contact relays have low contact resistance, while the Tungsten contact relays can switch higher voltages.

PCB or Panel Mount, via Nylon studs, versions are available.

Connection options, for the HV, include PCB, solder turret(wire wrap), flying lead and 0.25" spade terminals.

- 10kV or 15kV Isolation
- Low Contact Resistance
- PCB or Panel Mount
- HV connections via Flying Leads, Solder Turret (wire wrap), or 1/4" Spade Terminals
- Excellent AC characteristics

<b>Contact Specification</b>	Unit Condition	10kV SPNO			10kV SPNC			15kV SPNO		
Contact Material Isolation across contact Switching Power Max. Switching Voltage Max. Switching Current Max. Carry Current Max	ts kV DC or AC peak W V DC or AC peak		um Tun 10 50 700 2		Rhodium 10 50 1000 3 4		sten		gsten	
Capacitance across contacts Lifetime operations Contact Resistance Insulation Resistance Coil Specification	pF coil to screen grounded dry switching 50W switching mΩ max (typical) Ωmin (typical)	<0.2 10° 10° 50 (15° 10¹0 (			<0.2 10° 10° 50 (15) 10¹0 ( 5V	<0.2  10 <sup>9</sup> 10 <sup>6</sup> 250(10 10 <sup>13</sup> )	0) <b>24V</b>		(100) 100) 12V	24V
Must Operate Voltage Must Release Voltage Operate Time Release Time Resistance Relay Specification	$\begin{array}{ll} \text{V} & \text{DC} \\ \text{V} & \text{DC} \\ \text{ms} & \text{diode fitted} \\ \text{ms} & \text{diode fitted} \\ \end{array}$	3.7 0.5 3.0 2.0 28	9 1.25 3.0 2.0 150	20 4 3.0 2.0 780	3.7 0.5 2.0 3.0 38	9 1.25 2.0 3.0 240	20 4 2.0 3.0 925	3.7 0.5 3.0 2.0 16	9 1.25 3.0 2.0 95	20 4 3.0 2.0 350
Isolation contact/coil Insulation resistance co to all terminals Envirnonmental Operating Temp range	kV ontact Ωmin (typical) °C	17 10 <sup>10</sup> (10 <sup>13</sup> ) -20 to +70		17 10 <sup>10</sup> (10 <sup>13</sup> ) -20 to +70			17 10 <sup>10</sup> (10 <sup>13</sup> ) -20 to +70			

<u>Please refer to this document for circuit design notes:-</u> http://www.cynergy3.com/blog/application-notes-reed-relays-0

# **Part Numbering System**

Contact Form A=n/o, B=n/c
Contact Material
R=Rhodium,
T=Tungsten
Moulding Ref. No.
Coil Voltage
05=5Vdc, 12=12Vdc,
24=24Vdc
Isolation between
Contacts
10=10kV, 15=15kV

**Mounting or Connection Style** 

No suffix indicates PCB mount F=PCB mount & coil connection with Flying lead HV connection P=Panel mount with wire wrap terminals S=PCB mount & coil connection with stud fixing & 1/4" spade HV connection (not available on 15kV models)

T=PCB mount & coil connection with stud fixing & wire wrap HV connection

www.cynergy3.com

Cynergy3 Components Ltd.
7 Cobham Road
Ferndown Industrial Estate
Wimborne, Dorset BH21 7PE
Telephone +44 (0) 1202 897969
Email:sales@cynergy3.com


ISO9001 CERTIFIED

D 2016




# **MECHANICAL**

#### **STANDARD**




#### PANEL MOUNT

(e.g. DAT71210P)




#### **FLYING LEAD**



TURRET (Wire Wrap)

(e.g. DAT71210T)




NOTE: PINS WHICH ARE NOT NUMBERED HAVE NO ELECTRICAL CONNECTION.

NOTE: PINS WHICH ARE NOT NUMBERED HAVE NO ELECTRICAL CONNECTION.

### **SPADE TYPE**

(e.g. DAT71210S)

'S' Suffix denotes the 0.250" 'Push On' blade connectors, M4 fixing bolts and Epoxy potting.



Cynergy3 Components Ltd.
7 Cobham Road
Ferndown Industrial Estate
Wimborne, Dorset BH21 7PE
Telephone +44 (0) 1202 897969
Email:sales@cynergy3.com

<u>Please refer to this document for circuit design notes:-</u> http://www.cynergy3.com/blog/application-notes-reed-relays-0

www.cynergy3.com