

FEATURES:

- Connector accepts cable types RG/U: 58, 58A, 58C, 141, 141A, 142, 142A, 142B, 223
- Meets interface requirements of MIL-STD-348

MATERIALS:

Body and Fittings – Brass
Outer Contact – Brass
Center Contact – Gold Plated Brass
Dielectric – PTFE
Gasket – Silicone Rubber

Finish:

Body – Tarnish Resistant
Outer Contact – Tarnish Resistant
Center Contact – Gold Plated

Marking: POMONA 4488

RATINGS:

Operating Voltage: 500 VRMS
Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 4488

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA




FIGURE #1

A. Strip cable jacket and dielectric to dimensions shown.

FIGURE #2

B. Slide clamp nut, flat washer and gasket over end of cable.
C. Fray cable braid and slide braid clamp over end of cable flush with end of cable jacket.

FIGURE #3

D. Solder or crimp contact onto center conductor.
E. Fold braid back over braid clamp and trim even with braid clamp.

FIGURE #4

F. Slide clamp nut, flat washer and gasket forward against braid clamp.
G. Thread body onto clamp nut and tighten 35-40 inch-pounds.

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4488](#)