





CODE NO.	CONTACT	A	B	C	D	E	F	G	H
CL683-0255-8-57	26	11.5	8.3	7	6	11.3	9.7	11.9	9.1
CL683-0270-1-57	30	12.5	9.3	8	7	12.3	10.7	12.9	10.1
CL683-0363-0-57	60	20	16.8	15.5	14.5	19.8	18.2	20.4	17.6
CL683-0395-7-57	70	22.5	19.3	18	17	22.3	20.7	22.9	20.1
CL683-0371-9-57	80	25	21.8	20.5	19.5	24.8	23.2	25.4	22.6

NOTES 1 : LEAD CO-PLANARITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1mm MAX.
2 IF THE RESIST PROCESSING HAS NOT MADE, IT HAS POSSIBILITY THAT THE TERMINAL TOUCHES WITH AREA. PLEASE BE NOTED THIS POINT.

			7	PS	CLEAR (REINFORCEMENT COLLAR)								
			6	PS	BLACK (PLASTIC REEL)								
2	POLYAMIDE (PA6T)	WHITE BEIGE , UL94V-0	5	POLYESTER	CLEAR (COVER TAPE)								
1	PHOSPHER BRONZE	CONTACT AREA : GOLD PLATED 0.1μm min LEAD AREA : GOLD PLATED 0.02μm min UNDER PLATING : NICKEL 1μm min	4	PS	CLEAR (EMBOSSED CARRIER TAPE)								
			3	PHOSPHER BRONZE	TIN PLATED 1μm min UNDER PLATING : NICKEL 1μm min								
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS								
UNITS mm			SCALE 5 : 1		COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED		DATE	
 HIROSE ELECTRIC CO. , LTD.			APPROVED : KH. IKEDA		11. 12. 19		DRAWING NO. EDC3-162763-77						
			CHECKED : TS. MIYAZAKI		11. 12. 19		PART NO. DF17B(3. 0H) - *DS-0. 5V(57)						
			DESIGNED : TR. YUNOKI		11. 12. 19		CODE NO. CL683						
			DRAWN : MS. SATO		11. 12. 19		 1/2						

