

103-016
75%/25% Blended Composite DuPont Aracon®/Metal
EMI/RFI Braided Shielding



Composite
Shielding

103-016-008
Product Series
Tubular Braid Size (Table I)




TABLE I: TUBULAR BRAID SIZE ORDER NUMBER							
Braid Size	Nominal I.D.	Wire Bundle Accomodation Range Ref.				Approx. Weight Per 100 Feet	
		Min.		Max.		Pounds	Grams
008	.250 (6.4)	.125 (3.2)		.317 (8.1)		.530	240.0
016	.500 (12.7)	.250 (6.4)		.625 (15.9)		1.100	499.0
024	.750 (19.1)	.500 (12.7)		.875 (22.2)		1.580	717.0
032	1.000 (25.4)	.812 (20.6)		1.187 (30.2)		2.420	1100.0
040	1.250 (31.8)	.938 (23.8)		1.312 (33.3)		3.780	1710.0
048	1.500 (38.1)	1.187 (30.1)		1.625 (41.3)		5.550	2520.0

Material: NiCu wire 36 AWG/nickel clad Aracon®
Metric dimensions (mm) are indicated in parentheses.

Aracon® is a registered trademark of DuPont Corporation.