



UNCONTROLLED DOCUMENT



NOTES:

1. ANODE
2. CATHODE
3. EMITTER
4. COLLECTOR



PART NUMBER
OCP-PCT114/X

REV.

REV. E.C.N. NUMBER AND REVISION COMMENTS

DATE

CAUTION: STATIC SENSITIVE DEVICE
FOLLOW PROPER E.S.D. HANDLING PROCEDURES
WHEN WORKING WITH THIS PART.



PART NUMBER TABLE	
PART=	CTR (%)
/X	
/A	60 TO 160
/B	130 TO 260
/C	200 TO 400
/D	300 TO 600
/E	60 TO 600

ABSOLUTE MAXIMUM RATINGS (Ta=25°C)				
	PARAMETER	SYMBOL	MAX	UNITS
I	FORWARD CURRENT	If	50	mA
	PEAK FORWARD CURRENT	Ifm	1	A
	REVERSE VOLTAGE	Vr	6	V
	POWER DISSIPATION	Pd	70	mW
O	COLLECTOR-EMITTER VOLTAGE	Vceo	60	V
	EMITTER-COLLECTOR VOLTAGE	Veco	6	V
	COLLECTOR CURRENT	Ic	50	mA
	COLLECTOR POWER DISSIPATION	Pc	150	mW
	TOTAL POWER DISSIPATION	Ptot	200	mW
	ISOLATION VOLTAGE 1 MIN.	Viso	5000	V RMS
	OPERATING TEMPERATURE	Topr	- 30 TO + 100	°C
	STORAGE TEMPERATURE	Tstg	- 55 TO + 125	°C
	SOLDERING TEMPERATURE	Tsol	+ 260	°C
	2.0mm FROM BODY		10 SEC. MAX	

I=INPUT, O=OUTPUT.

ELECTRO-OPTICAL CHARACTERISTICS (Ta=25°C)						
	PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX UNITS
I	FORWARD VOLTAGE	Vf	If=20mA	-	1.2	1.4 V
	PEAK FORWARD VOLTAGE	Vfm	Ifm=0.5A	-	-	3.5 V
	REVERSE CURRENT	Ir	Vr=4V	-	-	10 µA
	TERMINAL CAPACITANCE	Ct	V=0, f=1kHz	-	30	- pF
O	COLLECTOR DARK CURRENT	Iceo	Vce=20V	-	-	10 ⁻⁷ A
T	CURRENT TRANSFER RATIO	CRT	If=2mA, Vce=5V	60	-	600 %
	COLLECTOR-EMITTER SATURATION VOLTAGE	Vce(sat)	If=20mA, Ic=1mA	-	0.1	0.3 V
	ISOLATION RESISTANCE	Riso	DC500V	5x10 ¹⁰	10 ¹¹	- ohm
	FLOATING CAPACITANCE	Cf	V=0, f=1MHz	-	0.6	1.0 pF
	CUT-OFF FREQUENCY	fc	Vce=5V, Ic=2mA, RL=100ohm	-	80	- kHz
	RESPONSE TIME (RISE)	tr	Vce=5V, Ic=2mA, RL=100ohm	-	5	20 µS
	RESPONSE TIME (FALL)	tf	Vce=5V, Ic=2mA, RL=100ohm	-	4	20 µS

I=INPUT, O=OUTPUT, T=TRANSFER CHARACTERISTICS.

UNCONTROLLED DOCUMENT

*UNLESS OTHERWISE SPECIFIED TOLERANCE IS ±0.25mm (±0.010")

REV.

PART NUMBER
OCP-PCT114/X

CONFIDENTIAL INFORMATION
THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

RELIABILITY NOTE
OUR MANY YEARS OF EXPERIENCE DATA ACCUMULATION INDICATE THAT SOLDER HEAT IS A MAJOR CAUSE OF EARLY AND FUTURE FAILURE. PLEASE PAY ATTENTION TO YOUR SOLDERING PROCESS.

LUMEX
INCORPORATED

290 E. HELLEN ROAD
PALATINE, ILLINOIS 60067
PHONE: 1-847-359-2790
WEB: HTTP://WWW.LUMEX.COM

DRAWN BY: CHECKED BY: APPROVED BY: DATE: 9-29-99

PAGE: 1 OF 1

SCALE: N/A

FOUR PIN DIP SINGLE CHANNEL PHOTOCOUPLER,
TRANSISTOR OUTPUT, NO EXTERNAL BASE CONNECTION.

CK/DU

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumex:

[OCP-PCT114/E-TR](#)