


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
DF	S0	P	LTR	DESCRIPTION	DATE	APVD
			L	REV PER ECO-05-014991	01FEB06	PY DE



- $\triangle 1$ TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = $\pm .12$ [± 3.0]
24 INCHES [609.6] & UP = $\pm 1\%$
2. MARKED PER MIL-STD-130.
3. TO MATE WITH AMP LGH-1/2
RECEPTACLE WITH .53 [13.4] BARREL DEPTH.
- $\triangle 4$ PIGTAIL IS SOLDER DIPPED
5. OPERATING VOLTAGE: 10 KVDC AT 0 TO 70,000 FEET, -55° C TO 125° C.
- $\triangle 6$ INSULATION CUT BUT NOT REMOVED

OBSOLETE OBSOLETE	6	107-022-0001	.39 [9.9]	.38 [9.7]	12.00 [304.8]	5-848407-2
	6	107-022-0001	.32 [8.1]	.38 [9.7]	16.00 [406.4]	5-848407-1
	4	-	.32 [8.1]	.38 [9.7]	60.00 [1524.0]	848407-4
	4	-	.32 [8.1]	.38 [9.7]	36.00 [914.4]	848407-3
	4	107-022-0001	.39 [9.9]	.38 [9.7]	12.00 [304.8]	848407-2
	4	107-022-0001	.32 [8.1]	.38 [9.7]	16.00 [406.4]	848407-1
REMARKS		CUSTOMER P/N INK STAMPED	C MAX	B 4 6	A 1	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 12-19-89 C.C.THOMAS		tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK 4-30-90 D.EABY			
		0 PLC ± -		APVD -		NAME LEAD ASS'Y, SGL. MOLDED END, LGH-1/2 WITH #20 AWG WIRE -	
		1 PLC ± -		PRODUCT SPEC			
		2 PLC ± .02 [0.5]		-			
		3 PLC ± -		APPLICATION SPEC			
		4 PLC ± -		-		SIZE	
		ANGLES ± -		-		CAGE CODE	
MATERIAL SEE CALLOUTS		FINISH -		WEIGHT -		DRAWING NO	
				CUSTOMER DRAWING		RESTRICTED TO	
				SCALE 4:1		SHEET 1 OF 1	
				REV L			