

Coaxial SMA Fixed Attenuator

50Ω 2W 30dB DC to 6000 MHz

VAT-30W2+ VAT-30W2



CASE STYLE: DC1066

Connectors	Model	Price	Qty.
SMA	VAT-30W2(+)	\$15.95 ea.	(1-9)
		\$12.45 ea.	(10-49)

+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.

Maximum Ratings

Operating Temperature	-45°C to 100°C
Storage Temperature	-55°C to 100°C


Features

- wideband coverage, DC to 6000 MHz
- 2 watt rating
- rugged unibody construction
- off-the-shelf availability
- very low cost

Applications

- impedance matching
- signal level adjustment

Outline Drawing



Outline Dimensions (inch/mm)

B	D	E	wt
.74	1.43	.312	grams
18.80	36.32	7.92	11.4

Electrical Specifications

FREQ. RANGE (MHz)	ATTENUATION * (dB)					VSWR (:1)					MAX. INPUT POWER (W)
	Flatness **										
	DC-3 GHz	3-5 GHz	5-6 GHz	DC-6 GHz		DC-3 GHz	3-5 GHz	5-6 GHz			
f_L-f_U	Nom.	Typ.	Typ.	Typ.	Typ.	Typ.	Max.	Typ.	Max.	Typ.	
DC-6000	30±0.3	0.70	0.45	0.20	1.30	1.25	1.35	1.45	1.70	1.60	2.0

* Attenuation varies by 0.3 dB max. over temperature.

** Flatness= variation over band divided by 2.

Typical Performance Data

Frequency (MHz)	Attenuation (dB)	VSWR (:1)
10.00	30.04	1.00
100.00	30.04	1.00
1000.00	29.72	1.04
2000.00	29.22	1.09
3000.00	28.80	1.16
4000.00	28.46	1.24
4500.00	28.22	1.30
5000.00	27.98	1.37
5500.00	27.87	1.46
6000.00	27.69	1.57

