



Rev	AWO #	Description	Date	Appr
-		RELEASED	11/08/04	



654321

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED
PCB LAYOUT



SPECIFICATIONS:

Material:
Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator Color: Black
Contacts: Phosphor Bronze
Plating:
Tin over Copper underplate overall
Electrical:
Operating voltage: 250 VAC max
Current rating: 1 Amp max
Contact resistance: 20 mohms max
Insulation resistance: 5000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 1000 VAC for 1 minute
Temperature Rating:
Operating temperature: -55°C to +105°C
Packaging:
Anti-ESD plastic tubes

A = .100 [2.54] X No. of Positions Per Row

Positions available: 6, 8, 14, 16, 18, 20, 24 & 26

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
INCHES .X ± .10 .XX ± .020 .XXX ± .015		HOLES ØX ± .10 ØXX ± .015 ØXXX ± .010	
APPROVALS		DATE	
DRAWN	SS	11/08/04	
CHECKED			
APPROVED			
TITLE		IC SOCKET, .300 ROW CENTERS, PCB,	
TIN PLATED			
SIZE	PART NO.	REV.	
X	ICS-3XX-T	-	
REF:	SCALE: NTS	SHEET 1 OF 1	