



© COPYRIGHT 2012 BY INDUSTRIAL FIBER OPTICS, INC.
ALL RIGHTS RESERVED.





2.0 [0.08"]
1.0 [0.04"]
STRIP LENGTH

- NOTES:
1. RoHS COMPLIANT
 2. UL94 HB FLAMMABILITY RATING
 3. -40° C TO 85° C OPERATING TEMPERATURE
 4. SUITABLE FOR 2.2mm OR 3mm JACKETED LIGHT PIPE WITH A FIBER DIAMETER UP TO 1.5mm
 5. DO NOT WAVE SOLDER WITH THIS DEVICE
 6. FOR BEST RESULTS USE ONLY NARROW VIEWING ANGLE NON-DIFFUSED LEDs WITH OUTPUT POWER GREATER THAN 100mcd
 7. NOT RECOMMENDED FOR DATA COMMUNICATIONS



METRIC

REVISIONS					
REV	DESCRIPTION	ECO	DATE	DWN	APVD
A	Initial release		1/3/2012	BB	AR



UNLESS OTHERWISE SPECIFIED		PRODUCT		Industrial Fiber Optics TEMPE, AZ 85281					
DIMENSIONS		MATERIAL							
MILLIMETERS [IN.]		Black Nylon 6/6		NAME T1-3/4 LED Cap					
TOLERANCES		FINISH							
0 PLC: ± 1		DRAWN BY							
1 PLC: ± .25		DATE							
2 PLC: ± .127		CHECKED BY							
3 PLC: ± .025		A. Reyes		SIZE A					
4 PLC: ± .013		DATE							
ANGLE: ± 1/2°		1/3/2012		SCALE 2:1		PART NUMBER 51 0322		REV A	
REMOVE BURRS AND SHARP EDGES		DATE		DO NOT SCALE DRAWING				Sheet 1 of 1	
FLATNESS .005mm PER mm		1/3/2012							
ALL DIMENSIONS AFTER FINISH									

SIZE	SCALE	PART NUMBER	REV
A	2:1	51 0322	A
DO NOT SCALE DRAWING		Sheet 1 of 1	