

MT-72000 SERIES

Secondary Furnished TH Inductors

MINNTRONIX

Wind Up the Best®




Phone: 1.605.884.0195
Fax: 1.605.884.0199
www.minntronix.com



- 2500Vrms Primary to Secondary Hi-pot
- Frequency range 20kHz to 200kHz
- Encapsulated construction

Mechanical Dimensions:



Electrical Specifications at 25°C - Operating Temperature -25°C to +125°C

Part Number	Schematic Figure	Secondary Turns	Secondary Inductance (mH min)	Secondary Inductance Test Voltage 15.75KHz	Secondary DCR (Ω max)	Secondary Rated Terminating Resistance (Ω nom)	Primary Unipolar (amp-us) Rating (max)	Primary Bipolar (amp-us) Rating (max)	1 Turn Primary Peak Sense Current (Amps)
MT-72001	A	50	5.0	0.5	0.7	50	150	300	20
MT-72002	A	100	20.0	1.0	1.40	100	300	600	20
MT-72003	A	200	80.0	2.0	4.50	200	600	1200	20
MT-72004	A	300	180.0	3.0	11.0	300	900	1800	20
MT-72005	B	50CT	5.0	0.5	0.7	50	150	300	20
MT-72006	B	100CT	20.0	1.0	1.40	100	300	600	20
MT-72007	B	200CT	80.0	2.0	4.50	200	600	1200	20
MT-72008	B	300CT	180.0	3.0	11.0	300	900	1800	20

MT-72100 SERIES

MINNTRONIX

Wind Up the Best®







Phone: 1.605.884.0195
Fax: 1.605.884.0199
www.minntronix.com

Primary and Secondary Furnished TH Transformers



- Encapsulated with plastic housing and potting
- 3750Vrms Primary to Secondary Hi-pot
- Frequency range 20kHz to 200kHz

Mechanical Dimensions:



UNIT : Inch (mm)

Electrical Specifications at 25°C - Operating Temperature -25°C to +125°C

Part Number	Schematic Figure	Secondary Turns	Secondary Inductance (mH min)	Secondary Inductance Test Voltage 15.75KHz	Secondary DCR (Ω max)	Secondary Rated Terminating Resistance (Ω nom)	Primary Unipolar (amp-us) Rating (max)	Primary Bipolar (amp-us) Rating (max)	1 Turn Primary Peak Sense Current (Amps)
MT-72101	A	50	5.0	0.5	0.7	50	150	300	20
MT-72102	A	100	20.0	1.0	1.40	100	300	600	20
MT-72103	A	200	80.0	2.0	4.50	200	600	1200	20
MT-72104	A	300	180.0	3.0	11.0	300	900	1800	20
MT-72105	B	50CT	5.0	0.5	0.7	50	150	300	20
MT-72106	B	100CT	20.0	1.0	1.40	100	300	600	20
MT-72107	B	200CT	80.0	2.0	4.50	200	600	1200	20
MT-72108	B	300CT	180.0	3.0	11.0	300	900	1800	20

Specifications subject to change. Custom versions of any Minntronix products are available upon request.

MT-72200 SERIES

Epoxy Coated Inductors

MINNTRONIX

Wind Up the Best®






Phone: 1.605.884.0195
Fax: 1.605.884.0199
www.minntronix.com



- 2500Vrms primary to secondary Hi-pot
- Frequency range 20kHz to 200kHz
- Epoxy coated construction

Mechanical Dimensions:



UNIT : Inch (mm)

Electrical Specifications at 25°C - Operating Temperature -25°C to +125°C

Part Number	Secondary Turns	Secondary Inductance (mH min)	Secondary Inductance Test Voltage 15.75KHz	Secondary DCR (Ω max)	Secondary Rated Terminating Resistance (Ω nom)	Primary Unipolar (amp•us) Rating (max)	Primary Bipolar (amp•us) Rating (max)	1 Turn Primary Peak Sense Current (Amps)
MT-72201	50	5.0	0.5	0.7	50	150	300	20
MT-72202	100	20.0	1.0	1.40	100	300	600	20
MT-72203	200	80.0	2.0	4.50	200	600	1200	20
MT-72204	300	180.0	3.0	11.0	300	900	1800	20

Specifications subject to change. Custom versions of any Minntronix products are available upon request.

MT-72200 SERIES

MT-72300 SERIES

SMD Current Sense Transformers

MINNTRONIX





Wind Up the Best®




Phone: 1.605.884.0195
Fax: 1.605.884.0199
www.minntronix.com

- Compatible with surface mount board assembly processes
- Optimal performance at 100kHz and above
- Primary rated for 6 Amps AC
- Custom designs available

Mechanical Dimensions:



RECOMMENDED PCB LAYOUT



UNIT : Inch (mm)

Electrical Specifications at 25°C—Operating Temperature -25°C to +125°C

Part Number	Turns Ratio Pri : Sec	Secondary Inductance at 10KHz 0.1V (uH min)	Secondary DCR (Ω max)	Primary Current max (Amps)	Hi-pot (Vrms)
MT-72301	1:70	980	4.75	6	500
MT-72302	1:40	320	1.14	6	500
MT-72303	1:30	180	0.87	6	500
MT-72304	1:20	80	0.55	6	500
MT-72305	1:50	500	1.50	6	500
MT-72306	1:60	720	1.75	6	500
MT-72307	1:100	2000	5.50	6	500
MT-72308	1:125	3000	6.50	6	500

Specifications subject to change. Custom versions of any Minntronix products are available upon request.

MT-72300A_{SERIES}

SMD Current Sense Transformers

MINNTRONIX




Wind Up the Best®




Phone: 1.605.884.0195
Fax: 1.605.884.0199
www.minntronix.com



- Surface mount board assembly process applicable
- Designed for switch power supply applications
- Optimal performance at 100kHz and above
- Primary rated for 6 Amps AC
- Special design available on customer request



(BOTTOM VIEW)



RECOMMENDED PCB LAYOUT


UNIT : Inch (mm)

Electrical Specifications at 25°C — Operating Temperature -25°C to +125°C

Part Number	Turns Ration Pri : Sec	Secondary Inductance At 10KHz, 0.1V (uH min)	Secondary DCR 20°C (Ω max)	Primary Current max (Amps)	Hi-pot (Vrms)
MT-72301A	1:70	980	4.75	6	500
MT-72302A	1:40	320	1.14	6	500
MT-72303A	1:30	180	0.87	6	500
MT-72304A	1:20	80	0.55	6	500
MT-72305A	1:50	500	1.50	6	500
MT-72306A	1:60	720	1.75	6	500
MT-72307A	1:100	2000	5.50	6	500
MT-72308A	1:125	3000	6.50	6	500


Specifications subject to change. Custom versions of any Minntronix products are available upon request.

MT-72300A_{SERIES}



- Low profile - height 4.1mm max
- Designed for automatic pick and place
- Operating frequency range 10kHz to 1MHz
- Primary rated for 20 Amps AC
- Custom design available on customer request

Mechanical Dimensions:



RECOMMENDED PCB LAYOUT UNIT : Inch (mm)

Electrical Specification at 25°C—Operating temperature -25°C to +125°C

Part Number	Secondary ¹ Inductance (uH min)	Secondary DCR 20°C (Ω max)	Turn Ratio (Pri : Sec)	Hi-pot (Vrms)	Primary Current max (Amps)
MT-72301C	66	0.50	1 : 20	500	20
MT-72302C	148	0.75	1 : 30	500	20
MT-72303C	264	1.03	1 : 40	500	20
MT-72304C	412	1.61	1 : 50	500	20
MT-72305C	594	1.98	1 : 60	500	20
MT-72306C	808	2.97	1 : 70	500	20
MT-72307C	1650	5.36	1 : 100	500	20
MT-72308C	2570	6.67	1 : 125	500	20
MT-72309C	6600	33.24	1 : 200	500	20

1. Secondary inductance tested at 10kHz, 0.1 Vrms

Specifications subject to change. Custom versions of any Minntronix products are available upon request.

MT-72400 SERIES


SMD Current Sense Transformers

MINNTRONIX

Wind Up the Best®







Phone: 1.605.884.0195
Fax: 1.605.884.0199
www.minntronix.com



- High current - primary rated for 35 Amps
- Designed for automatic pick and place
- Operating frequency range: 50kHz to 500kHz
- Low profile - 10mm max height

Mechanical Dimensions:



UNIT: Inch (mm)

RECOMMENDED PCB LAYOUT

Electrical Specifications at 25°C - Operating Temperature -25°C to +125°C

Part Number	Turns Ratio Pri : Sec	Secondary Inductance at 10KHz 0.1V (mH min)	Secondary DCR (Ω max)	Primary Current max (Amps)	Hi-pot (Vrms)
MT-72401	1:30	0.50	0.34	35	500
MT-72402	1:50	1.40	0.57	35	500
MT-72403	1:70	2.70	0.80	35	500
MT-72404	1:100	5.60	1.50	35	500
MT-72405	1:200	22.0	5.00	35	500
MT-72406	1:300	50.0	12.00	35	500

Specifications subject to change. Custom versions of any Minntronix products are available upon request.

MT-72400 SERIES

MT-72500 SERIES


TH Current Sense Transformers

MINNTRONIX

Wind Up the Best®






Phone: 1.605.884.0195
Fax: 1.605.884.0199
www.minntronix.com




- 3000Vrms gate to drive winding test
- Operating frequency from 50kHz to 500kHz
- Popular winding configurations

Mechanical Dimensions:



(BOTTOM VIEW)

UNIT: Inch (mm)



Electrical Specifications at 25°C - Operating Temperature -25°C to +125°C

Part Number	Turns Ratio PRI 1: PRI 2 : SEC 2	Primary Inductance 15KHz 0.1V (mH min)	DCR PRI (Ω max)	DCR SEC1 (mΩ max)	DCR SEC2 (mΩ max)	Hi-pot (Pri-Sec) (Vrms)
MT-72501	50:1:1	5	0.7	5.0	5.0	3000
MT-72502	100:1:1	20	1.4	5.0	5.0	3000
MT-72503	200:1:1	80	4.5	5.0	5.0	3000
MT-72504	300:1:1	180	11.0	5.0	5.0	3000
MT-72505	40:1:1	3.2	0.56	5.0	5.0	3000

Specifications subject to change. Custom versions of any Minntronix products are available upon request.

MT-72600 SERIES


SMD Current Sense Transformers

MINNTRONIX






Wind Up the Best®



Phone: 1.605.884.0195
Fax: 1.605.884.0199
www.minntronix.com



- High current - primary rated for 35 Amps
- Operating frequency range up to 100kHz
- Designed for automatic pick and place
- Low profile - height 7.0mm max



UNIT : Inch (mm)

Electrical Specifications at 25°C - Operating Temperature -25°C to +125°C

Part Number	Turns Ratio Pri : Sec	Secondary Inductance at 10KHz 0.1V (mH min)	Secondary DCR (Ω max)	Primary Current max (Amps)	Hi-pot (Vrms)
MT-72601	1:30	0.20	0.25	35	500
MT-72602	1:50	0.55	0.65	35	500
MT-72603	1:70	1.10	1.40	35	500
MT-72604	1:100	2.10	3.00	35	500
MT-72605	1:200	9.00	8.00	35	500
MT-72606	1:300	20.0	20.0	35	500

Specifications subject to change. Custom versions of any Minntronix products are available upon request.

MT-72600 SERIES

D9

MT-72700 SERIES

Current Sense Transformers

MINNTRONIX

Wind Up the Best®









Phone: 1.605.884.0195
Fax: 1.605.884.0199
www.minntronix.com



- Perfect for high efficiency synchronous converters
- Frequency range 20kHz to 500kHz
- 50Arms peak primary currents, 35Arms sustained
- Ultra low primary resistance
- High strength construction
- 1500Vrms primary to secondary Hi-pot

Mechanical Dimensions:



UNIT: inch (mm)

Tolerances: 0~0.3 ± 0.012 (0~7.62 ± 0.305)
0.31~0.5 ± 0.02 (7.87~12.7 ± 5.08)

Electrical Specifications at 25°C - Operating Temperature -40°C to +125°C

Part Number	Turns Ratio Pri : Sec	Secondary Inductance at 10KHz 0.1V (mH min)	Secondary DCR (mΩ ± 15%)	Primary RMS Current (Amps)	Primary Current max (Amps)	Hi-pot (Vrms)
MT-72700	1:25	1.0	57	35	50	1500
MT-72705	1:50	5	215	35	50	1500
MT-72710	1:75	10	530	35	50	1500
MT-72715	1:100	20	850	35	50	1500
MT-72720	1:200	70	3400	35	50	1500

MT-72800 SERIES


Current Sense Transformers

MINNTRONIX


Wind Up the Best®



Phone: 1.605.884.0195
Fax: 1.605.884.0199
www.minntronix.com



- Low profile - height 3.0mm max
- Primary rated for 2.0 Amps
- Operating frequency range up to 300kHz
- Designed for automatic pick and place



Electrical Specifications at 25°C - Operating Temperature -25°C to +125°C

Part Number	Turns Ratio Pri : Sec	Secondary Inductance at 100 KHz 0.1V (mH min)	Secondary DCR (Ω max)	Primary Current max (Amps)	Hi-pot (Vrms)
MT-72801	1:50	0.2	7.0	2	500
MT-72802	1:75	0.5	11.0	2	500
MT-72803	1:100	0.85	14.0	2	500
MT-72804	1:150	1.3	20.0	2	500

Specifications subject to change. Custom versions of any Minntronix products are available upon request.

MT-72800 SERIES

MT-73000 SERIES

INDUSTRIAL - Current Transformers

MINNTRONIX

Wind Up the Best®



Phone: 1.605.884.0195
Fax: 1.605.884.0199
www.minntronix.com

MT-73000 SERIES



- UL and CUL listing per Minntronix XODW2 Instrument Transformer Classification
- These rugged units offer great value in industrial class CT coils
- Applicable Standard: ANSI C57.13. All accuracy classes available
- Insulation: 10kV BIL Full Wave (600 Volt Class)
- All cases are marked for polarity. Optional marking available
- Mounts easily on the conductor. No mounting brackets necessary
- Green and black cases available (custom colors by request)
- Frequency Range: 50-400Hz. (Extended ranges and accuracies available)
- All round models include two #16 or #18 AWG, 24" long secondary leads (X1=white, X2=black)

Standard Case Size Information

External Case Dimensions			
MTX Case Style	Nominal SAE Inch (mm)		
	OD	ID	HT
A-Round	2.539 (64.5)	1.122 (28.5)	0.965 (24.5)
B-Round	3.571 (90.7)	1.504 (38.2)	1.488 (37.8)
C-Round	3.539 (89.9)	1.563 (39.7)	1.087 (27.6)
D-Round	4.224 (107.3)	2.059 (52.3)	1.504 (38.2)
E-Round	4.354 (110.6)	2.248 (57.1)	1.402 (35.6)
H-Round	2.445 (62.1)	0.980 (24.9)	1.764 (44.8)
F-Square w/Terminals/Integrated Base	4.705 (119.5)	2.476 (62.9)	1.154 (29.3)
G-Square with Terminals	6.713 (170.5)	4.252 (108)	1.358 (34.5)
J-Square with Terminals	4.685 (119)	3.02 (76.7)	0.787 (20)

MT-73110^{SERIES}

INDUSTRIAL - Current Transformers

MINNTRONIX

Wind Up the Best®




Phone: 1.605.884.0195
Fax: 1.605.884.0199
www.minntronix.com



- UL and CUL listing per the Minntronix XODW2 Instrument Transformer Classification available
- These economical units offer great value in a general purpose CT coil.
- All cases are marked for polarity as shown
- All models include two #16 or #18 AWG, 24" long secondary leads (X1=white, X2=black)
- Frequency Range: 50-400 Hz
- Insulation: 10kV BIL Full Wave (600 Volt Class)
- Applicable Standard: ANSI C57.13
- Mounts easily on the conductor. No mounting brackets necessary, but available if needed
- Available in standard Minntronix green or black.

Customer supplied primary winding



Dimensions	Inches (mm)
Height Max	0.98 (24.9)
OD Max	2.6 (66.04)
ID Ref	1.1 (27.94)
Weight	0.20lb (0.45kg)

Part Number*	Current Rating (Amps)	VA Rating		Accuracy Rated Current	DCR @25°C (mΩ) Typ.
		@ 60Hz	@400Hz		
MT-73110-050	50:5	1.0	2.0	±2%	29.8
MT-73110-060	60:5	1.0	2.0	±2%	40.4
MT-73110-075	75:5	1.5	3.0	±2%	48
MT-73110-080	80:5	1.5	3.0	±2%	55.6
MT-73110-100	100:5	2.0	4.0	±1%	---
MT-73110-120	120:5	2.5	5.0	±1%	---
MT-73110-125	125:5	2.5	5.0	±1%	---
MT-73110-150	150:5	2.5	5.0	±1%	---
MT-73110-200	200:5	2.5	5.0	±1%	---
MT-73110-250	250:5	2.5	5.0	±1%	---
MT-73110-300	300:5	2.5	5.0	±1%	---
MT-73110-500	500:5	1.0	2.0	±1%	275

* Mounting Options: For Bracket add "-B" to part # (ex. MT-73110-080-B)

** Rating Factor 1.0 @ 30°C Ambient

Other turn ratios, brackets, colors, terminals, connectors, etc. available by request.

Specifications subject to change. Custom versions of any Minntronix products are available upon request.

MT-73110 SERIES

MT-73150^{SERIES}

INDUSTRIAL - Current Transformers

MINNTRONIX

Wind Up the Best®




Phone: 1.605.884.0195
Fax: 1.605.884.0199
www.minntronix.com



- UL and CUL Listing per the Minntronix XODW2 Instrument Transformer Classification available
- These economical units offer great value in a general purpose CT coil
- All cases are marked for polarity as shown
- All models include two #16 or #18 AWG, 24" long secondary leads (X1= white, X2 = black)
- Frequency Range: 50-400 Hz
- Insulation: 10kV BIL Full Wave (600 Volt Class)
- Applicable Standard: ANSI C57.13
- Mounts easily on the conductor. No mounting brackets necessary, but available if needed.
- Available in standard Minntronix green or black

Customer supplied primary winding



Dimensions	Inches (mm)
Height Max	1.1 (27.94)
OD Max	3.57 (90.68)
ID Ref	1.55 (39.37)
Weight	0.46lb (1.00kg)

Part Number*	Current Rating (Amps)	VA Rating		Accuracy Rated Current	DCR @25°C (mΩ) Typ.
		@ 60Hz	@400Hz		
MT-73150-100	100:5	2.0	4.0	±1%	29.8
MT-73150-150	150:5	2.5	5.0	±1%	40.4
MT-73150-200	200:5	5.0	12.5	±1%	48
MT-73150-250	250:5	5.0	12.5	±1%	55.6
MT-73150-300	300:5	5.0	12.5	±1%	64.6
MT-73150-400	400:5	12.5	25.0	±1%	88.3
MT-73150-500	500:5	12.5	25.0	±1%	114.4
MT-73150-600	600:5	25.0	50.0	±1%	133.7
MT-73150-750	750:5	15.0	30.0	±1%	180
MT-73150-800	800:5	17.5	35.0	±1%	190
MT-73150-1000	1000:5	20.0	40.0	±1%	240
MT-73150-1200	1200:5	20.0	40.0	±1%	270

* Mounting Options: For Bracket add "-B" to part # (ex. MT-73110-080-B)

** Rating Factor 1.0 @ 30°C Ambient

Other turn ratios, brackets, colors, terminals, connectors, etc. available by request.

Specifications subject to change. Custom versions of any Minntronix products are available upon request.

MT-73151_{SERIES}

INDUSTRIAL - Current Transformers

MINNTRONIX

Wind Up the Best®




Phone: 1.605.884.0195
Fax: 1.605.884.0199
www.minntronix.com



- UL and CUL Listing per Minntronix XODW2 Instrument Transformer Classification available
- These economical units offer great value in a general purpose CT coil
- All cases are marked for polarity as shown
- All models include two #16 or #18 AWG, 24" long secondary leads (X1 =white, X2 =black)
- Frequency Range: 50-400 Hz
- Insulation: 10kV BIL Full Wave (600 Volt Class)
- Applicable Standard: ANSI C57.13
- Mounts easily on the conductor. No mounting brackets necessary, but available if needed
- Available in standard Minntronix green or black

Customer supplied primary winding



Dimensions	Inches (mm)
Height Max	1.5(38.1)
OD Max	3.6 (91.44)
ID Min	1.5 (38.1)
Weight	1.2 lbs

Part Number*	Current Rating (Amps)	VA Rating	Accuracy Rated Current	DCR @25°C (mΩ) Typ.
		@ 60Hz		
MT-73151-300	300:5A	5.0	±1%	80.00
MT-73151-400	400:5A	7.5	±1%	100.00
MT-73151-500	500:5A	12.5	±1%	130.00
MT-73151-750	750:5A	15.0	±1%	180.00
MT-73151-800	800:5A	17.5	±1%	190.00
MT-73151-1000	1000:5A	20.0	±1%	240.00
MT-73151-1200	1200:5A	20.0	±1%	270.00

* Mounting Options: For Bracket add "-B" to part # (ex. MT-73110-080-B)

** Rating Factor 1.0 @ 30°C Ambient

Other turn ratios, brackets, colors, terminals, connectors, etc. available by request.

Specifications subject to change. Custom versions of any Minntronix products are available upon request.

MT-73151
SERIES

MT-73200_{SERIES}

INDUSTRIAL - Current Transformers

MINNTRONIX

Wind Up the Best®




Phone: 1.605.884.0195
Fax: 1.605.884.0199
www.minntronix.com

MT-73200 SERIES



- UL and CUL Listing per Minntronix XODW2 Instrument Transformer Classification Available
- These economical units offer great value in a general purpose CT coil
- All cases are marked for polarity as shown
- All models include two #16 or #18 AWG, 24" long secondary leads (X1 =white, X2 =black)
- Frequency Range: 50-400 Hz
- Insulation: 10kV BIL Full Wave (600 Volt class)
- Applicable Standard: ANSI C57.13
- Mounts easily on the conductor. No mounting brackets necessary, but available if needed
- Available in standard Minntronix green or black

Customer supplied primary winding



Dimensions	Inches (mm)
Height Max	1.50 (38.1)
OD Max	4.25 (107.95)
ID Min	2.06 (52.3)
Weight	1.3 lbs

Part Number*	Current Rating (Amps)	VA Rating	Accuracy Rated Current
		@ 60Hz	
MT-73200-050	50:5	0.5	±3%
MT-73200-075	75:5	0.5	±1%
MT-73200-100	100:5	1.0	±1%
MT-73200-150	150:5	2.5	±1%
MT-73200-200	200:5	4.0	±1%
MT-73200-250	250:5	6.0	±1%
MT-73200-300	300:5	7.5	±1%
MT-73200-400	400:5	10.0	±1%
MT-73200-500	500:5	12.5	±1%
MT-73200-600	600:5	15.0	±1%
MT-73200-750	750:5	7.0	±1%
MT-73200-800	800:5	8.0	±1%
MT-73200-1000	1000:5	10.0	±1%
MT-73200-1200	1200:5	12.5	±1%

* Mounting Options: For Bracket add "-B" to part # (ex. MT-73110-080-B)

** Rating Factor 1.0 @ 30°C Ambient

Other turn ratios, brackets, colors, terminals, connectors, etc available by request.

4810559R/4810966R


Current Sense Transformers

MINNTRONIX

Wind Up the Best®






Phone: 1.605.884.0195
Fax: 1.605.884.0199
www.minntronix.com



- For use with Linear Technology LT2940 Power and Current Monitor
- For 47-400Hz applications
- High isolation
- Two versions available to meet varying cost vs. accuracy requirements

4810559R/4810966R



Electrical Specifications at 25°C - Operating Temperature -25°C to +125°C

Part Number	Turns Ratio Pri : Sec	Secondary Inductance @ 1KHZ, 0.1V (mH Ref)	Nominal Accuracy	Secondary DCR (Ω max)	Primary Current max (Arms)	Hi-pot (Vrms)
4810559R	1:500	250	2.5%	20	10	3000
4810966R	1:500	600	1%	20	10	3000

Specifications subject to change. Custom versions of any Minntronix products are available upon request.

Custom CT Design Request Form

INDUSTRIAL-Current Transformers

MINNTRONIX

Wind Up the Best®



Phone: 1.605.884.0195
Fax: 1.605.884.0199
www.minntronix.com

Name & Address:

email:

phone:

CT Turns Ratio: **1**^(PRI-H1)
Customer Supplied

to


(SEC X1-X2) Integrated primary

also available

1. Operating / Storage Temp range _____ / _____ to _____ / _____ °C

2. Frequency Range _____ to _____ Hz _____ / _____ VA

3. Primary (H1) Current Ranges:



6. Burden:

(Customer supplied) External: _____ Ω nom _____ % Accuracy or PPM Class

(Optional) Internal: _____ Ω nom _____ % Accuracy or PPM Class

7. Standards requirements:

Build to:

Certify to: Please check all that are needed

IEEE / ANSI C57.13 (2008) ☐

IEC 6044-1 ☐

IEC 6044-6 ☐

UL XODW Instr. Txfrmr Std. ☐

Other: _____

Minimum fee may apply

BIL rating _____ KV

HiPot rating _____ KVrms

8. Size Requirements:

Standard Minntronix Case: A B C D E F G H (Circle One) or choose:

Alternate Casing: Glass Cloth Tape, Varnish, Bare, Other: _____

Custom Case:

Minimum ID (Window) _____ mm or in

Maximum OD (Width) _____ mm or in

Maximum Height (Thickness) _____ mm or in



9. Connections / Mounting:

Tinned Wire Leads: _____ Length _____ AWG _____ Volt

Terminals: _____ Length _____ Size (i.e. M8, 5/32, etc.)

Marking/Other: _____ (Brackets, Connectors, Lugs

Special instructions, etc.)

10. Annual Quantity / Price Target: _____ pcs / _____ US\$ - _____ pcs / _____ US\$

For Reference Only

Specifications subject to change. Custom versions of any Minntronix products are available upon request.