



NOTES:


1. ROHS COMPLIANT
2. HEADER: DAP (DIALLYL PHTHALATE) WITH FLAMMABILITY RATING UL 94V-0 OR BETTER.
3. STORAGE TEMPERATURE: -20°C TO +125°C
4. COMPLIANCE TO J-STD:
  - A. J-STD-002: SOLDERABILITY AT 245°C REFLOW PROFILE
  - B. J-STD-020: LEVEL 1, NO MOISTURE SENSITIVE
  - C. J-STD-075: R7, 245°C MAXIMUM THROUGH REFLOW SOLDER
5. TO ORDER TAPE & REEL PACKAGING ADD A "T" SUFFIX TO THE PART NUMBER(i.e H5019EFNL BECOMES H5019EFNLT).



FINAL OUTLINE

© Copyright, 2014. Pulse Electronics Corp. All rights reserved. Pulse confidential & proprietary. (06/30/14)

| PRODUCT DESCRIPTION   | TLA DRAWING  | PS DRAWING    | SHEET  | PART NO.  | DATASHEET REV. |
|-----------------------|--------------|---------------|--------|-----------|----------------|
| MDL,SIN,1GD,1:1,SM,TU | H5019EFNL-10 | PS-2761.001-A | 1 OF 3 | H5019EFNL | A              |



SCHEMATIC


ELECTRICAL CHARACTERISTICS AT +25°C UNLESS OTHER SPECIFIED

MEETS IEEE 802.3 SPECIFICATION

| PARAMETER                                | SPECIFICATIONS                            |                                        |                                        |
|------------------------------------------|-------------------------------------------|----------------------------------------|----------------------------------------|
| OPERATING TEMP                           | 0°C – 70 °C                               |                                        |                                        |
| URNS RATIO                               | 1 : 1 ±2%                                 |                                        |                                        |
| POLARITY                                 | PER SCHEMATIC                             |                                        |                                        |
| OCL, TRANSMIT CHANNEL                    | 350 uh MIN. WITH 8mA DC BIAS, –0 TO 70 °C |                                        |                                        |
| INSERTION LOSS                           | 100 KHz                                   | 1–100 MHz                              | 125 MHz                                |
|                                          | –1.2 dB MAX                               | –1.0 dB MAX                            | –3.0 dB MAX                            |
| RETURN LOSS<br>(Z OUT = 100 OHM ±15%)    | 1–40 MHz                                  |                                        | 40–100 MHz                             |
|                                          | –16 dB MIN                                | –18 dB MIN<br>(ZOUT=100 OHMS)          | –10+20*LOG <sub>10</sub> (f/80) dB MIN |
| CROSSTALK (TX–RX)                        | 1 MHz                                     | 30–100 MHz                             |                                        |
|                                          | –50 dB MIN                                | –55+24*LOG <sub>10</sub> (f/10) dB MIN |                                        |
| DIFFERENTIAL TO COMMON<br>MODE REJECTION | 2 MHz                                     | 30–100 MHz                             |                                        |
|                                          | –50 dB MIN                                | –43+22*LOG <sub>10</sub> (f/30) dB MIN |                                        |
| INPUT – OUTPUT<br>ISOLATION              | 1500 VRMS @ 60 SECONDS                    |                                        |                                        |

NOTE: f IS FREQUENCY IN MHZ.



LEGEND




ALL CHANNELS ARE  
IN PHASE BETWEEN  
INPUT AND OUTPUT

© Copyright, 2014. Pulse Electronics Corp. All rights reserved. Pulse confidential & proprietary. (06/30/14)

| PRODUCT DESCRIPTION   | TLA DRAWING  | PS DRAWING    | SHEET  | PART NO.  | DATASHEET REV. |
|-----------------------|--------------|---------------|--------|-----------|----------------|
| MDL,SIN,1GD,1:1,SM,TU | H5019EFNL-10 | PS-2761.001-A | 2 OF 3 | H5019EFNL | A              |



SUGGESTED LAND PATTERN



DIMENSIONS ARE IN INCHES [MILLIMETERS] WITH THE FOLLOWING TOLERANCES: [MILLIMETERS] ARE FOR REFERENCE ONLY.  
 .XX= ±.01 [±0.25]  
 .XXX= ±.005 [±0.13]

© Copyright, 2014. Pulse Electronics Corp. All rights reserved. Pulse confidential & proprietary. (06/30/14)

| PRODUCT DESCRIPTION   | TLA DRAWING  | PS DRAWING    | SHEET  | PART NO.  | DATASHEET REV. |
|-----------------------|--------------|---------------|--------|-----------|----------------|
| MDL,SIN,1GD,1:1,SM,TU | H5019EFNL-10 | PS-2761.001-A | 3 OF 3 | H5019EFNL | A              |