






P.C.B MOUNTING



CIRCUIT: SPST

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY.
4. TRAVEL: 0.25mm +0.2/-0.1
5. RATING: 50mA, 12VDC
6. OPERATING FORCE: 260 \pm 50gf
7. CONTACT RESISTANCE: 100M OHM MAX.
8. ACTUATOR COLOR: BLACK
9. ▲ DENOTES CRITICAL PARAMETER
- ▲10. PACKAGING: TAPE AND REEL 1,500 PCS PER
- ▲11. 2002/95/EC (ROHS) COMPLIANT

TERMINALS TO BE COPLANAR
WITH IN 0.10 TOTAL**E-SWITCH®**

TITLE TL3303F260QG

SCALE 4:1

DATE 3/29/2006

DR PH

DWG P010346

REV D

D	15915	REVISED REDRAWN	3/29/06	PH
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED