

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [35746-0310](#)
Status: **Active**
Overview: [VersaBlade™](#)
Description: Crimp Terminal 35746, 18+18, 20+20 AWG

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-35150-001 \(PDF\)](#)
[Product Specification PS-35182-003 \(PDF\)](#)
[Packaging Specification PK-35151-002 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Crimp Terminals
Series [35746](#)
Application Power
Crimp Quality Equipment Yes
Overview [VersaBlade™](#)
Product Name VersaBlade™
UPC 800754378482

Physical
Gender Female
Material - Metal Phosphor Bronze
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 0.346/g
Packaging Type Reel
Plating min - Mating 0.813µm
Plating min - Termination 0.813µm
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 6.00mm max.
Wire Size AWG 18+18, 20+20
Wire Size mm² N/A

Material Info

Reference - Drawing Numbers
Packaging Specification PK-35151-002
Product Specification PS-35150-001, PS-35182-003
Sales Drawing SD-35746-003




image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[35746Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
FineAdjust™	0638629200
Applicator	
Extraction Tool	0638132700
T2 Terminator Die	0638529200
Hand Crimp Tool for 1.80mm-Wide Crimp Terminals	0638190700
Hand Crimp Tool for Industry standard 1.78mm Tab Terminals, 24-26 AWG Wire	0638196900

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

onlinecomponents.com