



# E-Z-Code®



Overview .....	P2
E-Z-Coder™ Wire Marker Printer.....	P3
E-Z-Coder™ Wire Marker Printer & Labels.....	P4
Identification Software .....	P5-P6
Wire Marker Books.....	P7-P9
Wire Marker Cards – Vinyl Cloth .....	P10-P16
Wire Marker Cards – Vinyl Cloth – Mini Books .....	P17
Cable Markers – Vinyl Cloth.....	P18-P19
Wire Marker Cards – Vinyl Self-Laminating.....	P20-P21
Write-On Markers & Roll Tape Markers.....	P22
Standard Wire Marker Combination Packs .....	P23
Conduit and Electrical Markers – Cards.....	P24
Industrial Markers.....	P25
Markers and PCB Warning Labels.....	P26
Roll Wire Marker Dispenser .....	P27
Color-Coded I.D. Tape .....	P28
Protect-A-Line® Warning Tapes .....	P29
Tape and Markers .....	P30
Customized Embossed Tags Stainless Steel Tape Embossing System.....	P31
Stainless Steel I.D. Tag .....	P32
PVC Sleeve and Clip-On Markers .....	P33
Lockout/Tagout.....	P34-P44
Accident Prevention Tags .....	P45
Transformer Safety Labels.....	P46
Electrical Safety Cards and Labels .....	P47
Safety Signs .....	P48-P52
Custom Sign Express Order Form .....	P53



Industrial construction, in-plant operations, and telecommunications. Computer installations and power facilities. Transportation and panel equipment. Wherever electrical and electronic components and systems are used to connect, fasten, insulate and identify wire and conduits, you'll find a Thomas & Betts quality product performing to industry-wide standards of excellence. For over a hundred years, Thomas & Betts has developed the products you need, with the quality you demand and at the right price.

E-Z-Code Identification Products are marketed nationally through an exclusive network of authorized stocking distributors, where emphasis is placed on customer service, experience and product knowledge. Staffed by trained professionals with a background in federal, state and local codes and regulations, your local T&B distributor can provide you with quotation service, up-to-date pricing, shipping costs and competitive product line evaluations when needed.

### Automated Wire Markers & Accessories

The E-Z-Coder™ Wire Marker Printer is one of the smallest, most portable wire marker printers in the industry. It is a simple, easy-to-use, and reliable tool that'll have you marking wires almost as soon as you pull it from the box. E-Z-Code Labeling Software is a full-featured labeling system for creating custom labels for your cabling and wire marking needs. E-Z-Code® Laser Printable Markers let you print your own markers to your requirements.

### Wire Marker Book, Cards and Labels

Pocket pack wire marker books are easy to carry, easy to use. T&B maintenance and production labels have been designed to provide extra-added convenience through positive, protected clear identification. Wire marking is simple, clean and fast...just pull tape out, tear and wrap. Compact size fits in your pocket or hangs from work belt.

### Lockout / Tagout

E-Z-Code offers an inclusive product line to supply the general requirements of the OSHA Lockout/Tagout standard. From comprehensive training videos to circuit breaker locking devices, E-Z-Code Lockout/Tagout products help insure that general industry workers will be protected from accidents during maintenance and servicing of equipment.

### Identification Tapes

Bright colors are not the only advantages of these Barricade and Burial Tapes. T&B's attention-getting Tapes are also inexpensive and easy to handle. Protect-A-Line tape is ideal for marking hazardous or off-limit barricade areas. A large assortment of Buried Utility Tape and Foil Backed Detectable Buried Utility Tapes help prevent potential accidents during excavations and underground installations.

### Electrical Hazard Safety Signs

T&B provides a large assortment of necessary Electrical Hazard Safety Signs to complete your construction and maintenance projects. Choose from either Aluminum, Plastic, or Self Sticking material to suit your environments. Or create your own sign to your specifications by ordering from our Specials Form.

# E-Z-Code®

## E-Z-Coder™ Wire Marker Printer



**The E-Z-Coder Wire Marker Printer is sold with one battery pack, a battery charger, one ribbon for general use labels and a wrist cord. The E-Z-Case, accessory batteries and all printing media are sold separately.**

### The E-Z-Coder™ Wire Marker Printer from Thomas & Betts. It's how to run wires without running wild.

The E-Z-Coder™ Wire Marker Printer is one of the smallest, most portable wire marker printers in the industry. It is a simple, easy-to-use, and reliable tool that'll have you marking wires almost as soon as you pull it from the box. When compared with other larger, more complicated systems, the E-Z-Coder™ printer is also one of the most affordable devices for producing custom labels for wire, face plates, outlets and electrical components. And the E-Z-Coder wire marker printer makes sharp, impressive labels that reflect the quality and professionalism that's required even on the toughest jobs.

- Compact unit that fits easily in the palm of your hand.
- Simple to use, no elaborate training is required.
- Weighs only a little over a pound.

- Powered from a single rechargeable battery, prints up to 250 labels from a single charge.
- Easy-loading label system.
- Wide, user-friendly buttons, with common electrical notations.
- Large, easy-to-read LCD display.
- Heavy-duty printing head for years of quality label printing.
- Self-adjusts the label to the correct printing position.
- Automatic label serialization.
- Three different printing position modes and either small or large type size, bold and normal type.
- Rugged construction.
- Simple instructions on the back of the printer.
- Wide variety of labels, including heat-shrinkable tubing.



### E-Z-Coder™ Wire Marker Printer

Cat. No.	Description	UPC No.
<b>EZ-CODER</b>	Printer (includes EZ-RBLACK Ribbon, battery, user's guide, battery charger and wrist/belt cord)	786210-37635
<b>EZ-BATTERY</b> <b>A</b>	Battery Pack	786210-37636
<b>EZ-CHARGER</b> <b>B</b>	Battery Charger	786210-37637
<b>EZ-CASE</b> <b>C</b>	Hard Shell Carrying Case	786210-37638
<b>EZ-RBLACK</b> <b>D</b>	Black Printer Ribbon for General Use Labels	786210-37639
<b>EZ-RBLACKHS</b>	Black Printer Ribbon for Heat Shrinkable Labels only	786210-37640

#### E-Z-Coder™ Wire Marker Printer Specifications

- Weight 1.6 lbs.
- Shuttle head impact printer.
- Two type sizes with normal and bold type available.
- Prints up to eight variable lines of text.
- Two-line liquid crystal display (LCD), 16 characters wide max.
- Operating temperature range: 40°F to 120°F.

- UL listed battery charger (120 VAC, 60 HZ input/9V DC 75 mA output).
- FCC class A approved.
- Prints up to 250 labels between battery charges.
- 6 month warranty.
- Automatic label serialization.
- 3 printing modes; wire, center and strip.

P

E-Z-Code®

**Thomas & Betts**

# E-Z-Code®


## E-Z-Coder™ Wire Marker Printer and Labels



Perfect for Datacom faceplates and Category 5 networks.



Component labels keep your entire job well-organized.



### E-Z-Coder™ Wire Marker Label Materials

Type	Max. Service Temp. °F (°C)	Use	Special Properties
Vinyl	150 (66)	Wire and cable labels	Heat and solvent resistant; conformable
Vinyl Cloth	180 (82)	General marking	Oil, water and humidity resistant; permanent or removable
Polyester	311 (155)	Tag for outdoor or harsh environments	Solvent, heat, abrasion resistant
Polyester Metallized	311 (155)	Metallized permanent label	Print receptive; CSA
Polyolefin	275 (135)	Wire ID and insulation	Permanent, shrinkable

Cat. No.	Material	Label Size (In.) Width x Height	Wire Size (AWG)	Qty. Per Roll
<b>Self-Laminating White/Transparent Vinyl Labels</b>				
<b>Wire Markers</b>				
<b>EZL-21-V75</b>	Vinyl	1.0 X .75	10 - 16	250
<b>EZL-21-V1</b>	Vinyl	1.0 X 1.0	10 - 12	250
<b>EZL-30-V</b>	Vinyl	.5 X 1.25	6 - 10	250
<b>EZL-30-V2S</b>	Vinyl	.5 X 1.25	6 - 10	250/500
<b>EZL-31-V</b>	Vinyl	1.0 X 1.25	6 - 10	250
<b>EZL-32-V</b>	Vinyl	1.5 X 1.25	6 - 10	250
<b>Cable Markers</b>				
<b>EZL-51-V</b>	Vinyl	1.0 X 2.5	Cable	100
<b>EZL-52-V</b>	Vinyl	1.5 X 2.5	Cable	100
<b>EZL-71-V</b>	Vinyl	1.0 X 4.0	Cable	100
<b>EZL-72-V</b>	Vinyl	1.5 X 4.0	Cable	100
<b>Wire Markers</b>				
<b>EZL-50-C</b>	Cloth	.5 X .75	10 - 16	250
<b>EZL-51-C</b>	Cloth	1.0 X .75	10 - 16	250
<b>EZL-70-C</b>	Cloth	.5 X 1.0	10 - 12	250
<b>EZL-71-C</b>	Cloth	1.0 X 1.0	10 - 12	250
<b>EZL-90-C</b>	Cloth	.5 X 1.25	6 - 10	250
<b>EZL-92-C</b>	Cloth	1.5 X 1.25	6 - 10	250
<b>Component and General Identification Labels</b>				
<b>EZL-22-PW</b>	Polyester White	1.5 X .4	500	
<b>EZL-30-PW</b>	Polyester White	.5 X .5	500	
<b>EZL-31-PW</b>	Polyester White	1.0 X .5	500	
<b>EZL-32-PW</b>	Polyester White	1.5 X .5	500	
<b>EZL-52-PW</b>	Polyester White	1.5 X .75	250	
<b>EZL-92-PW</b>	Polyester White	1.5 X 1.25	250	
<b>EZL-22-PC</b>	Polyester Cloth	1.5 X .4	500	
<b>EZL-52-PC</b>	Polyester Cloth	1.5 X .75	250	
<b>EZL-31-PM</b>	Polyester Metallized	1.0 X .5	500	
<b>EZL-52-PM</b>	Polyester Metallized	1.5 X .75	250	
<b>EZL-92-PM</b>	Polyester Metallized	1.5 X 1.25	250	
<b>Heat-Shrink White Polyolefin Labels</b>				
<b>EZS-11-125</b>	Heat Shrink	1.0 X .235	22 - 16	100
<b>EZS-11-187</b>	Heat Shrink	1.0 X .335	18 - 12	100
<b>EZS-21-250</b>	Heat Shrink	1.0 X .439	16 - 10	100
<b>EZS-31-375</b>	Heat Shrink	1.0 X .645	12 - 6	100
<b>EZS-41-500</b>	Heat Shrink	1.0 X .851	8 - 1	100

### Cloth Markers

Cat. No.	Sheet Size (in.)	Markers per Sheet	Marker Size (in.) W L	Max Wire Dia. (in.)
WEC-12112	9½ x 12	104	½ x 1 7/16	7/16
WEC-10112	9½ x 12	64	2 9/32 x 1 7/16	7/16

### Paper Markers

Cat. No.	Sheet Size (in.)	Markers per Sheet	Marker Size (in.) W L	Max Wire Dia. (in.)
WEL-3414	9½ x 11	297	¾ x ¼	¼
WEL-1012	9½ x 11	154	1 x ¾	¾

### Labels for use with the E-Z-Code High-Volume Wire Marking System Self-Laminating Markers

Cat. No.	Sheet Size (in.)	Markers per Sheet	Marker Size (in.) W L	Print Area (in.) W L	Max Wire Dia. (in.)
WES-12112	9½ x 8	64	½ x 1 ½	½ x ½	7/16
WES-1112	9½ x 8	32	1 x 1 ½	1 x ½	7/16
WES-2112	9½ x 8	16	2 x 1 ½	2 x ½	7/16
WES-12214	9½ x 9	48	½ x 2 ¼	½ x ¾	15/32
WES-12114	9½ x 9	24	1 x 2 ¼	1 x ¾	15/32
WES-2214	9½ x 9	12	2 x 2 ¼	2 x ¾	15/32
WES-12334	9½ x 9	32	½ x 3 ¾	½ x 1	7/8
WES-1334	9½ x 9	16	1 x 3 ¾	1 x 1	7/8
WES-2334	9½ x 9	8	2 x 3 ¾	2 x 1	7/8
WES-2512	9½ x 12	8	2 x 5 ½	2 x 1	1 ½
WES-2128	9½ x 9	3	2 ½ x 8 ½	2 ½ x 2	2

Standard package is 25 sheets.

Add suffix **A** for 500 sheets, **B** for 1,000 sheets.

WEC, WEL, and WES labels may be used on any standard pin-feed dot-matrix printer. WLP labels may be used on any standard laser printer.

P

E-Z-Code®

**Thomas & Betts**

# E-Z-Code®

## Identification Software



- **1 Mil Polyester (same material as WPR rolls).**
- **Works on most laser printers.**
- **More markers per sheet than leading manufacturer's sheets.**
- **Leader template included with each 25 pack.**

### Laser Printable Markers

E-Z-Code® Laser Printable Markers let you print your own markers to your requirements. These self-laminating markers have a clear overlay of polyester that protects the legend against

oils, grease, water, chemicals and foreign matter. They also feature a strong adhesive for maximum adhesion to the wire and are available in a variety of sizes both as standard and specials.

Cat. No.	Sheet Size	Markers Per Sheet	Marker Size	Max. Wire Dia.
<b>WLP-1112</b>	8½" x 11"	48	1" x 1½"	5/16"
<b>WLP-1214</b>	8½" x 11"	32	1" x 2¼"	15/32"
<b>WLP-12112</b>	8½" x 11"	96	½" x 1½"	5/16"
<b>WLP-12214</b>	8½" x 11"	64	½" x 2¼"	15/32"
<b>WLP-12300</b>	8½" x 11"	48	½" x 3"	7/8"
<b>WLP-1300</b>	8½" x 11"	24	1" x 3"	7/8"
<b>WLP-1500</b>	8½" x 11"	16	1" x 5"	1¼"
<b>WLP-1900</b>	8½" x 11"	8	1" x 9"	2"
<b>WLP-2112</b>	8½" x 11"	24	2" x 1½"	5/16"
<b>WLP-2214</b>	8½" x 11"	16	2" x 2¼"	15/32"
<b>WLP-2300</b>	8½" x 11"	12	2" x 3"	7/8"
<b>WLP-2500</b>	8½" x 11"	8	2" x 5"	1¼"
<b>WLP-2900</b>	8½" x 11"	4	2" x 9"	2"

Standard package is 25 sheets to a package. Case quantity is 30 packages (of 25 sheets each).

Add suffix **A** for 500 sheets, **B** for 1,000 sheets.

WEC, WEL, and WES labels may be used on any standard pin-feed dot-matrix printer. WLP labels may be used on any standard laser printer.

### Typewriter Printable Markers, self laminating

Cat. No.	Description	Sheet Size	Marker Size W L	Write-On Area W L	Character per Marker	Max. Wire Size	No. per Sheet
<b>WTW-12112</b>	25 sheets, 1,600 markers	9" x 8"	½" x 1½"	½" x ½"	4	#4	64
<b>WTW-1112</b>	25 sheets, 800 markers	9" x 8"	1" x 1½"	1" x ½"	9	#4	32
<b>WTW-2112</b>	25 sheets, 400 markers	9" x 8"	2" x 1½"	2" x ½"	19	#4	16
<b>WTW-1214</b>	25 sheets, 600 markers	9" x 9"	1" x 2¼"	1" x ¾"	9	#1	24
<b>WTW-2214</b>	25 sheets, 300 markers	9" x 9"	2" x 2¼"	2" x ¾"	19	#1	12
<b>WTW-1334</b>	25 sheets, 400 markers	9" x 9"	1" x 3¼"	1" x 1"	9	400	16
<b>WTW-2334</b>	25 sheets, 200 markers	9" x 9"	2" x 3¼"	2" x 1"	19	400	8

Order by sheets—Standard package 25 identical individual sheets per poly bag.

# E-Z-Code®

## Wire Marker Books





**Pocket pack wire marker books are easy to carry, easy to use. The material is an all purpose vinyl coated cloth tape exclusively designed to resist abrasion, oil, water and dirt. From Thomas & Betts you get the one-piece wire marker and terminal marker. A slight die-cut allows you to easily remove the terminal marker if you need it or leave it in place for a longer marker.**

- Size 3" x 5" (76 mm x 146 mm).
- Quantity of pages: 10.
- Material: vinyl cloth.
- Cover keeps markers clean.
- Books are 3" x 5½" pocket size.
- 10 pages per book.

### Vinyl Cloth, Standard Books

Cat. No.	Number of Markers and Legends
<b>WM-0 thru 9</b>	40 Markers each: 0 thru 9; 10 Markers each: T1, T2, T3, L1, L2, L3, WM-0 thru -9
<b>WM-0-9M</b>	46 Markers each page; full page of 1, full page of 2, etc.
<b>WM-0-45</b>	10 Markers each: 0 thru 45
<b>WM-46-90</b>	10 Markers each 46 thru 90
<b>WM-A-Z</b>	10 Markers each: A thru Z, +, -, and 0 thru 15
<b>WM-123</b>	150 Markers each: 1, 2, 3
<b>WM-ABC</b>	150 Markers each: A, B, C
<b>WM-A-33</b>	10 Markers each: 1 thru 33, A, B, C, +, -, T1, T2, T3, L1, L2, L3
<b>WM-A-90</b>	6 Markers each: 0 thru 15; 4 Markers each: 16 thru 90; 2 Markers each: A thru Z
<b>WM-0 thru WM-9</b>	460 Markers each of any number 0 thru 9
<b>WM-A, -B, -C, -D, -E, -F, -G, -L, -N, -P, -R, -S, -T, or X</b>	460 Markers each of any letter; -A, -B, -C, -D, -E, -F, -G, -L, -N, -P, -R, -S, -T or X
<b>WM-GRD</b>	120 Markers 7/16" x 2 1/2" or 240 Markers 7/16" x 1 1/4" with "GRD" legend
<b>WMLC-1</b>	24 Legends, 2 legends each per page, 480 markers per book for house wiring and circuit breakers; 5/8" x 1 3/2" (16mm x 10mm)
<b>WM-T3</b>	10 Pages T <sub>1</sub> , T <sub>2</sub> , T <sub>3</sub> ; 140 Markers ea.; total 420
<b>WM-L3</b>	10 Pages L <sub>1</sub> , L <sub>2</sub> , L <sub>3</sub> ; 140 markers ea.; total 420
<b>WM-9T</b>	3 Pages 1, 2, 3; 42 markers ea.; 3 Pages A, B, C; 42 markers ea.; 2 Pages T <sub>1</sub> , T <sub>2</sub> , T <sub>3</sub> ; 28 markers ea.; 2 Pages L <sub>1</sub> , L <sub>2</sub> , L <sub>3</sub> ; 28 markers ea.; total 140
<b>WM-1-30</b>	10 Pages 1-30; 14 markers ea.; total 140
<b>WM-12</b>	A-Z 8 1/2 Pages, 14 markers ea.; Blank Write Ons 1 Page, 22 markers ea.; Plus & Minus 1/2 Page, 7 markers ea.; total 393
<b>WM-13</b>	Plus & Minus, AC, DC, 1 Page ea., 46 markers ea.; Pos. Neg. Gnd. 1 Page ea., 28 markers ea.; Spare, Neut. 1 Page ea., 22 markers ea.; Blank Write Ons 1 Page ea., 22 markers ea.; total 256
<b>WM-0-90</b>	5 Pages ea. 0-45; 5 markers ea.; 5 Pages ea. 46-90; 5 markers ea.; total 455

Minimum order quantity is 10.



P

E-Z-Code®


**Thomas & Betts**

# E-Z-Code®


## Wire Marker Books




- **Bold letters / numbers, easy to apply and read.**
- **Convenient alphanumeric and loadcenter legends.**
- **E-Z-Snap feature, removes the entire sheet more easily from the booklet.**
- **Custom / private label covers available.**
- **Vinyl coated cloth.**



**Make your own laminated markers by using these blank write-ons.**



**Clear area covers print legend for extra protection.**



**Use these clear markers to protect labels or to apply over non-sticking markers.**

### E-Z-Code® Compact Wire Marker Books

Introducing a handy solution to your identification needs. The new E-Z-Code® Compact Wire Marker books from T&B feature:

Cat. No.	Legend	Sheets Per Book	Markers Per Page	Marker Size	Wt /Lbs. 100 Books
WCMB-0-9			128 markers 0-9, ABC, +/-; marker size $1/4" \times 1\frac{1}{2}"$		
WCMB-LC			176 markers Loadcenter Labels; marker size $1\frac{1}{32}'' \times \frac{3}{4}''$		

Standard package is 20 books. Case quantity is 480 books (24 cartons).

### Vinyl Self Laminating, Standard Books

Cat. No.	Number of Markers and Legends
WMSL 1-33, A-G	400 Markers: $1/4" \times 1\frac{1}{4}"$ – printed area $5/8"$ ; 10 markers each: 1 thru 33 and A thru G
WMSL-0-9	40 Markers each 0 thru 9; 10 Markers each: T1, T2, T3, L1, L2, L3
WMSL-0-45	10 Markers each 0 thru 45
WMSL-46-90	10 Markers each 46 thru 90
WMSL-A-Z	10 Markers each: A thru Z; +, -, and 0 thru 15
WMSL-A-90	6 Markers each: 0 thru 15; 4 markers each 16 thru 90; 2 markers each A thru Z

Minimum order quantity is 10.

### Cat. No. Number of Markers and Legends

WM-BW3	30 $1" \times 4\frac{1}{8}"$ blank write-on self-laminating transparent vinyl markers; marking area: $1" \times 1"$
WM-BW5	50 $1" \times 2\frac{3}{8}"$ blank write-on, self laminating transparent vinyl markers; marking area: $1" \times \frac{3}{4}"$
WM-BW12	200 $\frac{1}{2}'' \times 1\frac{1}{4}''$ blank write-on, self laminating transparent vinyl markers; marking area: $\frac{1}{2}'' \times \frac{5}{8}''$
WM-BW14	400 $\frac{1}{4}'' \times 1\frac{1}{4}''$ blank write-on, self-laminating transparent vinyl markers; marking area: $\frac{1}{4}'' \times \frac{5}{8}''$
WM-BW34	140 $\frac{3}{8}'' \times 1\frac{1}{4}''$ blank write-on, self-laminating transparent vinyl markers; marking area: $\frac{3}{4}'' \times \frac{5}{8}''$

Minimum order quantity is 10.

### Vinyl Self Laminating, Standard Laminator Book


Cat. No.	Number of Markers and Legends
WM-LAM	50, $3\frac{1}{2}'' \times 5"$ Clear Cable Laminators

Minimum order quantity is 10.


**Thomas&Betts**

# E-Z-Code®

## Wire Marker Books



When you need to color code your wiring, this book can solve your problems. Available in two sizes, it allows you to color rather than number your wires for coding and other applications.



### E-Z-Code® Pocket Pack Production Quality Control Markers.

- Easy to carry – marker books fit in shirt pocket.
- Easy to use – just peel the marker from the page.
- Clean and convenient – markers are tabbed so that fingers never touch the adhesive.

### Vinyl, Color Coding Standard Books

Cat. No.	Size W L	Number of Markers and Legends
WM-COL14	1/4" x 1 1/4"	460 Markers each: 1 page yellow and blue, 2 pages red, white, green and black
WM-COL1	1" x 2 1/4"	50 Markers each: 1 page yellow and blue, 2 pages red, white, green and black

Minimum order quantity is 10.

### Polyolefin E-Z-Code® Pocket Pack Markers

Our line of E-Z-Code pre-printed quality control, production and maintenance labels help prevent problems before they occur. Now you can positively identify defective products, tools in need of calibration etc. by using these T&B labels. Available on cards with a choice of 8 legends or in our exclusive book design of 22 different legends.

Twenty two legends highlight the variety that our exclusive Pocket Pack

label books are available in. Each book contains 240 identical labels. The Pocket Pack keeps the markers clean, handy and ready to use.

Order exactly what you need from our large selection of stock labels for dating, coding, inspection, calibration, etc. or contact T&B for a special application or legend requirement to suit your particular needs.

### Pocket Pack Markers


Cat. No.	Legends 240 Identical per Book	Description
WTMP-1B	CALIBRATED (blk)	
WTMP-2B	CERTIFICATION (blk)	
WTMP-3B	MAINTENANCE (blue)	
WTMP-4B	REJECTED (red)	
WTMP-5B	ACCEPTED (green)	
WTMP-6B	HOLD (red)	
WTMP-7B	RETURN TO VENDOR (orange)	15 Pages per Book
WTMP-8B	REWORK (blk)	
WTMP-9B	HOLD FOR INSPECTION (blue)	
WTMP-11B	CAUTION (blk)	16 Markers per Page
WTMP-16B	DATE INSTALLED (blk)	
WTMP-18B	DUE FOR INSPECTION (orange)	Each Label is
WTMP-19B	DO NOT USE AFTER (red)	1/2" x 5/8"
WTMP-20B	INSPECTED (blk)	
WTMP-21B	BLANK HEADING	Each Book Contains
WTMP-22B	REPAIRED BY (orange)	240 Identical Labels
WTMP-24B	SCRAPPED (orange)	
WTMP-25B	TESTED (green)	
WTMP-26B	CALIBRATION (green)	
WTMP-52B	PROPERTY TAG (blk)	
WTMP-53B	SERIAL NO. (blk)	
WTMP-55B	TOOL NO. (blue)	

Minimum order quantity is 10.

P

E-Z-Code®


**Thomas & Betts**



### Solid Numbers

Cat. No.	Legend	Markers per Legend	
		1½" (38 mm)	¾" (19 mm)
WCZEROS	0	36	72
WC1S thru WC99S	1 thru 99	36	72
WC100S	100	25	50
WC101S thru WC600S	101 thru 600	25	50
WC601 thru 605S	601, 602, 603, 604, 605	5	10
WC606-610S thru WC996-999S	606, 607, 608, 609, 610 thru 996, 997, 998, 999	5	10

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.  
Minimum order quantity is 25.




*Printed in groups of 5 identical, 5 legends per card.*

### Numbers in Sequence

Cat. No.	Legend	Markers per Legend	
		1½" (38 mm)	¾" (19 mm)
WC1 thru 33S	1 thru 33	1	2
WC34 thru 66S	34 thru 66	1	2
WC67 thru 99S	67 thru 99	1	2
WC100 thru 124S	100 thru 124	1	2
WC125 thru 149S thru WC275 thru 299S	125 thru 149 thru 275 thru 299	1	2
WC300 thru 324S thru WC1975 thru 1999S	300 thru 324 thru 1975 thru 1999	1	2

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.  
Minimum order quantity is 25.




### Numbers in Sequence Repeated

Cat. No.	Legend	Markers per Legend	
		1½" (38 mm)	¾" (19 mm)
WC1 thru 3S	1-3	12	24
WC1 thru 4S	1-4	9	18
WC1 thru 5S	1-5	7	14
WC0 thru 10S	0-10	3	6
WC1 thru 12S	1-12	3	6
WC1 thru 18S	1-18	2	4
WC19 thru 36S	19-36	2	4

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.  
Minimum quantity is 25.

# E-Z-Code®

## Wire Marker Cards – Vinyl Cloth




Fast and Easy to use paired markers in sequence to mark both ends of the wire with the same legend.

### Paired Numbers in Sequence

Cat. No.	Legend	Markers per Legend	
		1½" (38 mm)	¾" (19 mm)
WC1 thru 16PS	1 thru 16	16	32
WC17 thru 32PS	17 thru 32	16	32
WC33 thru 48PS	33 thru 48	16	32

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.




### Suffix Numbers

Cat. No.	Legend	Markers per Legend	
		1½" (38 mm)	¾" (19 mm)
WC00S	00	36	72
WC01S thru WC09S	01 thru 09	36	72
WC0009S	00 thru 09	36	72

Catalog No. WC0009S has three sequences of 00 thru 09 on a card. WC0009D has six sequences of 00 thru 09 on a card.

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.



### Solid Numbers on a Colored Background

Cat. No.	Legend	Background Color	Markers per Card	
			1½" (38 mm)	¾" (19 mm)
WCBLZEROS	0	Dark Blue	36	72
WCBL1S thru WCBL50S	1 thru 50	Dark Blue	36	72
WCGRZEROS	0	Dark Green	36	72
WCGR1S thru WCGR50S	1 thru 50	Dark Green	36	72
WCORZEROS	0	Orange	36	72
WCOR1S thru WCOR50S	1 thru 50	Orange	36	72
WCRDZEROS	0	Red	36	72
WCRD1S thru WCRD50S	1 thru 50	Red	36	72
WCYLZEROS	0	Yellow	36	72
WCYL1S thru WCYL50S	1 thru 50	Yellow	36	72


Dark blue, dark green and red markers have white legends; orange and yellow markers have black legends.

When a ¾" length marker is required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.

P

E-Z-Code®


Thomas & Betts



### Numbers in Sequence on a Colored Background

Cat. No.	Legend	Sequences per Card	
		1½" (38 mm)	¾" (19 mm)
<b>On Black</b>			
WCBK1 thru 33S	White Characters	1 thru 33	1 2
WCBK34 thru 66S		34 thru 66	1 2
WCBK67 thru 99S		67 thru 99	1 2
WCBK100 thru 124S		100 thru 124	1 2
<b>On Dark Blue</b>			
WCBL1 thru 33S	White Characters	1 thru 33	1 2
WCBL34 thru 66S		34 thru 66	1 2
WCBL67 thru 99S		67 thru 99	1 2
WCBL100 thru 124S		100 thru 124	1 2
<b>On Brown</b>			
WCBR1 thru 33S	White Characters	1 thru 33	1 2
WCBR34 thru 66S		34 thru 66	1 2
WCBR67 thru 99S		67 thru 99	1 2
WCBR100 thru 124S		100 thru 124	1 2
<b>On Dark Green</b>			
WCGR1 thru 33S	White Characters	1 thru 33	1 2
WCGR34 thru 66S		34 thru 66	1 2
WCGR67 thru 99S		67 thru 99	1 2
WCGR100 thru 124S		100 thru 124	1 2
<b>On Red</b>			
WCRD1 thru 33S	White Characters	1 thru 33	1 2
WCRD34 thru 66S		34 thru 66	1 2
WCRD67 thru 99S		67 thru 99	1 2
WCRD100 thru 124S		100 thru 124	1 2
<b>On Orange</b>			
WCOR1 thru 33S	Black Characters	1 thru 33	1 2
WCOR34 thru 66S		34 thru 66	1 2
WCOR67 thru 99S		67 thru 99	1 2
WCOR100 thru 124S		100 thru 124	1 2
<b>On Yellow</b>			
WCYL1 thru 33S	Black Characters	1 thru 33	1 2
WCYL34 thru 66S		34 thru 66	1 2
WCYL67 thru 99S		67 thru 99	1 2
WCYL100 thru 124S		100 thru 124	1 2

When a ¾" length marker is required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.



### Solid Letters


Cat. No.	Legend	Markers per Legend	
		1½" (38 mm)	¾" (19 mm)
WCAS	A	36	72
WCBS thru WCZS	B thru Z	36	72
WCLAS	a	36	72
WCLBS thru WCLZS	b thru z	36	72

Order by cards – not by individual markers. Standard box – 25 cards.

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.

# E-Z-Code®

## Wire Marker Cards – Vinyl Cloth




### Letters in Sequence

Cat. No.	Legend	Sequences per Legend	
		1½" (38 mm)	¾" (19 mm)
WCAZAJ5	A thru Z plus A thru J	1	2
WCAZ09S	A thru Z plus 0 thru 9	1	2
WCLAZAJ5	a thru Z plus a thru J	1	2

Order by cards – not by individual markers. Standard box – 25 cards.


When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.



### Letters in Sequence on a Colored Background

Cat. No.	Legend A-Z and A-J	Markers per Legend	
		1½" (38 mm)	¾" (19 mm)
WCBKA-ZS	Black (White legend)	36	72
WCLBA-ZS	Dark Blue (White legend)	36	72
WCBRA-ZS	Brown (White legend)	36	72
WCGRA-ZS	Dark Green (White legend)	36	72
WCRDA-ZS	Red (White legend)	36	72
WCORA-ZS	Orange (Black legend)	36	72
WCYLA-ZS	Yellow (Black legend)	36	72

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.



### Solid Letters and Numbers


Cat. No.	Legend	Markers per Card	
		1½" (38 mm)	¾" (19 mm)
WCA1S thru WCA5S	A1 thru A5	36	72
WCB1S thru WCB5S	B1 thru B5	36	72
WCC1S thru WCC5S	C1 thru C5	36	72
WCD1S thru WCD5S	D1 thru D5	36	72
WCE1S thru WCE5S	E1 thru E5	36	72
WCF1S thru WCF4S	F1 thru F4	36	72
WCG1S thru WCG4S	G1 thru G4	36	72
WCH1S thru WCH5S	H1 thru H5	36	72
WCJ1S thru WCJ4S	J1 thru J4	36	72
WCK1S thru WCK4S	K1 thru K4	36	72
WCL1S thru WCL5S	L1 thru L5	36	72
WCM1S thru WCM5S	M1 thru M5	36	72
WCP1S thru WCP4S	P1 thru P4	36	72
WCR1S thru WCR5S	R1 thru R5	36	72
WCS1S thru WCS5S	S1 thru S5	36	72
WCT0S thru WCT9S	T0 thru T9	36	72
WCT10S thru WCT15S	T10 thru T15	26	52
WCU1S thru WCU2S	U1 thru U2	36	72
WCV1S thru WCV2S	V1 thru V2	36	72
WCW1S thru WCW2S	W1 thru W2	36	72
WCX1S thru WCX4S	X1 thru X4	36	72
WCY1S thru WCY4S	Y1 thru Y4	36	72
WCZ1S thru WCZ4S	Z1 thru Z4	36	72

When a ¾" length marker is required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.

P

E-Z-Code®

Thomas & Betts




### Solid Symbols – Miscellaneous

Cat. No.	Legend	Markers per Card	
		1½" (38 mm)	¾" (19 mm)
WCPLSS	+	36	72
WCMINS	-	36	72
WCAPLSS	A±	25	50
WCAMINS	A-	25	50
WCBPLSS	B+	25	50
WCBMINS	B-	25	50
WCPOSS	POS	25	50
WCNEGS	NEG	25	50
WCPHS	Phase	18	36
WCPHAS	Phase A	18	36
WCPHBS	Phase B	18	36
WCPHCS	Phase C	18	36
WC1PHS	1 Phase	18	36
WC2PHS	2 Phase	18	36
WC3PHS	3 Phase	18	36
WCINS	IN	36	72
WCOUTS	OUT	25	50
WCHOTS	HOT	25	50
WCGRDS	GRD	25	50
WCNEUTS	NEUT	22	44
WCLINES	LINE	22	44
WCLPLS	L+	25	50
WCLMIS	L-	25	50
WCLOADS	LOAD	22	44
WCPUS	PU	36	72
WCGRCS	—	36	72
WCGENS	GEN	25	50
WCACCS	AC	36	72
WCDCS	DC	36	72
WCCOMS	COM	25	50
WCBATS	BAT	25	50
WCBBS	BB	36	72
WCCBS	CB	36	72
WCCTS	CT	36	72
WCIGNS	IGN	25	50
WCSIGS	SIG	25	50
WCSECS	SEC	25	50
WCPSS	PS	36	72
WCPRIS	PRI	25	50
WCPLS	PL	36	72
WCTBS	TB	36	72
WCSSS	SS	36	72
WCSPARES	SPARE	18	36
WCCYSS	~	36	72
WCGRSS	—	36	72
WCPES	PE	36	72
WCPENS	PEN	25	50
WC1US	1U	36	72
WC2US	2U	36	72
WC1VS	1V	36	72
WC2VS	2V	36	72
WC1WS	1W	36	72
WC2WS	2W	36	72

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.

# E-Z-Code®

## Wire Marker Cards – Vinyl Cloth



### Solid Symbols – Voltages


Cat. No.	Legend	Markers per Card	
		1½" (38 mm)	¾" (19 mm)
WC3VS	3V	36	72
WC6VS	6V	36	72
WC12VS	12V	25	50
WC24VS	24V	25	50
WC110VS	110V	22	44
WC115VS	115V	22	44
WC120VS	120V	22	44
WC125VS	125V	22	44
WC180VS	180V	22	44
WC220VS	220V	22	44
WC230VS	230V	22	44
WC240VS	240V	22	44
WC270VS	270V	22	44
WC280VS	280V	22	44
WC440VS	440V	22	44
WC460VS	460V	22	44
WC480VS	480V	22	44

When a ¾" length marker is required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.

P

E-Z-Code®


**Thomas & Betts**



### Solid Machine Tool Markers

Cat. No.	Legend	Markers per Card	
		1½" (38 mm)	¾" (19 mm)
WC1L1S	1L1	25	50
WC1L2S	1L2	25	50
WC1L3S	1L3	25	50
WC2L1S	2L1	25	50
WC2L2S	2L2	25	50
WC2L3S thru WC6L1S	2L3 thru 6L1	25	50
WC6L2S	6L2	25	50
WC6L3S	6L3	25	50
WC1T1S	1T1	25	50
WC1T2S	1T2	25	50
WC1T3S	1T3	25	50
WC2T1S	2T1	25	50
WC2T2S	2T2	25	50
WC2T3S thru WC7T1S	2T3 thru 7T1	25	50
WC7T2S	7T2	25	50
WC7T3S	7T3	25	50
WCLL1S	LL1	25	50
WCLL2S	LL2	25	50
WCLL3S	LL3	25	50

When a ¾" length marker is required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.








### Machine Tool Markers in Sequence

Cat. No.	Legend	Sequences per Card	
		1½" (38 mm)	¾" (19 mm)
WC1T1-3T3S	1T1, 1T2, 1T3 2T1, 2T2, 2T3 3T1, 3T2, 3T3	3	6
WC4T1-6T3S	4T1, 4T2, 4T3 5T1, 5T2, 5T3 6T1, 6T2, 6T3	3	6
WC7T1-9T3S	7T1, 7T2, 7T3 8T1, 8T2, 8T3 9T1, 9T2, 9T3	3	6
WCLL1-LL3S	LL1, LL2, LL3	9	18
WCA1-S2S	A1, A2, F1 F2, S1, S2	6	12

When a ¾" length marker is required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.

# E-Z-Code®

## Wire Marker Cards – Vinyl Cloth – Mini Markers



### Terminal Markers

Cat. No.	Legend	Sequences per Card Marker Size $\frac{5}{16}$ " x $\frac{3}{16}$ "
WC1 thru 48TM	1 thru 48	3
WC49 thru 96TM	49 thru 96	3
WCA thru ZTM	A thru Z	3

### Solid Numbers – Mini Markers

Cat. No.	Legend	Markers per Card $\frac{1}{2}$ " (13 mm)
WCZEROMIN	0	150
WC1MIN thru WC99MIN	1 thru 99	150
WC100MIN	100	102
WC101MIN thru WC250MIN	101 thru 250	102

### Numbers in Sequence – Mini Markers

Cat. No.	Legend	Markers per Card $\frac{1}{2}$ " (13 mm)
WC0 thru 49MIN	0 thru 49	3
WC50 thru 99MIN	50 thru 99	3
WC100 thru 132MIN	100 thru 132	3
WC133 thru 165MIN thru WC463 thru 495MIN	133 thru 165 thru 463 thru 495	3

### Solid Letters – Mini Markers


Cat. No.	Legend	Markers per Card $\frac{1}{2}$ " (13 mm)
WCAMIN	A	150
WCBMIN thru WCZMIN	B thru Z	150

### Letters in Sequence – Mini Markers

Cat. No.	Legend	Sequences per Card $\frac{1}{2}$ " (13 mm)
WCAZMIN	A thru Z	6

P

E-Z-Code®




**Vinyl Cloth cable markers are a large 3 1/2" (89mm) x 1/2" (13mm) marker that have many uses including large conductors, multi-wire circuits, electrical cables and tubing for hydraulic systems. Help prevent dangerous mistakes, and time consuming trial and error searches during electrical or hydraulic systems repair.**

### Solid Numbers – Cable Markers

Cat. No.	Legend	Markers per Card	
		3 1/2" (89 mm)	1 3/4" (45 mm)
WCCM0S	0	18	36
WCCM1S	1	18	36
WCCM2S	2	18	36
WCCM3S	3	18	36
WCCM4S	4	18	36
WCCM5S	5	18	36
WCCM6S	6	18	36
WCCM7S	7	18	36
WCCM8S	8	18	36
WCCM9S	9	18	36


When 1 3/4" length cable markers are required substitute the last **S** in the part number with a **D**, eg. WCCM1S would become WCCM1D.



### Solid Letters – Cable Markers

Cat. No.	Legend	Markers per Card	
		3 1/2" (89 mm)	1 3/4" (45 mm)
WCCMAS	A	18	36
WCCMBS	B	18	36
WCCMCS	C	18	36
WCCMDS	D	18	36
WCCMES	E	18	36
WCCMFS	F	18	36
WCCMNS	N	18	36

When 1 3/4" length cable markers are required substitute the last **S** in the part number with a **D**, eg. WCCM1S would become WCCM1D.




### Numbers or Letters in Sequence – Cable Markers

Cat. No.	Legend	Markers per Card	
		3 1/2" (89 mm)	1 3/4" (45 mm)
WCCM01-09S	01 thru 09	2	4
WCCM1-9S	1 thru 9	2	4
WCCM1-18S	1 thru 18	1	2
WCCM19-36S	19 thru 36	1	2
WCCM37-54S	37 thru 54	1	2
WCCM55-72S	55 thru 72	1	2
WCCM73-90S	73 thru 90	1	2
WCCM91-99S	91 thru 99	2	4
WCCMA-IS	A thru I	2	4
WCCMJ-RS	J thru R	2	4
WCCMS-ZS	S thru Z	2	4

When 1 3/4" length cable markers are required substitute the last **S** in the part number with a **D**, eg. WCCM1S would become WCCM1D.

# E-Z-Code®


## Cable Markers – Vinyl Cloth



### Solid NEMA Color Markers – No Printing

Cat. No.	Legend	Markers per Legend	
		1½" (38 mm)	¾" (19 mm)
WCBLKS	Black	36	72
WCBLDS	Blue-dark	36	72
WCBLLS	Blue-light	36	72
WCBRNS	Brown	36	72
WCGRYS	Gray	36	72
WCDGRS	Green-dark	36	72
WCGRLS	Green-light	36	72
WCMARS	Maroon	36	72
WCOLIS	Olive	36	72
WCORAS	Orange	36	72
WCPINS	Pink	36	72
WCPURS	Purple	36	72
WCREDs	Red	36	72
WCTANS	Tan	36	72
WCWHIS	White	36	72
WCYELs	Yellow	36	72


When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.



### Blank Write-On Markers

Cat. No.	Marker Size	Markers per Card	
		1½" x ¾"	¾" x 1½"
WCBW14X34D	¾" x ¾"	72	
WCBW14X112S	¾" x 1½"	36	
WCBW1132X112S	1½" x 1½"	26	
WCBW12X12D	½" x ½"	54	
WCBW12X112S	½" x 1½"	18	
WCBW58X112S	½" x 1½"	14	
WCBW34X12D	¾" x ½"	36	
WCBW34X214S	¾" x 2½"	12	
WCBW1X112S	1" x ½"	9	
WCBW112X112S	1½" x 1½"	6	

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WC1S would become WC1D.



### Vinyl Cloth, Maintenance and Production Labels (Cards)


Cat. No.	Wording	Colors Background	Labels per Card	Label Size W L
				1½" x ¾"
WCMP5	Accepted	Green	14	1½" x ¾"
WCMP1	Calibrated	Black	14	1½" x ¾"
WCMP26	Calibration	Green	14	1½" x ¾"
WCMP2	Certification	Black	14	1½" x ¾"
WCMP18	Due For Inspection	Orange	14	1½" x ¾"
WCMP4	Rejected	Red	14	1½" x ¾"
WCMP25	Tested	Green	14	1½" x ¾"
WCMP75	Calibration	Green	9	2½" x 1"

**T&B** maintenance and production labels have been designed to provide extra-added convenience through positive, protected clear identification. Coding, dating, testing, inspecting and recordkeeping data are maintained through consistent labeling.

P

E-Z-Code®


**Thomas & Betts**



### Solid Numbers

Cat. No.	Legend	Markers per Card	
		1½" (38 mm)	¾" (19 mm)
WSZEROS	0	36	100
WS1S thru WS99S	1 thru 99	36	100
WS100S	100	25	68
WS101S thru WS600S	101 thru 600	25	

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WS1S would become WS1D.




### Numbers in Sequence

Cat. No.	Legend	Markers per Card	
		1½" (38 mm)	¾" (19 mm)
WS1 thru 95	1 thru 9	4	
WS0 thru 49D*	0 thru 49		2
WS50 thru 99D*	50 thru 99		2
WS1 thru 33S	1 thru 33	1	
WS34 thru 66S	34 thru 66	1	
WS67 thru 99S	67 thru 99	1	
WS100 thru 124S	100 thru 124	1	
WS125 thru 149S thru WS975 thru 999S	125 thru 149 thru 975 thru 999	1	

\* Only available in double tab.

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WS1S would become WS1D.




### Solid Letters

Cat. No.	Legend	Pairs of Markers per Card	
		1½" (38 mm)	¾" (19 mm)
WSAS	A	36	100
WSBS thru WSZS	B thru Z	36	100

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WS1S would become WS1D.

# E-Z-Code®


## Wire Marker Cards – Vinyl Self-Laminating



### Solid Letters and Numbers

Cat. No.	Legend	Markers per Card	
		1½" (38 mm)	¾" (19 mm)
WSA1S	A1	36	100
WSA2S	A2	36	100
WSA3S	A3	36	100
WSA4S	A4	36	100
WSD1S thru WSD5S	D1 thru D5	36	100
WSF1S	F1	36	100
WSF2S	F2	36	100
WSL1S thru WSL5S	L1 thru L5	36	100
WSS1S	S1	36	100
WSS2S	S2	36	100
WST1S thru WST6S	T1 thru T6	36	100
WSX1S	X1	36	100
WSX2S	X2	36	100
WSSPARES	SPARE	18	25
WSGRDS	GROUND	18	25

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WS1S would become WS1D.



### Letters and Numbers in Sequence


Cat. No.	Legend	Sequences per Card	
		1½" (38 mm)	¾" (19 mm)
WSAZ09S	A thru Z plus 0 thru 9	1	2

When ¾" length markers are required substitute the last **S** in the part number with a **D**, eg. WS1S would become WS1D.

P


E-Z-Code®

**Thomas & Betts**




### Blank Write-On Markers

Cat. No.	Description	Width of Each Marker	Markers per Card 1½" (38 mm)
WSBW14x112S		1/4" (6mm)	36
WSBW38x112S		3/8" (10mm)	26
WSBW12x112S	Single markers	1/2" (13 mm)	18
WSBW34x112S		3/4" (19mm)	12
WSBW1x112S		1" (25mm)	9
WSBW112x112S		1½" (38mm)	6



### Blank Write-On Markers


Cat. No.	Description	Width of Each Marker	Markers per Card 1¾" (38 mm)
WSBW18x34D		1/8" (3mm)	144
WSBW950x34D		3/16" (5mm)	100
WSBW14x34D		1/4" (6mm)	72
WSBW38x34D	Double markers	3/8" (10mm)	52
WSBW12x34D		1/2" (13mm)	36
WSBW34x34D		3/4" (19mm)	24
WSBW1x34D		1" (25mm)	18
WSBW112x34D		1½" (38mm)	12





**Self-laminating write-on markers are made from a durable Vinyl material to provide excellent legend protection. These self-laminating write-on markers protect your code, even when submerged in water and oils. Constructed of Vinyl plastic with a write-on area and a transparent extension that laminates the code when wrapped around itself.**

1. Apply legend area to cable first.
2. Roll the clear area around the cable, making sure it covers the legend.
3. Legend is protected against water, grease, chemicals and other foreign matter.

Make your own laminated markers by using these blank write-ons.




## Standard Wire Marker Combination Packs



**T&B offers three styles of combination packs to help you to easily meet your needs for wire identification. In addition to the convenience of ordering sets of marker cards by the pack you save money over buying individual cards.**

- **WBC Vinyl Cloth**
- **WBC Vinyl Cloth mini's**
- **WSL Vinyl Self-Laminating**



### WBC Vinyl Cloth

Cat. No. Single Markers 1½" (38 mm)	Legend (one card each legend in each pack)
<b>WCCP1 thru 25S</b>	1 thru 25
<b>WCCP26 thru 50S</b>	26 thru 50
<b>WCCP51 thru 75S</b>	51 thru 75
<b>WCCP76 thru 100S</b>	76 thru 100
<b>WCCP101 thru 125S thru WCCP576 thru 600S</b>	101 thru 125 thru 576 thru 600
<b>WCCPA thru ZS</b>	A thru Z

When ¾" length markers are required substitute the last S in the part number with a D, e.g., WCCP1-25D.

### WSL Vinyl Self-Lam

Cat. No. Single Markers 1½" (38 mm)	Legend (one card each legend in each pack)
<b>WSCP1 thru 25S</b>	1 thru 25
<b>WSCP26 thru 50S</b>	26 thru 50
<b>WSCP51 thru 75S</b>	51 thru 75
<b>WSCP76 thru 100S</b>	76 thru 100
<b>WSCP101 thru 125S thru WSCP576 thru 600S</b>	101 thru 125 thru 576 thru 600
<b>WSCPA thru ZS</b>	A thru Z

When ¾" length markers are required substitute the last S in the part number with a D, e.g., WSCP1-25S, WSCP1-25D.

### WBC Vinyl Cloth Mini-Marker

Cat. No. Triple Markers ½" (13 mm)	Legend (one card each legend in each pack)	Markers per Card
<b>WCCP1 thru 25MIN</b>	1 thru 25	150
<b>WCCP26 thru 50MIN thru WCCP226 thru 250MIN</b>	26 thru 50 thru 226 thru 250	150
<b>WCCPA thru ZMIN</b>	A thru Z	150

How to order: Each catalog number is for one pack of assorted marker cards. For example: Catalog number WCCP1-25S is one pack of cloth wire markers containing one card each of a solid card number 1, 2, 3 etc. thru 25.

Important: Order combination packs by the pack not by the card; letter packs A to Z contain 26 cards.



Identify all electrical systems, including conduits, buss ducts, cable trays, load centers, circuit breakers, switches or any other vital electrical equipment with T&B's Self-Sticking WDA Vinyl Electrical markers. Help prevent dangerous mistakes, time consuming trial and error searching during electrical service work. Manufactured of rugged WDA Self-Sticking Vinyl with high contrast black printing for OSHA compliance and visibility.



STYLE A: 2 1/4" x 9"  
(1 marker per card)



STYLE B: 1 1/8" x 4 1/2"  
(4 markers per 2 1/4" x 9" card)



STYLE C: 1/2" x 2 1/4"  
(18 markers per 2 1/4" x 9" card)  
Black letters on orange background


### WDA Vinyl, Conduit and Electrical Markers

Style A 2 1/4" x 9"	Style B 1 1/8" x 4 1/2"	Style C 1/2" x 2 1/4"	Legend (Black on Orange)
WJT-5010	WDT-5010	WAT-5010	110 VOLTS
WJT-5011	WDT-5011	WAT-5011	115 VOLTS
WJT-5012	WDT-5012	WAT-5012	120 VOLTS
WJT-5045	WDT-5045	WAT-5045	120/208 VOLTS
WJT-5013	WDT-5013	WAT-5013	208 VOLTS
WJT-5014	WDT-5014	WAT-5014	220 VOLTS
WJT-5015	WDT-5015	WAT-5015	230 VOLTS
WJT-5016	WDT-5016	WAT-5016	240 VOLTS
WJT-5017	WDT-5017	WAT-5017	250 VOLTS
WJT-5018	WDT-5018	WAT-5018	277 VOLTS
WJT-5046	WDT-5046	WAT-5046	277/480 VOLTS
WJT-5057	WDT-5057	WAT-5057	380 VOLTS
WJT-5044	WDT-5044	WAT-5044	415 VOLTS
WJT-5019	WDT-5019	WAT-5019	440 VOLTS
WJT-5020	WDT-5020	WAT-5020	460 VOLTS
WJT-5021	WDT-5021	WAT-5021	480 VOLTS
WJT-5022	WDT-5022	WAT-5022	550 VOLTS
WJT-5023	WDT-5023	WAT-5023	600 VOLTS
WJT-5024	WDT-5024	WAT-5024	2200 VOLTS
WJT-5025	WDT-5025	WAT-5025	2300 VOLTS
WJT-5026	WDT-5026	WAT-5026	2400 VOLTS
WJT-5027	WDT-5027	WAT-5027	4160 VOLTS
WJT-5028	WDT-5028	WAT-5028	4800 VOLTS
WJT-5058	WDT-5058	WAT-5058	5000 VOLTS
WJT-5029	WDT-5029	WAT-5029	6900 VOLTS
WJT-5030	WDT-5030	WAT-5030	7200 VOLTS
WJT-5059	WDT-5059	WAT-5059	12,000 VOLTS
WJT-5060	WDT-5060	WAT-5060	13,000 VOLTS
WJT-5047	WDT-5047	WAT-5047	13,200 VOLTS
WJT-5031	WDT-5031	WAT-5031	13,800 VOLTS
WJT-5032	WDT-5032	WAT-5032	AC
WJT-5043	WDT-5043	WAT-5043	Air Conditioning
WJT-5052	WDT-5052	WAT-5052	Circuit Breaker
WJT-5051	WDT-5051	WAT-5051	Circuit #____
WJT-5038	WDT-5038	WAT-5038	DC
WJT-5050	WDT-5050	WAT-5050	Electric Out of Service
WJT-5033	WDT-5033	WAT-5033	Emergency Service
WJT-5039	WDT-5039	WAT-5039	Exit Lights
WJT-5040	WDT-5040	WAT-5040	Fire Alarm
WJT-5053	WDT-5053	WAT-5053	Fuse Box
WJT-5041	WDT-5041	WAT-5041	Heating Circuit
WJT-5037	WDT-5037	WAT-5037	Lights
WJT-5042	WDT-5042	WAT-5042	Light & Power
WJT-5048	WDT-5048	WAT-5048	On/Off
WJT-5036	WDT-5036	WAT-5036	Power
WJT-5034	WDT-5034	WAT-5034	Single Phase
WJT-5055	WDT-5055	WAT-5055	Spare
WJT-5056	WDT-5056	WAT-5056	Telephone
WJT-5035	WDT-5035	WAT-5035	Three Phase
WJT-5054	WDT-5054	WAT-5054	____ VOLTS

Standard package quantity 25 cards.

# E-Z-Code®


## Industrial Markers



### Number or Letters, WBC Vinyl Cloth


#### Series 003

Cat. No.	Description	Legend	Character Height	Marker Size W	Marker per Card
WCNL003A thru WCNL003Z	Letters	A thru Z	5/16"	3/8" x 1/2"	78
WCNL003ZERO	Numbers	0	5/16"	3/8" x 1/2"	78
WCNL0031 thru WCNL0039	Numbers	1 thru 9	5/16"	3/8" x 1/2"	78
WCNL003AZ	Letters in sequence	A thru Z (3 each)	5/16"	3/8" x 1/2"	78
WCNL00309	Numbers in sequence	0 thru 9 (7 each)	5/16"	3/8" x 1/2"	70
WCNL003AZ09	Letter & Number Combination – in seq.	A thru Z and 0 thru 9 (2 each)	5/16"	3/8" x 1/2"	72



#### Series 063

Cat. No.	Description	Legend	Character Height	Marker Size W	Marker per Card
WCNL063A thru WCNL063Z	Letters	A thru Z	5/8"	9/16" x 3/4"	32
WCNL063ZERO	Numbers	0	5/8"	9/16" x 3/4"	32
WCNL0631 thru WCNL0639	Numbers	1 thru 9	5/8"	9/16" x 3/4"	32
WCNL063AZ	Letters in sequence	A thru Z (1 each)	5/8"	9/16" x 3/4"	32
WCNL06309	Numbers in sequence	0 thru 9 (3 each)	5/8"	9/16" x 3/4"	32



#### Series 100

Cat. No.	Description	Legend	Character Height	Marker Size W	Marker per Card
WCNL100A thru WCNL100Z	Letters	A thru Z	1"	7/8" x 1 1/2"	10
WCNL100ZERO	Numbers	0	1"	7/8" x 1 1/2"	10
WCNL1001 thru WCNL1009	Numbers	1 thru 9	1"	7/8" x 1 1/2"	10
WCNL100AJ	Letters in sequence	A thru J	1"	7/8" x 1 1/2"	10
WCNL100KT	Letters in sequence	K thru T	1"	7/8" x 1 1/2"	10
WCNL100UZ	Letters in sequence	U thru Z	1"	7/8" x 1 1/2"	10
WCNL10009	Numbers in sequence	0 thru 9	1"	7/8" x 1 1/2"	10



#### Series 200

Cat. No.	Description	Legend	Character Height	Marker Size W	Marker per Card
WCNL200A thru WCNL200Z	Letters	A thru Z	2"	7/8" x 2 1/4"	10
WCNL200ZERO	Numbers	0	2"	7/8" x 2 1/4"	10
WCNL2001 thru WCNL2009	Numbers	1 thru 9	2"	7/8" x 2 1/4"	10
WCNL200AJ	Letters in sequence	A thru J	2"	7/8" x 2 1/4"	10
WCNL200KT	Letters in sequence	K thru T	2"	7/8" x 2 1/4"	10
WCNL200UZ	Letters in sequence	U thru Z	2"	7/8" x 2 1/4"	10
WCNL20009	Numbers in sequence	0 thru 9	2"	7/8" x 2 1/4"	10

Packed 5 identical per plastic bag.

P

E-Z-Code®

Thomas & Betts



**High contrast reflective yellow on a black background, three standard sizes are available.**  
**Durable, trouble-free WRM Reflective Industrial Markers reflect light up to 100 times brighter than white or yellow painted surfaces.**  
**Manufactured from self-sticking WRM reflective material, these markers keep right on performing even in the most severe weather conditions.**



**T&B has put our most popular size reflective markers in a kit. Manufactured from the same tough materials as the individual markers, the kit will keep the WRUM series markers organized and free from damage and that means economy.**

### Reflective Industrial Markers

Cat. No.	Size	Description	
		Character Height	Marker Size
WRSUM*	Small	1½"	1¾" x 1¾"
WRUM*	Standard	2½"	1¾" x 2¾"
WRLUM*	Large	3¾"	2¾" x 4¾"

\* Add Letter (A-Z) or Number (0-9) desired in place of asterisk to complete Cat. No. Example **WRSUM1, WRSUM2, WRSUMA** etc.

25 single markers per bag.

### Reflective Industrial Marker Kits

Cat. No.	Marker Series	Contents
NB-0056	WRUM Markers Marker Size 1¾" x 2¾" Character Height 2½"	50 zeros 50 number one 25 each two thru nine total 300 reflective markers
NB-0057	WRUM Markers Marker Size 1¾" x 2¾" Character Height 2½"	Letter Kit 320 letters A-Z

Each kit is shipped within its own sealed plastic bag to insure factory newness until needed.

# E-Z-Code®

## Roll Wire Marker Dispenser



- Wire marking is simple, clean and fast...just pull tape out, tear and wrap. Compact size fits in your pocket or hangs from work belt.

- Unique design allows easy access to all legends during use or when refilling.
- Lifetime guarantee on T&B pack dispenser.

### Wire Marker Dispenser

Cat. No.	Description
WDFP	Empty Dispenser
WDFP-0-9	Loaded Dispenser with Legends 0 thru 9
WDFP-NEMA	Loaded Dispenser with 10 NEMA colors

### Refills – Polyester Tape

Cat. No.	Legend	Rolls	Cat. No.	Legend	Rolls
WDFPR-0	0	10	WDFPR-T1	T1	10
WDFPR-1	1	10	WDFPR-T2	T2	10
WDFPR-2	2	10	WDFPR-T3	T3	10
thru WDFPR-9	thru 9	10	WDFPR-MIN	–	10
WDFPR-0-9	0-9	1*	WDFPR-BLS	+	10
WDFPR-10-19	10-19	1*	WDFPR-YEL	YELLOW	10
WDFPR-A	A	10	WDFPR-WHT	WHITE	10
thru WDFPR-B-Z	thru Z	10	WDFPR-BLK	BLACK	10
WDFPR-L1	L1	10	WDFPR-BRN	ORANGE	10
WDFPR-L2	L2	10	WDFPR-BLU	BLUE	10
WDFPR-L3	L3	10	WDFPR-GRN	GREEN	10
			WDFPR-RED	RED	10

\*1 Pkg. equals 10 rolls, one of each number in the series.

P

E-Z-Code®

**Thomas & Betts**

# E-Z-Code®

## Color-Coded I.D. Tape



### Color-Coded I.D. Tape

Cat. No. 1" Wide	Cat. No. 2" Wide	Cat. No. 3" Wide	Cat. No. 4" Wide	Color
AA-1121	BA-1121	CA-1121	NA-1121	Silver
AA-1122	BA-1122	CA-1122	NA-1122	Black
AA-1123	BA-1123	CA-1123	NA-1123	Blue
AA-1124	BA-1124	CA-1124	NA-1124	Brown
AA-1125	BA-1125	CA-1125	NA-1125	Green
AA-1126	BA-1126	CA-1126	NA-1126	Orange
AA-1127	BA-1127	CA-1127	NA-1127	Purple
AA-1128	BA-1128	CA-1128	NA-1128	Red
AA-1129	BA-1129	CA-1129	NA-1129	White
AA-1130	BA-1130	CA-1130	NA-1130	Yellow
AA-1131	BA-1131	CA-1131	NA-1131	Clear

60 yards per roll

### Tel-A-Code Kits

Cat. No.	Description
NB-0060	Tel-A-Code Kits contain ten 20-foot rolls of 12 different colors and are packed and sold as individual kits; 1" wide rolls



P

E-Z-Code®

**Thomas & Betts**



### Barricade Tape

Bright colors are not the only advantages of these Barricade Tapes. T&B's attention-getting Barricade Tape is also inexpensive and easy to handle. Protect-A-Line tape is ideal for marking hazardous or off-limit areas. Convenient and reusable, it performs well both indoors and out-of-doors.

- Available in 3" X 1000' rolls.



### Buried Utility Tape

Now you can help insure against costly dig-ins. Place T&B's Buried Utility Tape 1 to 1½ feet below the ground surface directly above the pipeline or cable below. Bright fade resistant colors warn equipment operators that a vital pipeline or cable is BURIED BELOW, before damage occurs. Buried utility tapes are printed black on a bright background.

- Available in 3" and 6" widths.



### Foil Backed Detectable Buried Utility Tape

In addition to bright colors, the Foil Backed Detectable Tape features a metallic backing that is designed to be detectable under normal earthen surfaces up to 18" with common metal detectors. A simple and fast method to relocating lines, cables and conduit for future renovation.

- Available in 3" and 6" widths.

## Protect-A-Line® Barricade and Burial Tapes

Cat. No.	Legend	Color
<b>Surveyors Tape 1½" x 1000'</b>		
NA-0200	No Legend, No Printing	Yellow
NA-0201	No Legend, No Printing	Red
NA-0202	No Legend, No Printing	Green
NA-0203	No Legend, No Printing	Blue
NA-0204	No Legend, No Printing	Orange
<b>Barricade Tape 3" x 1000'</b>		
NA-0250	CAUTION	Yellow
NA-0253	CAUTION CONSTRUCTION AREA	Yellow
NA-0254	CAUTION DO NOT ENTER	Yellow
NA-0256	CAUTION HARD HAT AREA	Yellow
NA-0257	CAUTION HIGH VOLTAGE	Yellow
NA-0258	CAUTION MEN WORKING	Yellow
NA-0261	CAUTION OPEN TRENCH	Yellow
NA-0267	DANGER, on Stripes	Red & White
<b>Buried Utility Tape 3" x 1000'</b>		
NA-0600	ELECTRIC LINE	Red
NA-0608	ELECTRIC LINE	Yellow
NA-0601	WATER LINE	Blue
NA-0602	TELEPHONE LINE	Orange
NA-0603	GAS LINE	Yellow
NA-0605	SEWER LINE	Green
NA-0606	HIGH VOLTAGE LINE	Red
NA-0609	FIBER OPTIC CABLE	Orange
<b>Foil Backed Detectable Buried Utility Tape 3" x 1000'</b>		
NAF-0600	ELECTRIC LINE	Red
NAF-0608	ELECTRIC LINE	Yellow
NAF-0601	WATER LINE	Blue
NAF-0602	TELEPHONE LINE	Orange
NAF-0603	GAS LINE	Yellow
NAF-0604	OIL LINE	Yellow
NAF-0605	SEWER LINE	Green
NAF-0606	HIGH VOLTAGE LINE	Red
NAF-0607	CABLE TV LINE	Orange
NAF-0609	FIBER OPTIC CABLE	Orange
<b>Buried Utility Tape 6" x 1000'</b>		
NA-0700	ELECTRIC LINE	Red
NA-0708	ELECTRIC LINE	Yellow
NA-0701	WATER LINE	Blue
NA-0702	TELEPHONE LINE	Orange
NA-0703	GAS LINE	Yellow
NA-0706	HIGH VOLTAGE LINE	Red
NA-0709	FIBER OPTIC CABLE	Orange
<b>Foil Backed Detectable Buried Utility Tape 6" x 1000'</b>		
NAF-0700	ELECTRIC LINE	Red
NAF-0708	ELECTRIC LINE	Yellow
NAF-0701	WATER LINE	Blue
NAF-0702	TELEPHONE LINE	Orange
NAF-0703	GAS LINE	Yellow
NAF-0704	OIL LINE	Yellow
NAF-0705	SEWER LINE	Green
NAF-0706	HIGH VOLTAGE LINE	Red
NAF-0707	CABLE TV LINE	Orange
NAF-0709	FIBER OPTIC CABLE	Orange

Note: All tapes are WBT 4 MIL polyethylene. They are not pressure sensitive. All legends are printed in black. Standard Package is 1 Roll.

# E-Z-Code®

## Tape And Markers



*Fast one step application of Self-Sticking HAZARDSTRIPÉ roll tapes save time and money over painting. Bold HAZARDSTRIPÉ tapes effectively warn of hazards, identify the protection equipment, traffic and housekeeping markings. All purpose tape, ideal for temporary hazards or markings. vinyl cloth HAZARDSTRIPÉ tapes are in 30 yard rolls.*

### Self-Sticking Vinyl Cloth Tape

Cat. No. 2" Wide	Cat. No. 3" Wide	Cat. No. 4" Wide	Color
<b>AZ-1100</b>	<b>BZ-1100</b>	<b>CZ-1100</b>	Black & Yellow Stripe
<b>AZ-1102</b>	<b>BZ-1102</b>	<b>CZ-1102</b>	Red & White Stripe
<b>AZ-1303</b>	<b>BZ-1303</b>	<b>CZ-1303</b>	Magenta and Yellow Stripe and Radiation Symbol

Length each roll—30 yards

*Long-lasting, smooth laminated vinyl roll tape is ideal temporary or permanent marking. WVP tapes are available in 18 yard rolls. Made of reflective material for permanent, all weather performance. Light that is directed on WRM reflective tape is bounced back with amazing brilliance—up to 200 times greater reflection than white or yellow paint surfaces.*

### Self-Sticking Laminated Vinyl Tape


Cat. No. 2" Wide	Cat. No. 3" Wide	Cat. No. 4" Wide	Color
<b>AZ-2104</b>	<b>BZ-2104</b>	<b>CZ-2104</b>	Black & Yellow Stripes
<b>AZ-2106</b>	<b>BZ-2106</b>	<b>CZ-2106</b>	Red & White Stripe

Length each roll—18 yards

### Self-Sticking Reflective Roll Tape

Cat. No. 2" Wide	Cat. No. 3" Wide	Cat. No. 4" Wide	Color
<b>AZ-3108</b>	<b>BZ-3108</b>	<b>CZ-3108</b>	Black & Yellow Stripe
<b>AZ-3110</b>	<b>BZ-3110</b>	<b>CZ-3110</b>	Red & White Stripe

Length each roll—5 yards



*Each T&B WVP Rigid Vinyl Sign still comes with self-sticking mounting pads and drilled corner mounting holes. This tape is easy to use and provides maximum adhesion on most all smooth clean dry surfaces.*

### Foam Mounting Tape—2 sided

Cat. No.	Description
<b>NA-0365</b>	2-Sided Foam Mounting Tape, length each roll—9 yards


P

E-Z-Code®

**Thomas&Betts**

# E-Z-Code®

## Customized Embossed Tags Stainless Steel Tape Embossing System



**Identify your cable bundles with permanent, Type 304 stainless steel imprinted tags applied with stainless steel cable ties. After imprinting the tags, merely slip a tie through slots in the tag and fasten with the installation tool.**

- Works with  $\frac{1}{4}$ " wide ties.

### I.D. Tagging System

Cat. No.	Width		Length		Weight	
	in.	mm	in.	mm	lbs.	kg.
SSID100	.75	19.05	2.0	51	0.5	.22
SSID101	1.50	38.10	2.5	63	1.2	.55
SSID102	.75	19.05	3.5	89	0.8	.36


304 Stainless Steel

Packaging Quantity: 100/box

.015" (.254mm) Thickness

Note: Customized pre-embossed tags are available. Please consult Customer Service for details.

Add suffix (316) for 316 Stainless Steel.



### I.D. Tag Imprinter

Cat. No.	Description	Weight	
		lbs.	kg.
WTID200	I.D. Tag Imprinter	29.5	13.41
WTID281	$\frac{1}{8}$ " character imprinting wheel	—	—
WTID283	$\frac{3}{16}$ " character imprinting wheel	—	—
WTID290	$\frac{3}{32}$ " character imprinting wheel	—	—

Packaging Quantity: 1/box

**For imprinting Thomas & Betts stainless steel I.D. tags. Includes special tag holder which provides quick, accurate positioning of tag. Comes with a  $\frac{3}{32}$ " character imprinting wheel.**



### S.S. Tape Embossing System

Cat. No.	Description	Weight	
		lbs.	kg.
WTID400	Hand-held tool for embossing S.S. I.D. Tape	2.57	1.17
WTID405	Replacement S.S. tape (21' long)	.18	.01

304 Stainless Steel

Packaging Quantity: 1/box

Note: The embossing tool comes complete with two rolls of stainless steel tape.

**After making your tag, apply with stainless steel cable ties.**


P

E-Z-Code®

**Thomas & Betts**

# E-Z-Code®

## Stainless Steel I.D. Tag



**The Thomas & Betts Stainless Steel R.D. Tagging System includes a complete range of individual letters, numbers, and symbols—slip them over carriers (shown above) or strips (below) and attach to your cable or hose with a variety of Thomas & Betts Stainless Steel Cable Ties.**



### Thomas & Betts Stainless Steel I.D. Tag

Cat. No.	Description	Length	Width	Std. Pkg.	Wt. per 100
ER010	A	.445"	.375"	100	.31
ER011	B	.445"	.375"	100	.31
ER012	C	.445"	.375"	100	.31
ER013	D	.445"	.375"	100	.31
ER014	E	.445"	.375"	100	.31
ER015	F	.445"	.375"	100	.31
ER016	G	.445"	.375"	100	.31
ER017	H	.445"	.375"	100	.31
ER018	I	.445"	.375"	100	.31
ER019	J	.445"	.375"	100	.31
ER020	K	.445"	.375"	100	.31
ER021	L	.445"	.375"	100	.31
ER022	M	.445"	.375"	100	.31
ER023	N	.445"	.375"	100	.31
ER024	O	.445"	.375"	100	.31
ER025	P	.445"	.375"	100	.31
ER026	Q	.445"	.375"	100	.31
ER027	R	.445"	.375"	100	.31
ER028	S	.445"	.375"	100	.31
ER029	T	.445"	.375"	100	.31
ER030	U	.445"	.375"	100	.31
ER031	V	.445"	.375"	100	.31
ER032	W	.445"	.375"	100	.31
ER033	Y	.445"	.375"	100	.31
ER034	Z	.445"	.375"	100	.31
ER018	1	.445"	.375"	100	.31
ER037	2	.445"	.375"	100	.31
ER038	3	.445"	.375"	100	.31
ER039	4	.445"	.375"	100	.31
ER040	5	.445"	.375"	100	.31
ER041	6	.445"	.375"	100	.31
ER021	7	.445"	.375"	100	.31
ER042	8	.445"	.375"	100	.31
ER041	9	.445"	.375"	100	.31
ER024	0	.445"	.375"	100	.31
ER035	Minus/Hyphen	.445"	.375"	100	.31
ER036	Blank	.445"	.375"	100	.31
ER046	Plus +	.445"	.375"	100	.31
ER047	Earth	.445"	.375"	100	.31
ER048	Sine	.445"	.375"	100	.31
ER049	Slash /	.445"	.375"	100	.31

Character size .218"

Material .025 316 stainless steel

### Thomas & Betts Stainless Steel I.D. Tag Strips/Carriers

Cat. No.	Description	Length	Width	Std. Pkg.	Wt. per 100
ER043	6 Character Carrier	3.64"	.38"	100	.73
ER044	10 Character Carrier	5.14"	.38"	100	1.25
ER045	16 Character Carrier	7.39"	.38"	100	1.47
ER050	Short Strip	4.25"	.38"	100	.98
ER051	Medium Strip	5.75"	.38"	100	1.33
ER052	Long Strip	8.0"	.38"	100	1.85
ER060	I.D. Tag Kit	—	—	1	—

I.D. Tag Kit contains 50 of each letter, number, symbol, carrier and strip in a handy carrying case.

# E-Z-Code®

## PVC Sleeve and Clip-On Markers



**The pre-printed sleeve wire markers permanently identify wires, cables, leads, harnesses, terminals, connectors and component parts to facilitate the installation, repair and servicing of equipment during production or maintenance. Sleeve markers are available in a variety of sizes and materials to meet all your needs—resistant to most chemicals, oils, solvents, fungus. Performs well in low and high temperatures.**



### Sleeve Markers

Cat. No.	Recommended Wire Range	AWG	Standard Legends	Color	Package
<b>SMS118*</b>	.051-.118	22-16	A-Z		10 strips of 25 markers
<b>SMS196*</b>	.098-.196	16-10		White	10 strips of 25 markers
<b>SMS394*</b>	.157-.394	10-4	0-9	w/Black	10 strips of 25 markers
<b>SMS630*</b>	.315-.630	6-00	/ = SLA, + = PLS, = = GRD,	Legend	20/Bag Loose
<b>†SMS984*</b>	.551-.984	0-350	- = MIN and blank		20/Bag Loose

\* To Order: Add letter, number or symbol desired in place of asterisk to complete each Cat. No.

† Must be ordered as special item.

Other colors are available as specials. Contact customer service for availability.

### Sleeve Markers

(1000 continuous on a reel)

Cat. No.	Recommended Wire Range	AWG	Standard Legends	Color	Package
<b>SMR118*</b>	.051-.118	22-16	A-Z	White	1000 markers
<b>SMR196*</b>	.098-.196	16-10	0-9	w/Black	continuous
<b>SMR394*</b>	.157-.394	10-4	/ = SLA, + = PLS, = = GRD,	Legend	on a reel
			- = MIN and blank		

\* To Order: Add letter, number or symbol desired in place of asterisk to complete each Cat. No.

### Clip-on Markers

Cat. No.	Recommended Wire Range	AWG	Standard Legends	Color	Package
<b>SMC118*</b>	.094-.118	18-16	A-Z	White	200/bag attached
<b>SMC157*</b>	.118-.157	16-14	0-9	w/Black	200/bag attached
<b>SMC197*</b>	.157-.197	12-10	/ = SLA, + = PLS,	Legend	200/bag attached
<b>SMC244*</b>	.197-.244	8-6	- = MIN and blank		200/bag attached

\* To Order: Add letter, number or symbol desired in place of asterisk to complete each Cat. No.

### Magazine Dispenser Feeds Left or Right

Cat. No.	Description	Recommended Wire Range	AWG	Legend	Color	Pkg.
<b>SMPP196A</b>	20 Strips of 25 Markers	.098-.196	16-10	0-9	White w/ Black legend	1
				0-9 and tool		
<b>SMPPT196A</b>	20 Strips of 25 Markers w/tool	.098-.196	16-10	0-9	White w/ Black legend	1
<b>SMPPCT196A</b>	21 Strips of Markers w/tool, assorted colors	.098-.196	16-10	0-9	Assorted Colors	1

### Application tools

Cat. No.	Description	Recommended Wire Range	AWG	Package
<b>SMAT118</b>	Application Tool	.051-.118	22-16	5/bag
<b>SMAT196</b>	Application Tool	.098-.196	16-10	5/bag

P

E-Z-Code®



# E-Z-Code®

## Lockout/Tagout



### Single Pole Circuit Breaker Lockout

'No Hole' Circuit Breaker Lockout device will lock out most single pole circuit breakers. Easy to install, provides secure locking protection. Device also available for 480/600 volt switches.



### Multi Pole Circuit Breaker Lockout

Multi-Pole lockout works with most major multi-pole breakers with tie-bar. Very convenient because no self-locking tie or screwdriver is needed to install.



### Plug Lockout

Designed for heavy duty applications, the Plug Lockout is an inexpensive way to safely lock out electrical plugs. Made of rugged polypropylene, the lockouts are available in two sizes: one to fit standard 110-volt grounded plugs and a larger size for 220- and 550-volt plugs.



### Gate Valve Lockout

Make locking out valves safe and easy. Available in five sizes to fit valve handles from 1 to 13 inches in diameter. Made of durable, non-adherent plastic to resist chemicals and hot and cold temperatures. Stainless steel hinge design adds strength & security. Unique knockout feature accommodates OS&Y or 'rising stem' gate valves.



### Cable Lockout

Flexible cable will lock out ALL sizes of gate valves & multiple disconnects in various energy distribution centers. Better than chains and just as effective, but a lot less weight. Great for security use too.



### Standard Ball Valve Lockout

Fits all major brand ball valves. Simple one-piece design makes it easy to use.

## E-Z Code® Lockout Devices

It is vitally important to control hazardous energy sources during servicing and maintenance of machines and equipment. The unexpected start up of the machines or equipment or release of stored energy could cause injury to employees. OSHA generally requires that energy sources for equipment be turned off or disconnected and that the switch either be locked or labeled with a warning tag. OSHA estimates compliance with the standard will prevent about 120 fatalities and approximately 28,000 serious and 32,000 minor injuries each year.



E-Z-Code offers an inclusive product line to supply the general requirements of the OSHA Lockout/Tagout standard. From comprehensive training videos to circuit breaker locking devices, E-Z-Code Lockout/Tagout products help insure that general industry workers will be protected from accidents during maintenance and servicing of equipment.

## Three Steps for Compliance

OSHA: Lockout/Tagout standard (29 CFR 1910.147) requires that all energy sources be turned off and "locked out" while machines are being serviced or maintained. Compliance with this regulation requires three basic steps ...

### Step 1: Develop a Written Program

This involves identifying and writing procedures for the control of hazardous energy. This also includes preparation for shutdown, equipment isolation, Lockout/Tagout application, release of stored energy and verification of energy isolation to each piece of equipment.

### Step 2: Training Employees


Both affected and authorized employees must be trained in the specific energy control procedures established by the company. Verification of this training is required.

### Step 3: Implement the Program

In addition to developing formal written procedures and training employees, T&B offers a variety of padlocks, tags, signs and lockout devices to help you implement lockout procedures for many different energy sources including: electricity, pneumatics, steam, gas, liquids, and many others.

# E-Z-Code®

## Lockout/Tagout



*The Lockout Compliance Manual helps you format your written program.*

### Lockout Compliance Manual

This two volume compliance set contains samples that highlight what OSHA is looking for and demonstrates what you must do to comply with Lockout/Tagout regulations. It helps you format your written program and gets you started on compliance. Remember, not having a thorough, written energy control program is the most common violation cited by OSHA.

#### Hazardous Energy Control Manual

85-page manual includes:

- Step-by-step instructions for developing your Lockout/Tagout compliance program.
- Suggested training program including outlines, training notes and handout materials.

- Forms and checklists for developing your hazardous energy control procedures.
- Sample programs and procedures.
- Copy of OSHA Standard 29 CFR 1910.147.


#### Hazardous Energy Control Procedures

Includes:

- Sample programs and forms for completing your inventory listing, equipment procedures and employee training log.
- Three ring binder designed to contain your written program and related information.

### Compliance Manuals

Cat. No.	Description	Qty.
LO16-103	Lockout/Tagout Manual and Procedures	1/pkg.



*Learn from other worker's tragic mistakes in this dramatic Lockout for Life Video.*


### Lockout for Life (Video)

- Video analyzes real-life scenarios to demonstrate what went wrong and how following proper lockout procedures could have saved lives.
- Examines various elements of the Lockout/Tagout Standard and demonstrates effective lockout techniques.


- Motivational program appropriate for new and experienced employees – ideal for annual retraining program.
- Running time: 19 minutes.

### Lockout Videos

Cat. No.	Description	Qty.
LO16-300	"Lockout For Life" Training Video	1/pkg.
LO16-301	"Controlling the Beast" Lockout Video	1/pkg.
LO16-104	Lockout Training Handbooks	10/pkg.



*Lockout/Tagout: Controlling the Beast Video*



P

E-Z-Code®

**Thomas & Betts**



**E-Z-Code® Ball Valve Lockout Devices** come in two sizes to lock out 1¼" to 1" and 1½" to 3" ball valves.

### Ball Valve Lockout Devices

- Best available method for locking out ball valves.
- Fits all major brand ball valves.
- Two new models accept ¾" shackle padlocks.
- Simple one-piece design makes it easy to use.
- Assists in compliance with OSHA's Lockout Standard.

### Ball Valve Lockout Device

Cat. No.	Valve Size	Padlock Shackle Max. Diameter	Min. Padlock Shackle Clearance	Material
LO16-403	1/4"-1"	5/32"	1"	Super Tough Nylon
LO16-406	1/4"-1"	3/8"	3/4"	Heavy Steel
LO16-404	1½"-3"	5/32"	3/4"	Heavy Steel
LO16-405	1½"-3"	3/8"	3/4"	Heavy Steel



Fits various shaped ball valve handles, as well as Block, Stop, Butterfly and T-handle valves.

### Universal Ball Valve Lockout Device

- Designed to lock out virtually any quarter turn valve – round, square or flat – and with odd shaped handles, straight or with angles.
- Accommodates handles up to 1¼" thick and 1¾" wide in almost any length.
- Unique design works with valves on insulated pipes.
- Constructed of durable nylon and steel materials making it strong, lightweight and resistant to most chemicals.

### Valve Handle Maximum

Cat. No.	Description	Thickness	Width
LO16-400	Small Universal Ball Valve Lockout Device	3/4"	1"
LO16-401	Large Universal Ball Valve Lockout Device	1 1/4"	1 5/8"



*Unique knockout feature can be removed by hand to accommodate OS&Y or "rising stem" gate valves.*

### Gate Valve Lockouts

- Makes locking out valves safe and easy.
- Available in five sizes to fit valve handles from 1" to 13" in diameter.
- Made of durable, non-adherent plastic to resist chemicals and hot and cold temperatures.
- Stainless steel hinge design for added strength and security.
- Available in red.
- Unique knockout feature accommodates OS&Y or "rising stem" gate valves.
- Service temperatures -20°F to 300°F.
- Designed to accept all locks with up to  $\frac{3}{8}$ " shackle diameter and  $\frac{3}{4}$ " or greater vertical shackle clearance.

### Gate Valve Lockouts

Cat. No.	Valve Handle Diameter
LO16-420	1"-2½"
LO16-421	2½"-5"
LO16-422	5"-6½"
LO16-423	6½"-10"
LO16-424	10"-13"




*The Cable Lockout Device enables you to lock out several disconnects in various energy distribution centers.*

### Cable Lockout Device

- Flexible, cost-effective cable locks out gate valves of all sizes and may also be used to lock out multiple valves all with one device.
- Lighter than chains, device is easy to carry and easy to use.
- Ideal for security use as well.
- 6 ft. cable is made of galvanized steel and is  $\frac{1}{8}$ " diameter.

Cat. No.	Description
LO16-402	Cable Lockout Device



*Cable Lockout device provides an easy and efficient method to lock out large gate valves.*



**Universal Multi-Pole Lockout** works with most two or three pole breakers utilizing a tie-bar.

### Circuit Breaker Lockout Devices

#### Universal Multi-Pole Breaker Lockout

- One multi-pole lockout works with most major multi-pole breakers with tie-bar.

- No self-locking tie needed.
- Applicable with GE, ITE, Sylvania, Challenger, Bryant, Westinghouse and General Switch Co.

Cat. No.	Description	Qty.
LO16-500	Universal Multi-Pole Breaker Lockout	5/pk



**Single Pole Circuit Breaker Lockout**

#### Single Pole Circuit Breaker Lockout

- Locks out most major brand breaker switches (except Federal Pacific and most other 277 volt breakers).

- Simple design snaps onto breaker switch and accepts up to  $\frac{3}{8}$ " shackle diameter lock or nylon tie.

Cat. No.	Description	Qty.
LO16-501	Single Pole Lockout	5/pk



**Oversized Breaker Lockout Device**

#### Oversized Breaker Lockout Device

- Oversized 480/600 volt frame lockout fits breakers up to  $2\frac{1}{2}$ " wide by  $\frac{7}{8}$ " thick.

Cat. No.	Description	Qty.
LO16-502	Oversize Circuit Breaker Lockout	1/pk



Covering a breaker with a piece of duct tape to "lock it out" isn't safe or effective and certainly doesn't satisfy OSHA. The E-Z-Code® "No Hole" Circuit Breaker Lockout Device gives you a new level of safety and compliance.

#### "No Hole" Circuit Breaker Lockout

- Enhanced device will lock out most single pole circuit breakers (including most Federal Pacific breakers).
- Easy to install.

- Provides secure locking protection.
- Accepts up to  $\frac{3}{8}$ " shackle diameter lock.
- Fits wider and thicker tongue switches: 277– $1\frac{19}{20}$ " wide by  $\frac{23}{30}$ " thick; 480/600 –  $1\frac{1}{8}$ " wide by  $1\frac{1}{20}$ " thick.

Cat. No.	Description	Qty.
LO16-503	Universal Small Pole Lockout 277 Volt No Hole	5/pk
LO16-504	Universal Breaker Lockout 480/600 Volt No Hole	1/pk



Step 1

Step 2

Step 3

#### Lockout Cleats

- Works in conjunction with "No Hole" Circuit Breaker Lockout (sold above).
- Assures positive lockout for those hard to lock out long sliding switch throws and switches with large

angular rotation commonly found with some Westinghouse, ITE, Square D and Federal Pacific breakers.

- Snap-on and off feature allows for use only when needed.

Cat. No.	Description	Qty.
LO16-510	General Use Cleat 277 Volt No Hole	5/pk
LO16-520	Large General Use Cleat 480/600 Volt No Hole	5/pk



110 Volt, 220/250 Volt Plug Lockout

### Electrical Lockout Devices

#### T&B Plug Lockout

- Designed for heavy-duty applications.
- Cost-effective way to safely lock out electrical plugs.
- Made of rugged polypropylene.
- Available in two sizes: one to fit standard 110-volt grounded plugs and a larger size for 220- and 550-volt plugs.

- Ideal for situations where plug is not under the exclusive control of the person performing the service or maintenance. Should maintenance personnel temporarily leave the area, device prevents anyone else from putting the plug back into the outlet.

Cat. No.	Description	Qty.
LO16-531	110 Volt Plug Lockout	1/pk
LO16-532	220/550 Volt Plug Lockout	1/pk



Plug-Safe™

#### Plug-Safe™

- Safe and effective method for locking out electrical plugs.
- Made of durable plastic.
- Chemically resistant.
- Lockout size: 6" tall and 3½" diameter.
- Adjusts to lock out a variety of plug sizes.

- Ability to lock out a plug up to 3" wide and 5¾" long with a maximum cord diameter of 1¼".
- Accepts standard locks up to ¾" shackle diameter.
- Standard package: one device.

Cat. No.	Description	Qty.
LO16-530	Electrical Plug Lockout	1/pk



Stopower™

#### Stopower™

- Ideal for office and other frequently locked out cords.
- Device slides over cord prongs and locks.

- Cord cannot be plugged in with Stopower™ in place.
- Device cannot be removed without a key.

Cat. No.	Description	Qty.
LO16-533	Stopower – Red	1/pk



Wall Switch Lockout



### Electrical Lockout Devices (continued)

#### Wall Switch Lockout

- Device may be used with most wall-mounted switches.

- Easy to install using existing screws.
- Locks switch in "on" or "off" position.

Cat. No.	Description	Qty.
LO16-540	Wall Switch Lockout	5/pk



Fuse Blockout Devices

#### Fuse Blockout Devices

- Unique locking mechanism prevents device from being accidentally removed from fuse block.

- Available in two sizes for most commonly used fuses.

Cat. No.	Description	Qty.
LO16-552	1/16", 5/32", 13/32" & 1/4" Fuses	5/pk
LO16-553	13/16", 1 1/16" & Blade Type Fuses	5/pk



**Using T&B's Pneumatic Quick-Disconnect Lockout to isolate pneumatic energy provides worker safety in lock out situations.**



**Lockout Tool Box with Components**



**Electrical Lockout Starter Kit**

### Pneumatic Lockout Devices

#### Pneumatic Quick-Disconnect Lockout

- Isolates pneumatic energy without the expense and inconvenience of installing in-line lockout valves.
- Device is applied to the male fitting, isolating equipment from all compressed air sources.

- With a "glove fit," lockout meets OSHA standards and accommodates the majority of 1/4", 3/8" and 1/2" male fittings.
- Center of device allows for permanent storage on an air hose and a loop on the side can be used to hang the hose and lockout device.
- Lockout using a padlock with 1/4" or 5/32" shackle.

Cat. No.	Description	Qty.
LO16-600	Pneumatic Lockout	5/pkg

### Lockout Kits

#### Lockout Tool Box With Components

- Everything you need to lock and mark your equipment and prevent its use until repairs have been completed.
- Kit contains: 1 - Plastic Lockout Tool Box w/Tray; 1 - 1" to 2 1/2" Gate Valve Lockout; 1 - Small Ball Valve Lockout; 1 - 3/4" Blue Padlock; 1 - 2" Blue

Padlock; 1 - Labeled Lockout Hasp; 5 - Lockout Tags; 1 - Universal Multi-Pole Lockout; 1 - 277 Volt "No Hole" Lockout; 1 - 480/600 Volt "No Hole" Lockout; 1 - Wall Switch Lockout; 1 - Small E-Z-Code® Plug Lockout.

- Toolbox also sold individually.

Cat. No.	Description	Qty.
LO16-770	Lockout Tool Box Kit with Components	1/pkg
LO16-700	Lockout Tool Box	1/pkg

#### Electrical Lockout Pouch

- Lightweight, portable pouch contains lockout devices to secure electrical equipment.
- Metal loops on pouch for hanging on a belt.
- Pouch kit contains: pouch, (1) 2" blue padlock, (1) labeled lockout hasp, (2)

heavy duty lockout tags, (1) 277" "no hole" breaker lockout, (1) universal multi-pole lockout, (1) small plug lockout.

- Pouch made of heavy duty nylon. 4 3/4" H, 7 1/2" W, 2" D.

Cat. No.	Description	Qty.
LO16-710	Electrical Lockout Kit	1/pkg



**E-Z-Code®'s high visibility Lockout Stations** make your locks, tags and lockouts easy to find and use. Built for the toughest conditions, Lockout Stations are made of durable plastic material.

### Lockout Stations

#### Four Lock Station

- Station with components.
- Components include: 4 blue bumper padlocks; 25 "Do Not Operate" tags;

and three 1" safety lockouts.

- Station size: 8" x 12".
- Station also sold individually.

Cat. No.	Description	Qty.
LO16-760	4 Lock Station with Components	1/pkg
LO16-750	4 Lock Station Only	


#### Ten Lock Station

- Station with components.
- Components include: 10 blue bumper padlocks; 25 "Do Not

Operate" tags; and three 1" safety lockouts.

- Station size: 19" x 12".
- Station also sold individually.

Cat. No.	Description	Qty.
LO16-740	10 Lock Station with Components	1/pkg
LO16-730	10 Lock Station Only	



**13 Lock Group Lock Box**

#### 13 Lock Group Lock Box

- Simplifies lockout of large equipment.
- After machine or process is locked out, the key or keys are placed in a lock box. Then, each authorized work team member places a personal lock or tagout device in the group lock box.

- Ensures that no one employee has access to the box unless ALL employees have removed their locks or tags.
- Accepts up to 13 individual locks.
- Heavy steel construction.

Cat. No.	Description	Qty.
LO16-811	13 Lock Group Lock Box	1/pkg

# E-Z-Code®

## Lockout/Tagout



**High security #3 Master Lock Padlocks are an ideal size for lockout applications.**

### Padlocks

#### Master Lock Padlocks

- Constructed of rustproofed steel case and nickel-plated shackle.
- Locks are 1 1/2" wide with 3/8" shackle diameter.
- Pair of brass keys included with each lock.

- Available in six different colored bumpers to provide easy visual identification by department or work team.
- Key numbers are ink-stamped on the bottom of the lock for easy lock/key identification.
- Standard package: 6 locks.

Cat. No.	Description	Qty.
LO16-900	3/4" Blue Bumper Pad Lock	6
LO16-901	3/4" Black Bumper Pad Lock	6
LO16-902	3/4" White Bumper Pad Lock	6
LO16-903	3/4" Red Bumper Pad Lock	6
LO16-904	3/4" Green Bumper Pad Lock	6
LO16-905	3/4" Yellow Bumper Pad Lock	6
LO16-906	2" Blue Bumper Pad Lock	6
LO16-907	2" Black Bumper Pad Lock	6
LO16-908	2" White Bumper Pad Lock	6
LO16-909	2" Red Bumper Pad Lock	6
LO16-910	2" Green Bumper Pad Lock	6
LO16-911	2" Yellow Bumper Pad Lock	6



- Allows up to six workers to lock out a single energy source.
- Constructed of vinyl-coated high tensile steel.
- Plated to resist rust.



- Allows up to six workers to lock out a piece of equipment and begin servicing it.
- Up to 5 additional employees can affix their locks and tags to the Labeled Lockout Hasps to assist in the servicing operation.
- Hasp size 7 1/4 x 3 x 3/8.
- Constructed from tough 5052 anodized aluminum alloy.

### Hasps

Cat. No.	Size	Qty.
L016-800	1"	12/pk
L016-801	1.5"	12/pk

### Labeled Lockout Hasp

Cat. No.	Size	Qty.
L016-810	—	5/pk

P

E-Z-Code®

**Thomas & Betts**

### Durable Lockout Tags

OSHA requirements for Lockout Tags are very specific, and E-Z-Code® Lockout Tags have been designed to comply with every performance standard. Tags are available in two sturdy materials: reusable dura-tag and economical vinyl. All tags have a reinforcing brass grommet  $\frac{7}{16}$ " diameter to accept most padlocks. All tag surfaces allow employees to easily personalize tags with their name, department and estimated completion information as required by regulations.



### Reusable Dura-Tag

Durable, plastic tags are encapsulated in matte polyester laminate. Tag meets OSHA 50 lb. pull requirement. These tags are designed for harsh plant environments and are chemically resistant. Supplied with heavy duty  $\frac{3}{8}$ " ID brass grommet and nylon ties. Matte finish accepts pencil, pen and marker. 25/pkg.

### Economy Polyester

Rigid polyester surface is easy to write on and stays legible longer. Wipes clean easily, ready to use again and again. Exceeds OSHA 50 pound pull-out requirement. 25/pkg.

## Lockout/Tagout Tags



#### Reusable Dura-Tag

**TG65502** - Rev. Side #1    **TG65503** - Rev. Side #1    **TG65504** - Rev. Side #1    **TG65505** - Rev. Side #1

**TG65670** - Rev. Side #2

#### Economy Polyester

**TG66050** - Rev. Side #1    **TG66053** - Rev. Side #1    **TG66055** - Rev. Side #1    **TG66057** - Rev. Side #1

**TG66052** - Rev. Side #2



#### Reusable Dura-Tag

**TG65506** - Rev. Side #1    **TG65515** - Rev. Side #1    **TG65520** - Rev. Side #1    **TG65526** - Rev. Side #1

**TG65671** - Rev. Side #2

#### Economy Polyester

**TG66059** - Rev. Side #1    **TG66061** - Rev. Side #1    **TG66063** - Rev. Side #1    **TG66066** - Rev. Side #1

**TG66065** - Rev. Side #2

## Reverse Side Options



Reverse Side #1

Reverse Side #2

### How to Order

Choose tag & material, order by part number for reverse side wanted.

E-Z-Code® Dura-Tag and economy polyester Lockout Tags exceed OSHA's 50 lb. pullout requirement. All tags have write-on surfaces and come in packages of 25 tags.

Description	Size	Grommet
Reusable Dura-Tag	5 $\frac{1}{2}$ " x 3"	$\frac{7}{16}$ " Brass
Economy Polyester	5 $\frac{3}{4}$ " x 3"	$\frac{3}{8}$ " Brass

# E-Z-Code®

## Accident Prevention Tags

There's an E-Z-Code® tag for every application and budget.

### Reusable Dura-Tag

Durable, plastic tags are encapsulated in matte polyester laminate. Tag meets OSHA 50 lb. pull requirement. These tags are designed for harsh plant environments and are chemically resistant. Supplied with heavy duty  $\frac{3}{8}$ " ID brass grommet and nylon ties. Matte finish accepts pencil, pen and marker. 25/pkg.

### Economy Polyester

Chemically resistant polyester tag meets OSHA's 50 lb. pull requirement. Supplied with  $\frac{3}{8}$ " ID metal grommet and nylon ties. 25/pkg.

### Cardstock

Economical yet durable cardstock. These disposable tags come with a  $\frac{3}{8}$ " grommet. 100/pkg.

Description	Size	Grommet
Reusable Dura-Tag	5 $\frac{1}{4}$ " x 3"	$\frac{3}{8}$ "
Economy Polyester	5 $\frac{1}{4}$ " x 3"	$\frac{3}{8}$ "
Card Stock Tags	5 $\frac{1}{4}$ " x 3"	$\frac{3}{8}$ "

## Accident Prevention Tags



### Reusable Dura-Tag

**TG86425** - Rev. Side 1   **TG86424** - Rev. Side 1   **TG86414** - Rev. Side 1   **TG86416** - Same Back   **TG86417** - Same Back

### Economy Polyester

**TG86544** - Rev. Side 1   **TG86543** - Rev. Side 1   **TG86533** - Rev. Side 1   **TG86535** - Same Back   **TG86536** - Same Back

### Cardstock Tags

**TG86654** - Rev. Side 1   **TG86653** - Rev. Side 1   **TG86643** - Rev. Side 1   **TG86645** - Same Back   **TG86646** - Same Back

## Reusable Dura-Tag



### Reusable Dura-Tag

**TG86418** - Rev. Side 1   **TG86442** - Same Back   **TG86454** - Same Back   **TG86438** - Same Back

### Economy Polyester

**TG86537** - Rev. Side 1   **TG86556** - Same Back   **TG86574** - Same Back   **TG86565** - Same Back

### Cardstock Tags

**TG86647** - Rev. Side 1   **TG86666** - Same Back   **TG86684** - Same Back   **TG86675** - Same Back



Reverse Side 1  
(For Caution Tags)



Reverse Side 1  
(For Danger Tags)

P

E-Z-Code®

**Thomas & Betts**

Fig. 1



Fig. 2

Designed to keep children away from switchgear and transformers.

Made of WPM pressure sensitive destructible vinyl film, making one piece removal virtually impossible.

These labels meet both NEMA and Underwriters Laboratory applicable standards.

### "Mr. Ouch" Nema Safety Labels

Cat. No.	Legend	Fig.	Nema Label Size
WUT-0366	WARNING	2	4½" x 8"
WUT-0367	DANGER	1	4½" x 8"
WUT-0368	WARNING (Bilingual)	4	5" x 10½"
WUT-0369	DANGER (Bilingual)	3	5" x 10½"

Standard package quantity 5 labels.




Fig. 3




Fig. 4

*Choose from four visual warning legends for use on machines and other equipment.*

### Magnetic Signs



Cat. No.	Label Size						
MG66002	5" x 3½"	MG66004	5" x 3½"	MG66006	5" x 3½"	MG66008	5" x 3½"
MG66003	7" x 5"	MG66005	7" x 5"	MG66007	7" x 5"	MG66009	7" x 5"



Fig. 1



Fig. 2



Fig. 3




LB86871  
Fig. 4



LB86860  
Fig. 5



LB86234  
Fig. 6



LB86235  
Fig. 7



LB86877  
Fig. 8



LB86861  
Fig. 9



LB86245  
Fig. 10



LB86204  
Fig. 11



LB86248  
Fig. 12



LB86250  
Fig. 13

New 2002 National Electric Code Requirement  
110.16 Flash Protection

The new requirement is intended to reduce the occurrence of serious injury or death due to arcing faults to workers who work on or near energized electrical equipment. The warning label should remind a qualified worker who intends to open the equipment for analysis or work that a serious hazard exists and that the worker should follow appropriate work practices and wear appropriate personal protection equipment (PPE) for the specific hazard.








### Vinyl Pressure Sensitive Accident Prevention Cards

Cat. No.	Figure	Legend	Color	Size
WJA-1100 WQA-1100	1	DANGER	White letters in a red oval on black	2 1/4" x 9" 5" x 14"
WJA-0076 WQA-0076	2	HIGH VOLTAGE	Red on white	2 1/4" x 9" 5" x 14"
WHA-0076	3	DANGER HIGH VOLTAGE	Red and black on white	2 per Card
LB86871	4	DANGER HIGH VOLTAGE	Red and black on white	3.5 x 5
LB86860	5	DANGER HIGH VOLTAGE	Red and black on white	3.5 x 5
LB86234	6	DANGER HIGH VOLTAGE PELIGRO ALTO VOLTAJE	Red and black on white	3.5 x 5
LB86235	7	DANGER HIGH VOLTAGE PELIGRO ALTO VOLTAJE	Red and black on white	3.5 x 5
LB86877	8	DANGER HIGH VOLTAGE	Red and black on white	3.5 x 5
LB86861	9	DANGER HIGH VOLTAGE	Red and black on white	3.5 x 5
LB86245	10	LOCKOUT HERE	Red and black on white	3.5 x 5
LB86204	11	LOCKOUT POINT	Red and black on white	3.5 x 5
LB86248	12	REMEMBER LOCKOUT ALL POWER SOURCES	Red and black on white	3.5 x 5
LB86250	13	REMEMBER LOCK, TAG, CLEAR, TRY	Red and black on white	3.5 x 5
LB94913 LB94914	14	WARNING ARC FLASH AND SHOCK	Orange and black on white	3.5" x 5" 5" x 7"

Order by cards. Standard package 5 identical cards per poly bag.



### Electrical Hazard Safety Signs

					
<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>	<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>
BP84827	SS	7x10	BP84843	SS	7x10
BP84828	SS	10x14	BP84844	SS	10x14
					
<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>	<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>
BP40655	AL	7x10	BP43109	AL	7x10
BP40656	AL	10x14	BP43110	AL	10x14
BP22091	PL	7x10	BP25532	PL	7x10
BP22092	PL	10x14	BP25533	PL	10x14
BP84066	SS	7x10	BP84876	SS	7x10
BP84067	SS	10x14	BP84877	SS	10x14
					
<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>	<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>
BP40667	AL	7x10	BP40669	AL	7x10
BP40668	AL	10x14	BP40670	AL	10x14
BP22103	PL	7x10	BP22105	PL	7x10
BP22104	PL	10x14	BP22106	PL	10x14
BP84083	SS	7x10	BP84085	SS	7x10
BP84084	SS	10x14	BP84086	SS	10x14
					
<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>	<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>
BP43143	AL	7x10	BP43145	AL	7x10
BP43144	AL	10x14	BP43146	AL	10x14
BP25566	PL	7x10	BP25568	PL	7x10
BP25567	PL	10x14	BP25569	PL	10x14
BP84929	SS	7x10	BP84933	SS	7x10
BP84930	SS	10x14	BP84934	SS	10x14
					
<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>	<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>
BP42739	AL	10x14	BP89152	SS	3x3
BP25162	PL	10x14			
BP89153	SS	3x3			
BP88497	SS	10x10			
					
<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>	<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>
BP42740	AL	10x14	BP42753	AL	7x10
BP25163	PL	10x14	BP25176	PL	7x10
BP88498	SS	10x10	BP88512	SS	7x7
					
<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>	<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>
BP84949	SS	3.5x10			
					
					
<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>	<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>
BP84963	SS	3.5x10			

<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>
BP42739	AL	10x14
BP25162	PL	10x14
BP89153	SS	3x3

<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>
BP89152	SS	3x3

<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>
BP42740	AL	10x14
BP25163	PL	10x14

<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>
BP42753	AL	7x10
BP25176	PL	7x10

<b>Ca No.</b>	<b>Mat.</b>	<b>Size</b>
BP88512	SS	7x7

**AL** - Aluminum  
5-8 yr durability  
**PL** - Plastic  
1-2 yr durability  
**SS** - Self Sticking  
5-8 yr durability

### Electrical Hazard Safety Signs



New 2002 National Electric Code Requirement  
110.16 Flash Protection

The new requirement is intended to reduce the occurrence of serious injury or death due to arcing faults to workers who work on or near energized electrical equipment. The warning label should remind a qualified worker who intends to open the equipment for analysis or work that a serious hazard exists and that the worker should follow appropriate work practices and wear appropriate personal protection equipment (PPE) for the specific hazard.



Cat No.	Mat.	Size
BP42560	AL	7x10
BP42561	AL	10x14
BP23037	PL	7x10
BP23038	PL	10x14
BP88183	SS	7x10
BP88184	SS	10x14

Cat No.	Mat.	Size
BP42564	AL	7x10
BP42565	AL	10x14
BP23041	PL	7x10
BP23042	PL	10x14
BP88187	SS	7x10
BP88188	SS	10x14



Cat No.	Mat.	Size
BP42584	AL	7x10
BP42585	AL	10x14
BP23061	PL	7x10
BP23062	PL	10x14
BP88217	SS	7x10
BP88218	SS	10x14

### Vinyl Pressure Sensitive Accident Prevention Cards

Cat. No.	Legend	Color	Size
LB94915	WARNING ARC	Orange and black on white	7" x 10"
LB94916	FLASH AND SHOCK		10" x 14"

Order by cards. Standard package 5 identical cards per poly bag.

### Chemical & Hazardous Material



Cat. No.	Mat.	Size
BP43237	AL	7x10
BP43238	AL	10x14
BP25660	PL	7x10
BP25661	PL	10x14
BP85175	SS	7x10
BP85176	SS	10x14

Cat. No.	Mat.	Size
BP40988	AL	7x10
BP40989	AL	10x14
BP22424	PL	7x10
BP22425	PL	10x14
BP84562	SS	7x10
BP84563	SS	10x14

Cat. No.	Mat.	Size
BP43517	AL	7x10
BP43518	AL	10x14
BP25920	PL	7x10
BP25921	PL	10x14
BP65950	SS	7x10
BP65949	SS	10x14

Cat. No.	Mat.	Size
BP43005	AL	7x10
BP43006	AL	10x14
BP25428	PL	7x10
BP25429	PL	10x14
BP84375	SS	7x10
BP84376	SS	10x14

Cat. No.	Mat.	Size
BP43319	AL	7x10
BP43320	AL	10x14
BP25742	PL	7x10
BP25743	PL	10x14
BP85553	SS	7x10
BP85554	SS	10x14

Cat. No.	Mat.	Size
BP40875	AL	7x10
BP40876	AL	10x14
BP22311	PL	7x10
BP22312	PL	10x14
BP84351	SS	7x10
BP84352	SS	10x14

### First Aid



Cat. No.	Mat.	Size
BP41225	AL	7x10
BP41226	AL	10x14
BP22661	PL	7x10
BP22662	PL	10x14
BP85349	SS	7x10
BP85350	SS	10x14

Cat. No.	Mat.	Size
BP41229	AL	7x10
BP22665	PL	7x10
BP85354	SS	7x10
BP85355	SS	10x14

### Fire Extinguisher



Cat. No.	Mat.	Size
BP43294	AL	14x10
BP25717	PL	14x10
BP86091	SS	14x10



Cat. No.	Mat.	Size
BP43295	AL	10x7
BP25718	PL	10x7
BP85261	SS	14x3.5

### Handicap



Cat. No.	Mat.	Size
BP91370	SS	14x10

**AL** - Aluminum  
5-8 yr durability  
**PL** - Plastic  
1-2 yr durability  
**SS** - Self Sticking  
5-8 yr durability

### No Smoking



Mat.	Size
AL	7x10
AL	10x14
PL	7x10
PL	10x14
SS	7x10
SS	10x14

Mat.	Size
AL	10x7
AL	14x10
PL	10x7
PL	14x10
SS	10x7
SS	14x10

Mat.	Size
AL	7x10
AL	10x14
PL	7x10
PL	10x14
SS	7x10
SS	10x14

Mat.	Size
AL	7x10
AL	10x14
PL	7x10
PL	10x14
SS	7x10
SS	10x14

Mat.	Size
AL	7x10
AL	10x14
PL	7x10
PL	10x14
SS	7x10
SS	10x14

### Sign Blanks



Mat.	Size
AL	7x10
AL	10x14
PL	7x10
PL	10x14
SS	7x10
SS	10x14

Mat.	Size
AL	7x10
AL	10x14
PL	7x10
PL	10x14
SS	7x10
SS	10x14

Mat.	Size
AL	7x10
AL	10x14
PL	7x10
PL	10x14
SS	7x10
SS	10x14

**AL** - Aluminum  
5-8 yr durability  
**PL** - Plastic  
1-2 yr durability  
**SS** - Self Sticking  
5-8 yr durability

### Lockout



Mat.	Size
AL	10x7
AL	14x10
PL	10x7
PL	14x10
SS	10x7
SS	14x10

Mat.	Size
SS	2.25x4.5

Mat.	Size
SS	2.25x4.5

Mat.	Size
SS	2.25x4.5

Mat.	Size
SS	2.25x4.5

Mat.	Size
In Accordance with OSHA Standard 1910.147, all equipment, machines and processes shall be locked out prior to servicing.	
Lockout procedures are posted in the operating area and/or by the main energy source of each machine.	
For additional information about the lockout procedures, please see your supervisor or the Safety Director.	
This standard will be strictly enforced.	



Mat.	Size
AL	14x10
PL	14x10

Mat.	Size
AL	7x10
AL	10x14
PL	7x10
PL	10x14

**AL** - Aluminum  
5-8 yr durability  
**PL** - Plastic  
1-2 yr durability  
**SS** - Self Sticking  
5-8 yr durability

### Personal Protection



Cat No.	Mat.	Size
BP42402	AL	7x10
BP42403	AL	10x14
BP22879	PL	7x10
BP22880	PL	10x14
BP85797	SS	7x10
BP85798	SS	10x14



Cat No.	Mat.	Size
BP40969	AL	7x10
BP40970	AL	10x14
BP22405	PL	7x10
BP22406	PL	10x14
BP84535	SS	7x10
BP84536	SS	10x14



Cat No.	Mat.	Size
BP42440	AL	7x10
BP42441	AL	10x14
BP22917	PL	7x10
BP22918	PL	10x14
BP85858	SS	7x10
BP85859	SS	10x14



Cat No.	Mat.	Size
BP41336	AL	7x10
BP41337	AL	10x14
BP22772	PL	7x10
BP22773	PL	10x14
BP85598	SS	7x10
BP85599	SS	10x14



Cat No.	Mat.	Size
BP42627	AL	7x10
BP42628	AL	10x14
BP25050	PL	7x10
BP25051	PL	10x14
BP88310	SS	7x10
BP88311	SS	10x14



Cat No.	Mat.	Size
BP42484	AL	7x10
BP42485	AL	10x14
BP22961	PL	7x10
BP22962	PL	10x14
BP85957	SS	7x10
BP85958	SS	10x14



Cat No.	Mat.	Size
BP43041	AL	7x10
BP43042	AL	10x14
BP25464	PL	7x10
BP25465	PL	10x14
BP84784	SS	7x10
BP84785	SS	10x14

Cat No.	Mat.	Size
BP40971	AL	7x10
BP40972	AL	10x14
BP22407	PL	7x10
BP22408	PL	10x14
BP84537	SS	7x10
BP84538	SS	10x14

Cat No.	Mat.	Size
BP40963	AL	7x10
BP40964	AL	10x14
BP22399	PL	7x10
BP22400	PL	10x14
BP84529	SS	7x10
BP84530	SS	10x14

Cat No.	Mat.	Size
BP41190	AL	7x10
BP41191	AL	10x14
BP22626	PL	7x10
BP22627	PL	10x14
BP85035	SS	7x10
BP85036	SS	10x14

Cat No.	Mat.	Size
BP40967	AL	7x10
BP40968	AL	10x14
BP22403	PL	7x10
BP22404	PL	10x14
BP84533	SS	7x10
BP84534	SS	10x14



Cat No.	Mat.	Size
BP42508	AL	7x10
BP42509	AL	10x14
BP22985	PL	7x10
BP22986	PL	10x14
BP88107	SS	7x10
BP88108	SS	10x14

Cat No.	Mat.	Size
BP42562	AL	7x10
BP42563	AL	10x14
BP23039	PL	7x10
BP23040	PL	10x14
BP88185	SS	7x10
BP88186	SS	10x14

### Admittance and Exit



Cat No.	Mat.	Size
BP40623	AL	7x10
BP40624	AL	10x14
BP22059	PL	7x10
BP22060	PL	10x14
BP84008	SS	7x10
BP84009	SS	10x14



Cat No.	Mat.	Size
BP40997	AL	7x10
BP40998	AL	10x14
BP22433	PL	7x10
BP22434	PL	10x14
BP84571	SS	7x10
BP84572	SS	10x14



Cat No.	Mat.	Size
BP40705	AL	7x10
BP40706	AL	10x14
BP22141	PL	7x10
BP22142	PL	10x14
BP84129	SS	7x10
BP84130	SS	10x14



Cat No.	Mat.	Size
BP40707	AL	7x10
BP40708	AL	10x14
BP22143	PL	7x10
BP22144	PL	10x14
BP84131	SS	7x10
BP84132	SS	10x14



Cat No.	Mat.	Size
BP40727	AL	7x10
BP40728	AL	10x14
BP22163	PL	7x10
BP22164	PL	10x14
BP84155	SS	7x10
BP84156	SS	10x14



Cat No.	Mat.	Size
BP40753	AL	7x10
BP40754	AL	10x14
BP22189	PL	7x10
BP22190	PL	10x14
BP84187	SS	7x10
BP84188	SS	10x14



Cat No.	Mat.	Size
BP41053	AL	7x10
BP41054	AL	10x14
BP22489	PL	7x10
BP22490	PL	10x14
BP84673	SS	7x10
BP84674	SS	10x14



Cat No.	Mat.	Size
BP43338	AL	7x10
BP43339	AL	10x14
BP25761	PL	7x10
BP25762	PL	10x14
BP84617	SS	7x10
BP84618	SS	10x14



Cat No.	Mat.	Size
BP41065	AL	7x10
BP41066	AL	10x14
BP22501	PL	7x10
BP22502	PL	10x14
BP84687	SS	7x10
BP84688	SS	10x14



Cat No.	Mat.	Size
BP41101	AL	7x10
BP41102	AL	10x14
BP22537	PL	7x10
BP22538	PL	10x14
BP84732	SS	7x10
BP84733	SS	10x14

**AL** - Aluminum  
5-8 yr durability  
**PL** - Plastic  
1-2 yr durability  
**SS** - Self Sticking  
5-8 yr durability

## Custom Sign Express Order Form

This Custom Sign Order Form is for the convenience of you and your authorized Thomas & Betts Distributor. To help expedite your order, please copy the order form and use a separate form to order signs that require different legends, different sizes, different headers or different materials.




**Fax your order to:**  
**901-252-1321**

### Materials (Check appropriate material)

Material	Sizes Available		
Aluminum	<input type="checkbox"/> 7x10	<input type="checkbox"/> 10x14	
Plastic	<input type="checkbox"/> 7x10	<input type="checkbox"/> 10x14	
Self-Sticking	<input type="checkbox"/> 3x5	<input type="checkbox"/> 5x7	<input type="checkbox"/> 7x10 <input type="checkbox"/> 9x12 <input type="checkbox"/> 10x14

### Header/Color (Check one of the options below)



**Quantity** \_\_\_\_\_

No minimum order. Orders for 50+ signs are welcome, call for delivery and additional volume discounts.

### Legend (Please print clearly)

Layout best way  
 Layout exactly as shown

### Pictograms:

A pictogram can be included on your custom sign, in black, at no additional charge. Please indicate pictogram number when placing order.



### Distributor Billing Location

Distributor Name: \_\_\_\_\_

Distributor Address: \_\_\_\_\_

P.O. Number: \_\_\_\_\_

Contact Name: \_\_\_\_\_

Phone Number: \_\_\_\_\_

Fax Number: \_\_\_\_\_

### Shipping Location

Your Name/Title: \_\_\_\_\_

Company Name: \_\_\_\_\_

Attn: \_\_\_\_\_

Address: \_\_\_\_\_

City: \_\_\_\_\_ State: \_\_\_\_\_ Zip: \_\_\_\_\_

Phone/Fax Number: \_\_\_\_\_

P.O. Number: \_\_\_\_\_

**Fax your order to: 901-252-1321**

**Thomas & Betts**