


FEATURES

- Turn off time less than $2\mu s$
- Maximum operating frequency greater than 500kHz
- Timing from microseconds to hours
- Operates in both astable and monostable modes
- High output current
- Adjustable duty cycle
- TTL compatible
- Temperature stability of 0.005% per $^{\circ}C$
- SE555 Mil std 883A,B,C available M38510 (JAN) approved, M38510 processing available.


PIN CONFIGURATIONS




APPLICATIONS

- Precision timing
- Pulse generation
- Sequential timing
- Time delay generation
- Pulse width modulation
- Pulse position modulation
- Missing pulse detector

F,N-14 PACKAGE




T PACKAGE




ABSOLUTE MAXIMUM RATINGS

PARAMETER	RATING	UNIT
Supply voltage		
SE555	+18	V
NE555, SE555C, SA555	+16	V
Power dissipation	600	mW
Operating temperature range		
NE555	0 to +70	$^{\circ}C$
SA555	-40 to +85	$^{\circ}C$
SE555, SE555C	-55 to +125	$^{\circ}C$
Storage temperature range	-65 to +150	$^{\circ}C$
Load temperature (soldering, 60sec)	300	$^{\circ}C$

EQUIVALENT SCHEMATIC



BLOCK DIAGRAM



DC ELECTRICAL CHARACTERISTICS $T_A = 25^\circ\text{C}$, $V_{CC} = +5\text{V}$ to $+15$ unless otherwise specified.


PARAMETER	TEST CONDITIONS	SE555			NE555/SE555C/SA555			UNIT
		Min	Typ	Max	Min	Typ	Max	
Supply voltage		4.5		18	4.5		16	V
Supply current (low state) ¹	$V_{CC} = 5\text{V}$ $R_L = \infty$		3	5		3	6	mA
	$V_{CC} = 15\text{V}$ $R_L = \infty$		10	12		10	15	mA
Timing error (monostable) Initial accuracy ² Drift with temperature Drift with supply voltage	$R_A = 2\text{k}\Omega$ to $100\text{k}\Omega$ $C = 0.1\mu\text{F}$		0.5	2.0		1.0	3.0	%
			30	100		50		ppm/ $^\circ\text{C}$
			0.05	0.2		0.1	0.5	%/V
Timing error (astable) Initial accuracy ² Drift with temperature Drift with supply voltage	$R_A, R_B = 1\text{k}\Omega$ to $100\text{k}\Omega$ $C = 0.1\mu\text{F}$ $V_{CC} = 15\text{V}$		1.5			2.25		%
			90			150		ppm/ $^\circ\text{C}$
			0.15			0.3		%/V
Control voltage level	$V_{CC} = 15\text{V}$	9.6	10.0	10.4	9.0	10.0	11.0	V
	$V_{CC} = 5\text{V}$	2.9	3.33	3.8	2.6	3.33	4.0	V
Threshold voltage	$V_{CC} = 15\text{V}$	9.4	10.0	10.6	8.8	10.0	11.2	V
	$V_{CC} = 5\text{V}$	2.7	3.33	4.0	2.4	3.33	4.2	V
Threshold current ³			0.1	0.25		0.1	0.25	μA
Trigger voltage	$V_{CC} = 15\text{V}$	4.8	5.0	5.2	4.5	5.0	5.6	V
	$V_{CC} = 5\text{V}$	1.45	1.67	1.9	1.1	1.67	2.2	V
Trigger current	$V_{TRIG} = 0\text{V}$		0.5	0.9		0.5	2.0	μA
Reset voltage ⁴		0.4	0.7	1.0	0.4	0.7	1.0	V
Reset current	$V_{RESET} = 0\text{V}$		0.1	0.4		0.1	0.4	mA
Reset current			0.4	1.0		0.4	1.5	mA
Output voltage (low)	$V_{CC} = 15\text{V}$							
	$I_{SINK} = 10\text{mA}$		0.1	0.15		0.1	0.25	V
	$I_{SINK} = 50\text{mA}$		0.4	0.5		0.4	0.75	V
	$I_{SINK} = 100\text{mA}$		2.0	2.2		2.0	2.5	V
	$I_{SINK} = 200\text{mA}$		2.5			2.5		V
	$V_{CC} = 5\text{V}$							
	$I_{SINK} = 8\text{mA}$		0.1	0.25		0.3	0.4	V
	$I_{SINK} = 5\text{mA}$		0.05	0.2		0.25	0.35	V
Output voltage (high)	$V_{CC} = 15\text{V}$							
	$I_{SOURCE} = 200\text{mA}$		12.5			12.5		V
	$I_{SOURCE} = 100\text{mA}$	13.0	13.3		12.75	13.3		V
	$V_{CC} = 5\text{V}$							
	$I_{SOURCE} = 100\text{mA}$	3.0	3.3		2.75	3.3		V
Turn off time ⁵	$V_{RESET} = V_{CC}$		0.5	2.0		0.5		μs
Rise time of output			100	200		100	300	ns
Fall time of output			100	200		100	300	ns
Discharge leakage current			20	100		20	100	na

NOTES


- Supply current when output high typically 1mA less.
- Tested at $V_{CC} = 5\text{V}$ and $V_{CC} = 15\text{V}$.
- This will determine the maximum value of $R_A + R_B$, for 15V operation, the max total $R = 10$ megohm, and for 5V operation, the max total $R = 3.4$ megohm.
- Specified with trigger input high.
- Time measured from a positive going input pulse from 0 to $0.8 \times V_{CC}$ into the threshold to the drop from high to low of the output. Trigger is tied to threshold.

TYPICAL PERFORMANCE CHARACTERISTICS


MINIMUM PULSE WIDTH
REQUIRED FOR TRIGGERING




SUPPLY CURRENT
vs SUPPLY VOLTAGE




DELAY TIME
vs TEMPERATURE




LOW OUTPUT VOLTAGE
vs OUTPUT SINK CURRENT




LOW OUTPUT VOLTAGE
vs OUTPUT SINK CURRENT




LOW OUTPUT VOLTAGE
vs OUTPUT SINK CURRENT



HIGH OUTPUT VOLTAGE DROP
vs OUTPUT SOURCE CURRENT



DELAY TIME vs
SUPPLY VOLTAGE



PROPAGATION DELAY
vs VOLTAGE LEVEL
OF TRIGGER PULSE

