

**Quick-Acting
Surface Mount
Fuse — 63 V**

Quick-acting surface mount fuse built according to IEC 127-4. UL listed, CSA certified, VDE approved (800 mA-1.25 A; 2.5 A). Breaks at 100 A/63 V AC/DC; low voltage drop. Material meets UL 94V-0 flammability. Fuse with clip also available. Larger quantities available on tape and reel.

Stock No.	Mfr.'s Type	Amps/ Volts	Typ. Voltage Drop	PER PK./100
798-0400	3405.0917.11	800 mA/63 V	150	35.00
798-0402	3405.0918.11	1.00 A/63 V	140	34.00
798-0404	3405.0919.11	1.25 A/63 V	130	34.00
798-0408	3405.0921.11	2.00 A/63 V	110	34.00
798-0414	3405.0924.11	4.00 A/63 V	80	35.00

Micron Guard Chip Fuse 1206

Form and fit substitute to other popular 1206 surface mount fuse packages. Functions with lower resistance, superior cycling, low let through energy. Interrupts at 50 amps AC and 300 amps DC. Larger quantities available on tape and reel.

Stock No.	Mfr.'s Type	Amps	PER PK./100
798-0702	3410.0022.01*	250 mA/125 V	69.99
798-0704	3410.0025.01	375 mA/125 V	69.99
798-0708	3410.0029.01	750 mA/125 V	69.99
798-0712	3410.0033.01	1.5 A/125 V	69.99
798-0714	3410.0035.01	2.0 A/125 V	69.99
798-0716	3410.0036.01	2.5 A/125 V	69.99

*Meets UL 1459/1950 test requirements.

**Surface Mount
Fuse 6125** — *NEW* —

Breaking Capacity: 300 A/125 VAC/VDC;
5-7 A 300 A/125 VAC 50 A/125 VDC.

Stock No.	Mfr.'s Type	Amps	EACH
798-5062	7010.9901.03	125 mA/125 V	.79
798-5063	7010.9902.03	250 mA/125 V	.79
798-5064	7010.9903.03	375 mA/125 V	.79
798-5065	7010.9904.03	500 mA/125 V	.79
798-5066	7010.9905.03	750 mA/125 V	.79
798-5067	7010.9906.03	1.0 A/125 V	.79
798-5068	7010.9907.03	1.5 A/125 V	.79
798-5069	7010.9908.03	2.0 A/125 V	.79
798-5070	7010.9909.03	2.5 A/125 V	.79
798-5071	7010.9910.03	3.0 A/125 V	.79
798-5072	7010.9911.03	3.5 A/125 V	.79
798-5073	7010.9912.03	4.0 A/125 V	.79
798-5074	7010.9913.03	5.0 A/125 V	.79
798-5075	7010.9914.03	7.0 A/125 V	.79

**Surface Mount
Fuse 250 V**

OMF and OMT 250 V fast-acting and time-lag surface mount fuses. OMF breaking capacity is 100 A/250 VAC/VDC. OMT breaking capacity is 1 mA/250 VAC (750 mA-1.25 A); 50 A/250 VAC (1.5-2 A); 100 A/125 VAC (2.5 A-5 A). Made from UL 94V-0 thermoplastic for reflow, vapor-phase and wave soldering. Larger quantities available on tape and reel.


OMF 250 V — Fast Acting

Stock No.	Mfr.'s Type	Amps	EACH
798-0338	3403.0012.11	400 mA/250 V	1.26
798-0340	3403.0013.11	500 mA/250 V	1.30
798-0346	3403.0016.11	1.00 A/250 V	1.30
798-0348	3403.0017.11	1.25 A/250 V	1.30
798-0350	3403.0018.11	1.60 A/250 V	1.26
798-0352	3403.0019.11	2.00 A/250 V	1.26
798-0354	3403.0020.11	2.50 A/250 V	1.26
798-0356	3403.0021.11	3.15 A/250 V	1.47

OMT 250 V — Lag-Time — *NEW* —

Stock No.	Mfr.'s Type	Amps	EACH
798-5052	3403.0129.11	750 mA/250 V	1.14
798-5053	3403.0116.11	1.00 A/250 V	1.14
798-5054	3403.0117.11	1.25 A/250 V	1.14
798-5055	3403.0130.11	1.50 A/250 V	1.14
798-5056	3403.0119.11	2.00 A/250 V	1.14
798-5057	3403.0120.11	2.50 A/125 V	1.14
798-5058	3403.0131.11	3.00 A/125 V	1.14
798-5059	3403.0132.11	3.50 A/125 V	1.14
798-5060	3403.0122.11	4.00 A/125 V	1.14
798-5061	3403.0123.11	5.00 A/125 V	1.14

**Resettable
Polymeric Fuses**



Type PFRA and PFRX radial leaded resettable fuses meet UL 94V-0. Both feature cured, flame retardant epoxy polymer insulating materials. Type PFRA is suitable for low voltage power supplies and where there is a load to be protected. Shape changes from round to square starting with PFRA.300. Type PFRX is suitable for 60+V applications. Type PFMD is a surface mount resettable fuse packaged according to EIA standard 481-2. Type PFMD is suitable for high density PC boards. All parts packaged bulk or tape and reel, except PFMD in tape and reel only. Call your local Allied sales representative for other available packaging options.

Stock No.	Mfr.'s Type	V Max. (Volts)	I Max. (Amps)	EACH	
				1-49	50-Up
798-0722	PFRA.010	60	40	.49	.28
798-0726	PFRA.020	60	40	.58	.35
798-0728	PFRA.025	60	40	.58	.35
798-0730	PFRA.030	60	40	.58	.35
798-0732	PFRA.040	60	40	.58	.37
798-0734	PFRA.050	60	40	.58	.37
798-0738	PFRA.075	60	40	.64	.42
798-0740	PFRA.090	60	40	.58	.38
798-0742	PFRA.110	30	40	.58	.38
798-0748	PFRA.185	30	40	.67	.42
798-0750	PFRA.250	30	40	.63	.43
798-0754	PFRA.400	30	40	.72	.48
798-0756	PFRA.500	30	40	.72	.51
798-0762	PFRA.800	30	40	.72	.57
798-0764	PFRA.900	30	40	.94	.61
798-0766	PFRX.110	60	40	.69	.42
798-0768	PFRX.135	60	40	.71	.45
798-0770	PFRX.160	60	40	.69	.46
798-0772	PFRX.185	60	40	.69	.46
798-0776	PFRX.300	60	40	.74	.53
798-0778	PFRX.375	60	40	.74	.56


Stock No.	Mfr.'s Type	V Max. (Volts)	I Max. (Amps)	Reel Qty.	PER REEL
798-8001	PFMD.020.2	30.0	10	1500	625.50
798-8002	PFMD.035.3	6.0	40	1500	625.50
798-8003	PFMD.050.2	15.0	40	1500	625.50
798-8004	PFMD.075.2	13.2	40	1500	625.50
798-8005	PFMD.110.2	6.0	40	1500	625.50

**Quick-Acting High Breaking
Microfuse — 125 V**

Fast-acting MSA 125 V fuse is according to IEC 127. 12 A and 15 A/32 V. Fuse breaks at 300 A/125 V AC. UL recognized, CSA certified 63 mA-15 A.

Stock No.	Mfr.'s Type	Amps	EACH
798-0198	0034.4807	63 mA	1.27
798-0200	0034.4810	125 mA	1.20
798-0202	0034.4813	250 mA	1.26
798-0204	0034.4815	375 mA	.93
798-0206	0034.4817	500 mA	.93
798-0208	0034.4820	750 mA	.90
798-0210	0034.4822	1.0 A	.93
798-0212	0034.4824	1.5 A	.90
798-0214	0034.4826	2.0 A	.87
798-0216	0034.4827	2.5 A	.93
798-0218	0034.4828	3.0 A	.93
798-0220	0034.4830	3.5 A	.93
798-0222	0034.4831	4.0 A	.93
798-0224	0034.4832	5.0 A	.87
798-0226	0034.4833	7.0 A	.93
798-0228	0034.4834	10.0 A	.93
798-0230	0034.4835	12.0 A	1.35
798-0232	0034.4836	15.0 A	1.35

**Fuseholders for
Microfuses**



798-0462. 0031.7501 125 V Vertical Fuseholder.....EACH .64
798-0524. 0031.7601 250 V Vertical Fuseholder.....EACH .64

Miniature Fuses/ Holders

**Quick-Acting and Time-Lag
Microfuses — 125 V/250 V**

MSF 125 V and MST/FRT 250 V built according to IEC 127. MSF 125 V breaks at 300 A/125 V AC. MSF/MST 250 V breaks at 35 A/250 V AC. FRT 250 V breaks at 100 A/250 V AC. UL recognized, CSA accepted (MSF 125 — 100 mA-5 A, MSF 250 — 40 mA-5 A, MST 250 — 50 mA-6.3 A). VDE approved (MSF 125; MST 250 — 50 mA-4 A; MSF 250 — 50 mA-3.15 A). Material meets UL 94V-0 flammability. 125 V and 250 V microfuse holders ordered separately. Larger quantities available on tape and reel.

Stock No.	Mfr.'s Type	Amps	EACH
798-0234	0034.4209	100 mA	2.29
798-0236	0034.4210	125 mA	2.23
798-0238	0034.4211	160 mA	2.05
798-0240	0034.4212	200 mA	2.16
798-0242	0034.4213	250 mA	2.05
798-0244	0034.4214	315 mA	2.16
798-0246	0034.4215	400 mA	2.16
798-0248	0034.4216	500 mA	2.05
798-0250	0034.4217	630 mA	2.16
798-0252	0034.4220	800 mA	2.16
798-0254	0034.4221	1.00 A	2.16
798-0256	0034.4222	1.25 A	2.05
798-0258	0034.4223	1.60 A	2.16
798-0260	0034.4224	2.00 A	2.16
798-0262	0034.4225	2.50 A	2.16
798-0264	0034.4226	3.15 A	2.05
798-0266	0034.4227	4.00 A	2.05
798-0268	0034.4228	5.00 A	2.16

MSF 250 V Quick-Acting

798-0270	0034.6003	80 mA	.57
798-0272	0034.6004	100 mA	.46
798-0274	0034.6005	125 mA	.49
798-0276	0034.6006	160 mA	.45
798-0278	0034.6007	200 mA	.45
798-0280	0034.6008	250 mA	.42
798-0282	0034.6009	315 mA	.45
798-0284	0034.6010	400 mA	.37
798-0286	0034.6011	500 mA	.49
798-0290	0034.6013	800 mA	.45
798-0292	0034.6014	1.00 A	.46
798-0294	0034.6015	1.25 A	.42
798-0296	0034.6016	1.60 A	.42
798-0298	0034.6017	2.00 A	.42
798-0300	0034.6018	2.50 A	.45
798-0302	0034.6019	3.15 A	.42
798-0304	0034.6020	4.00 A	.42
798-0306	0034.6021	5.00 A	.42

MST 250 V Time-Lag

798-0466	0034.6604	80 mA	.73
798-0468	0034.6605	100 mA	.65
798-0470	0034.6606	125 mA	.70
798-0472	0034.6607	160 mA	.53
798-0474	0034.6608	200 mA	.52
798-0476	0034.6609	250 mA	.47
798-0478	0034.6610	315 mA	.46
798-0480	0034.6611	400 mA	.57
798-0482	0034.6612	500 mA	.47
798-0484	0034.6613	630 mA	.47
798-0486	0034.6614	800 mA	.47
798-0488	0034.6615	1.00 A	.47
798-0490	0034.6616	1.25 A	.46
798-0492	0034.6617	1.60 A	.47
798-0494	0034.6618	2.00 A	.47
798-0496	0034.6619	2.50 A	.47
798-0498	0034.6620	3.15 A	.47
798-0500	0034.6621	4.00 A	.50
798-0502	0034.6622	5.00 A	.47

FRT 250 T Time-Lag for Telecom — *NEW* —

798-5076	7100.1009.13	250 mA	.70
798-5077	7100.1011.13	400 mA	.70
798-5078	7100.1012.13	500 mA	.70
798-5079	7100.1014.13	800 mA	.70
798-5080	7100.1015.13	1.00 A	.70
798-5081	7100.1016.13	1.25 A	.70
798-5082	7100.1018.13	2.00 A	.70
798-5083	7100.1019.13	2.50 A	.70
798-5084	7100.1020.13	3.15 A	.70
798-5085	7100.1021.13	4.00 A	.70
798-5086	7100.1022.13	5.00 A	.70
798-5087	7100.1023.13	6.30 A	.70

FRT 250 F Quick-Acting — *NEW* —

798-5088	7100.1059.13	250 mA	.65
798-5089	7100.1061.13	400 mA	.65
798-5090	7100.1062.13	500 mA	.65
798-5091	7100.1064.13	800 mA	.65
798-5092	7100.1065.13	1.00 A	.65
798-5093	7100.1066.13	1.25 A	.65
798-5094	7100.1068.13	2.00 A	.65
798-5095	7100.1069.13	2.50 A	.65
798-5096	7100.1070.13	3.15 A	.65
798-5097	7100.1071.13	4.00 A	.65
798-5098	7100.1072.13	5.00 A	.65
798-5099	7100.1073.13	6.30 A	.65