

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2011 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
DW

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
B3		REVISED (ECR-14-002413)	05JUN14	SW	SC

NOTES:

1. MATERIAL:

HOUSING: THERMOPLASTIC (SEE TABLE), WITH 30% GF, UL 94V-0, BLACK COLOR.

CONTACT: PHOSPHOR BRONZE, (t=0.25mm).

SHIELD: COLD ROLL STEEL, (t=0.35mm)





GROUNDING STRIP: STAINLESS, (t=0.20 & 0.25mm)

2. FINISH :

CONTACT: 0.762 μ m [30 μ "] MIN. GOLD PLATING ON CONTACT AREA,
3.81 μ m [150 μ "] MIN. BRIGHT TIN PLATING ON SOLDERTAILS,1.27 μ m [50 μ "] MIN. NICKEL UNDERPLATING OVERALL.SHIELD: 3.048 μ m [120 μ "] MIN. NICKEL PLATED OVERALL.

⚠ WAVE SOLDER CAPABLE TO 245°C PER TE SPEC109-201, CONDITION A.

⚠ REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.

RECOMMENDED P.C.B. LAYOUT (THICKNESS=1.6mm)
(TOP VIEW) (TOLERANCE:±0.05mm)

REAR VIEW

OBSOLETE	⚠ PA9T	W/	W/O	2-1734084-2
OBSOLETE	⚠ PBT	W/	W/O	2-1734084-1
OBSOLETE	⚠ PA9T	W/O	W/	1-1734084-2
OBSOLETE	⚠ PBT	W/O	W/	1-1734084-1
	⚠ PA9T	W/O	W/O	0-1734084-2
OBSOLETE	⚠ PBT	W/O	W/O	0-1734084-1
	HSG.MATERIAL	GROUND PANEL B	GROUND PANEL A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

SEE NOTE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± 0.35
2 PLC	± 0.25
3 PLC	± 0.15
4 PLC	± -
ANGLES	± 3°

FINISH

SEE NOTE

DWN O. HU 07JUL2005

CHK S. JOU 07JUL2005

APVD W.J. KF 07JUL2005

PRODUCT SPEC

108-57549

APPLICATION SPEC

WEIGHT 6.16 GRAMS

CUSTOMER DRAWING



TE Connectivity

RCPT, STACKED, USB, R/A, A TYPE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=1734084	-

SCALE	SHEET	REV
-	1 of 2	B3

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2011 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR


DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.




7.30 Kg	6.16 Kg	100	10	1000
GROSS WEIGHT	NET WEIGHT	PCS/TRAY	TRAY /CARTON	QUANTITY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

MATERIAL

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME



TE Connectivity

RCPT, STACKED, USB, R/A, A TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1734084

SCALE

SHEET

2 of 2

REV B3