

Customer Information Sheet

DRAWING No.: M20-784XXXX

SHEET 3 OF 3


IF IN DOUBT - ASK

©

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

**SPECIFICATION:****MATERIAL:**MOULDING - NYLON 6T UL94V-0, BLACK
CONTACTS - PHOSPHOR BRONZE**FINISH:**42 - GOLD ON CONTACT AREA, 100% TIN ON TAILS
46 - 100% TIN**ELECTRICAL:**

CURRENT RATING - 3A

VOLTAGE PROOF - 600V AC FOR 1 MINUTE

CONTACT RESISTANCE - 20 MILLIOHMS MAX


INSULATION RESISTANCE - 1,000 MEGOHMS MIN

ENVIRONMENTAL:

TEMPERATURE RANGE - -40° TO +105°

PACKING:

TUBE

FOR COMPLETE SPECIFICATION SEE COMPONENT
SPECIFICATION C001XX (LATEST ISSUE)**ORDER CODE:****M20-784XXXX****No. OF WAYS**

02 TO 40

FINISH:

42 - SELECTIVE GOLD + 100% TIN

46 - 100% TIN

NOTES:

1. THIS CONNECTOR CAN ALSO
BE USED FOR TOP ENTRY.

RA	3	12.11.08	10203
NAME	ISS.	DATE	C/NOTE
APPROVED: <i>[Signature]</i>			
CHECKED: <i>[Signature]</i>			
DRAWN: JM BROOKES			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN USA TEL: 603 893 5376 FAX: 603 893 5396 mis@harwin.com	HARWIN Europe (UK) TEL: 023 9231 4545 FAX: 023 9231 4590 mis@harwin.co.uk	HARWIN Asia TEL: +65 6 779 4909 FAX: +65 6 779 3868 mis@harwin.com.sg
--	--	--

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²**TITLE:**2.54mm PITCH SIL PC TAIL
DUAL ENTRY SOCKET ASSY**DRAWING NUMBER:****M20-784XXXX**SHT
3
OF
3