

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

95503-6894

Status:


Active

Overview:

Modular Plugs - Jacks

Description:

8/8 Low Profile Jack, Surface Mount Short Version, Tin (Sn) Plated



- Documents:
- 3D Model

Drawing (PDF)

Product Specification PS-95503-001 (PDF)

Application Specification AS-85513-001 (PDF)

Test Summary STR-1181 (PDF)

Test Summary STR-1429 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E107635

General

Product Family

Series

Component Type

Magnetic

Overview

Performance Category

Power over Ethernet (PoE)

Product Name

UPC

Modular Jacks/Plugs

95503

PCB Jack

No

Modular Plugs - Jacks

3

N/A

RJ45

800756804392

Physical

Color - Resin

Durability (mating cycles max)

Flammability

Inverted / Top Latch

Jack Height

Keying to Mating Part

Lightpipes/LEDs

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Orientation

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Ports

Positions / Loaded Contacts

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

Waterproof / Dustproof

Wire/Cable Type

Black

750

94V-0

N/A

12.70mm

None

None

Brass

Gold

Tin

High Temperature Thermoplastic

2.570/g

Vertical (Top Entry)

Yes

Yes

1.57mm

Tube

1.02mm

1.27mm

1.270µm

1.905µm

1

8/8

Yes

-40°C to +80°C

Surface Mount

No

N/A

Electrical

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

95503Series

Mates With

90075 Modular Plug

Current - Maximum per Contact	1.5A
Shielded	No
Voltage - Maximum	125V DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	40
Lead-free Process Capability	Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature	3
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Application Specification	AS-85513-001
Product Specification	PS-95503-001, RPS-95503-002
Sales Drawing	SD-95503-003
Test Summary	STR-1181, STR-1429

This document was generated on 08/13/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[95503-6894](#)