


Metal Film, Standard, Professional



FEATURES

- Stable metal film on high quality ceramic
- Low temperature coefficient and tolerances
- Lead (Pb)-free solder contacts
- Pure tin plating provides compatibility with Lead (Pb)-free and lead containing soldering processes
- Compatible with "Restriction of the use of Hazardous Substances" (RoHS) directive 2002/95/EC (issue 2004)
- Excellent stability
- Force fitted metal caps retain a good electrical connection to the resistive film
- Suitable for commercial and professional applications



STANDARD ELECTRICAL SPECIFICATIONS							
MODEL	SIZE	POWER RATING $P_{70^{\circ}\text{C}}$ W	LIMITING ELEMENT VOLTAGE MAX. $V_{\cong}$	TEMPERATURE COEFFICIENT ppm/K	TOLERANCE %	RESISTANCE RANGE Ω	E-SERIES
SMA0204 MK1	0204	0.4	250	± 25	± 0.5	10R - 1M0	24 - 192
SMA0204 MK1	0204	0.4	250	± 50	± 0.5 ± 1	10R - 1M0 1R0 - 10M	24 - 192 24 - 96
SMA0204 MK1	0204	0.4	250	± 100	± 5	R22 - 10M	24
SMA0204*	0204	0.5	250	± 15	$\pm 0.1, \pm 0.25, \pm 0.5$	51R1 - 332K	24 - 192
SMA0204*	0204	0.5	250	± 25	± 0.1 ± 0.25 ± 0.5	51R1 - 322K 22R - 322K 10R - 511K	24 - 192 24 - 192 24 - 192
SMA0204*	0204	0.5	250	± 50	± 0.5 ± 1	10R - 511K 1R0 - 7M5	24 - 192 24 - 96
SMA0204*	0204	0.5	250	± 100	± 5	1R0 - 7M5	24
SMA0207 MK2	0207	0.25	350	± 5	$\pm 0.1, \pm 0.25, \pm 0.5$	1K0 - 100K	192
SMA0207 MK2	0207	0.25	350	± 10	$\pm 0.1, \pm 0.25, \pm 0.5$	510R - 100K	192
SMA0207 MK2	0207	0.6	350	± 15	$\pm 0.1, \pm 0.25, \pm 0.5$	47R - 1M0	24 - 192
SMA0207 MK2	0207	0.6	350	± 25	± 0.1 ± 0.25 ± 0.5	47R - 1M0 10R - 1M0 1R0 - 2M2	24 - 192 24 - 192 24 - 192
SMA0207 MK2	0207	0.6	350	± 50	± 0.5 ± 1	1R0 - 2M2 1R0 - 10M	24 - 96 24 - 96
SMA0207 MK2	0207	0.6	350	± 100	± 5	R16 - 10M	24
SMA0309	0309	0.7	350	± 50	± 1	10R - 1M0	24 - 96
SMA0309	0309	0.7	350	± 100	± 5	10R - 1M0	24
SMA0411	0411	1.0	500	± 15	$\pm 0.1, \pm 0.25, \pm 0.5$	47R - 1M0	24 - 192
SMA0411	0411	1.0	500	± 25	± 0.1 $\pm 0.25, \pm 0.5$	47R - 1M0 10R - 1M0	24 - 192 24 - 192
SMA0411	0411	1.0	500	± 50	± 0.5 ± 1	10R - 1M0 1R0 - 10M	24 - 96 24 - 96
SMA0411	0411	1.0	500	± 100	± 5	1R0 - 10M	24
MK4	0414	1.0	500	± 25	± 0.5	10R - 2M4	24 - 192
MK4	0414	1.0	500	± 50	± 0.5 ± 1.0	10R - 2M4 1R0 - 10M	24 - 96 24 - 96
MK4	0414	1.0	500	± 100	± 5	R22 - 10M	24
MK5	0617	1.2	600	± 50	± 0.5 ± 1	10R - 2M4 1R0 - 5M1	24 - 96 24 - 96
MK5	0617	1.2	600	± 100	± 5	R22 - 5M1	24
MK8	0922	1.5	600	± 50	± 0.5 ± 1	10R - 2M4 1R0 - 2M4	24 - 96 24 - 96
MK8	0922	1.5	600	± 100	± 5	R22 - 2M4	24

- Temperature coefficient $\leq 10 \text{ ppm}/^{\circ}\text{C}$: temperature range $-25^{\circ}\text{C}..+85^{\circ}\text{C}$
- Limiting element voltage $\sqrt{P \times R}$
- Further values and tolerances on request
- For Zero-ohm resistors, special assembly versions, and marking please see appropriate catalog or web page.

**PART NUMBER AND PRODUCT DESCRIPTION SMA-SERIES**

PART NUMBER: SMA02040D5620DD5

S M A 0 2 0 4 0 D 5 6 2 0 D D 5																	
MODEL/SIZE		SPECIAL CHARACTER		TC		VALUE		TOLERANCE		PACKING		SPECIAL					
SMA0204 SMA0207 SMA0309 SMA0411		0 = Neutral		G = ± 5 ppm/K F = ± 10 ppm/K E = ± 15 ppm/K D = ± 25 ppm/K C = ± 50 ppm/K B = ± 100 ppm/K		3 digit value 1 digit multiplier		B = ± 0.1 % C = ± 0.25 % D = ± 0.5 % F = ± 1 % J = ± 5 %		12 = A2 (G26) 2C = AC 21 = A1 (G53) 22 = A2 (G53) 25 = A5 41 = A1 (G73) DE = RE D5 = R5 D3 = R3		up to 2 digits 00 = Standard					
						MULTIPLIER											
						7 = *10 ⁻³ 8 = *10 ⁻² 9 = *10 ⁻¹ 0 = *10 ⁰ 1 = *10 ¹ 2 = *10 ² 3 = *10 ³ 4 = *10 ⁴ 5 = *10 ⁵ 6 = *10 ⁶											

PRODUCT DESCRIPTION: SMA0204 25 562R 0.5% R5

PRODUCT DESCRIPTION: SMA0204 25 562R 0.5% R5

SMA0204	25	562R	0.5 %	R5
MODEL	TC	RESISTANCE VALUE	TOLERANCE	PACKING ¹⁾
SMA0204 SMA0207 SMA0309 SMA0411	± 5 ppm/K ± 10 ppm/K ± 15 ppm/K ± 25 ppm/K ± 50 ppm/K ± 100 ppm/K	49K9 = 49.9 K Ω 50R1 = 50.1 Ω	± 0.1 % ± 0.25 % ± 0.5 % ± 1 % ± 5 %	AC A1 G53 A2 G53 A2 G26 A5 A1 G73 RE R3 R5

¹⁾ Please refer to table PACKING, page 3.**PART NUMBER AND PRODUCT DESCRIPTION MK-SERIES**

PART NUMBER: MK102040D5620DD5

M	K	1	0	2	0	4	0	D	5	6	2	0	D	D	5		
MODEL\SIZE	SPECIAL CHARACTER				TC			VALUE			TOLERANCE		PACKING		SPECIAL		
MK10204 MK20207 MK40414 MK50617 MK80922	0 = Neutral				G = ± 5 ppm/K F = ± 10 ppm/K E = ± 15 ppm/K D = ± 25 ppm/K C = ± 50 ppm/K B = ± 100 ppm/K			3 digit value 1 digit multiplier			B = ± 0.1 % C = ± 0.25 % D = ± 0.5 % F = ± 1 % J = ± 5 %		2C = AC 21 = A1 (G53) 22 = A2 25 = A5 41 = A1 (G73) DE = RE D5 = R5 GP = RP G1 = R1		up to 2 digits 00 = Standard		
								MULTIPLIER									
								7 = *10 ⁻³ 8 = *10 ⁻² 9 = *10 ⁻¹ 0 = *10 ⁰ 1 = *10 ¹ 2 = *10 ² 3 = *10 ³ 4 = *10 ⁴ 5 = *10 ⁵ 6 = *10 ⁶									

PRODUCT DESCRIPTION: MK1 25 562B 0.5% R5


PRODUCT DESCRIPTION: MK1 25 562R 0.5% R5

MK1	25	562R	0.5 %	R5
MODEL	TC	RESISTANCE VALUE	TOLERANCE	PACKING ¹⁾
MK1 MK2 MK4 MK5 MK8	± 5 ppm/K ± 10 ppm/K ± 15 ppm/K ± 25 ppm/K ± 50 ppm/K ± 100 ppm/K	49K9 = 49.9 K Ω 50R1 = 50.1 Ω	± 0.1 % ± 0.25 % ± 0.5 % ± 1 % ± 5 %	AC A1 G53 A2 A5 A1 G73 RE R5 RP R1

¹⁾ Please refer to table PACKING, page 3.

PACKING					
MODEL	REEL		BOX		MIN.ORDER QTY PACKING UNITS
	PIECES / REEL	CODE	PIECES / BOX	CODE	
SMA0204	5000	R5	2 000 500	A2 AC	1
MK1	5 000	R5	5 000 2 000	A5 A2	1
SMA0207	5000	R5	2 000 1 000 500	A2 A1 AC	1
MK2	5000	R5	5 000 2 000	A5 A2	1
SMA0309	3000	R3	5 000 2 000	A5 A2	1
SMA0411	2500	RE	1 000 500	A1 AC	1
	2500	RE	1 000	A1	1
MK4	2500	RE	1 000	A1	1
MK5	1500	RP	1 000	A1	1
MK8	1000	R1	500	AC	1

DIMENSIONS





- Taping in acc. with IEC60286-1
- D and L measured in acc. with IEC60294
- d according to IEC60301


¹⁾ Also available in 26mm taping. *9mm for MK5, MK8

MODEL	DIMENSIONS [in millimeters]					
	D _{max}	L	L ₁ MAX	B	d	e
SMA0204/MK1	1.6 _{-0.3}	3.6 _{-0.4}	4.0	53 ±1 ¹⁾	0.5	5.0
SMA0204	1.8 _{-0.25}	3.6 _{-0.3}	4.0	53 ±1 ¹⁾	0.5	5.0
SMA0207/MK2	2.5 _{-0.3}	6.3 _{-0.5}	7.0	53 ±1 ¹⁾	0.6	7.5
SMA0309	3.0 _{-0.4}	8.2 _{-0.6}	9.5	53 ±1	0.7	10
SMA0411	3.7 _{-0.4}	10.5 _{-0.6}	12.5	53 ±1	0.7	12.5
MK4	4.1 _{-0.5}	12.0 _{-1.5}	14.0	73 ±1	0.8	15
MK5	6.0 _{-0.5}	16.5 _{-1.5}	18.5	77 ±1	0.8	17.5
MK8	9.0 _{-0.5}	20.0 _{-1.5}	24.0	77 ±1	0.8	22.5


**TECHNICAL SPECIFICATIONS**

PARAMETER	UNIT	MK1	SMA0204 ²⁾	SMA0207/MK2	SMA0309	SMA0411	MK4	MK5	MK8
Rated Dissipation at 70 °C	W	0.4	0.5	0.6	0.7	1.0	1.0	1.2	1.5
Limiting Element Voltage ²⁾	V _≧	≤250	≤250	≤350	≤350	≤500	≤500	≤600	≤600
Insulation Voltage (1min)	V _{eff}	>500	>500	>700	>700	>700	>500	>500	>500
Thermal Resistance	K/W	≤200	≤170	≤140	≤120	≤100	≤95	≤70	≤60
Insulation Resistance	Ω	≥10 ¹¹							
Category Temperature Range	°C	-55 to +155							
Failure Rate	10 ⁻⁹ /h	<1							
Terminal Strength, axial	N	>30	>30	>50	>60	>60	>80	>80	>80
Weight	g	0.1	0.14	0.22	0.31	0.52	0.67	1.5	3.3

²⁾Rated Voltage $\sqrt{P \times R}$ **DERATING****TEMPERATURE RISE**










NON-LINEARITY



CURRENT NOISE

STABILITY NOMOGRAM, TYPICAL VALUES (For handling see General Information)





PERFORMANCE		
TEST	CONDITIONS OF TEST	REQUIREMENTS*
Endurance at 70°C IEC 60115-1 4.25.1	1000 hours at 70°C 1.5 hours "ON", 0.5 hours "OFF" 8000 hours at 70°C 1.5 hours "ON", 0.5 hours "OFF"	$\leq \pm 0.5\%$ $\leq \pm 1.0\%$
Endurance at Upper Category Temperature IEC 60115-1 4.25.3	1000 hours at 155°C without load 8000 hours at 155°C without load	$\leq \pm 0.5\%$ $\leq \pm 1.0\%$
Overload Test IEC 60115-1 4.13	Short time overload at 6.25 x rated power 2 seconds for size 0204 and 5s for sizes ≥ 0207	$\leq \pm 0.1\%$
Thermal Shock IEC 60115-1 4.19 IEC 60068-2-14	Rapid change between upper and lower category temperature	$\leq \pm 0.1\%$
Climatic Sequence IEC 60115-1 4.23	Dry heat, damp heat cyclic, cold, low air pressure	$\leq \pm 0.5\%$
Damp Heat Steady State IEC 60115-1 4.24 IEC 60068-2-3	56 days at 40°C and 93% relative humidity	$\leq \pm 0.5\%$
Resistance to Soldering Heat IEC 60115-1 4.18; IEC 60068-2-20	10 seconds at 260°C solder bath temperature	$\leq \pm 0.1\%$
Robustness of Terminations IEC 60115-1 4.16	Tensile, bending and torsion	$\leq \pm 0.1\%$
Vibration IEC 60115-1 4.22	0.75mm or 10g, 10Hz - 500Hz 6 hours	$\leq \pm 0.1\%$

* for a resistance range from 10Ω to 2MΩ, limits for change of resistance at test

APPLICABLE SPECIFICATIONS
- CECC 40000 / 40100 / 40101 - EN 140 000 / 140 100



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.