

LOC	DIST	REVISIONS				
		REV	LTR	DESCRIPTION	DATE	DWN
AJ	16	A1		REVISED PER ECO-11-005030	11MAR11	RK

- 1

ZINC PER QQ-Z-363.
- 2

POLYMETHYLPENTENE PER ASTM-D-1238.
- 3

PHOSPHOR BRONZE PER QQ-B-750.
- 4




BRASS PER ASTM-B-453.
- 5

BRASS PER ASTM-B-16.
- 6

NICKEL PLATE PER QQ-N-290,
3.81 μ m [.000150] MINIMUM THICK.
- 7

TIN PLATE PER ASTM-B-545,
3.81 μ m [.000150] MINIMUM THICK.
- 8

SEE INSTRUCTION SHEET 408-2769.




RECOMMENDED PANEL CUTOUT

PCB CONFIGURATION

5227661-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ALCORTA - 26APR2005	 TE Connectivity	
		CHK J. HAVENER - 26APR2005		
DIMENSIONS: mm [INCHES]		APVD J. LIPPERT - 26APR2005	NAME	
		PRODUCT SPEC		JACK, RIGHT ANGLE, PCB 50 OHM, SERIES BNC
		APPLICATION SPEC		
MATERIAL 		WEIGHT —		RESTRICTED TO —
FINISH 		CUSTOMER DRAWING		
		SCALE 4:1		SHEET 1 OF 1
		REV A1		