




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		N2	REVISED PER ECO-11-005030	11MAR11	RK	HMR



VIEW B



VIEW C

1. FOR CABLE SELECTION, FERRULE AND HANDTOOL PART NUMBERS, SEE I.S. 2024-2

- 2 GOLD PLATE PER MIL-G-45204,.000027 MINIMUM THICKNESS
- 3 GOLD PLATE PER MIL-G-45204,.000045 MINIMUM THICKNESS
- 4 GOLD PLATE PER MIL-G-45204,.000030 MINIMUM THICKNESS
- 5 GOLD PLATE PER MIL-G-45204,.000050 MINIMUM THICKNESS
- 6 TIN PLATE PER MIL-T-10272
- 7 BRASS PER QQ-B-626
- 8 BRASS PER MIL-C-50
- 9 POLYPROPYLENE,GENERAL PURPOSE
- 10 BRASS PER ASTM-B-135
- 11 STAINLESS STEEL,SPRING TEMPER PER QQ-S-766
- 12 PTFE PER MIL-P-19468
- 13 SIGHT HOLE VISIBLE THROUGH THE PORT SLOT ON RETENTION SPRING
- 14 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

13	OBSOLETE	A	2/4	7/8/9/11	1-51565-5
14	OBSOLETE	A	2/4	7/8/9/11	1-51565-4
	OBSOLETE	B	3/5	7/8/9/11/12	1-51565-3
	OBSOLETE	C	3/5/6	7/8/9/10/11	51565-6
	OBSOLETE	B	3/5	7/8/9/11	51565-5
	OBSOLETE	A	3/5	7/8/9/11	51565-4
	OBSOLETE	C	2/4/6	7/8/9/10/11	51565-3
		B	2/4	7/8/9/11	51565-2
		A	2/4	7/8/9/11	51565-1
		VIEW	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. WERNER 4-23-91	TE Connectivity		
DIMENSIONS: INCHES		CHK D. DOYE 5-3-91			
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH	APVD -	NAME SOCKET ASSEMBLY, SERIES SUBMINIATURE -		
		PRODUCT SPEC -			
		APPLICATION SPEC -			
MATERIAL SEE TABLE	SEE TABLE	WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=51565
CUSTOMER DRAWING			SCALE 8:1	SHEET 1 of 1	REV N2