

Home: Ring and Spade Terminals >

Part Number: 50460-7025

Spade Tongue Terminal for 20-24 AWG, Closed Un-insulated Brazed Barrel, Stud Size 2 (M2), Oxygen-Free Copper, Length 12.50mm



Status: **OBSOLETE**

Replacement: Contact Molex

Series: 50460

Category: Ring and Spade Terminals

CHECK DISTRIBUTOR INVENTORY

Add to My Parts

Email this page

Go to **Part Detail**▼

Series image - Reference only

Product Environmental Compliance

EU ELV:Product not active

EU RoHS:Product not active

EU RoHS Phthalates:Product not active

China RoHS:

REACH SVHC:Product not active

Low-Halogen Status:Product not active

EU RoHS Certificate of Compliance (PDF)

Multiple Part Product Compliance Statements

EU RoHS, REACH SVHC, & Low-Halogen

Multiple Part Industry Compliance Documents

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

Questions on Product Environmental Compliance? Email ProductCompliance@molex.com

Request Molex's CMRT from conflictminerals@molex.com

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Japan

Description	Product #
Hand Crimper For JIS Terminal	57343-5001

Crimp Quality Equipment

[Molex also offers wire strippers, pull testers, shut-height gauges, micro-meters and more](#)

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Part Detail

COLLAPSE ALL

▼ General

Status	Obsolete
Category	Ring and Spade Terminals
Series	50460
Mil-Spec	N/A
Product Name	Y (Spade)
Type	Spade
UPC	800754838016

▼ Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Packaging Type	Bag
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Stud Size	2 (M2)
Termination Interface: Style	Crimp or Compression
Wire Size AWG	20, 22, 24

▼ Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)

UL	E134962
----	---------

PRODUCTS

Antennas
Application Tooling
Cable Assemblies
Connected Lighting
Connectors
Copper Flex
Electrical Products
Industrial Automation
Membrane Switches
Optical Solutions
Printed Electronic Solutions

QUICK LINKS

Company Information
Contact Molex
Cross-Reference
Koch Industries
Industries
Investor Relations
Literature
Molex Racing
Press Room / Press Releases
Product Index
Sitemap
Terms & Conditions

RESOURCES

Supply Chain Transparency
Business Continuity
Compliance
ecocare
Feedback | Help
Jobs
Legal | Trademarks
Mobile Site
Supplier Portal
Privacy Policy
Tradeshows

STAY CONNECTED

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2017