



# 40ns, Low-Power, 3V/5V, Rail-to-Rail Single-Supply Comparators

## General Description

The MAX9140/MAX9141 are single and the MAX9142/MAX9144 are dual/quad high-speed comparators optimized for systems powered from a 3V or 5V supply. The MAX9141 features latch enable and device shutdown. These devices combine high speed, low power, and rail-to-rail inputs. Propagation delay is 40ns, while supply current is only 150µA per comparator.

The input common-mode range of the MAX9140/MAX9141/MAX9142/MAX9144 extends beyond both power-supply rails. The outputs pull to within 0.3V of either supply rail without external pullup circuitry, making these devices ideal for interface with both CMOS and TTL logic. All input and output pins can tolerate a continuous short-circuit fault condition to either rail. Internal hysteresis ensures clean output switching, even with slow-moving input signals.

The MAX9140/MAX9141/MAX9142/MAX9144 are higher-speed, lower-power, and lower-cost upgrades to industry-standard comparators MAX941/MAX942/MAX944.

The MAX9140 are offered in tiny 5-pin SC70 and SOT23 packages. The MAX9141 and MAX9142 are available in 8-pin SOT23 and SO packages, while the MAX9144 is available in both 14-pin SO and TSSOP packages.

## Applications

Line Receivers  
Battery-Powered Systems  
Threshold Detectors/Discriminators  
3V/5V Systems  
Zero-Crossing Detectors  
Sampling Circuits

## Features

- ♦ Fast, 40ns Propagation Delay (10mV Overdrive)
- ♦ Low Power  
150µA Supply Current Per Comparator (3V)
- ♦ Optimized for 3V and 5V Applications
- ♦ Rail-to-Rail Input Voltage Range
- ♦ Low, 500µV Offset Voltage
- ♦ Internal Hysteresis for Clean Switching
- ♦ Outputs Swing 300mV of Power Rails
- ♦ CMOS/TTL-Compatible Outputs
- ♦ Output Latch (MAX9141 Only)
- ♦ Shutdown Function (MAX9141 Only)
- ♦ Available in SC70 and SOT23 Packages

## Ordering Information

| PART*                 | PIN-PACKAGE | TOP MARK |
|-----------------------|-------------|----------|
| <b>MAX9140</b> AAUK+T | 5 SOT23     | +AFEJ    |
| MAX9140AAXK+T         | 5 SC70      | +ASW     |
| MAX9140AAXK/V+T       | 5 SC70      | +AUG     |
| MAX9140EXK-T          | 5 SC70      | ACC      |
| MAX9140EUK-T          | 5 SOT23     | ADQP     |
| <b>MAX9141</b> EKA-T  | 8 SOT23     | AAFD     |
| MAX9141ESA            | 8 SO        | —        |
| <b>MAX9142</b> EKA-T  | 8 SOT23     | AAFE     |
| MAX9142ESA            | 8 SO        | —        |
| <b>MAX9144</b> EUD    | 14 TSSOP    | —        |
| MAX9144ESD            | 14 SO       | —        |

**Note:** All E-grade devices are specified over the -40°C to +85°C operating temperature range. All A-grade devices are specified over the -40°C to +125°C operating temperature range.


+ Denotes a lead(Pb)-free/RoHS-compliant package.

- Denotes a package containing lead(Pb).

T = Tape and reel.

/V denotes an automotive qualified part.

## Pin Configurations



# 40ns, Low-Power, 3V/5V, Rail-to-Rail Single-Supply Comparators

## ABSOLUTE MAXIMUM RATINGS

### Power-Supply Ranges

|                                                    |                              |
|----------------------------------------------------|------------------------------|
| Supply Voltage ( $V_{CC}$ to GND).....             | +6V                          |
| Differential Input Voltage.....                    | -0.3V to ( $V_{CC} + 0.3$ V) |
| Common-Mode Input Voltage to GND ..-               | 0.3V to ( $V_{CC} + 0.3$ V)  |
| $\overline{LE}$ Input Voltage (MAX9141 only) ..... | -0.3V to ( $V_{CC} + 0.3$ V) |
| SHDN Input Voltage (MAX9141 only)....              | -0.3V to ( $V_{CC} + 0.3$ V) |

Current into Input Pins .....±20mA  
 Input/Output Short-Circuit Duration to

$V_{CC}$  or GND .....Continuous

Continuous Power Dissipation ( $T_A = +70^\circ\text{C}$ )

5-Pin SC70 (derate 3.1mW/ $^\circ\text{C}$  above  $+70^\circ\text{C}$ ).....247mW

|                                                                                |                                              |
|--------------------------------------------------------------------------------|----------------------------------------------|
| 5-Pin SOT23 (derate 7.1mW/ $^\circ\text{C}$ above $+70^\circ\text{C}$ ).....   | 571mW                                        |
| 8-Pin SOT23 (derate 9.1mW/ $^\circ\text{C}$ above $+70^\circ\text{C}$ ).....   | 727mW                                        |
| 8-Pin SO (derate 5.9mW/ $^\circ\text{C}$ above $+70^\circ\text{C}$ ).....      | 470.6mW                                      |
| 14-Pin TSSOP (derate 9.1mW/ $^\circ\text{C}$ above $+70^\circ\text{C}$ ) ..... | 727mW                                        |
| 14-Pin SO (derate 8.33mW/ $^\circ\text{C}$ above $+70^\circ\text{C}$ ).....    | 666.7mW                                      |
| Operating Temperature Range                                                    |                                              |
| E grade .....                                                                  | -40 $^\circ\text{C}$ to $+85^\circ\text{C}$  |
| A grade .....                                                                  | -40 $^\circ\text{C}$ to $+125^\circ\text{C}$ |
| Storage Temperature Range .....                                                | -65 $^\circ\text{C}$ to $+150^\circ\text{C}$ |
| Lead Temperature (soldering, 10s) .....                                        | $+300^\circ\text{C}$                         |

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

## ELECTRICAL CHARACTERISTICS

( $V_{CC} = 5\text{V}$ ,  $V_{CM} = 0\text{V}$ ,  $\overline{SHDN} = \overline{LE} = V_{CC}$  (MAX9141 only),  $C_L = 15\text{pF}$ ,  $T_A = T_{MIN}$  to  $T_{MAX}$ , unless otherwise noted. Typical values are at  $T_A = +25^\circ\text{C}$ .) (Note 1)

| PARAMETER                    | SYMBOL     | CONDITIONS                                             |                                                  | MIN              | TYP            | MAX            | UNITS           |
|------------------------------|------------|--------------------------------------------------------|--------------------------------------------------|------------------|----------------|----------------|-----------------|
| Operating Supply Voltage     | $V_{CC}$   | (Note 2)                                               |                                                  | 2.7              |                | 5.5            | V               |
| Input Voltage Range          | $V_{CMR}$  | (Note 3)                                               |                                                  | -0.2             |                | $V_{CC} + 0.2$ | V               |
| Input Offset Voltage         | $V_{OS}$   | (Note 4)                                               | $T_A = +25^\circ\text{C}$                        |                  | 0.5            | 2.0            | mV              |
|                              |            |                                                        | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ |                  |                | 4.5            |                 |
|                              |            |                                                        | MAX9140AA_ _                                     |                  |                | 6.0            |                 |
| Input Hysteresis             | $V_{HYST}$ | (Note 5)                                               |                                                  |                  | 1.5            |                | mV              |
| Input Bias Current           | $I_B$      | (Note 6)                                               | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ |                  | 90             | 320            | nA              |
|                              |            |                                                        | MAX9140AA_ _                                     |                  |                | 350            |                 |
| Input Offset Current         | $I_{OS}$   | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$       |                                                  |                  | 8              | 120            | nA              |
|                              |            | MAX9140AA_ _                                           |                                                  |                  |                | 140            |                 |
| Common-Mode Rejection Ratio  | CMRR       | $V_{CC} = 5.5\text{V}$<br>(Note 7)                     | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ |                  | 80             | 800            | $\mu\text{V/V}$ |
|                              |            |                                                        | MAX9140AA_ _                                     |                  |                | 850            |                 |
| Power-Supply Rejection Ratio | PSRR       | $2.7\text{V} \leq V_{CC} \leq 5.5\text{V}$             | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ |                  | 80             | 750            | $\mu\text{V/V}$ |
|                              |            |                                                        | MAX9140AA_ _                                     |                  |                | 800            |                 |
| Output High Voltage          | $V_{OH}$   | $I_{SOURCE} = 4\text{mA}$                              | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | $V_{CC} - 0.425$ | $V_{CC} - 0.3$ |                | V               |
|                              |            |                                                        | MAX9140AA_ _                                     | $V_{CC} - 0.47$  |                |                |                 |
| Output Low Voltage           | $V_{OL}$   | $I_{SINK} = 4\text{mA}$                                | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ |                  | 0.3            | 0.425          | V               |
|                              |            |                                                        | MAX9140AA_ _                                     |                  |                | 0.45           |                 |
| Output Leakage Current       | $I_{LEAK}$ | $\overline{SHDN} = \text{GND}$ , MAX9141 only (Note 8) |                                                  |                  | 0.04           | 1              | $\mu\text{A}$   |

# 40ns, Low-Power, 3V/5V, Rail-to-Rail Single-Supply Comparators

## ELECTRICAL CHARACTERISTICS (continued)

( $V_{CC} = 5V$ ,  $V_{CM} = 0V$ ,  $\overline{SHDN} = \overline{LE} = V_{CC}$  (MAX9141 only),  $C_L = 15pF$ ,  $T_A = T_{MIN}$  to  $T_{MAX}$ , unless otherwise noted. Typical values are at  $T_A = +25^\circ C$ .) (Note 1)

| PARAMETER                       | SYMBOL                   | CONDITIONS                                                        | MIN                                              | TYP                | MAX | UNITS   |
|---------------------------------|--------------------------|-------------------------------------------------------------------|--------------------------------------------------|--------------------|-----|---------|
| Supply Current (Per Comparator) | $I_{CC}$                 | $V_{CM} = V_{CC} = 3V$                                            | MAX9141                                          | 165                | 275 | $\mu A$ |
|                                 |                          |                                                                   | MAX9140,<br>$T_A = -40^\circ C$ to $+85^\circ C$ | 150                | 250 |         |
|                                 |                          |                                                                   | MAX9140AA__                                      |                    | 360 |         |
|                                 |                          |                                                                   | MAX9142/MAX9144                                  | 150                | 250 |         |
|                                 |                          | $V_{CM} = V_{CC} = 5V$                                            | MAX9141                                          | 200                | 320 |         |
|                                 |                          |                                                                   | MAX9140,<br>$T_A = -40^\circ C$ to $+85^\circ C$ | 165                | 300 |         |
|                                 |                          |                                                                   | MAX9140AA__                                      |                    | 400 |         |
|                                 |                          |                                                                   | MAX9142/MAX9144                                  | 165                | 300 |         |
|                                 |                          | MAX9141 only, $\overline{SHDN} = GND$ ;<br>$V_{CC} = V_{CM} = 3V$ |                                                  | 12                 | 30  |         |
| Propagation Delay               | $t_{PD+}$ ,<br>$t_{PD-}$ | $V_{CC} = 3V$ , $V_{OD} = 10mV$                                   |                                                  | 40                 |     | ns      |
| Differential Propagation Delay  | $dt_{PD}$                | $V_{OD} = 10mV$ (Note 9)                                          |                                                  | 2                  |     | ns      |
| Propagation Delay Skew          |                          | $V_{OD} = 10mV$ (Note 10)                                         |                                                  | 2                  |     | ns      |
| Logic Input-Voltage High        | $V_{IH}$                 | (Note 11)                                                         | $(V_{CC}/2) + 0.4$                               | $V_{CC}/2$         |     | V       |
| Logic Input-Voltage Low         | $V_{IL}$                 | (Note 11)                                                         | $V_{CC}/2$                                       | $(V_{CC}/2) - 0.4$ |     | V       |
| Logic Input Current             | $I_{IL}$ , $I_{IH}$      | $V_{LOGIC} = 0$ to $V_{CC}$ (Note 11)                             |                                                  | 2                  | 10  | $\mu A$ |
| Data-to-Latch Setup Time        | $t_S$                    | (Note 12)                                                         |                                                  | 16                 |     | ns      |
| Latch-to-Data Hold Time         | $t_H$                    | (Note 12)                                                         |                                                  | 16                 |     | ns      |
| Latch Pulse Width               | $t_{LPW}$                | (Note 12)                                                         |                                                  | 45                 |     | ns      |
| Latch Propagation Delay         | $t_{LPD}$                | (Note 12)                                                         |                                                  | 60                 |     | ns      |
| Shutdown Enable Time            |                          | (Note 13)                                                         |                                                  | 1                  |     | $\mu s$ |
| Shutdown Disable Time           |                          | (Note 13)                                                         |                                                  | 5                  |     | $\mu s$ |

**Note 1:** All devices are 100% production tested at  $T_A = +25^\circ C$ . Specifications over temperature are guaranteed by design.

**Note 2:** Inferred from PSRR test.

**Note 3:** Inferred from CMRR test. Note also that either or both inputs can be driven to the absolute maximum limit (0.3V beyond either supply rail) without damage or false output inversion.

**Note 4:**  $V_{OS}$  is defined as the center of the input-referred hysteresis zone. See Figure 1.

**Note 5:** The input-referred trip points are the extremities of the differential input voltage required to make the comparator output change state. The difference between the upper and lower trip points is equal to the width of the input-referred hysteresis zone. See Figure 1.

**Note 6:** The polarity of  $I_B$  reverses direction as  $V_{CM}$  approaches either supply rail.

**Note 7:** Specified over the full common-mode voltage range ( $V_{CMR}$ ).

**Note 8:** Specification is for current flowing into or out of the output pin for  $V_{OUT}$  driven to any voltage from  $V_{CC}$  to GND while the part is in shutdown.

**Note 9:** Specified between any two channels in the MAX9142/MAX9144.

**Note 10:** Specified as the difference between  $t_{PD+}$  and  $t_{PD-}$  for any one comparator.

**Note 11:** Applies to the MAX9141 only for both  $\overline{SHDN}$  and  $\overline{LE}$ .

**Note 12:** Applies to the MAX9141 only. Comparator is active with  $\overline{LE}$  driven high and is latched with  $\overline{LE}$  driven low ( $V_{OD} = 10mV$ ). See Figure 2.







**Note 13:** Applicable to the MAX9141 only. Comparator is active with the  $\overline{SHDN}$  driven high and is shutdown with  $\overline{SHDN}$  driven low. Shutdown enable time is the delay when the  $\overline{SHDN}$  is driven high to the time the output is valid. Shutdown disable time is the delay when the  $\overline{SHDN}$  is driven low to the time the comparator shuts down.

MAX9140/MAX9141/MAX9142/MAX9144

# 40ns, Low-Power, 3V/5V, Rail-to-Rail Single-Supply Comparators

## Typical Operating Characteristics







( $V_{CC} = 3.0V$ ,  $V_{CM} = 0V$ ,  $C_L = 15pF$ ,  $V_{OD} = 10mV$ ,  $T_A = +25^\circ C$ , unless otherwise noted.)



# 40ns, Low-Power, 3V/5V, Rail-to-Rail Single-Supply Comparators

## Typical Operating Characteristics (continued)

( $V_{CC} = 3.0V$ ,  $V_{CM} = 0V$ ,  $C_L = 15pF$ ,  $V_{OD} = 10mV$ ,  $T_A = +25^\circ C$ , unless otherwise noted.)






MAX9140/MAX9141/MAX9142/MAX9144

# 40ns, Low-Power, 3V/5V, Rail-to-Rail Single-Supply Comparators

## Typical Operating Characteristics (continued)

( $V_{CC} = 3.0V$ ,  $V_{CM} = 0V$ ,  $C_L = 15pF$ ,  $V_{OD} = 10mV$ ,  $T_A = +25^\circ C$ , unless otherwise noted.)



## Pin Description

| PIN     |         |         |         | NAME              | FUNCTION                                                                                                                        |
|---------|---------|---------|---------|-------------------|---------------------------------------------------------------------------------------------------------------------------------|
| MAX9140 | MAX9141 | MAX9142 | MAX9144 |                   |                                                                                                                                 |
| —       | —       | 1       | 1       | OUTA              | Comparator A Output                                                                                                             |
| —       | —       | 2       | 2       | INA-              | Comparator A Inverting Input                                                                                                    |
| —       | —       | 3       | 3       | INA+              | Comparator A Noninverting Input                                                                                                 |
| 5       | 1       | 8       | 4       | $V_{CC}$          | Positive Supply                                                                                                                 |
| —       | —       | 5       | 5       | INB+              | Comparator B Noninverting Input                                                                                                 |
| —       | —       | 6       | 6       | INB-              | Comparator B Inverting Input                                                                                                    |
| —       | —       | 7       | 7       | OUTB              | Comparator B Output                                                                                                             |
| —       | —       | —       | 8       | OUTC              | Comparator C Output                                                                                                             |
| —       | —       | —       | 9       | INC-              | Comparator C Inverting Input                                                                                                    |
| —       | —       | —       | 10      | INC+              | Comparator C Noninverting Input                                                                                                 |
| 2       | 4       | 4       | 11      | GND               | Ground                                                                                                                          |
| —       | —       | —       | 12      | IND+              | Comparator D Noninverting Input                                                                                                 |
| —       | —       | —       | 13      | IND-              | Comparator D Inverting Input                                                                                                    |
| —       | —       | —       | 14      | OUTD              | Comparator D Output                                                                                                             |
| 3       | 2       | —       | —       | IN+               | Noninverting Input                                                                                                              |
| 4       | 3       | —       | —       | IN-               | Inverting Input                                                                                                                 |
| —       | 6       | —       | —       | $\overline{SHDN}$ | Shutdown: MAX9141 is active when $\overline{SHDN}$ is driven high; MAX9141 is in shutdown when $\overline{SHDN}$ is driven low. |
| —       | 5       | —       | —       | $\overline{LE}$   | The output is latched when $\overline{LE}$ is low. The latch is transparent when $\overline{LE}$ is high.                       |
| 1       | 7       | —       | —       | OUT               | Comparator Output                                                                                                               |
| —       | 8       | —       | —       | N.C.              | No Connection. Not internally connected.                                                                                        |

# 40ns, Low-Power, 3V/5V, Rail-to-Rail Single-Supply Comparators

## Detailed Description

The MAX9140/MAX9141/MAX9142/MAX9144 single-supply comparators feature internal hysteresis, high speed, and low power. Their outputs are pulled to within 300mV of either supply rail without external pullup or pulldown circuitry. Rail-to-rail input voltage range and low-voltage single-supply operation make these devices ideal for portable equipment. The MAX9140/MAX9141/MAX9142/MAX9144 interface directly to CMOS and TTL logic.

Most high-speed comparators oscillate in the linear region because of noise or undesired parasitic feedback. This tends to occur when the voltage on one input is at or equal to the voltage on the other input. To counter the parasitic effects and noise, the MAX9140/MAX9141/MAX9142/MAX9144 have an internal hysteresis of 1.5mV.

The hysteresis in a comparator creates two trip points: one for the rising input voltage and one for the falling input voltage (Figure 1). The difference between the trip points is the hysteresis. The average of the trip points is the offset voltage. When the comparator's input voltages are equal, the hysteresis effectively causes one comparator input voltage to move quickly past the other, thus taking the input out of the region where oscillation occurs. Standard comparators require hysteresis to be added with external resistors. The MAX9140/MAX9141/MAX9142/MAX9144's fixed internal hysteresis eliminates these resistors. To increase hysteresis and noise margin even more, add positive feedback with two resistors as a voltage divider from the output to the noninverting input.

Figure 1 illustrates the case where  $IN^-$  is fixed and  $IN^+$  is varied. If the inputs were reversed, the figure would look the same, except the output would be inverted.

The MAX9141 includes an internal latch that allows storage of comparison results. The  $\overline{LE}$  pin has a high input impedance. If  $\overline{LE}$  is high, the latch is transparent (i.e., the comparator operates as though the latch is not present). The comparator's output state is latched when  $\overline{LE}$  is pulled low (Figure 2).

### Shutdown Mode (MAX9141 Only)

The MAX9141 shuts down when the  $\overline{SHDN}$  pin is low. When shut down, the supply current drops to less than 12 $\mu$ A, and the three-state output becomes high impedance. The  $\overline{SHDN}$  pin has a high-input impedance. Connect  $\overline{SHDN}$  to  $V_{CC}$  for normal operation. Exit shutdown with  $\overline{LE}$  high (transparent state); otherwise, the output will be indeterminate.




Figure 1. Input and Output Waveform, Noninverting Input Varied

### Input Stage Circuitry

The MAX9140/MAX9141/MAX9142/MAX9144 include internal protection circuitry that prevents damage to the precision input stage from large differential input voltages. This protection circuitry consists of two back-to-back diodes between  $IN^+$  and  $IN^-$  as well as two series 4.1k $\Omega$  resistors (Figure 3). The diodes limit the differential voltage applied to the internal circuitry of the comparators to be no more than  $2V_F$ , where  $V_F$  is the forward voltage drop of the diode (about 0.7V at +25°C).

For a large differential input voltage (exceeding  $2V_F$ ), this protection circuitry increases the input bias current at  $IN^+$  (source) and  $IN^-$  (sink).

$$\text{Input Current} = \frac{(IN^+ - IN^-) - 2V_F}{2 \times 4.1k\Omega}$$

Input current with large differential input voltages should not be confused with input bias current ( $I_B$ ). As long as the differential input voltage is less than  $2V_F$ , this input current is equal to  $I_B$ . The output is in the correct logic state if one or both inputs are within the common-mode range.

# 40ns, Low-Power, 3V/5V, Rail-to-Rail Single-Supply Comparators




Figure 2. MAX9141 Timing Diagram with Latch Operator

## Output Stage Circuitry

The MAX9140/MAX9141/MAX9142/MAX9144 contain a current-driven output stage as shown in Figure 4. During an output transition,  $I_{SOURCE}$  or  $I_{SINK}$  is pushed or pulled to the output pin. The output source or sink current is high during the transition, creating a rapid slew rate. Once the output voltage reaches  $V_{OH}$  or  $V_{OL}$ , the source or sink current decreases to a small value, capable of maintaining the  $V_{OH}$  or  $V_{OL}$  static condition. This significant decrease in current conserves power after an output transition has occurred.

One consequence of a current-driven output stage is a linear dependence between the slew rate and the load capacitance. A heavy capacitive load will slow down a voltage output transition. This can be useful in noise-sensitive applications where fast edges may cause interference.

## Applications Information

### Circuit Layout and Bypassing

The high-gain bandwidth of the MAX9140/MAX9141/MAX9142/MAX9144 requires design precautions to realize the full high-speed capabilities of these comparators. The recommended precautions are:

- 1) Use a PCB with a good, unbroken, low-inductance ground plane.
- 2) Place a decoupling capacitor (a 0.1µF ceramic capacitor is a good choice) as close to  $V_{CC}$  as possible.




Figure 3. Input Stage Circuitry

- 3) Pay close attention to the decoupling capacitor's bandwidth, keeping leads short.
- 4) On the inputs and outputs, keep lead lengths short to avoid unwanted parasitic feedback around the comparators.
- 5) Solder the device directly to the PCB instead of using a socket.

# 40ns, Low-Power, 3V/5V, Rail-to-Rail Single-Supply Comparators

MAX9140/MAX9141/MAX9142/MAX9144




Figure 4. Output Stage Circuitry




Figure 5. 3.3V Digitally Controlled Threshold Detector




Figure 6. Line Receiver Application

## Chip Information


PROCESS: Bipolar

# 40ns, Low-Power, 3V/5V, Rail-to-Rail Single-Supply Comparators

## Package Information

For the latest package outline information and land patterns, go to [www.maxim-ic.com/packages](http://www.maxim-ic.com/packages). Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

| PACKAGE TYPE | PACKAGE CODE | DOCUMENT NO.            |
|--------------|--------------|-------------------------|
| 8 SOT23      | K8-5         | <a href="#">21-0078</a> |
| 5 SOT23      | U5-1         | <a href="#">21-0057</a> |
| 5 SC70       | X5+1         | <a href="#">21-0076</a> |
| 14 TSSOP     | U14-1        | <a href="#">21-0066</a> |
| 8 SO, 14 SO  | S8-2, S14-1  | <a href="#">21-0041</a> |




# 40ns, Low-Power, 3V/5V, Rail-to-Rail Single-Supply Comparators

## Package Information (continued)

For the latest package outline information and land patterns, go to [www.maxim-ic.com/packages](http://www.maxim-ic.com/packages). Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

MAX9140/MAX9141/MAX9142/MAX9144

SOT-23 5L .EPS



### NOTES:



- ALL DIMENSIONS ARE IN MILLIMETERS.
- FOOT LENGTH MEASURED AT INTERCEPT POINT BETWEEN DATUM A & LEAD SURFACE.
- PACKAGE OUTLINE EXCLUSIVE OF MOLD FLASH & METAL BURR. MOLD FLASH, PROTRUSION OR METAL BURR SHOULD NOT EXCEED 0.25 MM.
- PACKAGE OUTLINE INCLUSIVE OF SOLDER PLATING.
- MEETS JEDEC MO178, VARIATION AA.
- LEADS TO BE COPLANAR WITHIN 0.10 mm.
- SOLDER THICKNESS MEASURED AT FLAT SECTION OF LEAD BETWEEN 0.08mm AND 0.15mm FROM LEAD TIP.

|                                                                                                                      |                                 |                                                                                       |       |
|----------------------------------------------------------------------------------------------------------------------|---------------------------------|---------------------------------------------------------------------------------------|-------|
|  <b>DALLAS</b><br>SEMICONDUCTOR |                                 |  |       |
| PROPRIETARY INFORMATION                                                                                              |                                 |                                                                                       |       |
| TITLE:<br>PACKAGE OUTLINE, SOT-23, 5L                                                                                |                                 |                                                                                       |       |
| APPROVAL                                                                                                             | DOCUMENT CONTROL NO.<br>21-0057 | REV.<br>F                                                                             | 1 / 1 |

# 40ns, Low-Power, 3V/5V, Rail-to-Rail Single-Supply Comparators

## Package Information (continued)


For the latest package outline information and land patterns, go to [www.maxim-ic.com/packages](http://www.maxim-ic.com/packages). Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.



| COMMON DIMENSIONS |            |      |      |
|-------------------|------------|------|------|
| SYMBOL            | MIN        | NOM  | MAX  |
| A                 | 0.80       | 0.95 | 1.10 |
| A1                | 0.00       | 0.07 | 0.10 |
| A2                | 0.80       | 0.90 | 1.00 |
| b                 | 0.15       | 0.22 | 0.30 |
| c                 | 0.10       | 0.14 | 0.18 |
| D                 | 1.80       | 2.00 | 2.20 |
| e                 | 0.65 BSC.  |      |      |
| E                 | 1.15       | 1.25 | 1.35 |
| HE                | 1.80       | 2.20 | 2.40 |
| L                 | 0.26       | 0.34 | 0.46 |
| L1                | 0.425 TYP. |      |      |
| Q1                | 0.10       | 0.25 | 0.40 |
| PKG. CODE         | X5-1       |      |      |

### NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. DIMENSIONS ARE INCLUSIVE OF PLATING.
3. DIMENSIONS ARE EXCLUSIVE OF MOLD FLASH & METAL BURR.
4. COMPLY TO JEITA SC-88A EXCEPT FOR DIMENSION "L".  
ALL DIMENSIONS COMPLY TO JEDEC MO-203.
5. COPLANARITY 4 MILS, MAX.
6. FOOT LENGTH MEASURED AT INTERCEPT POINT BETWEEN DATUM "A" AND LEAD SURFACE.
7. MARKING IS FOR PACKAGE ORIENTATION REFERENCE ONLY.
8. LEAD CENTERLINES TO BE AT TRUE POSITION AS DEFINED BY BASIC DIMENSION "e",  $\pm 0.05$ .



-DRAWING NOT TO SCALE-

|                                                                                                                      |                                 |                                                                                       |       |
|----------------------------------------------------------------------------------------------------------------------|---------------------------------|---------------------------------------------------------------------------------------|-------|
|  <b>DALLAS</b><br>SEMICONDUCTOR |                                 |  |       |
| TITLE:<br>PACKAGE OUTLINE, 5L SC70                                                                                   |                                 |                                                                                       |       |
| APPROVAL                                                                                                             | DOCUMENT CONTROL NO.<br>21-0076 | REV.<br>E                                                                             | 1 / 1 |

SC70, 5LEPS


# 40ns, Low-Power, 3V/5V, Rail-to-Rail Single-Supply Comparators

## Package Information (continued)

For the latest package outline information and land patterns, go to [www.maxim-ic.com/packages](http://www.maxim-ic.com/packages). Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

MAX9140/MAX9141/MAX9142/MAX9144

TSSOP4.40mm.EPS



### NOTES

1. DIMENSIONS D AND E DO NOT INCLUDE FLASH
2. MOLD FLASH OR PROTRUSIONS NOT TO EXCEED 0.15mm PER SIDE
3. CONTROLLING DIMENSION: MILLIMETER
4. MEETS JEDEC OUTLINE MD-153. SEE JEDEC VARIATIONS TABLE
5. "N" REFERS TO NUMBER OF LEADS
6. LEAD COPLANARITY 0.10 MM MAX.
7. NUMBER OF LEADS SHOWN ARE FOR REFERENCE ONLY
8. MARKING IS FOR PACKAGE ORIENTATION REFERENCE ONLY
9. BENT LEAD 0.10 MM MAX.
10. ALL DIMENSIONS APPLY TO BOTH LEADED (-) AND PBFREE (+) PKG. CODES.

-DRAWING NOT TO SCALE-

| SYMBOL         | COMMON DIMENSIONS |      |                |      |
|----------------|-------------------|------|----------------|------|
|                | MILLIMETERS       |      | INCHES         |      |
|                | MIN.              | MAX. | MIN.           | MAX. |
| A              | —                 | 1.10 | —              | .043 |
| A <sub>1</sub> | 0.05              | 0.15 | .002           | .006 |
| A <sub>2</sub> | 0.85              | 0.95 | .033           | .037 |
| b              | 0.19              | 0.30 | .007           | .012 |
| b <sub>1</sub> | 0.19              | 0.25 | .007           | .010 |
| c              | 0.09              | 0.20 | .004           | .008 |
| c <sub>1</sub> | 0.09              | 0.14 | .004           | .006 |
| D              | SEE VARIATIONS    |      | SEE VARIATIONS |      |
| E              | 4.30              | 4.50 | .169           | .177 |
| e              | 0.65              | BSC  | .026           | BSC  |
| H              | 6.25              | 6.55 | .246           | .258 |
| L              | 0.50              | 0.70 | .020           | .028 |
| N              | SEE VARIATIONS    |      | SEE VARIATIONS |      |
| α              | 0°                | 8°   | 0°             | 8°   |
| bbb            | 0.10 MAX          |      |                |      |

| JEDEC<br>MD-153 | N  | PKG.<br>CODES                  | VARIATIONS  |      |        |      |
|-----------------|----|--------------------------------|-------------|------|--------|------|
|                 |    |                                | MILLIMETERS |      | INCHES |      |
|                 |    |                                | MIN.        | MAX. | MIN.   | MAX. |
| AB-1            | 14 | D<br>U14-1;<br>U14-2           | 4.90        | 5.10 | .193   | .201 |
| AB              | 16 | D<br>U16-1;<br>U16-2           | 4.90        | 5.10 | .193   | .201 |
| AC              | 20 | D<br>U20-2;<br>U20M-2<br>U20-3 | 6.40        | 6.60 | .252   | .260 |
| AD              | 24 | D<br>U24-1                     | 7.70        | 7.90 | .303   | .311 |
| AE              | 28 | D<br>U28-1;<br>U28-2;<br>U28-3 | 9.60        | 9.80 | .378   | .386 |

**MAXIM**


TITLE:  
PACKAGE OUTLINE,  
TSSOP 4.40mm BODY

|          |                                 |        |     |
|----------|---------------------------------|--------|-----|
| APPROVAL | DOCUMENT CONTROL NO.<br>21-0066 | REV. J | 1/1 |
|----------|---------------------------------|--------|-----|


# 40ns, Low-Power, 3V/5V, Rail-to-Rail Single-Supply Comparators

## Package Information (continued)


For the latest package outline information and land patterns, go to [www.maxim-ic.com/packages](http://www.maxim-ic.com/packages). Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.



TOP VIEW



END VIEW



SIDE VIEW

| COMMON DIMENSIONS |        |      |      |      |
|-------------------|--------|------|------|------|
| SYMBOL            | INCHES |      | MM   |      |
|                   | MIN.   | MAX. | MIN. | MAX. |
| A                 | .053   | .069 | 1.35 | 1.75 |
| A1                | .004   | .010 | 0.10 | 0.25 |
| b                 | .014   | .019 | 0.35 | 0.49 |
| c                 | .007   | .010 | 0.19 | 0.25 |
| E                 | .150   | .157 | 3.80 | 4.00 |
| e                 | .050   | BSC  | 1.27 | BSC  |
| H                 | .228   | .244 | 5.80 | 6.20 |
| L                 | .016   | .050 | 0.40 | 1.27 |
| a                 | 0°     | 8°   | 0°   | 8°   |

| VARIATION A |                                                               |      |      |      |
|-------------|---------------------------------------------------------------|------|------|------|
| SYMBOL      | INCHES                                                        |      | MM   |      |
|             | MIN.                                                          | MAX. | MIN. | MAX. |
| D           | .189                                                          | .197 | 4.80 | 5.00 |
| N           | 8                                                             |      |      |      |
| MS012       | AA                                                            |      |      |      |
| PKG. CODE   | S8-2, S8-4, S8-5, S8-6F, S8-7F, S8-8F, S8-10F, S8-11F, S8-16F |      |      |      |

| VARIATION B |                                                            |      |      |      |
|-------------|------------------------------------------------------------|------|------|------|
| SYMBOL      | INCHES                                                     |      | MM   |      |
|             | MIN.                                                       | MAX. | MIN. | MAX. |
| D           | .337                                                       | .344 | 8.55 | 8.75 |
| N           | 14                                                         |      |      |      |
| MS012       | AB                                                         |      |      |      |
| PKG. CODE   | S14-1, S14-4, S14-5, S14-6; S14M-4, S14M-5, S14M-6, S14M-7 |      |      |      |

| VARIATION C |                                                                            |      |      |       |
|-------------|----------------------------------------------------------------------------|------|------|-------|
| SYMBOL      | INCHES                                                                     |      | MM   |       |
|             | MIN.                                                                       | MAX. | MIN. | MAX.  |
| D           | .386                                                                       | .394 | 9.80 | 10.00 |
| N           | 16                                                                         |      |      |       |
| MS012       | AC                                                                         |      |      |       |
| PKG. CODE   | S16-1, S16-3, S16-5, S16-6, S16-8, S16-7F, S16-9F, S16-10F; S16M-3, S16M-6 |      |      |       |

### NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
2. MATERIAL MUST COMPLY WITH BANNED AND RESTRICTED SUBSTANCES SPEC # 10-0131.
3. DIMENSIONS D AND E DO NOT INCLUDE MOLD PROTRUSION. ALLOWABLE MOLD PROTRUSION IS 0.15 MM (.006") PER SIDE.
4. LEADS TO BE COPLANAR WITHIN 0.10mm (.004").
5. MEETS JEDEC MS012
6. ALL DIMENSIONS APPLY TO BOTH LEADED (-) AND PbFREE (+) PKG. CODES.

-DRAWING NOT TO SCALE-

# MAXIM

TITLE:  
PACKAGE OUTLINE,  
8L, 14L, 16L SOIC .150 INCH

|          |                      |      |     |
|----------|----------------------|------|-----|
| APPROVAL | DOCUMENT CONTROL NO. | REV. | 1/1 |
|          | 21-0041              | C    |     |

# 40ns, Low-Power, 3V/5V, Rail-to-Rail Single-Supply Comparators

## Revision History

| REVISION<br>NUMBER | REVISION<br>DATE | DESCRIPTION                                                                            | PAGES<br>CHANGED |
|--------------------|------------------|----------------------------------------------------------------------------------------|------------------|
| 0                  | 6/01             | Initial release                                                                        | —                |
| 1                  | 1/07             | Updated <i>Absolute Maximum Ratings</i> with $\pm 20\text{mA}$ current into input pin. | 2                |
| 2                  | 12/07            | Added two new automotive grade products.                                               | 1, 2             |
| 3                  | 1/10             | Added automotive qualified part                                                        | 1                |

MAX9140/MAX9141/MAX9142/MAX9144

Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.

Maxim Integrated Products, 120 San Gabriel Drive, Sunnyvale, CA 94086 408-737-7600 \_\_\_\_\_ 15