







LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
-	-	C		REVISED PER ECO 13-001843.	08FEB2013	MGM CT



SINGLE POLARIZATION



DOUBLE POLARIZATION



PANEL CUTOUT

1. DWV RATING: 725 VAC @ SEA LEVEL
2. WORKING TEMPERATURE: -55°C ~ +125°C

3 MATERIAL:

CONTACT : COPPER ALLOY

SHELL : COPPER ALLOY

INSULATOR : PEEK

O RING : SILICONE RUBBER

4 FINISH

CONTACT: GOLD OVER NICKEL

SHELL : BLACK CHROMIUM

5. WATER PROOF: 1M IMMERSION

6 THE CONNECTOR IS MARKED WITH TE PART NUMBER, CHINA, DATE CODE, AND LOT ID.

7 ALL TOLERANCES ±0.20 UNLESS NOTED.

CAVITY IDENTIFICATION WHEN VIEWED
FROM MATING FACE OF CONNECTOR

CHROMIUM-BLACK	DOUBLE	SOLDERING	2.54	ø0.5	15.45	ø14	M14X1	ø18	2	2157538-2
CHROMIUM-BLACK	SINGLE	SOLDERING	2.54	ø0.5	15.45	ø14	M14X1	ø18	2	2157538-1
FINISH	POLARIZATION	TERMINATION	N	d	L	T	M THREAD	D	SHELL SIZE	TE CONNECTIVITY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN C.C THOMAS 05MAY2011	TE Connectivity		
DIMENSIONS: mm			CHK R. GROSS 05MAY2011			
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD R. GROSS 05MAY2011	NAME		
0 PLC ± - 7			PRODUCT SPEC	CIRCULAR HD RECEPTACLE WITH SOCKET, JAM NUT, FRONT MOUNTING, STRAIGHT PCB 12 POS.		
1 PLC ± -			108-127005			
2 PLC ± 0.20			APPLICATION SPEC	SIZE		
3 PLC ± -				CAGE CODE		
4 PLC ± -				DRAWING NO		
ANGLES ± 3°				RESTRICTED TO		
FINISH				A2 00779 C=2157538		
MATERIAL 3 -			WEIGHT -	SCALE NTS		
4 -			CUSTOMER DRAWING	SHEET 1 of 1		
				REV C		