

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT — By —

LOC

G

	DIST
--	------

14

REVISIONS

	F
--	---

LT

DESCRIPTION

DATE _____

	DWN
--	-----

	APVD
--	------


F2

REVISÉD PER ECO-12-003796

28FEB12

KH

DR



- 1 22-18 STAMP AMP APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPEC SAE AS7928
COMMERCIAL WIRE RANGE IS 22-16
- 2 WIRE INSUL DIA, 2.67-3.56[.105-.140]
- 3 TONGUE MATL THK, 0.79±0.05[.031±.002]
- 4 BODY: GOLD PLATE 0.00127[.000050]MIN EXT.
THK PER ASTM B488, TYPE 1, CODE C OVER
NICKEL FLASH PER SAE AMS QQ-N-290
OVER WOODS NICKEL FLASH PER ASTM B558.
- 5 NOTE DELETED.

260°C [500°F]		1000	LOOSE PIECE	321892-1
649°C [1200°F]	—	1000	LOOSE PIECE	321892
MAX OPERATING TEMP	FINISH	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEM		MAX RECOMMENDED OPERATING TEMPERATURE: SEE TABLE	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L OLMEDA 100CT94 CHK M ELLIS 100CT94 APVD S BORTNER 100CT94 PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		 TE Connectivity			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: — —	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:  0 PLC ± — 1 PLC ± — 2 PLC ± 0.20 [.008] 3 PLC ± — 4 PLC ± — ANGLES ± — FINISH	NAME TERMINAL, RING TONGUE, STRATOTHERM, DIAMOND GRIP, WIRE SIZE: 22-16AWG	SIZE	CAGE CODE	DRAWING NO	RESTRICTED T
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 0.26mm ² –1.65mm ² [509–3260] STRANDED WIRE	MATERIAL BODY, NI PER ASTM B162 SLEEVE, NI SIL PER ASTM B122	SEE TABLE	A300779C-321892			—		
FOR ORDER ENTRY	1-800-526-5142	CUSTOMER DRAWING			SCALE	6:1	SHEET	1 OF 1	REV	F2