



(2,00 mm) .0787"

SMM-115-02-S-D

SMM-135-02-L-D-K

SMM-108-02-L-S

SMM-110-02-L-S

SMM SERIES

TIGER EYE™ SOCKET STRIP

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?SMM

Insulator Material:

Black Liquid Crystal Polymer

Contact Material:

BeCu

Plating: Sn or Au over

50µ" (1,27 µm) Ni

Current Rating (TMM/SMM):

3.2 A per pin

(1 pin powered per row)

Voltage Rating:

350 VAC

Operating Temp Range:

-55°C to +125°C

Contact Resistance:

10 mΩ

Insertion Depth:

(3,05 mm) .120" to

(3,25 mm) .128"

Insertion Force:

(Single contact only)

2.0 oz (0,56 N) average

Withdrawal Force:

(Single contact only)

1.5 oz (0,42 N) average

Max Cycles:

100 with 10µ" (0,25 µm) Au

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,10 mm) .004" max

Mates with:


TMM, TMMH,

MTMM, MMT, LTMM,

TW, TCMD, PTT, ZLTMM



10 year Mixed Flowing Gas with 30µ" Gold
Call Samtec for maximum mated cycles



SMM	1	NO. PINS PER ROW	02	PLATING OPTION	ROW OPTION	OTHER OPTION
-----	---	------------------	----	----------------	------------	--------------

02 thru 40

-F
= Gold flash
on contact,
Matte Tin on tail

-L
= 10µ" (0,25 µm)
Gold on contact,
Matte Tin on tail

-S
= 30µ" (0,76 µm)
Gold on contact,
Matte Tin on tail

-S
= Single
Row





-D
= Double
Row

-“XX”
= Polarized
Position

-K
= (5,50 mm)
.217" DIA
Polyimide
Film
Pick &
Place Pad
(2 positions
minimum,
-02 thru -05
requires -TR)

-P
= Plastic Pick
& Place Pad
(-02 thru -05
requires -TR)

-TR
= Tape & Reel
Packaging
(27 positions
maximum)



RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



ALSO AVAILABLE (MOQ Required)

- Locking clip (Manual placement required)
- Other platings
- Contact Samtec.

POLARIZING KEY

Specify PK-01-07 for polarizing key (Available in wheels of six each). Also polarizes TCSD Series IDC Cable.

Note: Some lengths, styles and options are non-standard, non-returnable.