



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
6832	5.0	.060	.050	0.63	100,000	C-2R
6152	5.0	.060	.150	1.89	5,000	C-2R
7132	5.0	.075	.090	1.13	25,000	C-2R
7152	5.0	.115	.150	1.89	40,000	C-2R

NOTES:

1. GLASS ENVELOPE TO BE OF TIPLESS AND SEAMLESS CONSTRUCTION TO PROVIDE UNDISTORTED END VIEWING.
2. WIRE TERMINALS TO BE TINNED DUMENT TYPE WIRE. OPTIONAL PLATING MATERIALS ARE AVAILABLE.
3. ALL LAMPS TO BE 100% AGED FOR AN EQUIVALENT OF TEN HOURS OF THE RATED VOLTAGES.
4. FINAL INSPECTION ON ALL LAMPS TO BE MIL. STD. 105-E. ELECTRICAL CHARACTERISTICS TO AN AQL OF 2.5 OR BETTER, LEVEL II. MECHANICAL TO AN AQL OF 4.0, LEVEL S-1. (NOTE: AS15 TYPE LAMPS WILL BE 100% INSPECTED FOR AMPERAGE AND MSCP RATINGS.)
5. ALL DIMENSIONS PROVIDED HEREIN, NOT LISTING TOLERANCES, ARE CONSIDERED REFERENCE DIMENSIONS ONLY.

METRIC		DIMENSIONS ARE IN MILLIMETERS		JKL COMPONENTS CORPORATION	
		TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE	
1 PL +/- 0.2		2 PL +/- 0		T-1 SHORTY WIRE TERMINAL LAMP	
ANGLE +/- 0		DRAWN BY L. WENGSTROM		DRAWING NO. WIRE TERMINAL SHORTY T-1	
APPV'D BY QC		DATE 5/21/01		SCALE	
- CAD DRAWING -		NONE		RELEASED DATE 07/07/97	
MANUAL REVISIONS NOT PERMITTED		REVISION DATE 5/21/01		REV. NO. C	
SHEET 1 OF 1					

REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE
C	DIM. CHNG. 0.8±0.13 TO 0.8 REF.	5/21/01
B	LEAD DIA. 0.25 TO 0.25 REF.	02/08/00
A	DRAWING TO CAD - LAMPS 2022, 6802 DELETED	01/14/00
	RELEASED	07/07/97