


CMPS5061
CMPS5062
CMPS5063
CMPS5064

**SURFACE MOUNT
SILICON CONTROLLED RECTIFIER**



SOT-23 CASE

Central™
Semiconductor Corp.

DESCRIPTION:

The CENTRAL SEMICONDUCTOR CMPS5061 Series types are epoxy molded PNP Silicon Controlled Rectifiers manufactured in an SOT-23 case, designed for control systems and sensing circuit applications.

Marking codes are P2A, P2B, P2C, and P2D respectively.

MAXIMUM RATINGS ($T_A=25^\circ\text{C}$)

	<u>SYMBOL</u>	<u>CMPS5061</u>	<u>CMPS5062</u>	<u>CMPS5063</u>	<u>CMPS5064</u>	<u>UNITS</u>
Peak Repetitive Off-State Voltage	V_{DRM}	100	200	300	400	V
Peak Repetitive Reverse Voltage	V_{RRM}	100	200	300	400	V
RMS On-State Current	$I_T(RMS)$			0.8		A
Average On-State Current ($T_C=67^\circ\text{C}$)	$I_T(AV)$			0.51		A
Power Dissipation	P_D			350		mW
Operating and Storage						
Junction Temperature	T_J, T_{stg}		-65 to +150			$^\circ\text{C}$
Thermal Resistance	Θ_{JA}		357			$^\circ\text{C/W}$


ELECTRICAL CHARACTERISTICS ($T_A=25^\circ\text{C}$ unless otherwise noted)

		<u>CMPS5061</u>		<u>CMPS5062</u>		<u>CMPS5063</u>		<u>CMPS5064</u>		<u>UNITS</u>
<u>SYMBOL</u>	<u>TEST CONDITIONS</u>	<u>MIN</u>	<u>MAX</u>	<u>MIN</u>	<u>MAX</u>	<u>MIN</u>	<u>MAX</u>	<u>MIN</u>	<u>MAX</u>	
I_{DRM}	$V_D=\text{Rated } V_{DRM}, R_{GK}=1K\Omega$		1.0		1.0		1.0		1.0	μA
I_{RRM}	$V_D=\text{Rated } V_{DRM}, R_{GK}=1K\Omega$		1.0		1.0		1.0		1.0	μA
I_{DRM}	$V_D=\text{Rated } V_{DRM}, R_{GK}=1K\Omega, T_C=125^\circ\text{C}$		50		50		50		50	μA
I_{RRM}	$V_D=\text{Rated } V_{DRM}, R_{GK}=1K\Omega, T_C=125^\circ\text{C}$		50		50		50		50	μA
V_T	$I_T=1.2\text{A}$		1.7		1.7		1.7		1.7	V
I_{GT}	$V_D=7.0\text{V}, R_L=100\Omega, R_{GK}=1K\Omega$		200		200		200		200	μA
V_{GT}	$V_D=7.0\text{V}, R_L=100\Omega, R_{GK}=1K\Omega$		0.8		0.8		0.8		0.8	V
V_{GD}	$V_D=\text{Rated } V_{DRM}, R_L=100\Omega, T_C=125^\circ\text{C}$	0.1		0.1		0.1		0.1		V
I_H	$V_D=7.0, R_{GK}=1K\Omega$		5.0		5.0		5.0		5.0	mA
t_{ON}	$V_D=\text{Rated } V_{DRM}, I_{GT}=1.0\text{mA}, R_{GK}=1.0\Omega,$ $di/dt=6.0\text{A}/\mu\text{s}$		2.8 TYP		2.8 TYP		2.8 TYP		2.8 TYP	μs

R6 (12-June 2001)

**SURFACE MOUNT
SILICON CONTROLLED RECTIFIER**

MECHANICAL OUTLINE - SOT-23



LEAD CODE:

- 1) CATHODE
- 2) GATE
- 3) ANODE

MARKING CODES:

CMPS5061:P2A
CMPS5062:P2B
CMPS5063:P2C
CMPS5064:P2D

DIMENSIONS				
SYMBOL	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.003	0.007	0.08	0.18
B	0.006	-	0.15	-
C	-	0.005	-	0.13
D	0.035	0.043	0.89	1.09
E	0.110	0.120	2.80	3.05
F	0.075		1.90	
G	0.037		0.95	
H	0.047	0.055	1.19	1.40
I	0.083	0.098	2.10	2.49
J	0.014	0.020	0.35	0.50

SOT-23 (REV: R3)