




- 1 0.38μm[.000015] MIN GOLD ON MATING AREA,
1.27μm[.000050] MIN BRIGHT TIN-LEAD ON CRIMP AREA, BOTH OVER
1.27μm[.000050] MIN NICKEL.
- 2 2.54μm[.000100] MIN BRIGHT TIN-LEAD, OVER
1.27μm[.000050] MIN NICKEL.
- 3 GOLD FLASH ON CRIMP AREA,
2.54μm[.000100] MIN TIN ON MATING AREA, BOTH OVER
1.27μm[.000050] MIN NICKEL.
- 4 0.38μm[.000015] MIN GOLD ON MATING AREA,
GOLD FLASH ON CRIMP AREA, BOTH OVER
1.27μm[.000050] MIN NICKEL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 6 GOLD PLATING MAY OR MAY NOT BE PRESENT ON THE BOTTOM OF THE CRIMP BARREL

5 OBSOLETE	4	487923-5
3	6	487923-4
5 OBSOLETE	1	487923-3
	2	487923-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.OBERMAN 3-7-90	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK R.STONE 3-8-90			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
	0 PLC ± -		CONTACT, SOLDER TAB,		
	1 PLC ± -		.050 C/L		
	2 PLC ± 0.13[.005]		-		
	3 PLC ± -		SIZE		
	4 PLC ± -		CAGE CODE		
	ANGLES ± -		DRAWING NO		
	FINISH		RESTRICTED TO		
MATERIAL PHOSPHOR BRONZE		SEE TABLE	WEIGHT		
			A2 00779 C=487923		
			CUSTOMER DRAWING		
			SCALE 10:1 SHEET 1 OF 1 REV D1		