

D

C

B


A

D


C

B


A



1. 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN-LEAD IN TIN-LEAD PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
2. WIRE RANGE: .5-2mm² [20-14 AWG].
INSULATION RANGE: 3.30-5.08[.130-.200] DIA.
3. DIMENSIONS IN BRACKETS ARE IN INCHES.
4. 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN MATTE TIN IN MATTE TIN PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.




SECTION B-B
SCALE 10:1



SECTION A-A
SCALE 10:1

GOLD	4	0.30[.012]	PH BRZ	1-770006-0
GOLD	1	0.30[.012]	PH BRZ	770006-4
PRE-TIN		0.30[.012]	PH BRZ	770006-3
FINISH		MATERIAL		PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH		

MATERIAL

SEE TABLE

DWN
S.CARPENTER
11AUG03

CHK
C.JONES
11AUG03

APVD
C.JONES
11AUG03

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
SOCKET, UNIVERSAL MATE-N-LOK(TM) II

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-770006

RESTRICTED TO
-

SCALE
4:1

SHEET
1 OF 1

REV
G1