





## Dimensions: mm (IN.)

**Mechanical Specifications:**

- Stroke: 0.25 +0.20 / -0.1 mm
- Operating Temperature: -25°C to +70°C
- Storage Temperature: -30°C to +80°C
- Type: SPST

**Electrical Specifications:**

- Electrical Life: 50,000 cycles for 160gf, 320gf  
30,000 cycles for 260gf, 520gf
- Rating: 50mA/12VDC
- Contact Resistance: 100mΩ max.
- Insulation Resistance: 100MΩ min. at 500VDC
- Dielectric Strength: 250VAC/ minute

**Materials:**

- Cover: Stainless steel
- Base: Nylon or PPA high-temp. thermoplastic, black
- Stem: Nylon high-temp. thermoplastic  
Color: brown (160gf), red (260gf),  
salmon (320gf), yellow (520gf)
- Contact Disc: Stainless with silver cladding
- Terminal: Brass with silver cladding

**Soldering Process:**

- Hand Soldering: Use a soldering iron of 30 watts, controlled at 608°F (320°C) approximately 2 seconds.
- Reflow Soldering: When applying reflow soldering, the peak temperature or the reflow oven should be set at 240°C max.
- Wave Soldering: Recommended solder temperature at 500°F (260°C) max. 5 seconds for through hole type.

Mountain Switch Part No.	Height	Color for Operating Force
TS4322T5202	5.0 (.197)	Y Yellow 520g
TS4322T3202	5.0 (.197)	S Salmon 320g
TS4322T2602	5.0 (.197)	R Red 260g
TS4322T1602	5.0 (.197)	N Brown 160g
TS4322T5201	4.3 (.169)	Y Yellow 520g
TS4322T3201	4.3 (.169)	S Salmon 320g
TS4322T2601	4.3 (.169)	R Red 260g
TS4322T1601	4.3 (.169)	N Brown 160g

**Tactile Switches (SMT)**

TS4322T5202, TS4322T3202, TS4322T2602  
 TS4322T1602, TS4322T5201, TS4322T3201  
 TS4322T2601, TS4322T1601

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-TS4322T3202](#) [101-TS4322T1602](#)