


RF & MICROWAVE TRANSISTORS UHF MOBILE APPLICATIONS

- 470 MHz
- 12.5 VOLTS
- EFFICIENCY 60%
- COMMON EMITTER
- $P_{OUT} = 5.0 \text{ W MIN. WITH } 8.5 \text{ dB GAIN}$



.280 2L STUD (M122)
epoxy sealed


ORDER CODE
SD1135

BRANDING
SD1135

DESCRIPTION

The SD1135 is a 12.5 V Class C epitaxial silicon NPN planar transistor designed primarily for UHF communications. This device utilizes improved metallization to achieve infinite VSWR at rated operating conditions.

PIN CONNECTION



- | | |
|--------------|------------|
| 1. Collector | 3. Base |
| 2. Emitter | 4. Emitter |

ABSOLUTE MAXIMUM RATINGS ($T_{case} = 25^{\circ}\text{C}$)

Symbol	Parameter	Value	Unit
V_{CBO}	Collector-Base Voltage	36	V
V_{CER}	Collector-Emitter Voltage	18	V
V_{CES}	Collector-Emitter Voltage	36	V
V_{EBO}	Emitter-Base Voltage	4.0	V
I_C	Device Current	2.0	A
P_{DISS}	Power Dissipation	37	W
T_J	Junction Temperature	+200	$^{\circ}\text{C}$
T_{STG}	Storage Temperature	- 65 to +150	$^{\circ}\text{C}$

THERMAL DATA

$R_{TH(j-c)}$	Junction-Case Thermal Resistance	11.6	$^{\circ}\text{C/W}$
---------------	----------------------------------	------	----------------------

SD1135

ELECTRICAL SPECIFICATIONS ($T_{case} = 25^{\circ}C$)

STATIC


Symbol	Test Conditions	Value			Unit
		Min.	Typ.	Max.	
BV_{CES}	$I_C = 10mA$ $V_{BE} = 0mA$	36	—	—	V
BV_{CEO}	$I_C = 50mA$ $I_B = 0mA$	16	—	—	V
BV_{EBO}	$I_E = 2mA$ $I_C = 0mA$	4.0	—	—	V
I_{CBO}	$V_{CB} = 15V$ $I_E = 0mA$	—	—	1	mA
h_{FE}	$V_{CE} = 5V$ $I_C = 200mA$	20	—	—	—

DYNAMIC


Symbol	Test Conditions	Value			Unit
		Min.	Typ.	Max.	
P_{OUT}	$f = 470 \text{ MHz}$ $P_{IN} = 0.70 \text{ W}$ $V_{CC} = 12.5 \text{ V}$	5.0	—	—	W
G_P	$f = 470 \text{ MHz}$ $P_{IN} = 0.70 \text{ W}$ $V_{CC} = 12.5 \text{ V}$	8.5	—	—	dB
C_{OB}	$f = 1 \text{ MHz}$ $V_{CB} = 12 \text{ V}$	—	19	—	pF

TYPICAL PERFORMANCE


POWER OUTPUT vs POWER INPUT





POWER OUTPUT vs FREQUENCY



CAPACITANCE vs VOLTAGE





IMPEDANCE DATA

TYPICAL INPUT
IMPEDANCETYPICAL COLLECTOR
LOAD IMPEDANCE

FREQ.	$Z_{IN} (\Omega)$	$Z_{CL} (\Omega)$
450 MHz	$1.4 + j 2.0$	$10.7 - j 6.9$
470 MHz	$1.4 + j 2.9$	$11.4 - j 5.8$
512 MHz	$1.5 + j 3.4$	$11.9 - j 3.2$

TEST CIRCUIT




C1, C2,
 C5, C6 : 0.8-10pF, Voltronics AJ10
 C3, C4 : ATC 100-B, 16pF, Chip Capacitor
 C7 : ATC 100-B, 620pF, Chip Capacitor
 C8 : 5.6μF, 35V, Electrolytic

C9 : 0.1μF, Disc-Ceramic
 C10 : 0.01μF, Disc-Ceramic
 L1 : 2 Turns, #22 Enameled, 0.1" I.D.
 RFC : 2 Turns in Ferroxcube VK 200/19-4B

Board Material 3M-K-6098, 1/16" Thick

PACKAGE MECHANICAL DATA

Ref.: Dwg. No.12-0122



SGS-THOMSON MICROELECTRONICS		
	MINIMUM Inches/mm	MAXIMUM Inches/mm
A	1.010/25,65	1.055/26,80
B	.220/5,59	.230/5,84
C	.270/6,86	.285/7,24
D	.003/0,08	.007/0,18
E	.117/2,97	.137/3,48
F	.572/14,53	
G	.130/3,30	
H	.245/6,22	.255/6,48
I	.640/16,26	
J	.175/4,45	.217/5,51
K	.275/6,99	.285/7,24

Information furnished is believed to be accurate and reliable. However, SGS-THOMSON Microelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of SGS-THOMSON Microelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. SGS-THOMSON Microelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of SGS-THOMSON Microelectronics.

© 1994 SGS-THOMSON Microelectronics - All Rights Reserved

SGS-THOMSON Microelectronics GROUP OF COMPANIES

Australia - Brazil - France - Germany - Hong Kong - Italy - Japan - Korea - Malaysia - Malta - Morocco - The Netherlands - Singapore - Spain - Sweden - Switzerland - Taiwan - Thailand - United Kingdom - U.S.A