


## Q6008LTH1LED Series




### Agency Approval

Agency	Agency File Number
	L Package : E71639

### Main Features

Symbol	Value	Unit
$I_{TRMS}$	8	A
$V_{DRM}/V_{RRM}$	600	V
DIAC $V_{BO}$	33 to 43	V

### Schematic Symbol



### Additional Information



[Datasheet](#)



[Resources](#)



[Samples](#)

### Description

The Quadrac is an internally triggered Triac designed for AC switching and phase control applications. It is a Triac and DIAC in a single package, which saves user expense by eliminating the need for separate Triac and DIAC components.

Q6008LTH1LED series is designed to meet low load current characteristics typical in LED lighting applications.

By keeping holding current at 6mA maximum, this Quadrac series is characterized and specified to perform best with LED loads. The Q6008LTH1LED series is best suited for LED dimming controls to obtain the lowest levels of light output with a minimum probability of flickering.

Q6008LTH1LED series is offered in the industry standard TO-220AB package with an isolated mounting tab that makes it best suited for adding an external heat sink.

### Features

- As low as 6mA max holding current
- UL recognized TO-220AB package
- 110°C rated junction temperature
- di/dt performance of 70A/μs
- QUADRAC version includes integrated DIAC
- RoHS compliant

### Benefits

- Provides full control of light output at the extreme low end of load conditions.
- 2500V<sub>AC</sub> min isolation between mounting tab and active terminals
- Improves margin of safe operation with less heat sinking required
- Enable survivability of typically LED load operating characteristics
- Simplicity of circuit design & layout

### Applications

Excellent for AC switching and phase control applications such as lighting and motor speed controls. Typical applications are AC solid-state switches, light dimmers with LED loads, small low current motor in power tools, and low current motors in home/brown goods appliances.

Internally constructed isolated package is offered for ease of heat sinking with highest isolation voltage.

### Absolute Maximum Ratings

Symbol	Parameter	Value	Unit	
$I_{T(RMS)}$	RMS forward current	8	A	
$I_{TSM}$	Peak non-repetitive surge current	single half cycle; $f = 50\text{Hz}$ ; $T_J$ (initial) = 25°C	80	
		single half cycle; $f = 60\text{Hz}$ ; $T_J$ (initial) = 25°C	85	
$I^2t$	$I^2t$ value for fusing	$t_p = 8.3\text{ms}$	$\text{A}^2\text{s}$	
$di/dt$	Critical rate-of-rise of on-state current	$f = 60\text{Hz}; T_J = 110^\circ\text{C}$	$\text{A}/\mu\text{s}$	
$I_{GM}$	Peak gate current	$T_J = 110^\circ\text{C}$	1.5	A
$T_{STG}$	Storage temperature range	-40 to 150	$^\circ\text{C}$	
$T_J$	Operating junction temperature range	-40 to 110	$^\circ\text{C}$	

### Electrical Characteristics ( $T_J = 25^\circ\text{C}$ , unless otherwise specified) – Alternistor Quadrac

Symbol	Test Conditions	Value	Unit
$I_H$	$I_T = 15\text{mA}$ (initial)	MAX.	mA
$dv/dt$	$V_D = V_{DRM}$ ; gate open; $T_J = 110^\circ\text{C}$	MIN.	$\text{V}/\mu\text{s}$
$dv/dt(c)$	$di/dt(c) = 0.54 \times I_{T(\text{rms})} / \text{ms}$ ; $T_J = 110^\circ\text{C}$	MIN.	$\text{V}/\mu\text{s}$
$t_{gt}$	(note 1)	TYP.	$\mu\text{s}$

(1) Reference test circuit in figure 7 and waveform in figure 8;  $C_T = 0.1\mu\text{F}$  with 0.1 $\mu\text{s}$  rise time.

### Trigger DIAC Specifications

Symbol	Test Conditions	Value	Unit
$\Delta V_{BO}$	Breakover Voltage Symmetry	MAX.	V
$V_{BO}$	Breakover Voltage, forward and reverse	MIN.	V
		MAX.	V
$[\Delta V \pm]$	Dynamic Breakback Voltage, forward and reverse (note 1)	MIN.	V
$I_{BO}$	Peak Breakover Current	MAX.	$\mu\text{A}$
$C_T$	Trigger Firing Capacitance	MAX.	$\mu\text{F}$

(1) Reference test circuit in figure 7 and waveform in figure 8.


### Static Characteristics

Symbol	Test Conditions	Value	Unit
$V_{TM}$	$I_T = 1.41 \times I_{T(\text{rms})} \text{ A}$ ; $t_p = 380\mu\text{s}$	MAX.	V
$I_{DRM} / I_{RRM}$	$V_{DRM} / V_{RRM}$	10	$\mu\text{A}$
		500	


### Thermal Resistances

Symbol	Parameter	Value	Unit
$R_{\theta(J-C)}$	Junction to case (AC)	2.8	$^\circ\text{C}/\text{W}$
$R_{\theta(J-A)}$	Junction to ambient	50	$^\circ\text{C}/\text{W}$


**Figure 1: Normalized DC Holding Current vs. Junction Temperature**




**Figure 3: Power Dissipation vs. RMS On-State Current (Typical)**




**Figure 2: On-State Current vs. On-State Voltage (Typical)**



**Figure 4: Maximum Allowable Case Temperature vs. RMS On-State Current**



**Figure 5: Surge Peak On-State Current vs. Number of Cycles**




Supply Frequency: 60Hz Sinusoidal  
Load: Resistive  
RMS On-State Current:  $[I_{T(\text{RMS})}]$ : Maximum Rated Value at Specific Case Temperature


Notes:

1. Gate control may be lost during and immediately following surge current interval.
2. Overload may not be repeated until junction temperature has returned to steady-state rated value.


**Figure 6: DIAC  $V_{BO}$  Change vs. Junction Temperature**




**Figure 7: Test Circuit**



**Figure 8: Test Circuit Waveform**




**Figure 9: Peak Output Current vs Triggering Capacitance (Per Figure 7)**



### Soldering Parameters

Reflow Condition		Pb – Free assembly
Pre Heat	- Temperature Min ( $T_{s(\min)}$ )	150°C
	- Temperature Max ( $T_{s(\max)}$ )	200°C
	- Time (min to max) ( $t_s$ )	60 – 180 secs
Average ramp up rate (Liquidus Temp) ( $T_L$ ) to peak		5°C/second max
$T_{S(\max)}$ to $T_L$ - Ramp-up Rate		5°C/second max
Reflow	- Temperature ( $T_L$ ) (Liquidus)	217°C
	- Temperature ( $t_L$ )	60 – 150 seconds
Peak Temperature ( $T_p$ )		260°C <sup>+0/-5</sup>
Time within 5°C of actual peak Temperature ( $t_p$ )		20 – 40 seconds
Ramp-down Rate		5°C/second max
Time 25°C to peak Temperature ( $T_p$ )		8 minutes Max.
Do not exceed		280°C



### Physical Specifications


<b>Terminal Finish</b>	1005 Matte Tin-plated
<b>Body Material</b>	UL Recognized epoxy meeting flammability classification 94v-0
<b>Lead Material</b>	Copper Alloy

### Design Considerations

Careful selection of the correct device for the application's operating parameters and environment will go a long way toward extending the operating life of the Thyristor. Good design practice should limit the maximum continuous current through the main terminals to 75% of the device rating. Other ways to ensure long life for a power discrete semiconductor are proper heat sinking and selection of voltage ratings for worst case conditions. Overheating, overvoltage (including  $dv/dt$ ), and surge currents are the main killers of semiconductors. Correct mounting, soldering, and forming of the leads also help protect against component damage.

### Environmental Specifications

Test	Specifications and Conditions
<b>High Temperature Voltage Blocking</b>	MIL-STD-750: Method 1040, Condition A Rated $V_{DRM}$ (VAC-peak), 110°C, 1008 hours
<b>Temperature Cycling</b>	MIL-STD-750: Method 1051 -40°C to 150°C, 15-minute dwell, 100 cycles
<b>Biased Temperature &amp; Humidity</b>	EIA/JEDEC: JESD22-A101 320VDC, 85°C, 85%RH, 1008 hours
<b>High Temp Storage</b>	MIL-STD-750: Method 1031 150°C, 1008 hours
<b>Low-Temp Storage</b>	-40°C, 1008 hours
<b>Resistance to Solder Heat</b>	MIL-STD-750: Method 2031 260°C, 10 seconds
<b>Solderability</b>	ANSI/J-STD-002, Category 3, Test A
<b>Lead Bend</b>	MIL-STD-750: Method 2036, Condition E

**Dimensions — TO-220AB (L-Package) — Isolated Mounting Tab**


Dimension	Inches		Millimeters	
	Min	Max	Min	Max
A	0.380	0.420	9.65	10.67
B	0.105	0.115	2.67	2.92
C	0.230	0.250	5.84	6.35
D	0.590	0.620	14.99	15.75
E	0.142	0.147	3.61	3.73
F	0.110	0.130	2.79	3.30
G	0.540	0.575	13.72	14.61
H	0.025	0.035	0.64	0.89
J	0.195	0.205	4.95	5.21
K	0.095	0.105	2.41	2.67
L	0.060	0.075	1.52	1.91
M	0.085	0.095	2.16	2.41
N	0.018	0.024	0.46	0.61
O	0.178	0.188	4.52	4.78
P	0.045	0.060	1.14	1.52
R	0.038	0.048	0.97	1.22


**Product Selector**

Part Number	Type	Package
Q6008LTH1LED	Alternistor Quadrac	TO-220L


Note: xx = Voltage

**Packing Options**

Part Number	Marking	Weight	Packing Mode	Base Quantity
Q6008LTH1LEDTP	Q6008LTH1	2.2 g	Tube	500 (50 per tube)

**Part Numbering System**

**Part Marking System**

TO-220 AB - (L Package)


 Date Code Marking  
 Y: Year Code  
 M: Month Code  
 XXX: Lot Trace Code