

CentralTM Semiconductor Corp.

145 Adams Avenue, Hauppauge, NY 11788 USA
Tel: (631) 435-1110 • Fax: (631) 435-1824

Manufacturers of World Class Discrete Semiconductors

2N4264

NPN SILICON TRANSISTOR

JEDEC TO-92 CASE

DESCRIPTION

The CENTRAL SEMICONDUCTOR 2N4264 type is a Silicon NPN Transistors designed for high speed switching applications.

MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$)

	SYMBOL		UNITS
Collector-Base Voltage	V_{CB0}	30	V
Collector-Emitter Voltage	V_{CEO}	15	V
Emitter-Base Voltage	V_{EBO}	6.0	V
Collector Current	I_C	200	mA
Power Dissipation	P_D	625	mW
Operating and Storage			
Junction Temperature	T_J, T_{stg}	-55 to +150	$^\circ\text{C}$
Thermal Resistance	θ_{JA}	200	$^\circ\text{C/W}$

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

SYMBOL	TEST CONDITIONS	MIN	MAX	UNITS
I_{CEV}	$V_{CE} = 12\text{V}, V_{BE(OFF)} = 0.25\text{V}$		0.1	μA
I_{CEV}	$V_{CE} = 12\text{V}, V_{BE(OFF)} = 0.25\text{V}, T_A = 100^\circ\text{C}$		10	μA
BV_{CEO}	$I_C = 1.0\text{mA}$	15		V
BV_{CBO}	$I_C = 10\mu\text{A}$	20		V
BV_{EBO}	$I_E = 10\mu\text{A}$	6.0		V
$V_{CE(SAT)}$	$I_C = 10\text{mA}, I_B = 1.0\text{mA}$		0.22	V
$V_{CE(SAT)}$	$I_C = 100\text{mA}, I_B = 10\text{mA}$		0.35	V
$V_{BE(SAT)}$	$I_C = 10\text{mA}, I_B = 1.0\text{mA}$	0.65	0.80	V
$V_{BE(SAT)}$	$I_C = 100\text{mA}, I_B = 10\text{mA}$	0.75	0.95	V
h_{FE}	$V_{CE} = 1.0\text{V}, I_C = 1.0\text{mA}$	25		-
h_{FE}	$V_{CE} = 1.0\text{V}, I_C = 10\text{mA}$	40	160	-
h_{FE}	$V_{CE} = 1.0\text{V}, I_C = 30\text{mA}$	40		-
h_{FE}	$V_{CE} = 1.0\text{V}, I_C = 100\text{mA}$	30		-
h_{FE}	$V_{CE} = 1.0\text{V}, I_C = 200\text{mA}$	20		-
f_T	$V_{CE} = 10\text{V}, I_C = 10\text{mA}, f = 100\text{MHz}$	350		MHz
C_{ib}	$V_{BE} = 0.5\text{V}, I_C = 0, f = 1.0\text{MHz}$		8.0	pF
C_{ob}	$V_{CB} = 5.0\text{V}, I_E = 0, f = 1.0\text{MHz}$		4.0	pF

(Continued on Reverse Side)

ELECTRICAL CHARACTERISTICS (Continued)

<u>SYMBOL</u>	<u>TEST CONDITIONS</u>	<u>MIN</u>	<u>MAX</u>	<u>UNITS</u>
t_d	$V_{CC} = 10V, V_{BE(OFF)} = 2.0V, I_C = 100mA, I_{B1} = 10mA$		8.0	ns
t_r	$V_{CC} = 10V, V_{BE(OFF)} = 2.0V, I_C = 100mA, I_{B1} = 10mA$		15	ns
t_s	$V_{CC} = 10V, I_C = 10mA, I_{B1} = I_{B2} = 10mA$		20	ns
t_f	$V_{CC} = 10V, I_C = 100mA, I_{B1} = I_{B2} = 10mA$		15	ns
t_{on}	$V_{CC} = 3.0V, V_{BE(OFF)} = 1.5V, I_C = 10mA, I_{B1} = 3.0mA$		25	ns
t_{off}	$V_{CC} = 3.0V, I_C = 10mA, I_{B1} = 3.0mA, I_{B2} = 1.5mA$		35	ns
Q_T	$V_{CC} = 3.0V, I_C = 10mA, I_B = 1.0mA$		80	pC

Central[™]
Semiconductor Corp.

145 Adams Avenue
Hauppauge, NY 11788 USA
Tel: (631) 435-1110 • Fax: (631) 435-1824
www.centrasemi.com

OUTSTANDING SUPPORT AND SUPERIOR SERVICES



PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options
- Custom bar coding for shipments
- Custom product packing

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities
- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

REQUESTING PRODUCT PLATING

1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
2. If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp.
145 Adams Avenue
Hauppauge, NY 11788 USA
Main Tel: (631) 435-1110
Main Fax: (631) 435-1824
Support Team Fax: (631) 435-3388
www.centrasemi.com

Worldwide Field Representatives:
www.centrasemi.com/wwreps

Worldwide Distributors:
www.centrasemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: www.centrasemi.com/terms