



## 3M™ PLEATED FOIL SHIELDED CABLE, 90202 SERIES

.025" 30 AWG STRANDED, TPE PRIMARY, THIN TPE COVER

**Regulatory:** For regulatory information about this product, visit [3M.com/regs](http://3M.com/regs) or contact your 3M representative.

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** For industrial use only. Not intended, labeled or packaged for consumer sale or use.

3M Company  
Electronics Materials Solutions Division  
13011 McCallen Pass, Bldg. C  
Austin, TX 78753-5380  
1-800-225-5373  
[www.3M.com/interconnect](http://www.3M.com/interconnect)

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION  
INTERCONNECT SOLUTIONS  
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.  
FOR TECHNICAL, SALES OR ORDERING  
INFORMATION CALL 800-225-5373

DESIGN REFERENCE		NEXT ASSEMBLY		ISSUE DATE AND DESCRIPTION	
REV	ECO	DATE	DATE	MFG	DATE
L SCHMIDT		DEC 16, 2021		APPL	
0101550		JAN 07, 2022		REDRAWN	
				WORK REQUEST 13221	
G 116219		MAY 15, 2024		JNC FJR	
F 0101550		REVISED UL INFORMATION			
DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		TITLE	
INCHES		.0 ± .1 .00 ± .05 .000 ± .010 .0000 ± .0005		3M Center St. Paul, MN 55144	
THIRD ANGLE PROJECTION		.0 ± .05 .00 ± .010 .000 ± .0100		© 3M COPYRIGHT 2024 This document and the information it contains are confidential and may not be distributed outside the 3M organization, or used or disclosed other than for 3M authorized purposes. All rights reserved.	
INTERPRET PER ASME Y14.5 - 2018		.0 ± .05 .00 ± .010 .000 ± .0100		PLEATED FOIL CABLE 90202 SERIES .025" 30AWG STRANDED	
MAX SURFACE ROUGHNESS DETAILED SURFACES MARKED ONLY		.0 ± .05 .00 ± .010 .000 ± .0100		CAGE SIZE DRAWING NO. D 78-5100-0730-1 G	
				REV. G	
				DET. LISTS YES NO SHT 2 OF 2	