






材料
MATERIAL
ナイロン66, UL94V-0
NYLON66, UL94V-0



47.5	51	22-01-1204	5102-20	20
45	48.5	▲ - 1194	▲ - 19	19
42.5	46	- 1184	- 18	18
40	43.5	- 1174	- 17	17
37.5	41	- 1164	- 16	16
35	38.5	- 1154	- 15	15
32.5	36	- 1144	- 14	14
30	33.5	- 1134	- 13	13
27.5	31	- 1124	- 12	12
25	28.5	- 1114	- 11	11
22.5	26	- 1104	- 10	10
20	23.5	- 1094	- 09	9
17.5	21	- 1084	- 08	8
15	18.5	- 1074	- 07	7
12.5	16	- 1064	- 06	6
10	13.5	- 1054	- 05	5
7.5	11	- 1044	- 04	4
5	8.5	▼ - 1034	▼ - 03	3
2.5	6	22-01-1024	5102-02	2
B	A	EDP. NO.	ENG. NO.	 NO. OF CKTS

注記
NOTE

使用ターミナル: ENG. NO. 5103*
APPLICABLE TERMINAL: ENG. NO. 5103*

REVISED EC NO: J2012-0647 DRAWN: SATO CHKD: KASAKAWA APPR: YOI TO	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
		10 UNDER	± 0.2	DRAWN BY H. IJIMA	DATE 1996/07/05	TITLE MINI SPOX HSG			
		10 OVER 30 UNDER	± 0.25	CHECKED BY M. FUKUSHIMA	DATE 1996/07/05				
		30 OVER	± 0.3	APPROVED BY M. ENOMOTO	DATE 1996/07/05	MOLEX INCORPORATED			
		ANGULAR	± 3 °	MATERIAL NO.					
	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			