




10 9 8 7 6 5 4 3 2 1

F

E

D

C

B

A

F





E

D

C

B

A



SPECIFICATIONS:

- Material:
 - Body: PA66
 - Screw: Steel
 - Wire Protector: QSn
 - Terminal: Brass
- Wire range: 24 - 14AWG.
- Electrical rating: 300V, 10A.
- MAX TORQUE: 3 in-lbs.
- Wire strip length: 5.00mm.
- Insulation resistance: DC500V, 500M.
- Operating temperature: -40C to +105C.
- A = N x P.
- B = (N - 1) x P
- P = (Pitch) = 5.00MM (.197").
- N = Number of positions available 2 through 24.

RELEASE EC NO: NEO2006-0310 DRWN: LROTHAUS 2006/01/09 CHKD: CYORK 2006/01/09 APPR: JPAWLICK 2006/01/10 A	DESCRIPTION QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
			mm	INCH	DRAWN BY LROTHAUS	DATE 10/7/05	TITLE 5.0MM, EURO TERM. BLOCK PC MOUNT, 45 DEGREE	
		4 PLACES	± ---	±.0015	CHECKED BY C. YORK	DATE 01/06/06		
		3 PLACES	±0.038	±.005	APPROVED BY	DATE		
		2 PLACES	±0.13	±.01	MOLEX MOLEX INCORPORATED			
		1 PLACE	±0.3	±---			DOCUMENT NO. SD-39543-001	
		ANGULAR ± 2 °		MATERIAL NO. See Chart		SHEET NO. 1 OF 1		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

9

8

7

6

5

4

3

2

1

