



TR14D3C Product Details

[Share](#) [Print](#) [Email](#)


TR14D3C
(1-1423393-2)

TE Internal Number: 1-1423393-2

 **Active**

Time Delay Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- TR - Control Relay - Timing Version Series
- Input Voltage = 215 VDC
- Contact - Arrangement = 4 Form C, 4PDT, 4 C/O
- Contact Rating = 10A
- Mounting Options = Socket

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Wiring Diagram](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Series = TR - Control Relay - Timing Version
- Termination Type = 16 Flat Base Pins
- Magnetic Blow-Out Device = Without

Electrical Characteristics:

- Input Voltage (VDC) = 215
- Contact Rating = 10A

Contact Features:

- Mounting Options = Socket
- Mode of Operation = Delay on Energization
- Delay Time = 1 second to 30 seconds
- Type of Control = Potentiometer Adjustable
- Repeatability, Max. = $\pm 2\%$
- Contact Base Material = Silver Plated
- Approx. Dimensions (L x W x H) (mm [in]) = 45.00 x 45.00 x 109.00 [1.773 x 1.773 x 4.294]

Configuration Features:

- [Contact - Arrangement](#) = 4 Form C, 4PDT, 4 C/O
- Multiple Timing Ranges = Without

Industry Standards:

- Approved Standards = CSA Certified, UL Listed
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- Temperature Range ($^{\circ}\text{C}$) = 0 - 50

Other:

- Brand = Agastat

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

