


#### General ordering data

|                  |                                                                                                                                                             |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Order No.        | 1687990000                                                                                                                                                  |
| Part designation | BL 3.5/13LH SN SW                                                                                                                                           |
| Version          | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 13, 180°, Box |
| EAN              | 4008190853549                                                                                                                                               |
| Qty.             | 50 pc(s).                                                                                                                                                   |

#### System parameters

|                                           |                          |
|-------------------------------------------|--------------------------|
| Conductor connection system               | Clamping yoke connection |
| Outgoing direction of conductor           | 180°                     |
| Pitch                                     | 3.5 mm                   |
| Pitch in inch                             | 0.138 inch               |
| No. of poles                              | 13                       |
| No. of rows                               | 1                        |
| Screwdriver blade                         | 0.4 x 2.5                |
| Screwdriver blade standard                | DIN 5264                 |
| Tightening torque, min.                   | 0.2                      |
| Tightening torque, max.                   | 0.25 Nm                  |
| Clamping screw                            | M 2                      |
| Stripping length                          | 6 mm                     |
| L1 in mm                                  | 42 mm                    |
| L1 in inch                                | 1.654 inch               |
| Electric shock protection to DIN VDE 0470 | IP 20                    |
| Electric shock protection to DIN VDE 0470 | Safe from finger touch   |

#### Material data

|                           |                     |
|---------------------------|---------------------|
| Insulating material       | PBT                 |
| Colour                    | black               |
| colour chart              | Similar to RAL 9011 |
| Insulating material group | IIIa                |
| Flammability class UL 94  | V-0                 |
| CTI                       | >= 200              |

#### Material data

|                       |              |
|-----------------------|--------------|
| Contact base material | Copper alloy |
| Contact surface       | tinned       |

#### Connectable conductors

|                                                   |                      |
|---------------------------------------------------|----------------------|
| Clamping range, min.                              | 0.08 mm <sup>2</sup> |
| Clamping range, max.                              | 1.5 mm <sup>2</sup>  |
| AWG, min.                                         | 14                   |
| AWG, max.                                         | 28                   |
| Solid, min. H05(07) V-U                           | 0.2 mm <sup>2</sup>  |
| Solid, max. H05(07) V-U                           | 1.5 mm <sup>2</sup>  |
| Flexible, min. H05(07) V-K                        | 0.2 mm <sup>2</sup>  |
| Flexible, max. H05(07) V-K                        | 1.5 mm <sup>2</sup>  |
| With wire end ferrule, acc. to DIN 46 228/1, min. | 0.2 mm <sup>2</sup>  |
| With wire end ferrule, acc. to DIN 46 228/1, max. | 1.5 mm <sup>2</sup>  |
| w. plastic collar ferrule, DIN 46228 pt 4, min.   | 0.2 mm <sup>2</sup>  |
| w. plastic collar ferrule, DIN 46228 pt 4, max.   | 1.5 mm <sup>2</sup>  |
| Gauge to EN 60999 a x b; ø                        | 2.4 mm x 1.5 mm;     |

#### DIN IEC rating data

|                                                                                |                   |
|--------------------------------------------------------------------------------|-------------------|
| Rated current, min. No. pins (Tu=20°C)                                         | 17 A              |
| Rated current, max. No. pins (Tu=20°C)                                         | 12 A              |
| Rated current, min. No. pins (Tu=40°C)                                         | 14.5 A            |
| Rated current, max. No. pins (Tu=40°C)                                         | 10 A              |
| Rated voltage for overvoltage class/pollution severity II/2                    | 320 V             |
| Rated voltage for overvoltage class/pollution severity III/2                   | 160 V             |
| Rated voltage for overvoltage class/pollution severity III/3                   | 160 V             |
| Rated impulse withstand voltage for overvoltage class/pollution severity II/2  | 2.5 kV            |
| Rated impulse withstand voltage for overvoltage class/pollution severity III/2 | 2.5 kV            |
| Rated impulse withstand voltage for overvoltage class/pollution severity III/3 | 2.5 kV            |
| Short-time withstand current resistance                                        | 3 x 1s with 100 A |

#### CSA rating data

|                                    |       |
|------------------------------------|-------|
| Rated voltage (Use group D)        | 300 V |
| Rated current (Use group D)        | 10 A  |
| AWG conductor (field wiring), min. | 28    |
| AWG conductor (field wiring), max. | 14    |

#### UL 1059 rating data

|                             |       |
|-----------------------------|-------|
| Rated voltage (Use group D) | 300 V |
| Rated current (Use group D) | 10 A  |
| AWG conductor, min.         | 28    |
| AWG conductor, max.         | 14    |

## Approvals

Approvals institutes



## Classifications

|            |             |
|------------|-------------|
| ETIM 2.0   | NK          |
| ETIM 3.0   | EC001284    |
| eClass 4.1 | 27-26-07-01 |
| eClass 5.0 | 27-26-07-01 |
| eClass 5.1 | 27-26-07-04 |

## Similar products

| Order No.  | Part designation | Version                                                                                                                                                    |
|------------|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1687650000 | BL 3.5/2LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 2, 180°, Box |
| 1687880000 | BL 3.5/2LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 2, 180°, Box |
| 1687660000 | BL 3.5/3LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 3, 180°, Box |
| 1687890000 | BL 3.5/3LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 3, 180°, Box |
| 1687670000 | BL 3.5/4LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 4, 180°, Box |
| 1687900000 | BL 3.5/4LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 4, 180°, Box |
| 1687680000 | BL 3.5/5LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 5, 180°, Box |
| 1687910000 | BL 3.5/5LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 5, 180°, Box |
| 1687690000 | BL 3.5/6LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 6, 180°, Box |
| 1687920000 | BL 3.5/6LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 6, 180°, Box |
| 1687700000 | BL 3.5/7LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 7, 180°, Box |

|            |                   |                                                                                                                                                             |
|------------|-------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1687930000 | BL 3.5/7LH SN SW  | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 7, 180°, Box  |
| 1687710000 | BL 3.5/8LH SN OR  | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 8, 180°, Box  |
| 1687940000 | BL 3.5/8LH SN SW  | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 8, 180°, Box  |
| 1687720000 | BL 3.5/9LH SN OR  | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 9, 180°, Box  |
| 1687950000 | BL 3.5/9LH SN SW  | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 9, 180°, Box  |
| 1687730000 | BL 3.5/10LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 10, 180°, Box |
| 1687960000 | BL 3.5/10LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 10, 180°, Box |
| 1687740000 | BL 3.5/11LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 11, 180°, Box |
| 1687970000 | BL 3.5/11LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 11, 180°, Box |
| 1687750000 | BL 3.5/12LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 12, 180°, Box |
| 1687980000 | BL 3.5/12LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 12, 180°, Box |
| 1687760000 | BL 3.5/13LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 13, 180°, Box |
| 1687770000 | BL 3.5/14LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 14, 180°, Box |
| 1688000000 | BL 3.5/14LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 14, 180°, Box |
| 1687780000 | BL 3.5/15LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 15, 180°, Box |
| 1688010000 | BL 3.5/15LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 15, 180°, Box |
| 1687790000 | BL 3.5/16LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 16, 180°, Box |

|            |                   |                                                                                                                                                             |
|------------|-------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1688020000 | BL 3.5/16LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 16, 180°, Box |
| 1687800000 | BL 3.5/17LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 17, 180°, Box |
| 1688030000 | BL 3.5/17LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 17, 180°, Box |
| 1687810000 | BL 3.5/18LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 18, 180°, Box |
| 1688040000 | BL 3.5/18LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 18, 180°, Box |
| 1687820000 | BL 3.5/19LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 19, 180°, Box |
| 1688050000 | BL 3.5/19LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 19, 180°, Box |
| 1687830000 | BL 3.5/20LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 20, 180°, Box |
| 1688060000 | BL 3.5/20LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 20, 180°, Box |
| 1687840000 | BL 3.5/21LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 21, 180°, Box |
| 1688070000 | BL 3.5/21LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 21, 180°, Box |
| 1687850000 | BL 3.5/22LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 22, 180°, Box |
| 1688080000 | BL 3.5/22LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 22, 180°, Box |
| 1687860000 | BL 3.5/23LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 23, 180°, Box |
| 1688090000 | BL 3.5/23LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 23, 180°, Box |
| 1687870000 | BL 3.5/24LH SN OR | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 24, 180°, Box |
| 1688100000 | BL 3.5/24LH SN SW | PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm <sup>2</sup> , Pitch: 3.50 mm, No. of poles: 24, 180°, Box |