

Surface Mount TRANSZORB® Transient Voltage Suppressors


SMBG (DO-215AA)


LINKS TO ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS	
V_{WM}	5.0 V to 188 V
V_{BR} (unidirectional)	6.4 V to 231 V
V_{BR} (bidirectional)	6.4 V to 231 V
P_{PPM}	600 W
I_{FSM} (unidirectional only)	100 A
T_J max.	150 °C
Polarity	Unidirectional, bidirectional
Package	SMBG (DO-215AA)

DEVICES FOR BIDIRECTION APPLICATIONS

For bidirectional devices use CA suffix (e.g. SMBG10CA).

Electrical characteristics apply in both directions.

FEATURES

- Low profile package
- Ideal for automated placement
- Glass passivated chip junction
- Available in unidirectional and bidirectional
- 600 W peak pulse power capability with a 10/1000 μ s waveform, repetitive rate (duty cycle): 0.01 %
- Excellent clamping capability
- Very fast response time
- Low incremental surge resistance
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
Available

TYPICAL APPLICATIONS

Use in sensitive electronics protection against voltage transients induced by inductive load switching and lighting on ICs, MOSFET, signal lines of sensor units for consumer, computer, industrial, automotive, and telecommunication.

MECHANICAL DATA

Case: SMBG (DO-215AA)

Molding compound meets UL 94 V-0 flammability rating

Base P/N-E3 - RoHS compliant, industrial grade

Base P/N-M3 - halogen-free, RoHS compliant, and industrial grade

Base P/NHE3 - RoHS compliant, AEC-Q101 qualified

Base P/NHM3 - halogen-free, RoHS compliant, and AEC-Q101 qualified

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3, M3, HE3, and HM3 suffix meets JESD 201 class 2 whisker test

Polarity: for unidirectional types the band denotes cathode end, no marking on bidirectional types

MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise noted)			
PARAMETER	SYMBOL	VALUE	UNIT
Peak pulse power dissipation with a 10/1000 μ s waveform ⁽¹⁾⁽²⁾ (fig. 1)	P_{PPM}	600	W
Peak pulse current with a 10/1000 μ s waveform ⁽¹⁾	I_{PPM}	See next table	A
Peak forward surge current 8.3 ms single half sine-wave unidirectional only ⁽²⁾	I_{FSM}	100	A
Operating junction and storage temperature range	T_J, T_{STG}	-55 to +150	°C

Notes

⁽¹⁾ Non-repetitive current pulse, per fig. 3 and derated above $T_A = 25$ °C per fig. 2

⁽²⁾ Mounted on 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pads to each terminal

**ELECTRICAL CHARACTERISTICS** ($T_A = 25^\circ\text{C}$ unless otherwise noted)

DEVICE TYPE MODIFIED GULL WING	DEVICE MARKING CODE		BREAKDOWN VOLTAGE V_{BR} AT I_T ⁽¹⁾ (V)		TEST CURRENT I_T (mA)	STAND-OFF VOLTAGE V_{WM} (V)	MAXIMUM REVERSE LEAKAGE AT V_{WM} I_D (μA) ⁽³⁾	MAXIMUM PEAK PULSE SURGE CURRENT I_{PPM} (A) ⁽²⁾	MAXIMUM CLAMPING VOLTAGE AT I_{PPM} V_C (V)
	UNI	BI	MIN.	MAX.					
(+)SMBG5.0A ⁽⁵⁾	KE	KE	6.40	7.07	10	5.0	800	65.2	9.2
(+)SMBG6.0A	KG	KG	6.67	7.37	10	6.0	800	58.3	10.3
(+)SMBG6.5A	KK	AK	7.22	7.98	10	6.5	500	53.6	11.2
(+)SMBG7.0A	KM	KM	7.78	8.60	10	7.0	200	50.0	12.0
(+)SMBG7.5A	KP	AP	8.33	9.21	1.0	7.5	100	46.5	12.9
(+)SMBG8.0A	KR	AR	8.89	9.83	1.0	8.0	50	44.1	13.6
(+)SMBG8.5A	KT	AT	9.44	10.4	1.0	8.5	20	41.7	14.4
(+)SMBG9.0A	KV	AV	10.0	11.1	1.0	9.0	10	39.0	15.4
(+)SMBG10A	KX	AX	11.1	12.3	1.0	10	5.0	35.3	17.0
(+)SMBG11A	KZ	KZ	12.2	13.5	1.0	11	5.0	33.0	18.2
(+)SMBG12A	LE	BE	13.3	14.7	1.0	12	5.0	30.2	19.9
(+)SMBG13A	LG	LG	14.4	15.9	1.0	13	1.0	27.9	21.5
(+)SMBG14A	LK	BK	15.6	17.2	1.0	14	1.0	25.9	23.2
(+)SMBG15A	LM	BM	16.7	18.5	1.0	15	1.0	24.6	24.4
(+)SMBG16A	LP	LM	17.8	19.7	1.0	16	1.0	23.1	26.0
(+)SMBG17A	LR	LR	18.9	20.9	1.0	17	1.0	21.7	27.6
(+)SMBG18A	LT	BT	20.0	22.1	1.0	18	1.0	20.5	29.2
(+)SMBG20A	LV	LV	22.2	24.5	1.0	20	1.0	18.5	32.4
(+)SMBG22A	LX	BX	24.4	26.9	1.0	22	1.0	16.9	35.5
(+)SMBG24A	LZ	BZ	26.7	29.5	1.0	24	1.0	15.4	38.9
(+)SMBG26A	ME	CE	28.9	31.9	1.0	26	1.0	14.3	42.1
(+)SMBG28A	MG	MG	31.1	34.4	1.0	28	1.0	13.2	45.4
(+)SMBG30A	MK	CK	33.3	36.8	1.0	30	1.0	12.4	48.4
(+)SMBG33A	MM	CM	36.7	40.6	1.0	33	1.0	11.3	53.3
(+)SMBG36A	MP	CP	40.0	44.2	1.0	36	1.0	10.3	58.1
(+)SMBG40A	MR	CR	44.4	49.1	1.0	40	1.0	9.3	64.5
(+)SMBG43A	MT	CT	47.8	52.8	1.0	43	1.0	8.6	69.4
(+)SMBG45A	MV	MV	50.0	55.3	1.0	45	1.0	8.3	72.7
(+)SMBG48A	MX	MX	53.3	58.9	1.0	48	1.0	7.8	77.4
(+)SMBG51A	MZ	MZ	56.7	62.7	1.0	51	1.0	7.3	82.4
(+)SMBG54A	NE	NE	60.0	66.3	1.0	54	1.0	6.9	87.1
(+)SMBG58A	NG	NG	64.4	71.2	1.0	58	1.0	6.4	93.6
(+)SMBG60A	NK	NK	66.7	73.7	1.0	60	1.0	6.2	96.8
(+)SMBG64A	NM	NM	71.1	78.6	1.0	64	1.0	5.8	103
(+)SMBG70A	NP	NP	77.8	86.0	1.0	70	1.0	5.3	113
(+)SMBG75A	NR	NR	83.3	92.1	1.0	75	1.0	5.0	121
(+)SMBG78A	NT	NT	86.7	95.8	1.0	78	1.0	4.8	126
(+)SMBG85A	NV	NV	94.4	104	1.0	85	1.0	4.4	137
(+)SMBG90A	NX	NX	100	111	1.0	90	1.0	4.1	146
(+)SMBG100A	NZ	NZ	111	123	1.0	100	1.0	3.7	162
(+)SMBG110A	PE	PE	122	135	1.0	110	1.0	3.4	177
(+)SMBG120A	PG	PG	133	147	1.0	120	1.0	3.1	193
(+)SMBG130A	PK	PK	144	159	1.0	130	1.0	2.9	209
(+)SMBG150A	PM	PM	167	185	1.0	150	1.0	2.5	243
(+)SMBG160A	PP	PP	178	197	1.0	160	1.0	2.3	259
(+)SMBG170A	PR	PR	189	209	1.0	170	1.0	2.2	275
SMBG188A	PS	PS	209	231	1.0	188	1.0	2.0	328

Notes

- (1) Pulse test: $t_p \leq 50$ ms
- (2) Surge current waveform per fig. 3 and derate per fig. 2
- (3) For bidirectional types having V_{WM} of 10 V and less, the I_D limit is doubled
- (4) All terms and symbols are consistent with ANSI/IEEE C62.35
- (5) For the bidirectional SMBG5.0CA, the maximum V_{BR} is 7.25 V
- (6) $V_F = 3.5$ V at $I_F = 50$ A (unidirectional only)
- (+) Underwriters laboratory recognition for the classification of protectors (QVGQ2) under the UL standard for safety 497B and file number E136766 for both unidirectional and bidirectional devices

THERMAL CHARACTERISTICS ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)			
PARAMETER	SYMBOL	VALUE	UNIT
Typical thermal resistance, junction to ambient ⁽¹⁾	$R_{\theta JA}$	100	$^{\circ}\text{C/W}$
Typical thermal resistance, junction to lead	$R_{\theta JL}$	20	

Note
⁽¹⁾ Mounted on minimum recommended pad layout

ORDERING INFORMATION (Example)				
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
SMBG5.0A-E3/52	0.096	52	750	7" diameter plastic tape and reel
SMBG5.0A-M3/52	0.096	52	750	7" diameter plastic tape and reel
SMBG5.0A-E3/5B	0.096	5B	3200	13" diameter plastic tape and reel
SMBG5.0A-M3/5B	0.096	5B	3200	13" diameter plastic tape and reel
SMBG5.0AHE3/52 ⁽¹⁾	0.096	52	750	7" diameter plastic tape and reel
SMBG5.0AHM3/52 ⁽¹⁾	0.096	52	750	7" diameter plastic tape and reel
SMBG5.0AHE3/5B ⁽¹⁾	0.096	5B	3200	13" diameter plastic tape and reel
SMBG5.0AHM3/5B ⁽¹⁾	0.096	5B	3200	13" diameter plastic tape and reel

Note
⁽¹⁾ AEC-Q101 qualified


RATINGS AND CHARACTERISTICS CURVES ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)


Fig. 1 - Peak Pulse Power Rating Curve




Fig. 2 - Pulse Power or Current vs. Initial Junction Temperature




Fig. 3 - Pulse Waveform




Fig. 5 - Typical Transient Thermal Impedance




Fig. 4 - Typical Junction Capacitance




Fig. 6 - Maximum Non-Repetitive Peak Forward Surge Current



PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

SMBG (DO-215AA)



Mounting Pad Layout





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.