

| | | | | | |
|-----------------------|--------|--------------------|--------------|--------------|-------|
| Messrs. Standard | | | | | |
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. |
| | | | B | Nov. 1, 06 | 1 |

LIQUID CRYSTAL DISPLAY MODULE
MODEL: NMTC-S20200BMNHSGW
Customer's No.: None.

•

| |
|------------|
| Acceptance |
| |

*Microtips Technology Inc.
12F. No.31 Lane 169, Kang Ning St., His-Chih,
Taipei Hsien, Taiwan, R.O.C.
FAX: 886-2-26958625*

| |
|-------------------------|
| Approved and Checked by |
| |

| Approved by | Checked by | Made by |
|-------------|------------|---------|
| | | |



Microtips Technology Inc.

| | | | | | |
|-----------------------|--------|--------------------|--------------|--------------|-------|
| Messrs. Standard | | | | | |
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. |
| | | | B | Nov. 1, 06 | 2 |

Revise Records

| Rev. | Date | Contents | Written | Approved |
|------|-----------|-------------|-------------|------------|
| A | 8/12/2002 | New edition | Joy Shen | Garry Chen |
| B | 11/1/2006 | See Note2. | Sherry Chan | Danny Lian |
| | | | | |
| | | | | |

Special notes

| | |
|--------|---------------------------------------|
| Note1. | White Edge-Lite LED Backlight |
| Note2. | The LCD module is compliant with RoHS |
| Note3. | |
| Note4. | |
| Note5. | |
| | |
| | |
| | |
| | |



Microtips Technology Inc.

| | | | | | |
|-----------------------|--------|--------------------|--------------|-------------------|-------|
| Messrs. Standard | | | | | |
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. |
| | | | <i>B</i> | <i>Nov. 1, 06</i> | 3 |

CONTENTS

| | |
|-----------------------------------|----|
| 1. General Specifications..... | 2 |
| 2. Electrical Specifications..... | 3 |
| 3. Optical Specification..... | 5 |
| 4. I/O Terminal..... | 7 |
| 5. Test..... | 9 |
| 6. Appearance Standards..... | 10 |
| 7. Handling and Precautions..... | 12 |
| 8. Warranty | 15 |
| 9. Dimensional Outline..... | 18 |



Microtips Technology Inc.

| | | | | | |
|-----------------------|--------|--------------------|--------------|--------------|-------|
| Messrs. Standard | | | | | |
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. |
| | | | B | Nov. 1, 06 | 4 |

1. General Specifications

| | |
|-------------------------------|---|
| Operating Temperature. | : Min. -20°C ~ Max. 70°C |
| Storage Temperature. | : Min. -30°C ~ Max. 80°C |
| Display Format | : 20 characters x 2 lines |
| Display Fonts | : 5 x 7 dots + cursor (1 character) |
| Viewing Area | : 82.2 (W) x 18.2 (H) mm |
| Outline Dimensions | : 116.0 (W) x 37.0 (H) x 14.5 max. (D) mm |
| Weight | : None. |
| LCD Type | : STN / Negative / Transmissive |
| Viewing Angle | : 6:00 |
| Backlight | : White Edge-Lite LED |
| Drawings | : As attached drawings |



Microtips Technology Inc.

| | | | | | |
|-----------------------|--------|--------------------|--------------|--------------|-------|
| Messrs. Standard | | | | | |
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. |
| | | | B | Nov. 1, 06 | 5 |

2. Electrical Specifications

2.1 Absolute Maximum Ratings

$V_{SS} = 0V$

| Parameter | Symbol | Conditions | Min. | Max. | Units |
|----------------------------|-------------------|------------|-------|----------------|-------|
| Supply Voltage (Logic) | $V_{DD} - V_{SS}$ | — | - 0.3 | 7.0 | V |
| Supply Voltage (LCD Drive) | $V_{DD} - V_{EE}$ | — | 0 | 13.0 | V |
| Input Voltage | V_I | — | - 0.3 | $V_{DD} + 0.3$ | V |

2.2 DC Characteristics

$T_a = 25^\circ C, V_{SS} = 0V$

| Parameter | Symbol | Conditions | Min. | Typ. | Max. | Units |
|----------------------------|-------------------|--------------------------|------|------|----------|-------|
| Supply Voltage (Logic) | $V_{DD} - V_{SS}$ | — | 4.5 | — | 5.5 | V |
| Supply Voltage (LCD Drive) | $V_{DD} - V_{EE}$ | Shown in 3.1 | | | | V |
| High Level Input Voltage | V_{IH} | $V_{DD} = 5.0V \pm 10\%$ | 2.2 | — | V_{CC} | V |
| Low Level Input Voltage | V_{IL} | $V_{DD} = 5.0V \pm 10\%$ | 0 | — | 0.6 | V |
| High Level Output Voltage | V_{OH} | $I_{OH} = -0.205mA$ | 2.4 | — | V_{CC} | V |
| Low Level Output Voltage | V_{OL} | $I_{OL} = 1.2mA$ | 0 | — | 0.4 | V |
| Supply Current | I_{CC} | $V_{DD} - V_{SS} = 5.0V$ | — | 1.5 | 5.0 | mA |



Microtips Technology Inc.

| | | | | |
|-----------------------|---------------------------|--------------|--------------|-------|
| Product Specification | Model: NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. |
| | | B | Nov. 1, 06 | 6 |

2.3 AC Characteristics

 $V_{CC} = 5.0V \pm 10\%$

| Parameter | Symbol | Conditions | Min. | Max. | Units |
|-----------------------|------------------|------------|------|------|-------|
| Enable Cycle Time | t_{CYC} | Fig.1, 2 | 500 | — | ns |
| Enable Pulse Width | PW_{EH} | Fig.1, 2 | 230 | — | ns |
| Enable Rise/Fall Time | t_{Er}, t_{Ef} | Fig.1, 2 | — | 20 | ns |
| Address Setup Time | t_{AS} | Fig.1, 2 | 40 | — | ns |
| Address Hold Time | t_{AH} | Fig.1, 2 | 10 | — | ns |
| Write Data Setup Time | t_{DSW} | Fig.1 | 80 | — | ns |
| Write Data Hold Time | t_{DHW} | Fig.1 | 10 | — | ns |
| Read Data Delay Time | t_{DDR} | Fig.2 | — | 160 | ns |
| Read Data Hold Time | t_{DHR} | Fig.2 | 5 | — | ns |





Fig.1 Write Operation Timing



| | | | | | | |
|-----------------------|--------|--------------------|--------------|--------------|--------------|-------|
| Messrs. Standard | | | | | | |
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Revision No. | Issued Date. | Page. |
| | | | B | | Nov. 1, 06 | 7 |


Fig.2 Read Operation Timing

2.4 Lighting Specifications

2.4.1 Absolute Maximum Ratings

| Ta=25°C | | | | | | |
|-----------------------|--------|------------|------|------|------|-------|
| Parameter | Symbol | Conditions | Min. | Typ. | Max. | Units |
| Forward Current | IF | Note 1 | — | -- | 30 | mA |
| Reverse Voltage | VR | — | — | — | 5 | V |
| LED Power Dissipation | PD | — | — | — | 70 | mW |

Note 1 : Refer to the forward current de-rating curve.



2.4.2 Operating Characteristics

| Ta=25°C | | | | | | |
|--------------------------------|----------------|----------------------|------|------|------|-------------------|
| Parameter | Symbol | Conditions | Min. | Typ. | Max. | Units |
| Forward Voltage | V _F | I _F =30mA | -- | 3.5 | 3.75 | V |
| Luminance of Backlight Surface | L | I _F =30mA | 45 | 65 | — | cd/m ² |

| | | | | | | |
|-----------------------|--------|--------------------|--------------|--------------|-------|---|
| Messrs. Standard | | | | | | |
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. | |
| | | | B | Nov. 1, 06 | | 8 |

3. Optical Specifications

3.1 LCD Driving Voltage

| Parameter | Symbol | Conditions | Min. | Typ. | Max. | Units |
|--|-----------------|-------------|------|------|------|-------|
| Recommended LCD Driving Voltage Note 1 | $V_{DD}-V_{EE}$ | Ta = -20 °C | — | — | -- | V |
| | | Ta = 0 °C | -- | -- | -- | V |
| | | Ta = 25 °C | — | 4.5 | -- | V |
| | | Ta = 50 °C | -- | -- | -- | V |
| | | Ta = 70 °C | -- | — | — | V |

Note 1 : Voltage (Applied actual waveform to LCD Module) for the best contrast. The range of minimum and maximum shows tolerance of the operating voltage. The specified contrast ratio and response time are not guaranteed over the entire range.

3.2 Optical Characteristics

Ta=25 °C, 1/16 Duty, 1/5 Bias, $V_{CC}=4.5V$ (Note 4), $\theta = 0^\circ$, $\phi = 270^\circ$

| Parameter | Symbol | Conditions | Min. | Typ. | Max. | Units |
|-----------------------|--------------|---|------|------|------|-------|
| Contrast Ratio Note 1 | CR | $\theta = 0^\circ$, $\phi = 270^\circ$ | — | 4.5 | — | |
| Viewing Angle | | Shown in 3.3 | | | | |
| Response Time | Rise Note 2 | T_{ON} | — | — | 150 | ms |
| | Decay Note 3 | T_{OFF} | — | — | 250 | ms |

Note 1 : Contrast ratio is defined as follows.

$$CR = L_{OFF} / L_{ON}$$

L_{ON} : Luminance of the ON segments, L_{OFF} : Luminance of the OFF segments

Note 2 : The time that the luminance level reaches 90% of the saturation level from 0% when ON signal is applied.

Note 3 : The time that the luminance level reaches 10% of the saturation level from 100% when OFF signal is applied.

Note 4 : Definition of Driving Voltage V_D . Assuming that the typical driving waveforms shown below are applied to the LCD Panel at /A Duty - 1/B Bias (A : Duty Number, B : Bias Number). Driving voltage V_D is defined as follows: $V_D = (V_{th1}+V_{th2}) / 2$


V_{th1} : The voltage VO-P that should provide 50% of the saturation level in the luminance at the segment which the ON signal is applied to.

V_{th2} : The voltage VO-P that should provide 50% of the saturation level in the luminance at the segment which the OFF signal is applied to.




Microtips Technology Inc.


| | | | | | |
|-----------------------|--------|--------------------|--------------|--------------|-------|
| Messrs. Standard | | | | | |
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. |
| | | | B | Nov. 1, 06 | 9 |



3.3 Definition of Viewing Angle and Optimum Viewing Area



3.4 Definition of Viewing Angle θ_f and θ_b




Optimum viewing angle with the naked eye and viewing angle θ at $C_{max.}$
Above are not always the same.

3.5 Definition of Contrast C, $C = \text{Brightness of selected dot (B1) / Brightness of unselected dot (B2)}$



Microtips Technology Inc.

| | | | | | |
|-----------------------|--------|--------------------|--------------|--------------|-------|
| Messrs. Standard | | | | | |
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. |
| | | | B | Nov. 1, 06 | 10 |



4. I/O Terminal


4.1 Pin Assignment

| No. | Symbol | Level | Function |
|-----|--------|-------|---|
| 1 | VSS | — | Power Supply (0V, GND) |
| 2 | VDD | — | Power Supply for Logic |
| 3 | VEE | — | Power Supply for LCD Drive |
| 4 | RS | H / L | Register Select Signal |
| 5 | R/W | H / L | Read/Write Select Signal H : Read L : Write |
| 6 | E | H / L | Enable Signal (No pull-up Resister) |
| 7 | DB0 | H / L | Data Bus Line / Non-connection at 4-bit operation |
| 8 | DB1 | H / L | Data Bus Line / Non-connection at 4-bit operation |
| 9 | DB2 | H / L | Data Bus Line / Non-connection at 4-bit operation |
| 10 | DB3 | H / L | Data Bus Line / Non-connection at 4-bit operation |
| 11 | DB4 | H / L | Data Bus Lin |
| 12 | DB5 | H / L | Data Bus Line |
| 13 | DB6 | H / L | Data Bus Line |
| 14 | DB7 | H / L | Data Bus Line |
| 15 | LEDA | -- | LED Anode (+) |
| 16 | LEDK | -- | LED Cathode (-) |



4.2 Example of Power Supply

It is recommended to apply a potentiometer for the contrast adjust due to the tolerance of the driving voltage and its temperature dependence.

| Messrs. Standard | | | | | |
|-----------------------|--------|--------------------|--------------|--------------|-------|
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. |
| | | | B | Nov. 1, 06 | 11 |



4.3 Block Diagram




| | | | | | |
|-----------------------|--------|--------------------|--------------|--------------|-------|
| Messrs. Standard | | | | | |
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. |
| | | | B | Nov. 1, 06 | 12 |

5. Reliability Test

5.1 Test Item

No change on display and in operation under the following test condition.

| No. | Test Item | Description | Condition | Note |
|-----|------------------------------|---|-----------------------------|------|
| 1. | High Temperature (Operation) | Durability test under long time high temperature with electrical stress (voltage, current) | 50°C ± 2°C 96hrs | |
| 2. | High Temperature (Storage) | Durability test under long time high temperature storage | 70°C ± 2°C 96hrs | 4 |
| 3 | Low Temperature (Operation) | Durability test under long time low temperature with electrical stress (voltage, current) | 0°C ± 2°C, 96hrs | 3 |
| 4 | Low Temperature (Storage) | Durability test under long time low temperature storage | -20°C ± 2°C, 96hrs | 3, 4 |
| 5 | Damp Proof Test | Durability test under long time high temperature and high humidity | 40°C ± 2°C, 90~95% RH 96hrs | 3, 4 |
| 6. | Vibration Test | Total fixed amplitude: 1.5mm Vibration frequency: 10~55Hz One cycle 60 seconds to 3 directions of X, Y, Z for each 15 minutes | -- | 5 |
| 7. | Shock Test | To be measured after dropping from 60cm high on the concrete surface in packing state. | | |



Dropping method corner dropping

A corner: once


Edge dropping

B, C, D edge: once

Face dropping

E, F, G face: once

| | | | | | |
|-----------------------|--------|--------------------|--------------|--------------|-------|
| Messrs. Standard | | | | | |
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. |
| | | | B | Nov. 1, 06 | 13 |



Note 1: Unless otherwise specified, tests will be conducted under the following condition,

Temperature : $25^{\circ}\text{C} \pm 2^{\circ}\text{C}$

Humidity : $65\% \pm 5\%$

Note 2: Unless otherwise specified, tests will be not conducted under functioning state.

Note 3: No dew condensation to be observed.

Note 4: The function test shall be conducted after 4 hours storage at the normal temperature and humidity after removed from the test chamber.

Note 5: Vibration test will be conducted to the product itself without putting it in a container.

5.2 Judgment Standard

| Failure Mode | Test Item | | | | | | | Judgment Standard |
|----------------------|-----------|---|---|---|---|---|---|--|
| | 1 | 2 | 3 | 4 | 5 | 6 | 7 | |
| Orientation | * | * | * | * | * | | | No remarkable degradation of appearance under bias/ non-bias condition |
| Current Value (IAC) | * | * | * | * | * | | | No remarkable increase |
| Contrast | * | | * | * | * | | | No remarkable poor contrast |
| Domain | * | * | * | * | * | | | Less than 20% of all dots have reverse tilt of more than one third of one dot area. |
| Bubble (Inside Cell) | * | * | * | * | * | * | | As per "Appearance Standard" (Note. including one which disappear after $25^{\circ}\text{C} 2\text{H}$) |
| Polarizer | * | | | | * | * | | As per "Appearance Standard" no remarkable appearance change |
| Glass Damage | | | | | | | * | As per "Appearance Standard" |

Note. 1. * is strong linkage between Failure Mode and Test Item.

2. Number of Test Item should be referred to former page.

3. Judgment and Standard value should be fixed by other inspection standard and criteria samples.

| | | | | | |
|-----------------------|--------|--------------------|--------------|--------------|-------|
| Messrs. Standard | | | | | |
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. |
| | | | B | Nov. 1, 06 | 14 |


6. Appearance Standards

6.1 Inspection Conditions

The LCD shall be inspected under 40W white fluorescent light.


The distance between the eyes and the sample shall be more than 30cm.

All directions for inspecting the sample should be within 45° against perpendicular line.



6.2 Definition of Applicable Zones

| | | | | | |
|-----------------------|--------|--------------------|--------------|--------------|-------|
| Messrs. Standard | | | | | |
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. |
| | | | B | Nov. 1, 06 | 15 |





A Zone : Active display area
 B Zone : Area from outside of "A Zone" to validity viewing area
 C Zone : Rest parts
 A Zone + B Zone = Validity viewing area

6.3 Standards


| No. | Parameter | Criteria | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|---------------------|---|--|------|---|-------------------|--|--|----------------|--|---|---|---|--------------|--|---|---|---|--------------------|--|---|---|---|---------------------|--|---|---|---|---------------------|--|---|---|---|-----------|--|---|---|---|------|--|-------------------|--|--|--------|--------|---|---|---|----|---------------|---|---|---|--------------|---------------|---|---|---|--|--|--|--|
| 1. | Black and White Spots, Foreign Substances | (1) Round Shape <table border="1"> <thead> <tr> <th colspan="2">Zone</th><th colspan="3">Acceptable Number</th></tr> <tr> <th>Dimension (mm)</th><th></th><th>A</th><th>B</th><th>C</th></tr> </thead> <tbody> <tr> <td>$D \leq 0.1$</td><td></td><td>*</td><td>*</td><td>*</td></tr> <tr> <td>$0.1 < D \leq 0.2$</td><td></td><td>3</td><td>5</td><td>*</td></tr> <tr> <td>$0.2 < D \leq 0.25$</td><td></td><td>2</td><td>3</td><td>*</td></tr> <tr> <td>$0.25 < D \leq 0.3$</td><td></td><td>0</td><td>1</td><td>*</td></tr> <tr> <td>$0.3 < D$</td><td></td><td>0</td><td>0</td><td>*</td></tr> </tbody> </table> <p>$D = (\text{Long} + \text{Short})/2$ *: Disregard</p> (2) Line Shape <table border="1"> <thead> <tr> <th colspan="2">Zone</th><th colspan="3">Acceptable Number</th></tr> <tr> <th>X (mm)</th><th>Y (mm)</th><th>A</th><th>B</th><th>C</th></tr> </thead> <tbody> <tr> <td>--</td><td>$0.03 \geq W$</td><td>*</td><td>*</td><td>*</td></tr> <tr> <td>$2.0 \geq L$</td><td>$0.05 \geq W$</td><td>3</td><td>3</td><td>*</td></tr> </tbody> </table> | Zone | | Acceptable Number | | | Dimension (mm) | | A | B | C | $D \leq 0.1$ | | * | * | * | $0.1 < D \leq 0.2$ | | 3 | 5 | * | $0.2 < D \leq 0.25$ | | 2 | 3 | * | $0.25 < D \leq 0.3$ | | 0 | 1 | * | $0.3 < D$ | | 0 | 0 | * | Zone | | Acceptable Number | | | X (mm) | Y (mm) | A | B | C | -- | $0.03 \geq W$ | * | * | * | $2.0 \geq L$ | $0.05 \geq W$ | 3 | 3 | * | | | | |
| Zone | | Acceptable Number | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Dimension (mm) | | A | B | C | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| $D \leq 0.1$ | | * | * | * | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| $0.1 < D \leq 0.2$ | | 3 | 5 | * | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| $0.2 < D \leq 0.25$ | | 2 | 3 | * | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| $0.25 < D \leq 0.3$ | | 0 | 1 | * | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| $0.3 < D$ | | 0 | 0 | * | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Zone | | Acceptable Number | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| X (mm) | Y (mm) | A | B | C | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| -- | $0.03 \geq W$ | * | * | * | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| $2.0 \geq L$ | $0.05 \geq W$ | 3 | 3 | * | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |

| | | | | | |
|-----------------------|--------|--------------------|--------------|--------------|-------|
| Messrs. Standard | | | | | |
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. |
| | | | B | Nov. 1, 06 | 16 |

| | | | 1.0 \geq L | 0.1 \geq W | 3 | 3 | * | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|----------------------|--|---|---|-------------------|---------------------|---|---|--|----------------|------|--|--|-------------------|--|--|---|---|---|--|--|--|--------------|---|---|---|--|--|--|----------------------|---|---|---|--|--|--|----------------------|---|---|---|--|--|--|-----------|---|---|---|--|--|--|
| | | | -- | 0.1 $<$ W | In the same way (1) | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | | | X : Length Y: Width *: Disregard Total defects shall not exceed 5. | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 2. | Air Bubbles (between glass & polarizer) | | <table border="1"> <thead> <tr> <th rowspan="2">Dimension (mm)</th> <th colspan="3">Zone</th> <th colspan="3">Acceptable Number</th> </tr> <tr> <th>A</th> <th>B</th> <th>C</th> <th></th> <th></th> <th></th> </tr> </thead> <tbody> <tr> <td>D \leq 0.3</td> <td>*</td> <td>*</td> <td>*</td> <td></td> <td></td> <td></td> </tr> <tr> <td>0.3 $<$ D \leq 0.4</td> <td>3</td> <td>*</td> <td>*</td> <td></td> <td></td> <td></td> </tr> <tr> <td>0.4 $<$ D \leq 0.6</td> <td>2</td> <td>3</td> <td>*</td> <td></td> <td></td> <td></td> </tr> <tr> <td>0.6 $<$ D</td> <td>0</td> <td>0</td> <td>*</td> <td></td> <td></td> <td></td> </tr> </tbody> </table> | | | | | | Dimension (mm) | Zone | | | Acceptable Number | | | A | B | C | | | | D \leq 0.3 | * | * | * | | | | 0.3 $<$ D \leq 0.4 | 3 | * | * | | | | 0.4 $<$ D \leq 0.6 | 2 | 3 | * | | | | 0.6 $<$ D | 0 | 0 | * | | | |
| Dimension (mm) | Zone | | | Acceptable Number | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | A | B | C | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| D \leq 0.3 | * | * | * | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0.3 $<$ D \leq 0.4 | 3 | * | * | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0.4 $<$ D \leq 0.6 | 2 | 3 | * | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0.6 $<$ D | 0 | 0 | * | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | | | *: Disregard Total defects shall not exceed 3. | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |

| No. | Parameter | Criteria |
|-----|------------------|--|
| 3. | The Shape of Dot | <p>(1) Dot Shape (with Dent)</p>  <p>As per the sketch of left hand.</p> <p>(2) Dot Shape (with Projection)</p>  <p>Should not be connected to next dot.</p> <p>(3) Pin Hole</p>  <p>$(X+Y)/2 \leq 0.2\text{mm}$ (Less than 0.1mm)</p> |

| | | | | | |
|-----------------------|---------------------------|--|----------------|-------------------------|----------|
| Messrs. Standard | | | | | |
| Product Specification | Model: NMTC-S20200BMNHSGW | | Revision No. B | Issued Date. Nov. 1, 06 | Page. 17 |

| | | | |
|----|--|--|-----------------|
| | | | is no counted.) |
| | | (4) Deformation | |
| | |  | (X+Y)/2 ≤ 0.2mm |
| | | Total acceptable number: 1/dot, 5/cell (Defect number of (4): 1pc.) | |
| 4. | Polarizer Scratches | Not to be conspicuous defects. | |
| 5. | Polarizer Dirts | If the stains are removed easily from LCDP surface, the module is not defective. | |
| 6. | Complex Foreign Substance Defects | Black spots, line shaped foreign substance or air bubbles between glass & polarizer should be 5pcs maximum in total. | |
| 7. | Distance between different Foreign Substance defects | $D \leq 0.2 : 20\text{mm or more}$ $0.2 < D : 40\text{mm or more}$ | |

7. Handling and Precautions

The Following precautions will guide you in handling our product correctly.

- 1 Liquid crystal display devices
 - 1.1 The liquid crystal display device panel used in the liquid crystal display module is made of plate glass. Avoid any strong mechanical shock. Should the glass break handle it with care.
 - 1.2 The polarizer adhering to the surface of the LCD is made of a soft material. Guard against scratching it.
- 2 Care of the liquid crystal display module against static electricity discharge.
 - 2.1 When working with the module, be sure to ground your body and any electrical equipment you may be using. We strongly recommend the use of anti static mats (made of rubber), to protect work tables against the hazards of electrical shock.
 - 2.2 Avoid the use of work clothing made of synthetic fibers. We recommend cotton clothing or other conductivity-treated fibers.
 - 2.3 Slowly and carefully remove the protective film from the LCD module, since this operation can generate static electricity.
- 3 When the LCD module alone must be stored for long periods of time:
 - 3.1 Protect the modules from high temperature and humidity.
 - 3.2 Keep the modules out of direct sunlight or direct exposure to ultra-violet rays.
 - 3.3 Protect the modules from excessive external forces.
- 4 Use the module with a power supply that is equipped with an over current protector circuit, since the module is not provided with this protective feature.



Microtips Technology Inc.

| | | | | | |
|-----------------------|--------|--------------------|--------------|--------------|-------|
| Messrs. Standard | | | | | |
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. |
| | | | B | Nov. 1, 06 | 18 |

- 5 Do not ingest the LCD fluid itself should it leak out of a damaged LCD module. Should hands or clothing come in contact with LCD fluid, wash immediately with soap.
- 6 Conductivity is not guaranteed for models that use metal holders where solder connections between the metal holder and the PCB are not used. Please contact us to discuss appropriate ways to assure conductivity.

8. Warranty

This product has been manufactured to your company's specifications as a part for use in your company's general electronic products. It is guaranteed to perform according to delivery specifications. For any other use apart from general electronic equipment, we cannot take responsibility if the product is used in medical devices, nuclear power control equipment, aerospace equipment, fire and security systems, or any other applications in which there is a direct risk to human life and where extremely high levels of reliability are required. If the product is to be used in any of the above applications, we will need to enter into a separate product liability agreement.

- 1 We cannot accept responsibility for any defect, which may arise from additional manufacturing of the product (including disassembly and reassembly), after product delivery.
- 2 We cannot accept responsibility for any defect, which may arise after the application of strong external force to the product.
- 3 We cannot accept responsibility for any defect, which may arise due to the application of static electricity after the product has passed your company's acceptance inspection procedures.
- 4 We cannot accept responsibility for industrial property, which may arise through the use of your product, with exception to those issues relating directly to the structure or method of manufacturing of our product. Microtips-origin longer than 2 (two) years from Microtips production or 1(one) year from Microtips overseas agent or distributor delivery which ever comes later.



Microtips Technology Inc.

| | | | | | |
|-----------------------|--------|--------------------|--------------|--------------|-------|
| Messrs. Standard | | | | | |
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. |
| | | | B | Nov. 1, 06 | 19 |


9. Dimensional Outlines

- See the next page.....



Microtips Technology Inc.

| | | | | | |
|-----------------------|--------|--------------------|--------------|--------------|-------|
| Product Specification | Model: | NMTC-S20200BMNHSGW | Revision No. | Issued Date. | Page. |
| | | | B | Nov. 1, 06 | 20 |



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microtips Technology:](#)

[NMTC-S20200BMNHSGW](#)