

MN1876476

Type	MN1876476										
ROM (x8-bit)	64K										
RAM (x8-bit)	928										
Minimum Instruction Execution Time	2/3 dividing 0.5µs (at 4.5 to 5.5V, 12MHz)										
Interrupts	<ul style="list-style-type: none"> • RESET • External 0 • External 1 • External 2 • External 3 • Timer 0 • Timer 1 • Timer 2 • I²C • Serial • Remote Control • Line 21 • MOSD • COSD 										
Timer Counter	<p>Timer Counter 0 : 8-bit x 1 Clock Source1/1, 1/4, 1/16, 1/64 of System Clock Interrupt SourceOverflow of Timer Counter 0</p> <p>Timer Counter 1 : 8-bit x 1 Clock Source1/2, 1/16, 1/64, 1/256, 1/512 of System Clock Interrupt SourceOverflow of Timer Counter 1</p> <p>Time Base Counter Clock Source1/4096 of System Clock Interrupt Source1/1, 1/2, 1/4, 1/8 of Timer Counter 2</p> <p>Watchdog Counter for Clock (Clock function) AC Counter</p>										
Serial Interface	<p>Serial 0 : 8-bit x 1 (Transmission/Reception of variable bit length, Transfer direction of MSB/LSB selectable, Clock Polarity selectable, Start Condition function)</p> <p>Clock SourceSystem Clock</p> <p>I²C x 1 (Two bus line system)</p>										
I/O Pins	<table border="1"> <tr> <td>I/O</td> <td>36</td> <td>• Common use : 28</td> </tr> <tr> <td>Input</td> <td>3</td> <td>• Common use : 3</td> </tr> <tr> <td>High Voltage Output</td> <td>7</td> <td>• Nch Open-drain (Breakdown Voltage 12V) : 7</td> </tr> </table>	I/O	36	• Common use : 28	Input	3	• Common use : 3	High Voltage Output	7	• Nch Open-drain (Breakdown Voltage 12V) : 7	
I/O	36	• Common use : 28									
Input	3	• Common use : 3									
High Voltage Output	7	• Nch Open-drain (Breakdown Voltage 12V) : 7									
A/D Inputs	5/7-bit x 10ch (without S/H)										
PWM	14-bit x 1ch (Repetition Cycle 16µs, at 12MHz), 8-bit x 8ch (Repetition Cycle 32µs, at 12MHz), 7-bit x 1ch (Repetition Cycle 16µs, at 12MHz)										
Special Ports	Hsync Detection, Remote Control Reception										
CRTC	Double OSD built-in (Menu OSD : 12 x 18, 512 letters, Caption OSD : 12 x 26, 176 letters)										
Notes	Remote Control Data Detection Circuit built-in										
Package	SDIP064-P-0750										

Electrical Characteristics

A/D Converter Characteristics

Parameter	Symbol	Condition	Limit			Unit
			min	typ	max	
A/D Conversion Time	TAD	fosc=12MHz	9/12			μs
Analog Input Voltage	VAD		VSS		VDD	V

(Ta= -20 to +70°C, VDD=5.0V, VSS=0V)

Support Tool


In-Circuit Emulator

PX-ICE1870 / 80 + PX-PRB1876462, PX-PRB1876476 (under development)

EPROM built-in Type

Use **MN18P76476** in SDIP064-P-0750 package.

Pin Assignment



SDIP064-P-0750

※ P04 • IRQ0 pin

TYPE A	Stand-by function is available	Input pin
TYPE B	Stand-by function is not available	I/O pin