



3M™ FOUR-WALL HEADER, 3000 SERIES


.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE



-X0XX  
HEADER WITHOUT LATCH EJECTOR



-X2XX  
HEADER WITH SHORT LATCH EJECTOR  
FOR 3M SOCKETS WITHOUT STRAIN RELIEF



-X3XX  
HEADER WITH LONG LATCH EJECTOR  
FOR 3M SOCKETS WITH STRAIN RELIEF

ORDERING INFORMATION

D= HIGH TEMP BLACK (PCT)/(AR PLATING REQ'D)  
N= HIGH TEMP BLACK (PCT)/(RB PLATING REQ'D)  
BLANK= HIGH TEMP BLACK (PCT)/(EB PLATING REQ'D)

3M PART NUMBER:  
(SEE TABLE 1)

PIN CONFIGURATION:  
5 = RIGHT ANGLE SOLDER TAILS  
6 = STRAIGHT SOLDER TAILS

X3XXX-XXXXXX

PLATING:

AR = 50μ"-150μ" [ 1.27μm-3.81μm ] NICKEL-OVERALL  
10μ" [ 0.25μm ] AVG. GOLD, 40-120μ" [ 1-3μm ] MATTE TIN TAILS  
RB = 50μ"-150μ" [ 1.27μm-3.81μm ] NICKEL-OVERALL  
30μ" [ 0.76μm ] AVG. GOLD, 200μ" [ 5.08μm ] MATTE TIN TAILS

TAIL:

02 = FOR .062 [ 1.57 ] THICK BOARD (N & D)  
03 = FOR .094 TO .125 [ 2.39 TO 3.18 ] THICK BOARD (N ONLY)

LATCH/EJECTOR SYSTEM:

0 = NO LATCH/EJECTOR INSTALLED  
2 = SHORT ROLL PIN LATCH/EJECTORS  
3 = LONG ROLL PIN LATCH/EJECTORS

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION  
INTERCONNECT SOLUTIONS  
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.  
FOR TECHNICAL, SALES OR ORDERING  
INFORMATION CALL 800-225-5373

- \* MILITARY (WITH 3M'S N3518 POLARIZING KEY) AND CENTERBUMP POLARIZATION.
- \* OPTIONAL EJECTOR LATCHES.
- \* MOUNTING HOLES FOR SECURING HEADER TO BOARD.
- \* OPTIONAL POLARIZING POSTS AVAILABLE.
- \* HIGH TEMPERATURE INSULATOR SUITABLE FOR "NO LEAD" SOLDERING OPERATIONS.
- \* SUITABLE FOR REFLOW SOLDERING USING "PASTE IN HOLE" TECHNIQUES.
- \* STRAIGHT, RIGHT ANGLE SOLDER TAIL OPTIONS.

2 PHYSICAL :

INSULATOR: HIGH TEMP GLASS FILLED POLYESTER (PCT)  
MATERIAL: UL94V-0  
FLAMMABILITY: BLACK  
COLOR: COPPER ALLOY  
CONTACT: PLATING: NICKEL-OVERALL (SEE ORDERING INFORMATION)  
WIPING AREA: GOLD (SEE ORDERING INFORMATION)  
SOLDER TAILS: MATTE TIN (SEE ORDERING INFORMATION)  
MARKINGS: 3M LOGO, PART IDENTIFICATION NUMBER AND ORIENTATION TRIANGLE

2 ELECTRICAL :

EIA CURRENT RATING: 5.00A, 1 CONTACT POWERED  
3.00A, 6 CONTACTS POWERED  
1.75A, ALL CONTACTS POWERED  
RATING CONDITIONS: EIA-364-070 METHOD 2, 30°C MAXIMUM TEMPERATURE RISE, 20% DERATED. REFERENCE APPROPRIATE 3M PRODUCT SPECIFICATION FOR DETAILED CURRENT DERATING CURVES.  
INSULATION RESISTANCE: >1 X 10<sup>9</sup>Ω AT 500 V<sub>DC</sub>  
WITHSTANDING VOLTAGE: 1,000V<sub>RMS</sub> AT SEA LEVEL  
UL CURRENT RATING: 1.0A ALL LINES POWERED  
UL VOLTAGE RATING: 250V

2 ENVIRONMENTAL :

UL TEMPERATURE RATING: 130C  
EIA TEMPERATURE RATING: -55°C TO 105°C  
PROCESS RATING: 260°C, PER J-STD-020C, SINGLE PASS  
MOISTURE SENSITIVITY LEVEL: 1 (PER J-STD-020C, SINGLE PASS)

- NOTES
1. REGULATORY INFORMATION: VISIT [3M.com/regs](http://3M.com/regs)
  2. IN THE EVENT OF CONFLICT BETWEEN THIS DATA AND THAT CONTAINED IN THE PRODUCT SPECIFICATION, THE PRODUCT SPECIFICATION TAKES PRECEDENT.
  3. NOTCHES A & C WILL ACCOMODATE 3M POLARIZING KEY: N3518.
  4. MOUNTING HARDWARE: FROM SOLDER SIDE OF PC BOARD USE #4-24 THREAD CUTTING SCREW (3M PART #3341-5) WITH Ø.116 [ 2.95 ] MOUNTING HOLE. FOR RIGHT ANGLE VERSION ONLY: #2-56 BOLT AND NUT (3M PART #3341-6) WITH Ø.106 [ 2.69 ] MOUNTING HOLE MAY BE USED.

|   |        |             |     |     |
|---|--------|-------------|-----|-----|
| X | 115955 | MAY 08,2024 | JNC | FJR |
| W | 112712 | NOV 29,2023 | JNC | FJR |
| V | 97909  | JUN 22,2021 | JNC | SAN |
| U | 93619  | JAN 07,2021 | JNC | SAN |
| T | 62689  | JUL 10,2015 | JNC | SN  |
| S | 60056  | MAR 06,2015 | JNC | RS  |
| R | 56068  | JUL 25,2014 | JNC | RS  |

|                                                                                                                                                                                                                                             |             |                            |             |        |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|----------------------------|-------------|--------|
| REV                                                                                                                                                                                                                                         | ECO         | ISSUE DATE AND DESCRIPTION | DRFT        | CHKD   |
| DRFT                                                                                                                                                                                                                                        | CATTIGLIONE | DATE JUL 25,2014           | DATE        |        |
| CHKD                                                                                                                                                                                                                                        |             | DATE                       | DATE        |        |
|                                                                                                                                                                                                                                             |             | APPR                       | DATE        |        |
|                                                                                                                                                                                                                                             |             | R. SCHERER                 | SEP 05,2014 |        |
| 3M Center St. Paul, MN 55144                                                                                                                                                                                                                |             |                            |             |        |
| © 3M COPYRIGHT 2024. This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved. |             |                            |             |        |
| TITLE 4-WALL HEADER, .100 X .100 LATCH/EJECT, STRAIGHT & RA                                                                                                                                                                                 |             |                            |             |        |
| CAGE NUMBER                                                                                                                                                                                                                                 | SIZE        | DRAWING NO.                | REV.        |        |
| D                                                                                                                                                                                                                                           |             | 78-5100-0772-3             | X           |        |
| MODEL                                                                                                                                                                                                                                       | 3400        | DET                        | LISTS       | YES    |
|                                                                                                                                                                                                                                             |             | NO                         | SHT         | 1 OF 5 |




DIMENSIONS: INCHES [ MM ]  
[ MM ] IS REF. ONLY

|                                 |                                                     |
|---------------------------------|-----------------------------------------------------|
| DESIGN REFERENCE                | NEXT ASSEMBLY                                       |
| AXIS CODES                      |                                                     |
| DIVISION                        | DIVISION CODE                                       |
| Interconnect Solutions          | EMSD                                                |
| DO NOT SCALE DRAWING            | TOLERANCES EXCEPT AS NOTED                          |
| THIRD ANGLE PROJECTION          | INCHES                                              |
| INTERPRET PER ASME Y14.5 - 2018 | 0 ± .1<br>.00 ± .01<br>.000 ± .005<br>.0000 ± .0002 |
| MAX. SURFACE ROUGHNESS          | MILLIMETERS                                         |
| ALL SURFACES                    | 0 ± .1<br>.00 ± .01<br>.000 ± .0002                 |
| MARKED ONLY                     | ANGLES                                              |

UL FILE NO: E68080

3M™ FOUR-WALL HEADER, 3000 SERIES

.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE



| TABLE 1  |                |                |                 |                 |               |                    |          |
|----------|----------------|----------------|-----------------|-----------------|---------------|--------------------|----------|
| PIN QTY. | 3M PART NUMBER | DIM. "A"       | DIM. "B"        | DIM. "C"        | DIM. "D"      | POLARIZING NOTCHES | PIN QTY. |
| 06       | 3869           | 1.06 [ 27.0 ]  | .905 [ 22.99 ]  | .665 [ 16.89 ]  | .51 [ 12.9 ]  | B*                 | 06       |
| 08       | 3889           | 1.16 [ 29.5 ]  | 1.005 [ 25.53 ] | .765 [ 19.43 ]  | .61 [ 15.5 ]  | B*                 | 08       |
| 10       | 3793           | 1.26 [ 32.1 ]  | 1.105 [ 28.04 ] | .865 [ 21.97 ]  | .71 [ 18.0 ]  | BC                 | 10       |
| 14       | 3314           | 1.46 [ 37.2 ]  | 1.305 [ 33.12 ] | 1.065 [ 27.05 ] | .91 [ 23.1 ]  | BC                 | 14       |
| 16       | 3408           | 1.56 [ 39.7 ]  | 1.405 [ 35.66 ] | 1.165 [ 29.59 ] | 1.01 [ 25.6 ] | ABC                | 16       |
| 20       | 3428           | 1.76 [ 44.8 ]  | 1.604 [ 40.74 ] | 1.365 [ 34.67 ] | 1.21 [ 30.7 ] | ABC                | 20       |
| 24       | 3627           | 1.96 [ 49.9 ]  | 1.805 [ 45.82 ] | 1.565 [ 39.75 ] | 1.41 [ 35.8 ] | ABC                | 24       |
| 26       | 3429           | 2.06 [ 52.4 ]  | 1.905 [ 48.36 ] | 1.665 [ 42.29 ] | 1.51 [ 38.3 ] | ABC                | 26       |
| 30       | 3440           | 2.26 [ 57.5 ]  | 2.105 [ 53.44 ] | 1.865 [ 47.37 ] | 1.71 [ 43.4 ] | ABC                | 30       |
| 34       | 3431           | 2.46 [ 62.6 ]  | 2.305 [ 58.52 ] | 2.065 [ 52.45 ] | 1.91 [ 48.5 ] | ABC                | 34       |
| 40       | 3432           | 2.76 [ 70.2 ]  | 2.605 [ 66.14 ] | 2.365 [ 60.07 ] | 2.21 [ 56.1 ] | ABC                | 40       |
| 50       | 3433           | 3.26 [ 82.9 ]  | 3.105 [ 78.84 ] | 2.865 [ 72.77 ] | 2.71 [ 68.8 ] | ABC                | 50       |
| 60       | 3372           | 3.76 [ 95.6 ]  | 3.605 [ 91.54 ] | 3.365 [ 85.47 ] | 3.21 [ 81.5 ] | ABC                | 60       |
| 64       | 3764           | 3.96 [ 100.7 ] | 3.805 [ 96.62 ] | 3.565 [ 90.55 ] | 3.41 [ 86.6 ] | ABC                | 64       |

\* AVAILABLE WITHOUT CENTER NOTCH B. CONTACT 3M

| TABLE 2               |                                               |               |                         |                      |                     |                                 |
|-----------------------|-----------------------------------------------|---------------|-------------------------|----------------------|---------------------|---------------------------------|
| 3M PART NUMBER SUFFIX | CONTACT TAIL                                  | DIM. "E"      | PIN CROSS SECTION       |                      |                     | DIM. "G"                        |
|                       |                                               |               | DIM. "F"                | DIAGONALS            | CORNER RADIUS       |                                 |
| -5XX2                 | .062 [ 1.57 ] THICK PC BOARD                  | .112 [ 2.84 ] | .0245+/- .0005 [ .622 ] | .028+/- .001 [ .71 ] | .0075 [ .191 ] REF. | .035+/- .003 [ .89 ] SEE NOTE 5 |
| -6XX2                 |                                               |               |                         |                      |                     |                                 |
| -5X03                 | .094 [ 2.39 ] TO .125 [ 3.18 ] THICK PC BOARD | .155 [ 3.94 ] | .0245+/- .0005 [ .622 ] | .028+/- .001 [ .71 ] | .0075 [ .191 ] REF. | .035+/- .003 [ .89 ]            |
| -6X03                 |                                               |               |                         |                      |                     |                                 |


|      |             |                            |            |                  |
|------|-------------|----------------------------|------------|------------------|
| X    | 115955      | MAY 08,2024                | JNC        | FJR              |
| W    | 112712      | NOV 29,2023                | JNC        | FJR              |
| V    | 97909       | JUN 22,2021                | JNC        | SAN              |
| U    | 93619       | JAN 07,2021                | JNC        | SAN              |
| T    | 62689       | JUL 10,2015                | JNC        | SN               |
| S    | 60056       | MAR 06,2015                | JNC        | RS               |
| R    | 56068       | JUL 25,2014                | JNC        | RS               |
| REV  | ECO         | ISSUE DATE AND DESCRIPTION | DRFT       | CHKD             |
| DRFT | CASTIGLIONE | DATE JUL 25,2014           | MFG        | DATE             |
| CHKD |             | DATE                       | APPRV      | DATE SEP 05,2014 |
|      |             |                            | R. SCHERER |                  |

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION  
INTERCONNECT SOLUTIONS  
<http://www.3M.com/interconnect>


3M IS A TRADEMARK OF 3M COMPANY.  
FOR TECHNICAL, SALES OR ORDERING  
INFORMATION CALL 800-225-5373

|                                 |  |                            |  |
|---------------------------------|--|----------------------------|--|
| DESIGN REFERENCE                |  | NEXT ASSEMBLY              |  |
| X                               |  | X                          |  |
| DIVISION                        |  | DIVISION CODE              |  |
| Interconnect Solutions          |  | EMSD                       |  |
| DO NOT SCALE DRAWING            |  | TOLERANCES EXCEPT AS NOTED |  |
| THIRD ANGLE PROJECTION          |  | INCHES                     |  |
| INTERPRET PER ASME Y14.5 - 2018 |  | MILLIMETERS                |  |
| MAX. SURFACE ROUGHNESS          |  | CAGE NUMBER                |  |
| ALL SURFACES MARKED ONLY        |  | DRAWING NO.                |  |
|                                 |  | REV.                       |  |
|                                 |  | MODEL                      |  |
|                                 |  | 3400                       |  |
|                                 |  | LISTS                      |  |
|                                 |  | YES                        |  |
|                                 |  | NO                         |  |
|                                 |  | SHT 2 OF 5                 |  |

3M™ FOUR-WALL HEADER, 3000 SERIES  
.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE



RECOMMENDED MOUNTING HOLE PATTERN  
(STRAIGHT VERSION)



RECOMMENDED MOUNTING HOLE PATTERN  
(RIGHT ANGLE VERSION)

PART CUSTOMIZATION



THIS SPEC SHEET DETAILS OUR STANDARD OFFERING.

3M HAS SEVERAL CAPABILITIES THAT CAN PROVIDE A PART TAILORED TO YOUR SPECIFIC NEEDS. ASK YOUR 3M SALES REPRESENTATIVE OR CUSTOMER SERVICE FOR MORE DETAILS.

BOTH SNAP-IN AND ROLL PIN LATCHES MAY BE ORDERED SEPARATELY. SNAP-IN AND ROLL PIN STYLE LATCHES ARE DIMENSIONALLY AND FUNCTIONALLY EQUIVALENT. IF ORDERING SNAP-IN OR ROLL PIN STYLE LATCHES SEPARATELY, PLEASE USE THE BELOW CHART.

| MATERIAL         | SHORT LATCH | LONG LATCH | LATCH STYLE | COLOR |
|------------------|-------------|------------|-------------|-------|
| HIGH TEMP. (PCT) | N3505-2B    | N3505-3B   | ROLL PIN    | BLACK |
| HIGH TEMP (PPA)  | N3505-30B   | N3505-31B  | SNAP-IN     | BLACK |

- \* SELECTIVE PIN REMOVAL (ATA OR OTHER COMPATABILITY)
- \* WIRE WRAP TAILS STYLE



LONG SHORT


SNAP-IN LATCHES

NOTE:  
SNAP-IN LATCHES CAN ONLY BE ORDERED SEPARATELY AND ARE THE CUSTOMERS RESPONSIBILITY TO INSTALL.

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION  
INTERCONNECT SOLUTIONS  
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.  
FOR TECHNICAL, SALES OR ORDERING  
INFORMATION CALL 800-225-5373


POLARIZING POST



| 3M PART NO. | MATERIAL | COLOR |
|-------------|----------|-------|
| 3201-4      | LCP      | BLACK |

NOTE:  
INSERT POST INTO ONE MOUNTING  
HARDWARE HOLE ON BOTTOM OF HEADER.  
SET POST TO PROTRUDE .115 [2.92]

POLARIZING KEYS



| 3M PART NO. | MATERIAL | COLOR | DIM. 'A' |
|-------------|----------|-------|----------|
| N3518       | LCP      | BLACK | .02      |

NOTE:  
#2216 B/A SCOTCHWELD CAN BE USED TO  
ADHERE KEYS.


|   |        |                                                             |     |     |
|---|--------|-------------------------------------------------------------|-----|-----|
| X | 115955 | MAY 08,2024<br>REMOVE 05 WWT TAIL                           | JNC | FJR |
| W | 112712 | NOV 29,2023<br>UL VOLTAGE WAS 125                           | JNC | FJR |
| V | 97909  | JUN 22,2021<br>REVISED ORDERING INFO                        | JNC | SAN |
| U | 93619  | JAN 07,2021<br>REMOVE TIN LEAD<br>PLATING AND KINK<br>TAILS | JNC | SAN |
| T | 62689  | JUL 10,2015<br>ADD 5X05 OPTION AND<br>REVISE NOTES          | JNC | SN  |
| S | 60056  | MAR 06,2015<br>REVISE ORDERING<br>NUMBER                    | JNC | RS  |
| R | 56068  | JUL 25,2014<br>REVISED AND REDRAWN                          | JNC | RS  |

| DESIGN REFERENCE                                     | NEXT ASSEMBLY | REV                                      | ECO | ISSUE DATE AND DESCRIPTION | DRFT | CHKD |
|------------------------------------------------------|---------------|------------------------------------------|-----|----------------------------|------|------|
| XXXXXX                                               | XXXXXX        | 1                                        | ECO | JUL 25,2014                | DRFT | CHKD |
| DIVISION<br>Interconnect Solutions                   |               | DIVISION CODE<br>EMSD                    |     | DATE<br>JUL 25,2014        |      |      |
| DO NOT SCALE DRAWING                                 |               | TOLERANCES EXCEPT AS NOTED               |     | DATE<br>SEP 05,2014        |      |      |
| THIRD ANGLE PROJECTION                               |               | INCHES<br>±.1<br>±.01<br>±.005<br>±.0002 |     | DATE<br>SEP 05,2014        |      |      |
| INTERPRET PER<br>ASME Y14.5 - 2018                   |               | MILLIMETERS<br>0 ±<br>0 ±<br>0 ±<br>0 ±  |     | DATE<br>SEP 05,2014        |      |      |
| MAX SURFACE ROUGHNESS<br>ALL SURFACES<br>MARKED ONLY |               | CAGE NUMBER<br>D78-5100-0772-3           |     | DATE<br>SEP 05,2014        |      |      |
|                                                      |               | MODEL<br>3400                            |     | DATE<br>SEP 05,2014        |      |      |

|                                                                      |      |                                                                                                                                                                                                                                               |      |
|----------------------------------------------------------------------|------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------|
| 3M                                                                   |      | © 3M COPYRIGHT 2024<br>This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved. |      |
| TITLE<br>4-WALL HEADER, .100 X<br>.100 LATCH/EJECT,<br>STRAIGHT & RA |      |                                                                                                                                                                                                                                               |      |
| CAGE NUMBER                                                          | SIZE | DRAWING NO.                                                                                                                                                                                                                                   | REV. |
| D78-5100-0772-3                                                      |      |                                                                                                                                                                                                                                               | X    |

3M™ FOUR-WALL HEADER, 3000 SERIES  
.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE


MOUNTING HARDWARE



3341-5


(INSTALL FROM BOTTOM OF BOARD)  
SEE NOTE 4

PANHEAD THREAD CUTTING SCREW:  
#4-24 X 5/16"  
TYPE: USA STD BT, FEDERAL BG  
MATERIAL: STAINLESS STEEL



3341-6

HEX HEAD BOLT, NUT AND WASHER:  
BOLT - #2-56 X 1/2"  
MATERIAL: STAINLESS STEEL




STRAIGHT VERSION INSTALL  
(MUST BE INSERTED PRIOR TO  
LATCH INSTALL)

RIGHT ANGLE VERSION INSTALL


3341-6

#2-56 NUT AND BOLT



#4-24 TYPE BT SELF THREADING SCREW  
WHEN USING LATCHES, MAXIMUM LENGTH  
OF SCREW IS .250 INCHES PLUS  
THICKNESS OF THE BOARD.

3341-5



3M ELECTRONICS MATERIALS SOLUTIONS DIVISION  
INTERCONNECT SOLUTIONS  
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.  
FOR TECHNICAL, SALES OR ORDERING  
INFORMATION CALL 800-225-5373

|                        |  |                                 |  |                                                      |  |                                          |  |                                 |  |                                                                      |      |
|------------------------|--|---------------------------------|--|------------------------------------------------------|--|------------------------------------------|--|---------------------------------|--|----------------------------------------------------------------------|------|
| DESIGN REFERENCE       |  | NEXT ASSEMBLY                   |  | REV                                                  |  | ECO                                      |  | ISSUE DATE AND DESCRIPTION      |  | DRFT                                                                 | CHKD |
| X                      |  | 115955                          |  | MAY 08,2024                                          |  | REMOVE 05 WWT TAIL                       |  | JNC                             |  | FJR                                                                  |      |
| W                      |  | 112712                          |  | NOV 29,2023                                          |  | UL VOLTAGE WAS 125                       |  | JNC                             |  | FJR                                                                  |      |
| V                      |  | 97909                           |  | JUN 22,2021                                          |  | REVISED ORDERING INFO                    |  | JNC                             |  | SAN                                                                  |      |
| U                      |  | 93619                           |  | JAN 07,2021                                          |  | REMOVE TIN LEAD PLATING AND KINK TAILS   |  | JNC                             |  | SAN                                                                  |      |
| T                      |  | 62689                           |  | JUL 10,2015                                          |  | ADD 5X05 OPTION AND REVISE NOTES         |  | JNC                             |  | SN                                                                   |      |
| S                      |  | 60056                           |  | MAR 06,2015                                          |  | REVISE ORDERING NUMBER                   |  | JNC                             |  | RS                                                                   |      |
| R                      |  | 56068                           |  | JUL 25,2014                                          |  | REVISED AND REDRAWN                      |  | JNC                             |  | RS                                                                   |      |
| REV                    |  | ECO                             |  | JUL 25,2014                                          |  | MFG                                      |  | DATE                            |  | DATE                                                                 |      |
| CHKD                   |  | CASTIGLIONE                     |  | DATE                                                 |  | APPR                                     |  | R. SCHERER                      |  | DATE                                                                 |      |
| DIVISION               |  | Interconnect Solutions          |  | DIVISION CODE                                        |  | EMSD                                     |  | 3M                              |  | 3M Center<br>St. Paul,<br>MN 55144                                   |      |
| DO NOT SCALE DRAWING   |  | SCALE                           |  | TOLERANCES EXCEPT AS NOTED                           |  | INCHES<br>±.1<br>±.01<br>±.005<br>±.0002 |  | MILLIMETERS<br>0<br>±<br>±<br>± |  | TITLE<br>4-WALL HEADER, .100 X<br>.100 LATCH/EJECT,<br>STRAIGHT & RA |      |
| THIRD ANGLE PROJECTION |  | INTERPRET PER ASME Y14.5 - 2018 |  | MAX SURFACE ROUGHNESS<br>ALL SURFACES<br>MARKED ONLY |  | CAGE NUMBER<br>D78-5100-0772-3           |  | SIZE<br>3400                    |  | DRAWING NO.<br>D78-5100-0772-3                                       |      |
| X                      |  | 1                               |  | REV.                                                 |  | X                                        |  | SHT 4 OF 5                      |  | DET<br>LISTS<br>YES<br>NO                                            |      |

# 3M™ FOUR-WALL HEADER, 3000 SERIES

.100" X .100" LATCH/EJECTOR, STRAIGHT AND RIGHT ANGLE

Regulatory: For regulatory information about this product, visit [3M.com/regs](http://3M.com/regs) or contact your 3M representative.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price.


Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: For industrial use only. Not intended, labeled or packaged for consumer sale or use.

3M Company  
Electronics Materials Solutions Division  
13011 McCallen Pass, Bldg. C  
Austin, TX 78753-5380  
1-800-225-5373  
[www.3M.com/interconnect](http://www.3M.com/interconnect)

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION  
INTERCONNECT SOLUTIONS  
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.  
FOR TECHNICAL, SALES OR ORDERING  
INFORMATION CALL 800-225-5373

|                                                                                                                 |        |                                                                                                                   |                  |                                                                                |
|-----------------------------------------------------------------------------------------------------------------|--------|-------------------------------------------------------------------------------------------------------------------|------------------|--------------------------------------------------------------------------------|
| X                                                                                                               | 115955 | MAY 08,2024                                                                                                       | JNC              | FJR                                                                            |
| W                                                                                                               | 112712 | REMOVE 05 WWT TAIL<br>NOV 29,2023<br>UL VOLTAGE WAS 125                                                           | JNC              | FJR                                                                            |
| V                                                                                                               | 97909  | JUN 22,2021<br>REVISED ORDERING INFO                                                                              | JNC              | SAN                                                                            |
| U                                                                                                               | 93619  | JAN 07,2021<br>REMOVE TIN LEAD<br>PLATING AND KINK<br>TAILS                                                       | JNC              | SAN                                                                            |
| T                                                                                                               | 62689  | JUL 10,2015<br>ADD 5X05 OPTION AND<br>REVISE NOTES                                                                | JNC              | SN                                                                             |
| S                                                                                                               | 60056  | MAR 06,2015<br>REVISE ORDERING<br>NUMBER                                                                          | JNC              | RS                                                                             |
| R                                                                                                               | 56068  | JUL 25,2014<br>REVISED AND REDRAWN                                                                                | JNC              | RS                                                                             |
| REV                                                                                                             | ECO    | ISSUE DATE AND DESCRIPTION                                                                                        | DRFT             | CHKD                                                                           |
| ACCESS CODES                                                                                                    |        | DRFT CASTIGLIONE                                                                                                  | DATE JUL 25,2014 | MFG DATE                                                                       |
|                                                                                                                 |        | CHKD                                                                                                              | DATE             | APPR. R. SCHERER                                                               |
|                                                                                                                 |        | DATE SEP 05,2014                                                                                                  |                  |                                                                                |
| DIVISION Interconnect Solutions                                                                                 |        | DIVISION CODE EMSD                                                                                                |                  |                                                                                |
| DO NOT SCALE<br>SCALE<br>DRAWING                                                                                |        | TOLERANCES EXCEPT AS NOTED                                                                                        |                  |                                                                                |
| <br>THIRD ANGLE PROJECTION |        | INCHES<br>.0 ± .1<br>.00 ± .01<br>.000 ± .005<br>.0000 ± .0002<br><br>MILLIMETERS<br>0 ±<br>.0<br>.00 ±<br>.000 ± |                  |                                                                                |
| INTERPRET PER ASME Y14.5 - 2018                                                                                 |        | TITLE<br>4 - WALL HEADER, .100 X<br>.100 LATCH/EJECT,<br>STRAIGHT & RA                                            |                  |                                                                                |
| MAX SURFACE ROUGHNESS<br>✓ <input type="checkbox"/> ALL SURFACES<br><input type="checkbox"/> MARKED ONLY        |        | CAGE NUMBER <b>D</b> 78-5100-0772-3                                                                               |                  | REV. X                                                                         |
|                                                                                                                 |        | MODEL 3400                                                                                                        |                  | DET. LISTS <input checked="" type="checkbox"/> YES <input type="checkbox"/> NO |
|                                                                                                                 |        | SHT 5 OF 5                                                                                                        |                  |                                                                                |