


HONEYWELL PART NUMBER
23SX59-T
PRODUCT CODE VDP5025
MILITARY PART NUMBER 24547-6



REV	DOCUMENT	CHANGED BY	CHECK
9	0051992	DSK 07MAY09	CMH



B

A

A



- NOTES
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188±.002 CENTERS
 - 2 - TERMINALS ARE PLATED FOR SOLDERING
 - 3 - MOVABLE CONTACT MATERIAL - 24 K SOLID GOLD
 - 4 - STATIONARY CONTACT MATERIAL - GOLD ALLOY
 - 5 - SWITCH WILL WITHSTAND TEMPERATURE OF 185° F

RELEASE NO.	PR-8433
REPLACES	

CHARACTERISTICS
OPERATING FORCE - - - 5 OZ MAX
RELEASE FORCE - - - - 1 OZ MIN
DIFFERENTIAL TRAVEL - - - .005 MAX
OVERTRAVEL - - - - - .004 MIN

ELECTRICAL DATA			
CONTACT ARRANGEMENT S P D T			
30 VOLTS DC RATING			
	SEA LEVEL	50,000 FT	
INDUCTIVE	0.5 AMP	0.5 AMP	
RESISTIVE	1 AMP	1 AMP	
MAXIMUM INRUSH 2 AMP			
APPROVALS	KEMA, CE	1A 250 V ~ T125 25E3	 05 
	UL, CSA	1A 125 VAC	  BRAND
			L22J

DESIGN UNITS: INCH			
TOLERANCES UNLESS NOTED:			
NO PLACE	X	±	-
ONE PLACE	.X	±	0.030
TWO PLACE	.XX	±	0.015
THREE PLACE	.XXX	±	0.005
FOUR PLACE	.XXXX	±	-
ANGLES		±	-
THIRD ANGLE PROJECTION			

DRAWN	SPK	22FEB08
CHECK	RJ	22FEB08
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell				
TITLE SWITCH - BASIC				
SIZE	TYPE	DRAWING NAME		REV
B	I	23SX59-T		9
SCALE	NONE	WEIGHT: .003 LB MAX	SHEET 1 OF 1	